



Fuse-link, LV, 10 A, AC 690 V, 14 x 51 mm, aM, IEC

**Catalog No.** C14M10

**EL-Nummer (Norway)** 0001600244

### Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	10
Rated voltage			AC 690 V
Size			14 x 51 mm
Utilization category			aM
usable for size/applications			motor protection for industrial applications
Standard/Approval			IEC
Shape			cylindrical
Standards/Regulations			IEC 60269-2

### Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Cylindrical fuse (EC002704)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Cylindrical fuse (safety fuse) (ecl@ss10.0.1-27-14-20-02 [AFZ797013])			
Size			14x51 mm
Rated voltage		V	690 - 690
Rated voltage			Other
Voltage type			AC
Utilization category			aM (switchgear protection)
Rated operating frequency		Hz	45 - 62
Nominal current		A	10
With striker			No
Release characteristic			Other
Breaking capacity		kA	80

### Additional product information (links)

Product datasheet (PDF)	<a href="http://www.cooperindustries.com/content/dam/public/bussmann/iec-electrical/resources/data-sheets/bus-iec-ds-720115-cylindricalfuselinks.pdf">http://www.cooperindustries.com/content/dam/public/bussmann/iec-electrical/resources/data-sheets/bus-iec-ds-720115-cylindricalfuselinks.pdf</a>
-------------------------	---