



**Part Number :** [2014510101](#)  
**Product Description :** 1.25mm Pitch SlimStack  
Floating Board-to-Board Receptacle, Surface Mount,  
Right-Angle, 4.20mm Stacking Height, 17.70mm Width,  
10 Circuits  
**Series Number :** 201451  
**Status :** Obsolete  
**Product Category :** Board-to-Board Connectors



## Documents & Resources

### Drawings


[2014510101 sd.pdf](#)  
[2014510101 stp.zip](#)

### Specifications

[2014510000-004.pdf](#)  
[2014510000-005.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Obsolete
Category	Board-to-Board Connectors
Series	0.8 and above, FSR1
Description	1.25mm Pitch SlimStack Floating Board-to-Board Receptacle, Surface Mount, Right-Angle, 4.20mm Stacking Height, 17.70mm Width, 10 Circuits
Application	Board-to-Board, Signal
Component Type	PCB Receptacle
Product Name	SlimStack
UPC	889056858618

### Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V AC (RMS)/DC

### Physical

Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Durability (mating cycles max)	10
Glow-Wire Capable	No
Guide to Mating Part	Yes
Mated Height	4.20mm

Mated Width	17.70mm
Material - Metal	Copper Alloy
Material - Plating Mating	Tin-Bismuth
Material - Plating Termination	Tin-Bismuth
Material - Resin	Liquid Crystal Polymer
Net Weight	803.630/mg
Number of Rows	2
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
PCB Locator	Yes
PCB Retention	Yes
Pitch - Mating Interface	1.25mm
Plating min - Mating	1.000µm
Plating min - Termination	1.000µm
Polarized to Mating Part	No
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Surface Mount

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
1.25mm Pitch SlimStack Floating Board-to-Board Plugs	<u>201452</u>