



Datasheet
196-4195
RSPRO-F20



2xAA Aluminium Focus Flashlight



Technical Data

250 Lumen White Osram P8 LED
Tough aircraft-grade aluminium construction
Easy twist flood-to-spot focus
Pure white 6500k colour temperature
Glow-in-the-Dark tail switch
Flawless domed lens for long distance beam
Safety strobe function
IPX4 water resistant
1m impact resistant

Product Size: 32 x 32 x 150 mm

Product Weight: 80.5g (not including batteries)

Battery: 2 x AA Alkaline Batteries (included)

Operation

High > Low > Strobe > Off

ADVICE & IMPORTANT INFORMATION!

- Only use high-quality Alkaline batteries or Ni-MH rechargeable batteries.
- DO NOT USE rechargeable LITHIUM batteries, these will damage your flashlight as they exceed rated voltage.
- Do not use batteries of different brands or mix old and new batteries. Please recycle used batteries responsibly.
- Battery life is affected by different battery brands, different ambient temperatures and different lighting modes.
- If you are not using the product for long periods of time (3 weeks or more), remove batteries to prevent battery leakage and battery depletion. Battery leaks are not covered under warranty.
- Do not look directly at the LED.
- Do not operate in direct sunlight or extreme temperature conditions (below -10°C or above 40°C).
- The LED will become hot when switched on; do not touch and do not place face down on any surface – risk of fire!
- Do not use the device if there is any visible damage to the housing.
- The aluminium housing can get warm. If it gets too hot turn down the brightness or turn off and allow to cool.
- Do not use the product in the immediate vicinity of flammable materials or gases.
- Children under 12 years of age should only use the product under adult supervision.
- Clean the product with a dry or slightly moist, clean, lint-free cloth and a mild detergent if required. Do not use cleaners that contain abrasives or solvents.
- Do not attempt to modify the product; this will void the warranty and can be dangerous.
- Improper use or modification is not covered under the warranty.
- Ensure the lens does not come into contact with hard/sharp objects; damage to the lens may affect light output.
- Protect the batteries from heat, intense sunlight, fire, water and moisture.
- If the batteries are damaged, fluids can leak out. AVOID contact as this can lead to skin irritation and possibly burns. If skin contact happens, rinse thoroughly with water. If irritation persists, seek medical advice. Also seek immediate medical assistance if battery fluid comes into contact with the eyes.
- Do not dispose of this device in normal household waste. It must be disposed of via an authorised disposal centre or at your local waste disposal unit.
- Please recycle packaging where possible.
- Keep these instructions for future reference or for subsequent possessors.

MODE			
HIGH	250 lm	130 m	2 hrs
LOW	75 lm	65 m	6 hrs
STROBE	--	--	3 hrs

