

Description

CHROME SWIVEL BOLT HOLE CASTOR, GREY RUBBER 150mm, 100kg

Part Number

Swivel
145331400A



A

Swivel with brake
145331420A



	Swivel	Swivel + Brake
Wheel Diameter ØD	150 mm	
Overall Height H	190 mm	
Center hole	12,5 mm	
Spacing between castor flanges	39 mm	
Offset F ±1	51 mm	51 mm
Axle Type	Bolt M8	
type de moyeu	2 Ball bearings	
Hub Length	38 mm	
Wheel Bore Diameter	8 mm	
Tread Width	32 mm	
Tread Width on the ground	29 mm	
Hardness Tread shore A ± 5	80	
Load capacity	100 Kg	
Weigth	1,0 kg	1,2 kg

Castor Assembly :

Chrome-plated pressed steel, swivel on two rows of balls
Upper row protected by plastic seal. Sheet metal thickness 2,5mm
Total lock (wheel and swivel). Short steel brake pedal.
Central bolt hole fitting

Wheel :

Wheel center made of grey polypropylene RAL 7037
Tread : Thermoplastic rubber, grey non marking. Two ball bearings.
Chrome-plated steel threadguards.

Features :

Silent and easy to push and pull which reduces the risk of injury and disorders to the individual using the product
Attractively designed, shiny chrome.
Easily accessible steel brake pedal
Non-marking thermoplastic rubber tyre fitted
Robust.