




MIS

TE Internal #: 92009-4

4 Position, Receptacle, Housing, Crimp, Wire-to-Board, UL 94V-0, 2.5 mm [.098 in] Centerline, 1 Row, 250 VAC, Wire & Cable, Power & Signal, MIS

[View on TE.com >](#)

Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Housing**

Connector & Housing Type: **Receptacle**

Mating Retention Type: **Latch**

Connector System: **Wire-to-Board**

UL Flammability Rating: **UL 94V-0**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Contact Base Material	Phosphor Bronze
Contact Type	Socket
Contact Current Rating (Max)	3 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------



Mechanical Attachment

Mating Retention Type	Latch
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	2.5 mm [.098 in]
Housing Material	Nylon GF

Dimensions

Connector Height	4.5 mm [.177 in]
Connector Length	12.5 mm [.492 in]
Wire Size	.14 – .34 mm ²

Usage Conditions

Operating Temperature Range	-25 – 105 °C [-13 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free


Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.


Compatible Parts



Also in the Series | MIS



Connector Contacts(1)




PCB Headers & Receptacles(23)




Rectangular Connector Housings(8)




Rectangular Power Connectors(8)



Standard Rectangular Connectors(11)




Wire-to-Board Connector Assemblies & Housings(11)



Wire-to-Board Headers & Receptacles (23)


Customers Also Bought




TE Part #42098-2
FF 250 TAB 18-14 AWG PTPB




TE Part #172339-1
MINI UMNL PLUG HOUSING 6P




TE Part #280591
AMPMODU MODU I REC HOUSING



TE Part #280592
AMPMODU I RECEPTACLE HOUSING.



TE Part #280593
AMP MODU MOD I RECEPT HSG



TE Part #280702-1
AMPMODU CONT.



TE Part #350766-4
03P UMNL PLUG HSG UL94V0



TE Part #640250-8
08P SL156 HSG W/LCK RAMP NATL



TE Part #640252-2
SL-156 RECEPTACLE



TE Part #2-794617-0
20POS,MICRO MNL,RCPT HSG

Documents

Product Drawings

[RCPT HSG METRIC INTERCONN SYS](#)

English

CAD Files

[3D PDF](#)

English

Customer View Model

[ENG_CVM_92009-4_C.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_92009-4_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_92009-4_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

[Crimp-Snap Metric Interconnect System](#)

English

Agency Approvals

[Agency Approval Document](#)

English