

Features

- Desktop
- DOE Level VI Efficiency
- Selectable Output Voltage
- Selectable Output Connectors
- 36 Watts
- UK AC Cable

RS PRO AC/DC Adapters

RS Stock No.: **0303988**



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

AC/DC Adapters

Product Description

This Desktop 5-15vdc 36watt power supply is suitable many applications and is supplied with selectable DC Connectors & UK Plug AC Cable

- Desktop with UK AC Cable Input
- Selectable DC Connectors

General Specifications

Type	Switched Mode Power Supply
Input Plug Type	UK Desktop
Output Connector	Multi Choice
Input Connector	UK Plug
Cable Length	1.8mtr
Cable Type	2 core Fig 8
Power Indicator	Yes
Over Current Protection	Yes
Short Current Protection	Yes
Over Current Protection	Yes
MTBF	30000 hours at maximum load
Medical Approval	No

Electrical Specifications

Input Specifications

Rated Input Voltage	100 to 240V ac
Full Input Voltage Range	90 – 264V ac
Rated Frequency	50/60Hz
Full Frequency Range	47/63Hz
Efficiency	77%
Power Factor	
Input Current (RMS Max.)	800mA @ 100vac
Inrush Current	60A Max
Leakage Current (max.)	0.25mA / 240V ac
Input Protection	Thermal fuse in Primary; Current Limit, Short Circuit

Output Specifications

Output Voltage	5.0 / 6.0 / 7.5 / 9.0 / 12.0 / 13.5 / 15.0Vdc	
Maximum No load Voltage	5.0 / 6.0 / 7.5 / 9.0 / 12.0 / 13.5 / 15.0Vdc	
Output Maximum Current	3A @ 5.0/6.0/7.5/9.0/12.0V dc ; 2.4A@13.5/15.0V dc	
Output Minimum Current	0A	
Output Regulation	+/-10%	
Rated Power	36W	
Start Up Delay	20ms	
Start Up Rise Time	20ms	
Hold Up Time	20ms	
Transient Response		
Number of Outputs	1	
Efficiency	77%	
Efficiency Level	VI	
Output Voltage Precision	5%	
Ripple & Noise	200mV	
Turn On Delay	4 Seconds Max.	
Insulation Class	II	
Switching Frequency	70KHz	
Isolation Resistance	100MΩ @500V dc	
Voltage Isolation	Input-Output	3000V ac
	Input-Ground	
	Output-Ground	

Mechanical Specifications

Dimension	
Length	116mm
Width	50mm
Depth	34mm
Weight	310g

Operation Environment Specifications

Operating Humidity	20% to 85% RH non-condensing
Cooling	Natural convection
Operating Temperature Range	0 to 25°C
Storage Temperature Range	-20 to 60°C
Temperature Coefficient	
Altitude During Operation	3000m
Vibration Resistance	To IEC-68-2-6
Shock Resistance	

Approvals

Compliance/Certifications	<u>CE/UKCA</u>
Declarations	MFR Declaration of Conformity
Medical Approval	NO

