



Slotted Grommet, Natural, Adh. PE, 2.5mm Max Panel, 30.5m L,PK1

GEE99F-A-C

The GEE99F-A-C Polyethylene Slotted Grommet Edging protects and prevents wires and cables from chafing against sharp edges of panel walls and knockouts. Slotted edging recommended for use on irregularly shaped and round panel holes. The material is highly flexible, while the adhesive lining ensures the product will stay in place. Packaged on a 100' (30.5m) reel for easy handling and dispensing. Polyethylene. Designed for 0.062"-0.099" (1.6mm-2.5mm) thick panels. Color Natural. 1 per package.

Specifications

Note	Designed for irregular shaped or round panel holes
Product Type	Slotted Grommet Edging
Color	Natural
Material	Polyethylene
Maximum Compatible Panel Thickness (In.)	0.099
Maximum Compatible Panel Thickness (mm)	2.5
Minimum Compatible Panel Thickness (In.)	0.062
Minimum Compatible Panel Thickness (mm)	1.6
Maximum Operating Temperature (°C)	50
Maximum Operating Temperature (°F)	122
Minimum Operating Temperature (°C)	-40
Minimum Operating Temperature (°F)	-40
Overall Length (ft.)	100
Overall Length (m)	30.48
Overall Width (In.)	0.17
Overall Width (mm)	4.3
Overall Height (In.)	0.19
Overall Height (mm)	4.7
Resistance Properties	Abrasion-Resistant
Standards Met	RoHS Compliant
Application	To Protect and Prevent Wires and Cables from Chafing Against Sharp Edges of Panel Walls and Knockouts.
Part Features	Provides protection for cables being installed where there might be sharp edges with irregular shaped and round panel holes.

Packaging Detail

UPC	07498362714
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	0.3169
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000