

NO	DESCRIPTION	DATE
⚠	NICKEL 100μ"MIN. → NICKEL	05.18.09'
⚠	ADD WORKING VOLTAGE ADD PROOF VOLTAGE ; 03.00 ADD 4.2 ; 5.2; 4.0 MAX. PANEL	08.03.12'
⚠	ADD MOUNTING HOLE	09.12.12'
⚠	DEL PROOF VOLTAGE WORKING VOLTAGE → VOLTAGE RATING	12.28.12'
⚠	ADD VSWR	07.10.13'

### 1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-6 GHz
- 1.2 NOMINAL IMPEDANCE: 50 OHM
- 1.3 VOLTAGE RATING: 375 VOLTS MAX. ⚠
- 1.4 VSWR: 1.3 MAX. @3 GHz ⚠

### 2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
- 2.2 CENTER CONTACT: BERYLLIUM COPPER PER ASTM B196 UNS C17300
- 2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

### 3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.






### 4.0 MECHANICAL

- 4.1 INTERFACE IN ACCORDANCE WITH: MIL-STD-348A
- 4.2 FOR USE WITH RG316U OR SIMILAR STYLE CABLE ⚠




### 5.0 ENVIRONMENTAL

- 5.1 OPERATING TEMPERATURE RANGE: -85° C TO +165° C
- 5.2 CONNECTOR MUST WITHSTAND WATERPROOF LEAK TEST PRESSURE 3kg/cm<sup>2</sup> MIN. ⚠

16	NUT II	BRASS	1	NICKEL 100μ" MIN.
15	O-RING V	SILICONE	1	BLACK
14	BRAID CLAMP II	BRASS	1	NICKEL 100μ" MIN.
13	O-RING IV	SILICONE	1	RED
12	BRAID CLAMP I	BRASS	1	NICKEL 100μ" MIN.
11	INSULATION III	TEFLON	1	NONE
10	CENTER CONTACT	BERYLLIUM COPPER	1	GOLD
9	O-RING III	SILICONE	1	BLACK
8	BODY	BRASS	1	NICKEL 100μ" MIN.
7	INSULATION II	TEFLON	1	NONE
6	O-RING II	SILICONE	1	BLACK
5	O-RING I	SILICONE	1	BLACK
4	WASHER II	BRASS	1	NICKEL 100μ" MIN.
3	INSULATION I	TEFLON	1	NONE
2	WASHER I	BRASS	1	NICKEL
1	NUT I	BRASS	1	NICKEL 100μ" MIN.
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH



STRIPPING DIMENSION



⚠ MOUNTING HOLE  
SCALE 2:1

APPROVED by \_\_\_\_\_ DATE: \_\_\_\_\_

DESCRIPTION		TNC STRAIGHT BULKHEAD JACK CLAMP	
製圖	DRAWN <i>Kristina</i>	TOLERANCE	品名 15-04-3 T.G.N
檢圖	CHECK <i>Ivan</i>	單位 mm(in)	DATE 07.14.00'
認定	APPROVAL <i>Angela</i>	單位	版次 B-5
		比例	DWG.NO. 15-0085
			7933610



