



Hammer Driver Drill LXT® DHP489

18v, 0 – 1 800 min⁻¹, 620 W

Model DHP489 is cordless hammer driver drill powered by 18V LXT® Li-Ion battery

The main features and benefits are: Excellent drilling capacity: Achieve exceptional drilling capacity, effortlessly tackling 2x lumber with up to 1" ship auger bit in high speed mode, Robust keyless drill chuck with single metal sleeve, Metal gear housing.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	0 - 550 / 1800 min ⁻¹
Max. fastening torque Hard/Soft	73 / 40 Nm
Max Torque	110 Nm
Torque setting	21
Impacts per Minute (IPM)	0 - 8250 / 27000 min ⁻¹
Max. Drilling Diameter in Masonry	16 mm
Max. Drilling Diameter in Steel	13 mm
Drilling Capacity Wood (Auger Bit)	38 mm
Drilling Capacity Wood (Self-feed bit)	51 mm
Drilling Capacity Flat bit	38 mm
Drilling Capacity Hole Saw	51 mm
Driving Shank	1/2"-20UNF "

User benefits

- Built-in LED light with pre-glow and afterglow functions illuminates the work area
- Battery protection system automatically shuts off power when the battery level is low
- Single sleeve keyless chuck enables easy bit installation/removal with one hand
- Mechanical 2-speed gearing; High speed mode for speedy drilling in light duty applications; Low speed mode for heavy duty applications requiring high torque
- Electric brake for maximum productivity and increased operator safety
- Reversing switch is conveniently located
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing