OT250E04P



OT250E04P SWITCH-DISCONNECTOR



General Information

Extended Product Type	OT250E04P		
Product ID	1SCA022710R0520		
EAN	6417019225982		
Catalog Description	OT250E04P SWITCH-DISCONNECTOR		
Long Description	4-pole, front operated, base mounted switch-diconnector with black IP65 handle and shaft, terminal bolt kit included		

Popular Downloads

Data Sheet, Technical Information	1SCC301020C0201
Instructions and Manuals	1SCC301031M0220
Mechanical Drawings	1SCC301392F0001 1SCC301201F0001 OT200-250E04.igs

Dimensions

Product Net Width	180.5 mm
Product Net Height	150 mm
Product Net Depth / Length	82.5 mm
Product Net Weight	1.9 kg

Technical

Rated Operational Current AC-21A (I _e)	(380 415 V) 250 A (500 V) 250 A (690 V) 250 A (1000 V) 250 A
Rated Operational Current AC-22A (I _e)	(380 415 V) 250 A (500 V) 250 A (690 V) 250 A
Rated Operational Current AC-23A (I _e)	(380 415 V) 250 A (500 V) 250 A (690 V) 250 A
Rated Operational Power AC-23A (P _e)	(220 240 V) 75 kW (400 415 V) 145 kW (500 V) 170 kW (690 V) 250 kW
Conventional Free-air Thermal Current (I_{th})	q = 40 °C 250 A

OT250E04P 2

Conventional Thermal Current (I _{the})	
Rated Impulse Withstand Voltage (V_{imp})	12 kV
Rated Insulation Voltage (U _i)	acc. to IEC/EN 60664-1 1000 V
Rated Operational Voltage	Main Circuit 1000 V
Rated Short-Circuit Making Capacity (I _{cm})	(690 V) 30 kA
Rated Short-time Withstand Current (I_{cw})	for 1 s 8 kA
Power Loss	at Rated Operating Conditions per Pole 6.5 W
Pollution Degree	3
Handle Color	Black
Handle Type	Handle and shaft included
Fourth Pole Position	Right Side
Fourth Pole Type	Switched - Simultaneous Function
Switches Operating Mechanism	Mechanism at the End of the Switch 04 (Left Side)
Distance Between Phases	Standard
Position of Line Terminals	Top In - Bottom Out Bottom In - Top Out
Operating Mode	Front operated
Standards	IEC 60947-3
Special Functions	No
Mounting Type	Base mounting
Number of Poles	4
Degree of Protection	Front IP00
Terminal Type	Lug terminals

Environmental

Terminal Width

Tightening Torque

Mechanical Durability

RoHS Status	Following EU Directive 2011/65/EU
Environmental Information	1SCC301149D0202

20 mm

20000

acc. IEC 60947-1 15...22 N·m

Certificates and Declarations (Document Number)

BV Certificate	1SCC301103D0201
Declaration of Conformity - CE	1SCC301131D2705
DNV GL Certificate	1SCC301174D0204
Environmental Information	1SCC301149D0202
GL Certificate	1SCC301139D0201
Instructions and Manuals	1SCC301031M0220
LR Certificate	1SCC301144D0201
RoHS Information	1SCC301149D0203

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	170 mm
	6.7 in

OT250E04P 3

Package Level 1 Depth / Length	190 mm 7.5 in
Package Level 1 Height	145 mm 5.7 in
Package Level 1 Gross Weight	2 kg 4.4 lb
Package Level 1 EAN	6417019225982

_

Classifications

Object Classification Code	Q	
ETIM 5	EC000216 - Switch disconnector	
ETIM 6	EC000216 - Switch disconnector	
ETIM 7	EC000216 - Switch disconnector	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)	
E-Number (Sweden)	3171163	

Categories

Low Voltage Products and Systems \rightarrow Switches \rightarrow Switch Disconnectors

