


## Auto Switch Guide Reed Switch Solid State Switch

13 Martin Carlos
Reed Switch
P 6-21
Const.
General Purpose Style
Band, Rail, Tie-rod, Direct mounting
•2 Colour Indication StyleP 6-40
Band, Rail, Tie-rod Mounting
Solid State Switch
P 6-43
1-1-1-1-1
General Purpose Style     P 6-44
Band, Rail, Tie-rod, Direct mounting
•2 Colour Indication StyleP 6-60
Band, Rail, Tie-rod, Direct mounting
• 2 Colour Indication Style with Diagnostic OutputP 6-67
Band, Rail, Tie-rod Mounting
• Water Resistant 2 Colour Indication StyleP 6-73
Band, Rail, Tie-rod, Direct mounting  • With Timer ······P 6-77
Band, Rail, Tie-rod, Direct mounting
Strong Magnetic Field Resistant 2 Colour Indication Style
Rail Mounting
• With Prewiered Connector ······P 6-86

1

## **SMC Auto Switch Variations**






**SMC** 

Band mounting

Rail mounting

### **SMC Auto Switch Variations**



## **Prior to Use Auto Switch Specifications**

### Precautions

#### Auto Switch Common Specifications

Auto switch style	Reed switch	Solid state switch			
Current leakage	None	3 wire: 100 $\mu\text{A}$ or less, 2 wire: 1mA or less			
Operating time	1.2ms	1ms or less <sup>(3)</sup>			
Shock resistance	300m/s <sup>2</sup> 1000m/s <sup>2</sup>				
Insulation resistance	50 M $\Omega$ or more at 500MV DC (between lead wire and the case)				
Withstand voltage	1500V AC/min.1000V AC/min.(between lead wire and the case) <sup>(1)</sup> (between lead wire and the case)				
Ambient temperature	-10 to 60°C				
Protective construction	IEC529 Standard IP67, Waterproof construction (JISC0920) <sup>(2)</sup>				

Note 1) Connector style (D-A73C/A80C/C73C/C80C) and D-9/9□A/A9/A9□V style: 1000V AC/min. (between lead wire and the case)


Note 2) IEC529 Standard IP63, Rainproof construction (JISC0920) for Terminal conduit style (D-A3/A3 A/A3 C/G39/G39A/G39A/K39A/K39A/K39A) and DIN teminal style (D-A44/A44A/A44C).

Note 3) Except solid state switch with timer (D-M5 TL, G5NTL, F7NTL, F5NTL) and Auto switch for strong magnetic field resistance (D-P5DWL). D-J51: 5ms or less

#### Lead Wire Length

#### How to Order

Ex.)



\* Applicable for the connector style (D- \*\* C) only

Note 1) Applicable auto switch with 5 meter lead wire ("Z")

Reed switch: D-B53/B54, D-C73 (C)/C80C,D-A73(C)(H)/A80C D-A53/A54, D-Z73, D-90/97/90A/93A

Solid state switch: Manufactured upon receipt of order as standard (Except D-M9/M9DV)

Note 2) The standard lead wire length of solid state switch with timer or with water resistant 2 colour indication is 3 meters. (Not available 0.5m)

Note 3) The standard lead wire length of strong magnetic field resistant solid state switch is 3 or 5 meters. (Not available 0.5m.)

#### Part No. of lead wire with connector (Available for connector style only.)

Part No.	Lead wire length
D-LC05	0.5m
D-LC30	3m
D-LC50	5m

#### Change of Lead Wire Colour

Lead wire colours of SMC auto switches have been changed in order to meet Nippon Electric Control Equipment Industries Association Standard No. 402.

#### 2 wire auto switch

	Old	New
Output (+)	Red	Brown
Output (-)	Black	Blue

3 wire auto switch					
Old New					
Power supply	Red	Brown			
GND	Black	Blue			
Output White Black					
Solid state auto switch with					

#### Solid state auto switch with diagnostic output

	Old	New
Power supply	Red	Brown
GND	Black	Blue
Output	White	Black
Diagnositc output	Yellow	Orange

latching style diagnostic output					
	Old	New			
Power supply	Red	Brown			
GND	Black	Blue			
Output	White	Black			
Latching style diagnostic outout	Yellow	Orange			

## **Prior to Use Auto Switch Hysteresis/Contact Protection Box**

#### Contact Protection Box/CD-P11, CD-P12

#### 1

#### The following auto switches are not incorporated with the contact protection box.

D-A7/A8, D-A7 H/A80H, D-A73C, A80C, D-C7/C8, D-C73C/C80C, D-E7 A, E80A, D-Z7/Z8, D-9/9 A, D-A9/A9 V, and D-A79W type

Use an auto switch with a contact protection box in any case listed below. Unless using a contact protection box, the contact life may be shortened.

(Due to permanent energizing conditions.)

D-A72(H) must be used with the contact protection box

regardless of load styles and lead wire length.

**Operating load is an inductive load.** 

2 The wiring length to load is more than 5m. 3 The load voltage is 100 or 200 V AC.

2

Contact SMC when using built-in contact protection circuit style (D-A34[A] [C], D-A44[A] [C], D-A54/A64, D-B54/B64,

D-A59W, D-B59W) in the following conditions: 1) The wiring length to load is more than 30m.

(2) When using PLC with large flow current


#### Contact Protection Box/Specifications

Contact i rotection Dox/Opecifications				
Part No.	CD-P11 CD-P12			
Load voltage	100V AC max.	24V DC		
Max. load current	25mA	12.5mA	50mA	


Lead wire length - Switch connecting side 0.5m



#### **Contact Protection Box/Internal Circuit**




#### **Contact Protection Box/Dimensions**



#### Auto Switch Hysteresis

The distance between the turn-on point (ON) of the switch by moving of the piston to the turn-off point (OFF) is called "Hysteresis". This hysteresis is included as part of the operating range (one side).




#### **Contact Protection Box/Connection Method**

For connection of the switch body and the contact protection box, connect the lead wire in the side indicated as "SWITCH" on the contact protection box to the lead wire from the switch body. The length of lead wire between the switch body and the contact protection box should be within 1m and they should be set as close together as possible.


## **Prior to Use**


Auto Switch Connection Method/Connection Example

#### **Basic Wiring**



#### Typical PLC (Programmable Logic Controller) Connection Circuits






Connect according to the input specification of PLC because the connection method varies with the input specification of PLC.


#### AND (Serial), OR (Parallel) Connection Examples

- •3 wire
- NPN/AND connection (with relay)




#### NPN/AND connection (with switch)






Indication lights up when both switches are ON.



•2 wire (2 pcs.)

#### AND connection



Load voltage at ON=Supply voltage-Internal drop voltage X 2 pcs. =24V-4V X 2 pcs.

Example) Supply voltage 24V DC, switch internal drop voltage 4V

**OR** connection Brown Load Switch 1 Blue Brown Switch 2 Blue

#### [Solid state switch]

When 2 switches are connected by OR, load voltage will increase at OFF and these connections may cause malfunction.

[Reed switch]

- There is no current leakage so that load voltage does not increase at OFF.
- The flowing current is broken up into the ON-state switches, so indicator light becomes dark or may not turn ON due to the lack of the current.

Load voltage at OFF=Leakage current X 2 pcs. X Load impedance

=1mA X 2 pcs. X 3k =6V

Example) Load impedance 3k , switch leakage current 1mA

**SMC** 

## **Reed Switch**

General Purpose Auto Switch 2 colour Indication Style

## Reed Switch/Band Mounting D-C73/D-C76/D-C80

#### Grommet



#### **Applicable Actuator Series**

Series	Bore size (mm)
CDJ2	ø6, ø10, ø16
CDVJ	ø10, ø16
CDLJ2	ø16
CDM2/CDBM2/CDVM3, 5 CDLM2	ø20, ø25, ø32, ø40
CDG1/MGG	ø20, ø25, ø32, ø40, ø50, ø63
CDLG1	ø20, ø25, ø32, ø40
RSDG	ø40, ø50
MGC	ø20, ø25, ø32, ø40, ø50
MLGC/RHC/REC	ø20, ø25, ø32, ø40

#### Specifications

PLC: Programmable Logic Controller

20mA

40mA


None

1 or less (Including 3m lead wire)

D-C7 (With indicator light)					
Auto switch model number	D-C73 D-C76				
Application	Relay/PLC IC circuit				
Load voltage	24V DC	24V DC 100V AC			
Max. load current and range	5 to 40mA 5 to 20mA 20mA				
Contact protection circuit	None				
Internal voltage drop	≤ 2.4V ≤ 0.8V				
Indicator light	ON: When red light emitting diode				
D-C8 (Without indicator lig	ıht)				
Auto switch model number	D-C80				
Application	Relay/PLC/IC circuit				
Load voltage	24V <sup>AC</sup> <sub>DC</sub> or less 48V <sup>AC</sup> <sub>DC</sub> 100V <sup>AC</sup> <sub>DC</sub>				

#### **Internal Circuit**

#### (): If not applicable for IEC Standard



2 In the case operation load is an inductive load.
 2 In the case the wiring length to load is more than 5m.

③ In the case the load voltage is 100V AC. Be sure to use the auto switch with the contact protection box in any case mentioned above. Refer to p.6-19 for the details of contact protection box.

#### Note 1) Refer to common specifications on p.6-18. Note 2) Refer to p.6-18 for lead wire length.


50mA

Lead wire - Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm<sup>2</sup>, 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m

#### **Dimensions**

Max. load current Contact protection circuit

Internal resistance



• •	<u> </u>								
• • • •	Bore size								
Actuator series	6	10	16	20	25	32	40	50	63
CDJ2	6	7	7	-	-	-	-	-	-
CDVJ	—	7	7	—	—	—	—	—	-
CDLJ2	—	—	7	_	-	-	-	-	-
CDM2/CDBM2/CDVM3, 5/CDLM2	—	—	—	7	8	8	8	—	-
CDG1/MGG	—	_	—	8	10	9	10	10	11
CDLG1	—	—	—	8	10	9	10	-	-
RSDG	—	-	-	-	-	-	10	10	-
MGC	-	-	—	8	10	9	10	10	-
MLGC/RHC/REC	_	_	_	8	10	9	10	-	-

Note) Average value at normal temperature including hysteresis. (Tolerance  $\pm$  30%)



## **Reed Switch/Band Mounting** D-B53/D-B54/D-B64

#### Grommet



#### **Applicable Actuator Series**

Series	Bore size (mm)
CDM2, CDBM2, CDVM3/5, CDLM2	ø20, ø25, ø32, ø40
CDG1, MGG	ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100
CDLG1	ø20, ø25, ø32, ø40
CDA1, CDBA1, CDV3, CDVS, CDLA, CDL1, CE2, CNA	ø40, ø50, ø63, ø80, ø100
MGC	ø20, ø25, ø32, ø40, ø50
MLGC, RHC, REC	ø20, ø25, ø32, ø40

#### Specifications

Specifications	PLC: Programmable Logic Controller							
D-B5 (With indicator light)								
Auto switch model number	D-B53		D-B	54				
Application	PLC		Relay/	PLC				
Load voltage	24V DC	24V DC	100V	AC	200V AC			
Load current range	5 to 50mA	5 to 50mA	5 to 25	ōmA	5 to 12.5mA			
Contact protection circuit	None		Built	-in				
Internal voltage drop	≤ 2.4V		≤ 2.4	4V				
Indicator light	0	N: When red ligh	nt emitting	diode				
D-B6 (Without indicator light)								
Auto switch model number	D-B64							
Application	Relay/PLC							
Load voltage	24V <sup>AC</sup> <sub>DC</sub> or less 100V AC 200V AC							


D-B6 (Without indicator light)					
Auto switch model number		D-B64			
Application		Relay/PLC			
Load voltage	$24V \frac{AC}{DC}$ or less	100V AC			
Max. load current	Max.50mA	Max.25mA			
Contact protection circuit	Built-in				
Internal resistance					

Lead wire ----- Oilproof vinyl heavy insulation cable, ø4, 0.3mm<sup>2</sup>, 2 cores (Brown, Blue), 0.5m

Note 1) Refer to common specifications on p.6-18.

Note 2) Refer to p.6-18 for lead wire length.

#### Dimensions




#### Operation Range ( *l* Dimension)

Actuator series	Bore size							
Actuator series	20	25	32	40	50	63	80	100
CDM2, CDBM2, CDVM3, 5 CDLM2	8	8	9	9	-	-	_	_
CDG1, MGG	8	10	9	10	10	11	11	11
CDLG1	8	10	9	10	-	-	-	_
CDA1, CDBA1, CDV3, CDVS, CDLA, CDL1, CE2, CNA	_	_	_	9	10	11	11	11
MGC	8	10	9	10	10	-	-	-
MLGC, RHC, REC	8	10	9	10	—	-	_	—

Note) Average value at normal temperature including hysteresis. (Tolerance  $\pm$  30%)

#### **Internal Circuit** (): If not applicable for IEC Standard



*∕∕∕∕S*SMC

(mm)

Max.12.5mA

## **Reed Switch/Band Mounting** D-C73C/D-C80C

#### Connector




#### ▲ Caution

#### **Precautions**

①Confirm that the connector is appropriately tightened. If tightened insufficiently, the water resistant performance will deteriorate.

2 Refer to p.6-88 for the details.

#### **Internal Circuit** (): If not applicable for IEC Standard



Note) 1 In the case operation load is an inductive load. ②In the case the wiring length to load is > 5m. Be sure to use the auto switch with the contact protection box in any case mentioned above. Refer to p.6-19 for the details of contact protection box.

#### **Applicable Actuator Series**

Series	Bore size (mm)		
CDJ2	ø6, ø10, ø16		
CDVJ	ø10, ø16		
CDLJ2	ø16		
CDM2, CDBM2, CDVM3, CDVM5, CDLM2	ø20, ø25, ø32, ø40		
CDG1, MGG	ø20, ø25, ø32, ø40, ø50, ø63		
CDLG1	ø20, ø25, ø32, ø40		
RSDG	ø40, ø50		
MGC	ø20, ø25, ø32, ø40, ø50		
MLGC, RHC, REC	ø20, ø25, ø32, ø40		

#### **Specifications**

73C (With indicator lig	
uto switch model number	D-C73C
pplication	Relay/PLC
oad voltage	24V DC
oad current range	5 to 40mA
Contact protection circuit	None
nternal voltage drop	≤ 2.4V
ndicator light	ON: When red light emitting diode

PLC: Programmable Logic Controller


(mm)

Auto switch model number	D-C80C
Application	Relay/PLC
Load voltage	≤ 24V <sup>AC</sup> <sub>DC</sub>
Max. load current	50mA
Contact protection circuit	None
Internal resistance	≤ 1 (Including 3m lead wire)

•Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm<sup>2</sup>, 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p. 6-18

Note 2) Refer to p. 6-18 for lead wire length. Note 3) Lead wire with connector may be shipped with switch.

#### Dimensions



#### Operation Range ( *l* Dimension)

Actuator series	Bore size								
Actuator series	6	10	16	20	25	32	40	50	63
CDJ2	6	7	7		—	—	—	—	—
CDVJ	—	7	7		_	-	—	—	—
CDLJ2	—	—	7			—	—	—	—
CDM2, CDBM2, CDVM3, CDVM5, CDLM2	—		_	7	8	8	8	—	—
CDG1, MGG	—	—		8	10	9	10	10	11
CDLG1	—	_	_	8	10	9	10	—	—
RSDG	—	—				—	10	10	—
MGC	—	—		8	10	9	10	10	—
MLGC, RHC, REC	_	_	_	8	10	9	10	_	_

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)



# Reed Switch/Band Mounting **D-A33/D-A34/D-A44**

#### Terminal conduit: D-A3 DIN terminal: D-A4




#### ▲ Caution

#### Precautions

- Use cable whose O. D. is within the size in the figure to maintain water resistant performance.
- ②After wiring, confirm that tightening gland and all screws are tightened.

#### **Internal Circuit**



#### **Applicable Actuator Series**


Series	Bore size (mm)
CDA1, CDBA1, CDV3, CDVS, CDLA, CE2, CNA	ø40, ø50, ø63, ø80, ø100
CDL1	ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160
CDS1	ø125, ø140, ø160, ø180, ø200
RHC	ø20, ø25, ø32, ø40

#### Specifications PLC: Programmable Logic Controller D-A3 (With indicator light) Terminal conduit D-A34 Auto switch model number **D-A33** Application PLC Relay/PLC 24V DC 100V AC Load voltage 24V DC 200V AC Load current range 5 to 50mA 5 to 50mA 5 to 25mA 5 to12.5mA Contact protection circuit None Built-in Internal voltage drop ≤ 2.4V Indicator light ON: When red light emitting diode

D-A44 (With indicator light) DIN terminal						
Auto switch model number		D-A44				
Application		Relay/PLC				
Load voltage	24V DC	100V AC	200V AC			
Load current range	5 to 50mA	5 to 25mA	5 to 12.5mA			
Contact protection circuit	Built-in					
Internal voltage drop	≤ 2.4V					
Indicator light	ON: V	When red light emitting	diode			

Note) Refer to common specifications on p.6-18.

#### Dimensions




Note) Average value at normal temperature including hysteresis. (Tolerance ± 30%)



# Reed Switch/Band Mounting D-A33A/D-A34A/D-A44A

#### Terminal conduit: D-A3□A DIN terminal: D-A44A





#### **Applicable Actuator Series**

Series

CDM2, CDBM2, CDLM2

Bore size (mm) ø20, ø25, ø32, ø40

D-A3□A (With indica	ator light) Te	erminal cond	luit		
Auto switch model number		D-A34A		D-A33A	
Application		Relay/PLC		PLC	
Load voltage	24V DC	100V AC	200V AC	24V DC	
Load current range	5 to 50mA	5 to 25mA	5 to12.5mA	5 to 50mA	
Contact protection circuit		Built-in		None	
Internal voltage drop		5	2.4V	·	
Indicator light		ON: When red l	ight emitting dic	de	
D-A44A (With indica	tor light) DI	V terminal			
Auto switch model number		D-A	44A		
Application		Rela	y/PLC		
Load voltage	24V DC	100	V AC	200V AC	
Load current range	5 to 50mA 5 to 25mA 5 to 12.5mA				
Contact protection circuit	Built-in				
Internal voltage drop	≤ 2.4V				
Indicator light	ON: When red light emitting diode				

#### ▲ Caution


#### Precautions

①Use cable whose O. D. is within the size in the figure to maintain water resistant performance.


②After wiring, confirm that tightening gland and all screws are tightened.

#### Dimensions

#### D-A3□A



#### **D-A44A**



 
 Actuator series
 Bore size

 20
 25
 32
 40

 CDM2, CDBM2, CDLM2
 8
 8
 9
 9

(mm)

Note) Average value at normal temperature including hysteresis. (Tolerance  $\pm$  30%)



## **Reed Switch/Rail Mounting** D-A72/D-A73/D-A80





#### **Applicable Actuator Series**

Series	Bore size (mm)
CDJ2, CDVJ	ø10, ø16
CDQ2	ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160
CDXW	Plate mounted ø10, ø16, ø20, ø25, ø32, Housing mounted ø16, ø20, ø25, ø32
CDY1S, CY1L	ø6, ø10, ø15, ø20, ø25, ø32, ø40
RSDQ	ø16, ø20, ø32, ø40, ø50
MDU	ø25, ø32, ø40, ø50, ø63
CE1	ø12, ø20, ø32, ø40, ø50, ø63
MK, MK2	ø20, ø25, ø32, ø40, ø50, ø63
СХТ	ø32, ø40


#### Specifications

PLC: Programmable Logic Controller

D-A7 (With indicator light)					
Auto switch model number	D-A72	D-A73			
Application	Relay/PLC	Relay/PLC			
Load voltage	200V AC	24V DC	100V AC		
Load current range	5 to 10mA	5 to 40mA 5 to 20mA			
Contact protection circuit	None				
Internal voltage drop	≤ 2.4V				
Indicator light	ON: When red light emitting diode				
D-A8 (Without indicate	or light)				
Auto switch model number		D-A80			
Application		Relay/IC circuit/PLC			
Load voltage	24V $\frac{AC}{DC}$ or less 48V $\frac{AC}{DC}$ 100V $\frac{AC}{DC}$				
Max. load current	50mA	40mA	20mA		
Contact protection circuit	None				
Internal resistance	1 or less (Including 3m lead wire)				

#### **Internal Circuit**

#### (): If not applicable for IEC Standard



Note) (1)In the case operation load is an inductive load. ②In the case the wiring length to load is ">" 5m.


③In the case the load voltage is 100 or 200V AC. Be sure to use the auto switch with the contact protection box in any case mentioned above. D-A72 must be used with contact protection box.

Refer to p.6-19 for the details of contact protection box.

Note 1) Refer to common specifications on the p.6-18. Note 2) Refer to the p.6-18 for lead wire length.

#### Dimensions

Lead wire —



-Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm<sup>2</sup>, 2 cores (Brown, Blue), 0.5m

#### Operation Range ( *l* Dimension)

Actuator se	rico		Bore size														
Actuator se	nes	6	10	12	15	16	20	25	32	40	50	63	80	100	125	140	160
CDJ2, CDVJ		—	8	—		9	—	—		-		_	—	-	—	—	—
CDQ2		—	—	10	_	12	12	12	12	11	10	12	12	13	13	13	13
CDXW	В		—			6	6	6	6								
CDXW	P		6			6	6	6	6								
CDY1S		6	6	—	6	—	6	6	6	6	_	_	—	-	—	—	—
CY1L		6	6	-	6	-	6	6	6	6	_	_	—	-	—	—	—
RSDQ		—	—	—	_	—	12	12	12	11	10	_	—	—	—	_	—
MDU		—	—	—		—	_	13	13	13	13	13	—	-	—	—	—
CE1		—	—	10	—	—	12	—	12	11	10	12	—	—	—	—	—
MK, MK2		—	—	—	—	—	12	12	12	11	10	12	—	—	—	—	—
СХТ		-	_	—	_	-		-	12	11	_	-	-	-	_	—	—

Note) Average value at normal temperature including hysteresis. (Tolerance  $\pm$  30%)

(mm)

## **Reed Switch/Rail Mounting** *D-A7 H/D-A80H*

Grommet
Electrical entry : In-line



#### **Applicable Actuator Series**

Series	Bore size (mm)
CDJ2, CDVJ	ø10, ø16
CDQ2	ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160
CDXW	Plate mounted ø10, ø16, ø20, ø25, ø32, Housing mounted ø16, ø20, ø25, ø32
CDY1S, CY1L	ø6, ø10, ø15, ø20, ø25, ø32, ø40
RSDQ	ø16, ø20, ø32, ø40, ø50
MDU	ø25, ø32, ø40, ø50, ø63
CE1	ø12, ø20, ø32, ø40, ø50, ø63
MK, MK2	ø20, ø25, ø32, ø40, ø50, ø63
СХТ	ø32, ø40

#### Specifications


Specifications		PLC: Programmable Logic Controller								
D-A7⊡H (With indicator light)										
Auto switch model number	D-A72H	D-A	73H	D-A76H						
Application	Relay/PLC	IC circuit								
Load voltage	200V AC	24V DC	100V AC	4 to 8V DC						
Max. load current and range	5 to 10mA	5 to 40mA	5 to 20mA	20mA						
Contact protection circuit		Nc	one							
Internal voltage drop		≤ 2.4V								
Indicator light	ON: When red light emitting diode									
D-A80H (Without indic	D-A80H (Without indicator light)									

#### D

Auto switch model number	D-A80H						
Applications	Relay/IC circuit/PLC						
Load voltage	$24V \frac{AC}{DC}$ or less	48V AC	100V <sup>AC</sup> <sub>DC</sub>				
Max. load current	50mA	20mA					
Contact protection circuit	None						
Internal resistance	1 or less (Including 3m lead wire)						

-Oilproof vinyl heavy insulation cable, 0.2mm<sup>2</sup>, 2 cores (Brown, Blue), 3 cores (Brown, Black, Blue), 0.5m • Lead wire -Note 1) Refer to common specifications on p.6-18. Note 2) Refer to p.6-18 for lead wire length.

#### Dimensions



(mm)


#### Operation Range ( *l* Dimension

Actuator se		Bore size															
		6	10	12	15	16	20	25	32	40	50	63	80	100	125	140	160
CDJ2, CDV	'J	—	8	—	—	9	-	—	-	-	—	—	—	-	—	—	—
CDQ2		—	—	10	—	12	12	12	12	11	10	12	12	13	13	13	13
0.027/11/	В		—	_		6	6	6	6								
CDXW	Ρ		6		_	6	6	6	6 6 -					_	_		
CDY1S		6	6	_	6	—	6	6	6	6	_	—	_	_	_	—	—
CY1L		6	6	—	6	—	6	6	6	6	—	—	—	-	—	—	—
RSDQ		—	-	_		—	12	12	12	11	10	—	—	_	-	—	—
MDU		—	_	—	_	—	—	13	13	13	13	13	—	-	_	—	—
CE1		—	—	10	_	—	12	-	12	11	10	12	—	-	_	—	—
MK, MK2		—	-	_	_	—	12	12	12	11	10	12	—	-	—	_	_
СХТ		—	—	—	—	—	—	—	12	11	—	—	—	-	_	—	—

Note) Average value at normal temperature including hysteresis. (Tolerance ± 30%)

#### **Internal Circuit**

(): If not applicable for IEC Standard



Note) 1 In the case operation load is an inductive load. 2 In the case the wiring length to load is ">" 5m.

③In the case the load voltage is 100 or 200V AC. Be sure to use the auto switch with the contact protection box in any case mentioned above.

D-A72H must be used with contact protection box. Refer to p.6-19 for the details of contact protection box.



## **Reed Switch/Rail Mounting** D-A73C/D-A80C

#### Connector



#### ∧ Caution

**Internal Circuit** 

#### **Precautions**

①Confirm that the connector is appropriately tightened. If tightened insufficiently, the water resistant performance will deteriorate.

2 Refer to p.6-88 for the details.

(	): If not app	licable for IEC Stand	ard
	Esistance Resistance Zener diode	Contact protection box CD-P12 Chocke coll Chocke coll	,
	D-A80C	Contact –o OUT(±) protection Brown(Red) box to CD-P11 to CD-P12 –o OUT(≠) Blue(Black)	

Note) In the case operation load is an inductive load. 2 In the case the wiring length to load is ">" 5m.

Be sure to use the auto switch with the contact protection box in any case mentioned above. Refer to p.6-19 for the details of contact protection box.


#### **Applicable Actuator Series**

Series		Bore size (mm)							
CDJ2, CDVJ		ø10, ø16							
CDQ2	ø12, ø16,	ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160							
CDXW	Plate mountee	d ø10, ø16, ø20, ø25, ø32, Housing mounted ø16, ø20, ø25, ø32							
CDY1S, CY1L		ø6, ø10, ø15, ø20, ø25, ø32, ø40							
RSDQ		ø16, ø20, ø32, ø40, ø50							
MDU		ø25, ø32, ø40, ø50, ø63							
CE1		ø12, ø20, ø32, ø40, ø50, ø63							
MK, MK2	ø20, ø25, ø32, ø40, ø50, ø63								
СХТ	ø32, ø40								
Specifications PLC: Programmable Logic Control									
D-A73C (Wit	D-A73C (With indicator light)								
Auto switch mo	del number	D-A73C							
Application		Relay/PLC							
Load voltage		24V DC							
Load current ra	inge	5 to 40mA							
Contact protect	tion circuit	None							
Internal voltage	e drop	≤ 2.4V							
Indicator light		ON: When red light emitting diode							
D-A80C (Wit	hout indic	ator light)							
Auto switch mo	del number	D-A80C							
Application		Relay/IC circuit/PLC							
Load voltage		24V AC							
Max. load curre	ent	50mA							
Contact protect	tion circuit	None							
Internal resista	nce	1 or less (Including 3m lead wire)							

 $\bullet$  Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.6-18.

Note 2) Refer to p.6-18 for lead wire length. Note 3) Lead wire with connector may be shipped with switch.

#### Dimensions



•			•	-	-	-	- /										(,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,
Astustance			Bore size														
Actuator series		6	10	12	15	16	20	25	32	40	50	63	80	100	125	140	160
CDJ2, CDV	/J	-	8	-	—	9	—	—	—	-	—	—	—	-	—	—	—
CDQ2		_	—	10	—	12	12	12	12	11	10	12	12	13	13	13	13
CDXW –	В		—			6	6	6	6								
	P		6			6	6	6	6								
CDY1S		6	6	—	6	-	6	6	6	6	—	—	—	-		—	—
CY1L		6	6	—	6	—	6	6	6	6	—	—	—	-	_	—	—
RSDQ		-	—	—	—	-	12	12	12	11	10	—	—	-		—	—
MDU		—	—	—	—	—	—	13	13	13	13	13	—	-	_	—	—
CE1		-	—	10	—	-	12	—	12	11	10	12	—	-		—	—
MK, MK2		—	—	—	—	-	12	12	12	11	10	12	—	-	_	—	_
СХТ		-		-	-	-	_	-	12	11	_	-	_	-	—	-	_

Note) Average value at normal temperature including hysteresis. (Tolerance  $\pm$  30%)



## **Reed Switch/Tie-rod Mounting D-A5**□/**D-A6**

#### Grommet



#### **Applicable Actuator Series**

Series	Bore size (mm)					
CDA1, CDBA1, CDV3, CDVS, CDLA, CE2, CNA	ø40, ø50, ø63, ø80, ø100					
CDL1	ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160					
CDS1	ø125, ø140, ø160, ø180, ø200					
MDB, MDBB	ø32, ø40, ø50, ø63, ø80, ø100					

#### Specifications

PLC: Programmable Logic Controllar

(mm)

D-A5 (With indicator light)										
Auto switch model number	D-A53		D-A54							
Application	PLC		IC circuit							
Load voltage	24V DC	24V DC	100V AC	200V AC	4 to 8V DC					
Max. load current	5 to 50m A	5 to 50m A	5 to 05 m A	5 to 40 5 m A	20mA					
and range	5 to 50mA	5 to 50mA	5 to 25mA	5 to 12.5mA						
Contact protection circuit	None		None							
Internal voltage drop		0.8V or less								
Indicator light	ON: When red light emitting diode									


#### D-A6 (Without indicator light)

Auto switch model number		D-A67									
Application		PLC/IC circuit									
Load voltage	$\leq 24V \frac{AC}{DC}$	100V AC	200V AC	MAX. 24V DC							
Max. load current	50mA	12.5mA	30mA								
Contact protection circuit		None									
Internal resistance		≤ 10	≤ 1 (Including 3m lead wire)								

#### **Internal Circuit**

#### (): If not applicable for IEC Standard


**D-A53** 



Lead wire — Oilproof vinyl heavy insulation cable, ø4, 0.3mm<sup>2</sup>, 2 cores (Brown, Blue), 0.5m or ø4, 0.2mm<sup>2</sup>, 3 cores (Brown, Black, Blue), 0.5m

Note 1) Refer to common specifications on p.6-18. Note 2) Refer to p.6-18 for lead wire length.

#### Dimensions



₽ 303== Indicator light 12 33 D-A64/A67:

without indicator light

#### **Operation Range (***l* **Dimension)**

•	-	•									()	
Actuator series		Bore size										
Actuator series	32	40	50	63	80	100	125	140	160	180	200	
CDA1, CDBA1, CDV3, CNA, CDVS, CDLA, CE2	—	9	10	11	11	11	_	_	_	_	_	
CDL1	—	9	10	11	11	11	10	10	10	—	_	
CDS1	—		_	_	—	—	10	10	10	10	10	
MDB, MDBB	9	9	10	11	11	11	—	—	—	—	_	

Note) Average value at normal temperature including hysteresis. (Tolerance  $\pm$  30%)




## **Reed Switch/Tie-rod Mounting** D-A33C/D-A34C/D-A44C

#### Terminal conduit: D-A3 C **DIN terminal: D-A44C**



#### Internal Circuit

Dimensions



#### **Applicable Actuator Series**

Series	Bore size (mm)
CDA1, CDBA1, CDV3, CDVS, CDLA, CDL1, CE2, CNA	ø40, ø50, ø63, ø80, ø

ø100

### Specifications

Specifications		PLC: Programmable Logic Controller						
D-A3 C (With indica	ator light) Te	erminal cond	luit					
Auto switch model number	D-A33C D-A34C							
Application	PLC	PLC Relay/PLC						
Load voltage	24V AC	24V DC	100V AC	200V AC				
Load current range	5 to 50mA	5 to 50mA	5 to 25mA	5 to 12.5mA				
Contact protection circuit	None		Built-in					
Internal voltage drop		≤ 2	.4V					
Indicator light	ON: When red light emitting diode							
D-A44C (With indica	tor light) DI	V terminal						
Auto switch model number		D-A	44C					
Application		Relay	/PLC					
Load voltage	24V DC	100	/ AC	200V AC				
Load current range	5 to 50m/	A 5 to 2	25mA	5 to 12.5mA				
Contact protection circuit	Built-in							
Internal voltage drop	≤ 2.4V							
Indicator light	ON: When red light emitting diode							
Note) Refer to common specifi	cations on p.6-18.							

#### ▲ Caution

#### **Precautions**

①Use cable whose O. D. is within the size in the figure to maintain water resistant performance.

2 After wiring, confirm that tightening gland and all screws are tightened.

ø6.8 to ø11.5)

Tightening gland

T'

6.5

6.5

7.5

9.5

#### 34 G(PF) 1/2 G(PF)1/2 D-A3 C Applicable cable O.D. **D-A44C** (Applicable cable O.D. ø6.8 to ø9.6) I Έ Operation range (Refer to the table below.) *i* Operation range C (Refer to the table below.) 16 HW Most sensitive position HW 16 Most sensitive position 26 Indicator light 26 3 3 36 49 49.5 2-M5 X 12 2-M5 X 12 Hex. socket head cap screw Hex. socket head cap screv Tightening gland 4-Z Hex. socket 6 head cap screw 4-Z Hex. socket head cap screw Operation Range ( *l* Dimension) Dimensions Bore size Bore size (mm) Switch part No. С НW н H' Т Actuator series (mm) 40 50 63 80 100 58(67.5) D-A3 C-4, D-A44C-4 50.5(60) CDA1, CDBA1, CDV3, 40 44 69 7.5 10 CDVS, CDLA, CDL1, 9 11 11 11 D-A3 C-5, D-A44C-5 59(68.5) 51.5(61) 50 52 77 8.5 CNA D-A3 C-6, D-A44C-6 61.5(71) 53(62.5) 63 64 91 10.5 D-A3 C-8, D-A44C-8 65(74.5) 54 5(64) 78 107 12.5 9.5 Note) Average value at normal temperature including 80 D-A3 C-10, D-A44C-10 100 92 68(77.5) 57.5(67) 15.5 hysteresis. (Tolerance ± 30%) 121 \* ( ): Values for D-A44C



(mm)

Ζ

M5 X 16

M5 X 20


M5 X 25

## Reed Switch/Direct Mounting D-A90/D-A93/D-A96






Internal Circuit
(): If not applicable for IEC Standard



Note) ①In the case operation load is an inductive load. ②In the case the wiring length to load is ">" 5m. ③In the case the load voltage is 100V AC.

Be sure to use the auto switch with the contact protection box in any case mentioned above. Refer to p.6-19 for the details of contact protection box.

#### Dimensions



### Operation Range ( $\ell^{24.5}$ Dimension)

Actuator						В	ore si	ze					
series	6	8	10	12	16	20	25	32	40	50	63	80	100
CDU	5	—	6	-	9	11	12.5	14	—	—	-	-	-
CDQS	-	-		6	7.5	10	10	—	—	-	—	—	-
CDQ2	-	-	-	-	-	—	-	9.5	9.5	9.5	11.5	9	11.5
MY1	—	—	—	—	5	5	-	—	—	-	-	—	-
MXU	5	—	6	—	9	—	_	_	—	_	-	-	
MXW	-	6		6	8.5	10	10	—	—	-	—	-	-
MXF	_	4.5	_	5	6	7	_	_	_	_	—	_	_
MXS	4.5	5	-	6	7	8	8	_	_	-	-	_	-

#### **Applicable Actuator Series**

Series	Bore size (mm)
CDU	ø6, ø10, ø16, ø20, ø25, ø32
CDQS	ø12, ø16, ø20, ø25
CDQ2*	ø32, ø40, ø50, ø63, ø80, ø100
MY1	ø16, ø20
MXU	ø6, ø10, ø16
MXW	ø8, ø12, ø16, ø20, ø25
MXF	ø8, ø12, ø16, ø20
MXS/MXQ	ø6, ø8, ø12, ø16, ø20, ø25
*Not applicable	for CDQP2

Series	Bore size (mm)
МХР	ø10, ø12, ø16
MTS	ø20, ø25, ø32, ø40
СХТ	ø12, ø16, ø20, ø25, ø32, ø40
МК	ø12, ø16
MK2	ø32, ø40, ø50, ø63
RSQ	ø12, ø32, ø40, ø50
CEP	ø12, ø20
CY1R	ø6, ø10, ø15, ø20

PLC: Programmable Logic Controller

**Specifications** 

#### D-A90 (Without indicator light)

<b>D</b> 7100 (								
Auto swich modle number	D-A90							
Application		IC circuit/Relay/PLC						
Load voltage	24V <sup>AC</sup> <sub>DC</sub> or less	100V <sup>AC</sup> <sub>DC</sub> or less						
Max. load current	50mA	40mA	20mA					
Contact protection circuit		None						
Internal resistance	1 0	r less (Including 3m lead v	wire)					
D-A93/D-A96	With indicator lig	ght)						
Auto switch model number	D-A93 D-A96							
Application	Relay	//PLC	IC circuit					
Load voltage	24V DC	100V AC	4 to 8V DC					
Max. load current and load current range	5 to 40mA	5 to 40mA 5 to 20mA						
Contact protection circuit	None							
Internal voltage drop	≤ 2.4V (up to 20mA)/≤ 3V (up to 40mA) ≤ 0.8V							
Indicator light	ON: When red light emitting diode							

#### Lead wire

D-A90/D-A93 — Oilproof vinyl heavy insulation cable, ø2.7, 0.18mm<sup>2</sup> X 2cores (Brown, Blue), 0.5m D-A96 — Oilproof vinyl heavy insulation cable, ø2.7, 0.15mm<sup>2</sup> X 3cores (Brown, Black, Blue), 0.5m Note 1) Refer to common specifications on p.6-18.

Note 2) Refer to p.6-18 for lead wire length.

#### ▲ Caution

#### **Precautions**

①Fix the switch with appropriate screw installed on the switch body. If using other screws, switch may be damaged.

#### **Operation Range (** *l* **Dimension)**

Actuator						Bore	e size					
series	6	8	10	12	15	16	20	25	32	40	50	63
MXQ	4.5	5	-	6	—	7	8	9	-	—	-	-
MXP	—	—	5	5	—	5	-	—	—	—	—	-
MTS	—	-	-	—	—	-	7.5	8	7	8	-	-
СХТ	—	—	—	6	—	7.5	10	10	9.5	9.5	_	_
МК	—	—	—	6	—	7.5	-	—	-	—	—	-
MK2	—	—	-	-	—	-	-	-	9.5	9.5	9.5	11.5
RSQ	—	—	—	—	—	—	-	—	9.5	9.5	9.5	-
CEP	—	—	-	5	—	—	6.5	—	-	—	—	-
CY1R	9	—	13	—	8	—	6	—	-	—	—	-
Note) Avera	de vali	ie at n	ormal	tempe	rature	includi	na hvs	teresis	(Tole	rance	+30%	)

(mm)

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)



(mm)


## Reed Switch/Direct Mounting D-A90V/D-A93V/D-A96V





#### Internal Circuit


#### (): If not applicable for IEC Standard



Note) ①In the case operation load is an inductive load. ②In the case the wiring length to load is ">" 5m.

③In the case the load voltage is 100V AC. Be sure to use the auto switch with the contact protection box in any case mentioned above. Refer to p.6-19 for the details of contact protection box.

#### Dimensions



#### Operation Range ( *l* Dimension)

Actuator		-			-	B	ore si	ze	_	_			
series	6	8	10	12	16	20	25	32	40	50	63	80	100
CDU	5	—	6	—	9	11	12.5	14	_	_		_	_
CDQS	—	—	-	6	7.5	10	10	—	—	-	—	—	-
CDQ2	Ι	_	_	—	_	_	_	9.5	9.5	9.5	11.5	9	11.5
MY1	-	—	_	—	5	5	-	—	—	-	—	_	-
MXU	5	-	6	-	9	—	-	—	-	-	-	-	-
MXW	—	6	-	6	8.5	10	10	—	—	-	-	—	-
MXF	—	4.5	—	5	6	7	—	—	—	-	—	—	-
MXS	4.5	5	_	6	7	8	8	_	—	-	—	_	-

#### **Applicable Actuator Series**

Series	Bore size (mm)			
CDU	ø6, ø10, ø16, ø20, ø25, ø32			
CDQS	ø12, ø16, ø20, ø25			
CDQ2*	ø32, ø40, ø50, ø63, ø80, ø100			
MY1	ø16, ø20			
MXU	ø6, ø10, ø16			
MXW	ø8, ø12, ø16, ø20, ø25			
MXF	ø8, ø12, ø16, ø20			
MXS/MXQ Ø6, Ø8, Ø12, Ø16, Ø20, Ø25				
*Not applicable	for CDQP2			

Series	Bore size (mm)
МХР	ø10, ø12, ø16
MTS	ø20, ø25, ø32, ø40
СХТ	ø12, ø16, ø20, ø25, ø32, ø40
МК	ø12, ø16
MK2	ø32, ø40, ø50, ø63
RSQ	ø12, ø32, ø40, ø50
CEP	ø12, ø20
CY1R	ø6, ø10, ø15, ø20

PLC: Programmable Logic Controller

#### Specifications

D-A90V (Without indicator light)

D AUUT (IIIIII	out manoutor ngin	-/						
Auto swich model number	D-A90V							
Application		IC circuit/Relay/PLC						
Load voltage	24V <sub>DC</sub> or less	48V <sup>AC</sup> <sub>DC</sub> or less	100V <sup>AC</sup> <sub>DC</sub> or less					
Max. load current	50mA	40mA	20mA					
Contact protection circuit		None						
Internal resistance	1 0	r less (Including 3m lead v	wire)					
D-A93V/D-A96	V (With indicator	<sup>·</sup> light)						
Auto switch model number	D-A	93V	D-A96V					
Application	Relay	//PLC	IC circuit					
Load voltag	24V DC	100V AC	4 to 8V DC					
Max. load current and load current range	5 to 40mA	5 to 20mA	20mA					
Contact protection circuit	None							
Internal voltage drop	2.7V or less 0.8V or less							
Indicator light	ON: When red light emitting diode							

#### Lead wire

D-A90V/D-A93V — Oilproof vinyl heavy insulation cable, ø2.7, 0.18mm<sup>2</sup> X 2cores (Brown, Blue), 0.5m D-A96V — Oilproof vinyl heavy insulation cable, ø2.7, 0.15mm<sup>2</sup> X 3cores (Brown, Black, Blue), 0.5m Note 1) Refer to common specifications on p.6-18.

Note 2) Refer to p.6-18 for lead wire length.

#### Caution

#### **Precautions**

①Fix the switch with appropriate screw installed on the switch body. If using other screws, switch may be damaged.

#### **Operation Range (** *l* **Dimension)**

Actuator						Bore	e size					
series	6	8	10	12	15	16	20	25	32	40	50	63
MXQ	4.5	5	-	6	—	7	8	9	-	-	-	-
MXP	-	—	5	5	—	5	-	-	-	-	-	-
MTS	-	—	—	-	—	—	7.5	8	7	8	—	-
СХТ	-	—	-	6	—	7.5	10	10	9.5	9.5	-	-
MK	-	—	—	6	—	7.5	-	—	—	-	—	-
MK2	-	—	-	-	—	-	-	-	9.5	9.5	9.5	11.5
RSQ	-	—	—	-	—	—	-	—	9.5	9.5	9.5	-
CEP	-	—	—	5	—	—	6.5	—	-	-	—	-
CY1R	9	—	13	-	8	—	6	—	—	-	—	-
Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)												

**SMC** 

(mm)

(mm)

## **Reed Switch/Direct Mounting** D-90/D-97

Grommet
Lead wire: Parallel cord



#### **Applicable Actuator Series**

Series	Bore size (mm)
CDJP-□D	ø6, ø10, ø15
CDU	ø6, ø10, ø16, ø20, ø25, ø32

#### Specifications

Specifications	PLC: Programmable Logic Controller					
D-90 (Without indicator lig	ght)					
Auto switch model number		D-90				
Application		Relay/IC circuit/PL	C			
Load voltage	5V AC	12V AC	24V AC			
Max. load current		50mA				
Internal resistance	1 or less (Including 3m lead wire)					
D-97 (With indicator light)						
Auto switch model number		D-97				
Application	Relay/PLC					
Load voltage	24V DC					
Load current range	5 to 40mA					
Internal voltage drop	≤ 2.4V					
Indicator light	ON: When red light emitting diode					
• Loop Julian Minute and the set of the						


• Lead wire — Vinyl parallel cable, 0.2mm<sup>2</sup>, 2 cores, 0.5m


Note 1) Refer to common specifications on p.6-18.

Note 2) Refer to p.6-18 for lead wire length.

#### Dimensions

#### D-90





#### **Operation Range (***l* **Dimension)**


Actuator series				Bore size							
6		10	15	16	20	25	32				
<b>CDJP-D</b> 5.5	5	8	9	-	—	-	—				
Without shield plate 5.5	5	7	-	9	11	12	14				
CDU With shield plate -		—	—	7	8	8	9				

(mm)

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)

#### **Internal Circuit**

(): If not applicable for IEC Standard



Note) ①In the case operation load is an inductive load.  $\textcircled{2}\$  In the case the wiring length to load is ">" 5m.

Be sure to use the auto switch with the contact protection box in any case mentioned above. Refer to p.6-19 for the details of contact protection box.

**GSMC** 

## **Reed Switch/Direct Mounting** D-90A/D-93A

Grommet	
Lead wire: Heavy insulation cable	



#### **Applicable Actuator Series**

Series	Bore size (mm)
CDJP-□D	ø6, ø10, ø15
CDU	ø6, ø10, ø16, ø20, ø25, ø32

Speci	ification	S	
		-	

PLC: Programmable Logic Controller

D-90A (Without indicator light)						
Auto switch model number	D-90A					
Application	Relay/IC circuit/PLC					
Load voltage	5V AC DC	12V AC DC	24V AC DC	100V AC DC		
Max. load current	50mA 20mA					
Internal resistance 1 or less (Including 3m lead wire)						
D-93A (With indicator light)						


Auto switch model number	D-93A				
Application	Rela	y/PLC			
Load voltage	24V DC	100V AC			
Load current range	5 to 40mA	5 to 20mA			
Internal voltage drop	≤ 2.4V				
Indicator light	ON: When red light emitting diode				
• Lead wire Oilproof vinul beaux insulation cable 0.2mm <sup>2</sup> , 2 cores (Brown, Blue), 0.5m					

• Lead wire — Oilproof vinyl heavy insulation cable, 0.2mm<sup>2</sup>, 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.6-18.


Note 2) Refer to p.6-18 for lead wire length.

#### Dimensions





#### **D-93A**




#### T **Operation Range (** *l* **Dimension)**

Operation Range ( <i>l</i> Dimension) (mm)										
Actuator series		Bore size								
		6	10	15	16	20	25	32		
CDJP-□D		5.5	8	9	—	—	—	—		
CDU	Without shield plate	5.5	7	—	9	11	12	14		
CDU	With shield plate	-	—	—	7	8	8	9		

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)

### **Internal Circuit**

(): If not applicable for IEC Standard



Note) In the case operation load is an inductive load. (2)In the case the wiring length to load is ">" 5m. ③In the case the load voltage is 100V AC.

Be sure to use the auto switch with the contact protection box in any case mentioned above. Refer to p.6-19 for the details of contact protection box.



## **Reed Switch/Direct Mounting** D-Z73/D-Z76/D-Z80

#### Grommet



**Internal Circuit** 

ww-Ø

ner diode Zer Reed

Blue(Black)

~~~~ Resistance

-⊀-

Reverse flow

prevent diode

-17

**D-Z73** 

switch

**D-Z76** 

switch

Reed

**D-Z80** 

switch

١æ

Ø

LĘD

(): If not applicable for IEC Standard

∘OUT(+)

to

P12 -OUT(-) Blue/P1

(+)

voltage

Power

(--)

-OUT(±)

to

oOUT(∓)

Brown(Red)

Blue(Black)

Brown(Red)

Blue(Black)

rotection

box

CD-P11

CD-P12

LED Brown(Red) Contact

DC(+) Brown(Red

Black(White)

Blue(Black)

Contact

box

protection

CD-P11

CD-P12

ÕUT

DC(-)

Load

#### **Applicable Actuator Series**

| Series           | Series Bore size (mm)                             |  |  |  |
|------------------|---------------------------------------------------|--|--|--|
| MGQ, MVGQ, MGP   | ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100 |  |  |  |
| CXS              | ø6, ø10, ø15, ø20, ø25, ø32                       |  |  |  |
| RSH              | ø20, ø32, ø50, ø63, ø80                           |  |  |  |
| MY1B             | ø25, ø32, ø40, ø50, ø63, ø80, ø100                |  |  |  |
| MY1M, MY1C, CY1R | ø25, ø32, ø40, ø50, ø63                           |  |  |  |
| MY1H, ML2B       | ø25, ø32, ø40                                     |  |  |  |
| MGF              | ø40, ø63, ø100                                    |  |  |  |
| CY1H             | ø10, ø15, ø20, ø25, ø32                           |  |  |  |

#### Specifications

PLC: Programmable Logic Controller

(mm)


| D-Z7 (With indicator light)              |                                              |            |       |  |  |  |  |
|------------------------------------------|----------------------------------------------|------------|-------|--|--|--|--|
| Auto swich model number                  | D-2                                          | 273        | D-Z76 |  |  |  |  |
| Application                              | Relay                                        | IC circuit |       |  |  |  |  |
| Load voltage                             | 24V DC                                       | 4 to 8V DC |       |  |  |  |  |
| Max. load current and load current range | 5 to 40mA                                    | 20mA       |       |  |  |  |  |
| Contact protection circuit               | None                                         |            |       |  |  |  |  |
| Internal voltage drop                    | ≤ 2.4V (up to 20mA)/≤ 3V (up to 30mA) ≤ 0.8V |            |       |  |  |  |  |
| Indicator light                          | ON: When red light emitting diode            |            |       |  |  |  |  |
| D 70 (With out indicator light)          |                                              |            |       |  |  |  |  |

#### D-Z8 (Without indicator light)

| •                          | <b>J</b> /                                                                                     |  |  |  |  |  |
|----------------------------|------------------------------------------------------------------------------------------------|--|--|--|--|--|
| Auto switch model number   | D-Z80                                                                                          |  |  |  |  |  |
| Application                | Relay/PLC/IC circuit                                                                           |  |  |  |  |  |
| Load voltage               | 24V $\stackrel{AC}{DC}$ or less 48V $\stackrel{AC}{DC}$ or less 100V $\stackrel{AC}{DC}$ or le |  |  |  |  |  |
| Max. load current          | 50mA 40mA 20mA                                                                                 |  |  |  |  |  |
| Contact protection circuit | None                                                                                           |  |  |  |  |  |
| Internal resistance        | 1 or less (Including 3m lead wire)                                                             |  |  |  |  |  |

• Lead wire - Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm<sup>2</sup>, 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.6-18. Note 2) Refer to p.6-18 for lead wire length.

#### Dimensions



#### Operation Range ( *l* Dimension)

| Actuator series |   |    |     |    |     | Bore | size |      |      |      |      |      |     |
|-----------------|---|----|-----|----|-----|------|------|------|------|------|------|------|-----|
| Actualor series | 6 | 10 | 12  | 15 | 16  | 20   | 25   | 32   | 40   | 50   | 63   | 80   | 100 |
| MGQ, MVGQ       | — | —  | 7.5 | —  | 8.5 | 9.5  | 9.5  | 11   | 11   | 11   | 13   | 13   | 14  |
| CXS             | 9 | 7  | —   | 9  | -   | 9    | 9    | 11   | —    | _    | -    | -    | —   |
| MGP             | — | —  | 7.5 | —  | 10  | 10   | 10   | 10.5 | 10.5 | 10.5 | 11.5 | 11.5 | 12  |
| RSH             | _ | —  | —   | —  | —   | 8.5  | —    | 7    | —    | 9.5  | 10.5 | 11.5 | —   |
| MY1B            | — | -  | —   | -  | -   | —    | 12   | 12   | 12   | 12   | 12   | 12   | 12  |
| MY1M, MY1C      | — | -  | —   | -  | -   | —    | 12   | 12   | 12   | 12   | 12   | _    | -   |
| MY1H, ML2B      | — | -  | —   | —  | -   | —    | 12   | 12   | 12   | —    | -    |      | -   |
| MGF             | — | —  | —   | —  | —   | —    | —    | —    | 13.5 | —    | 12   | -    | 13  |
| CY1H            | — | 8  | —   | 6  | -   | 6    | 6    | 9    | —    | —    | -    | —    | -   |
| CY1R            | _ | _  | _   | —  | _   | _    | 9    | 9    | 11   | 11   | 11   | _    | -   |


Note) ①In the case operation load is an inductive load. ②In the case the wiring length to ">" 5m. ③In the case the load voltage is 100V AC.

Be sure to use the auto switch with the contact protection box in any case mentioned above. Refer to the p.6-19 for the details of contact protection box.

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)

## **Reed Switch/Direct Mounting Type** D-R73/D-R80






Left hand mounting Right hand mounting

#### Auto switch internal circuit

(): Before IEC standard



#### Applicable rotary actuator series

| Series | Size                |
|--------|---------------------|
| CDRB1  | 20, 30, 50, 80, 100 |
| CDRBU  | 20, 30              |
| MDSUB  | 7, 20               |

#### Auto switch specificatoins

| Auto switch specificatoins               |                     |                  | PLC: Programmable Logic Controller             |                   |            |  |
|------------------------------------------|---------------------|------------------|------------------------------------------------|-------------------|------------|--|
| D-R73□ (With indicator light)            |                     |                  | D-R80 (Without indicator light)                |                   |            |  |
| Auto switch model no.                    | D-R731              | /D-R732          | D-R801/D-R802                                  |                   |            |  |
| Applicable load                          | Relay               | , PLC            | Relay, IC circuit, PLC                         |                   |            |  |
| Load voltage                             | 100V AC             | 24V DC           | $C = 24V_{DC}^{AC}$ or less $48V_{DC}^{AC}$ 10 |                   | 100V AC DC |  |
| Max. load current and load current range | 5 to 20mA 5 to 40mA |                  | 50mA                                           | 40mA              | 20mA       |  |
| Contact protection circuit               | Nc                  | ne               | None                                           |                   |            |  |
| Internal voltage drop                    | 2.4V or less        |                  | 0                                              |                   |            |  |
| Indicator light                          | ON: Red light       | emitting diode   | None                                           |                   |            |  |
| ← Oil p                                  | proof vinyl heavy   | insulation cable | 0.2mm <sup>2</sup> , X2 wire                   | (Brown, blue) 0.5 | im         |  |


Note 1) Refer to p.6-18 for common specifications of reed switch.


Note 2) Refer to p.6-18 for lead wire length.

#### Dimensions

#### **D-R731: Right hand mounting**


#### D-R732: Left hand mounting





#### D-R801: Right hand mounting

#### D-R802: Left hand mounting






## **Reed Switch/Direct Mounting Type** *D-R73 C/D-R80 C*

| Connector                 |  |
|---------------------------|--|
| Electrical Entry: In-line |  |
|                           |  |





Left hand mounting Right hand mounting

#### Auto switch internal circuit (): Before IEC standard

#### D-R731/R732 Brown Emitting diode (Red) Contact –o OUT (+) protection Brown (I switch Resistance Brown (Red) -bh box Zener Reed diode CD-P11 CD-P12 →OUT (-) Blue ..... Blue (Black) (Black) D-R801/R802 Contact -o OUT (±) protection Brown (Red) box ~ CD-P11 -> OUT (±) CD-P12 1 Blue (Black) ▲ Specific product precautions

#### A Caution

Confirm that there is no looseness after wiring. The looseness will decrease water resistance.

#### Applicable rotary actuator series

| Series | Size                |
|--------|---------------------|
| CDRB1  | 20, 30, 50, 80, 100 |
| CDRBU  | 20, 30              |
| MDSUB  | 7, 20               |

#### Auto switch specifications

| Auto switch spe                 | o switch specifications PLC: Programmable Logic Con |                                         |  |  |  |
|---------------------------------|-----------------------------------------------------|-----------------------------------------|--|--|--|
| D-R73□C ( With indicator light) |                                                     | D-R80 C (Without indicator light)       |  |  |  |
| Auto switch model no.           | D-R731C/D-R732C                                     | D-R801C/D-R802C                         |  |  |  |
| Applicable load                 | Relay, PLC                                          | Relay, PLC                              |  |  |  |
| Load voltage                    | 24V DC                                              | 24V <sup>AC</sup> <sub>DC</sub> or less |  |  |  |
| Load current range              | 5 to 40mA                                           | 50mA                                    |  |  |  |
| Contact protection circuit      | None                                                | None                                    |  |  |  |
| Internal voltage drop           | 2.4V or less                                        | 0                                       |  |  |  |
| Indicator light                 | ON: Red light emitting diode                        | None                                    |  |  |  |
|                                 |                                                     |                                         |  |  |  |


Lead wire — Oil proof vinyl heavy insulation cable ø3.4, 0.2mm<sup>2</sup> Note 1) Refer to p.6-18 for common specifications of reed switch.


Note 2) Refer to p.6-18 for lead wire length.

#### Dimensions


#### **D-R731C: Right Hand Mounting**

**D-R732C: Left Hand Mounting** 






#### 70-1-(D-R732) 32.5 8.5 Most sensitive position





**D-R801C: Right hand mounting** 

#### D-R802C: Left hand mounting









## **Reed Switch/Direct Mounting** D-E73A/D-E76A/D-E80A

#### Grommet





#### **Applicable Actuator Series**

| Series | Bore size (mm) |
|--------|----------------|
| CDBX   | ø10            |
| ML1    | ø25, ø32, ø40  |

#### Specifications


| Specifications                           | PLC: Programmable Logic Controlle |                         |            |  |  |  |
|------------------------------------------|-----------------------------------|-------------------------|------------|--|--|--|
| D-E7□A (With indicate                    | or light)                         |                         |            |  |  |  |
| Auto swich model number                  | D-E                               | 73A                     | D-E76A     |  |  |  |
| Application                              | Rela                              | y/PLC                   | IC circuit |  |  |  |
| Load voltage                             | 24V DC                            | 24V DC 100V AC          |            |  |  |  |
| Max. load current and load current range | 5 to 40mA                         | 5 to 40mA 5 to 20mA     |            |  |  |  |
| Contact protection circuit               |                                   | None                    |            |  |  |  |
| Internal voltage drop                    | ≤ 2                               | ≤ 2.4V ≤ 0.8V           |            |  |  |  |
| Indicator light                          | ON: V                             | Vhen red light emitting | g diode    |  |  |  |
| D-E80A (Without indic                    | ator light)                       |                         |            |  |  |  |
| Auto switch model number                 |                                   | D-E80A                  |            |  |  |  |
| Application                              | Relay/PLC/IC circuit              |                         |            |  |  |  |
| Lood voltage                             | 24V AC or loss                    | AOV AC                  | 100V AC    |  |  |  |

| Load voltage               | 24V $\frac{AC}{DC}$ or less        | 48V AC<br>DC | 100V AC<br>DC |  |  |
|----------------------------|------------------------------------|--------------|---------------|--|--|
| Max. load current          | 50mA                               | 40mA         | 20mA          |  |  |
| Contact protection circuit | None                               |              |               |  |  |
| Internal resistance        | 1 or less (Including 3m lead wire) |              |               |  |  |

• Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm<sup>2</sup>, 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.6-18.

Note 2) Refer to p.6-18 for lead wire length.


#### **Internal Circuit** (): If not applicable for IEC Standard



Note) 1 In the case operation load is an inductive load. 2 In the case the wiring length to load is ">" 5m. ③In the case the load voltage is 100V AC.

Be sure to use the auto switch with the contact protection box in any case mentioned above. Refer to p.6-19 for the details of contact protection box.

#### **Dimensions**



| Actuator corios | Bore size |    |    |    |  |  |  |
|-----------------|-----------|----|----|----|--|--|--|
| Actuator series | 10        | 25 | 32 | 40 |  |  |  |
| CDBX            | 6         | —  | —  | —  |  |  |  |
| MI 1            | _         | 6  | 6  | 6  |  |  |  |

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)

# 2 Colour Indication Style Reed Switch/Band Mounting **D-B59W**

#### Grommet

The suitable operating point can be indicated with a green light. (Red Green Red)



#### **Applicable Actuator Series**

| Series                                           | Bore size (mm)                          |
|--------------------------------------------------|-----------------------------------------|
| CDM2, CDBM2, CDVM3,<br>CDVM5, CDLM2              | ø20, ø25, ø32, ø40                      |
| CDG1, MGG                                        | ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100 |
| CDLG1                                            | ø20, ø25, ø32, ø40                      |
| CDA1, CDBA1, CDV3, CDVS,<br>CDLA, CDL1, CE2, CNA | ø40, ø50, ø63, ø80, ø100                |
| MGC                                              | ø20, ø25, ø32, ø40, ø50                 |
| MLGC, RHC, REC                                   | ø20, ø25, ø32, ø40                      |

#### Specifications

PLC: Programmable Logic Controller


(mm)

| D-B59W (With indicator light) |                                                                                                   |  |  |  |  |  |  |
|-------------------------------|---------------------------------------------------------------------------------------------------|--|--|--|--|--|--|
| Auto switch model number      | D-B59W                                                                                            |  |  |  |  |  |  |
| Application                   | Relay/PLC                                                                                         |  |  |  |  |  |  |
| Load voltage                  | 24V DC                                                                                            |  |  |  |  |  |  |
| Load current range            | 5 to 40mA                                                                                         |  |  |  |  |  |  |
| Contact protection circuit    | Built-in                                                                                          |  |  |  |  |  |  |
| Internal voltage drop         | ≤ 4V                                                                                              |  |  |  |  |  |  |
| Indicator light               | Operating point: Red light emitting diode<br>Suitable operating point: Green light emitting diode |  |  |  |  |  |  |


 Lead wire ——Oilproof vinyl heavy insulation cable, ø4, 0.3mm<sup>2</sup>, 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.6-18. Note 2) Refer to the p.6-18 for lead wire length.

#### **Internal Circuit**

#### (): If not applicable for IEC Standard



#### Dimensions



#### Operation Range ( $\ell$ Dimension)

| Actuator series                                  | Bore size |    |    |    |    |    |    |     |  |  |
|--------------------------------------------------|-----------|----|----|----|----|----|----|-----|--|--|
| Actuator series                                  | 20        | 25 | 32 | 40 | 50 | 63 | 80 | 100 |  |  |
| CDM2, CDBM2, CDVM3,<br>CDVM5, CDLM2              | 12        | 12 | 13 | 13 | _  | _  | _  | _   |  |  |
| CDG1                                             | 13        | 13 | 14 | 14 | 14 | 17 | 16 | 18  |  |  |
| CDLG1                                            | 13        | 13 | 14 | 14 | —  | —  | —  | —   |  |  |
| CDA1, CDBA1, CDV3, CDVS,<br>CDLA, CDL1, CNA, CE2 | _         | _  | _  | 14 | 14 | 17 | 16 | 18  |  |  |
| MGG, MGC                                         | 13        | 13 | 14 | 14 | 14 | _  | _  | _   |  |  |
| MLGC, RHC, REC                                   | 13        | 13 | 14 | 14 | —  | —  | —  | —   |  |  |

Note) Average value at normal temperature including hysteresis. (Tolerance  $\pm 30\%)$ 

## 2 Colour Indication Style Reed Switch/Rail Mounting **D-A79W**

#### Grommet

The suitable operating point can be indicated with a green light. (Red Green Red)



#### **Applicable Actuator Series**

| Bore size (mm)                                                         |
|------------------------------------------------------------------------|
| ø10, ø16                                                               |
| ø16                                                                    |
| ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80,<br>ø100, ø125, ø140, ø160 |
| ø20, ø25, ø32, ø40, ø50                                                |
| ø25, ø32, ø40, ø50, ø63                                                |
| ø12, ø20, ø32, ø40, ø50, ø63                                           |
| ø20, ø25, ø32, ø40, ø50, ø63                                           |
| ø32, ø40                                                               |
|                                                                        |


#### Specifications

PLC: Programmable Logic Controller

| D-A/9W (With indicator lig | D-A/9W (With indicator light)                                                                     |  |  |  |  |  |  |  |  |
|----------------------------|---------------------------------------------------------------------------------------------------|--|--|--|--|--|--|--|--|
| Auto switch model number   | D-A79W                                                                                            |  |  |  |  |  |  |  |  |
| Application                | Relay/PLC                                                                                         |  |  |  |  |  |  |  |  |
| Load voltage               | 24V DC                                                                                            |  |  |  |  |  |  |  |  |
| Load current range         | 5 to 40mA                                                                                         |  |  |  |  |  |  |  |  |
| Contact protection circuit | None                                                                                              |  |  |  |  |  |  |  |  |
| Internal voltage drop      | ≤ 4V                                                                                              |  |  |  |  |  |  |  |  |
| Indicator light            | Operating point: Red light emitting diode<br>Suitable operating point: Green light emitting diode |  |  |  |  |  |  |  |  |


• Lead wire ---- Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm<sup>2</sup>, 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on the p.6-18. Note 2) Refer to the p.6-18 for lead wire length.

#### **Internal Circuit** (): If not applicable for IEC Standard



Note) ①In the case operation load is an inductive load. 2 In the case the wiring length to load is more than 5m. Be sure to use the auto switch with the contact protection box in any case mentioned above. Refer to the p.6-19 for the details of contact protection box.

#### Dimensions



#### **Operation Range (***ℓ* **Dimension)**

| Actuator series |   | Bore size |    |    |    |    |    |    |    |    |    |    |     |     |     |     |
|-----------------|---|-----------|----|----|----|----|----|----|----|----|----|----|-----|-----|-----|-----|
| Actuator series | 6 | 10        | 12 | 15 | 16 | 20 | 25 | 32 | 40 | 50 | 63 | 80 | 100 | 125 | 140 | 160 |
| CDJ2, CDVJ      | — | 11        | —  | —  | 13 | -  | -  | -  | —  | —  | —  | —  |     | -   | —   | —   |
| CDLJ2           | — | —         | —  | —  | 13 | —  | —  | _  | —  | —  | —  | —  | —   | —   | —   | —   |
| CDQ2            | — | —         | 13 | —  | 13 | 13 | 13 | 13 | 14 | 14 | 16 | 15 | 17  | 17  | 17  | 17  |
| RSDQ            | — | —         | —  | —  | —  | 13 | 13 | 13 | 14 | 14 | —  | —  | —   | —   | —   | —   |
| MDU             | — | —         | —  | —  | —  | -  | 13 | 13 | 14 | 14 | 14 | -  | -   | -   | —   | —   |
| CE1             | — | —         | 13 | —  | —  | 13 | —  | 13 | 14 | 14 | 16 | —  | —   | —   | —   | —   |
| MK, MK2         | — | —         | —  | —  | —  | 13 | 13 | 13 | 14 | 14 | 16 | -  | —   | -   | —   | —   |
| СХТ             | — | _         | —  | —  | _  | —  | -  | 13 | 14 | _  | —  | —  | _   | —   | _   | —   |

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)



(mm)

# 2 Colour Indication Style Reed Switch/Tie-rod Mounting **D-A59W**

#### Grommet

The suitable operating point can be indicated with a green light. (Red Green Red)




#### **Applicable Actuator Series**


| Series                                     | Bore size (mm)                                                                                    |
|--------------------------------------------|---------------------------------------------------------------------------------------------------|
| CDA1, CDBA1, CDV3, CDVS,<br>CDLA, CE2, CNA | ø40, ø50, ø63, ø80, ø100                                                                          |
| CDL1                                       | ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160                                                        |
| CDS1                                       | ø125, ø140, ø160, ø180, ø200                                                                      |
| MDB, MDBB                                  | ø32, ø40, ø50, ø63, ø80, ø100                                                                     |
| Specifications                             | PLC: Programmable Logic Controller                                                                |
| D-A59W (With indicator light               | ght)                                                                                              |
| Auto switch model number                   | D-A59W                                                                                            |
| Application                                | Relay/PLC                                                                                         |
| Load voltage                               | 24V DC                                                                                            |
| Load current range                         | 5 to 40mA                                                                                         |
| Contact protection circuit                 | Built-in                                                                                          |
| Internal voltage drop                      | ≤ 4V                                                                                              |
| Indicator light                            | Operating point: Red light emitting diode<br>Suitable operating point: Green light emitting diode |

•Lead wire — Oilproof vinyl heavy insulation cable, ø4, 0.3mm<sup>2</sup>, 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.6-18. Note 2) Refer to p.6-18 for lead wire length.

#### Internal Circuit (): If not applicable for IEC Standard



#### Dimensions



#### **Operation Range (***t* **Dimension)**

| Actuator series                            | Bore size |    |    |    |    |     |     |     |     |     |     |  |
|--------------------------------------------|-----------|----|----|----|----|-----|-----|-----|-----|-----|-----|--|
| Actuator series                            | 32        | 40 | 50 | 63 | 80 | 100 | 125 | 140 | 160 | 180 | 200 |  |
| CDA1, CDBA1, CDV3, CDVS,<br>CDLA, CE2, CNA | _         | 13 | 13 | 14 | 14 | 15  | _   | -   | _   | _   | _   |  |
| CDL1                                       | —         | 13 | 13 | 14 | 14 | 15  | 17  | 17  | 17  | -   | -   |  |
| CDS1                                       | —         | —  | —  | —  | —  | _   | 17  | 17  | 17  | 17  | 17  |  |
| MDB, MDBB                                  | 13        | 13 | 13 | 14 | 14 | 15  | _   | -   | -   | -   | _   |  |

(mm)

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)

## **Solid State Switch**

General Purpose Auto Switch, 2 Colour Indication Style, 2 Colour Indication Style with Diagnostic Output, Water Resistant 2 Colour Indication Style, With Timer, Strong Magnetic Field Resistant Style

# Solid State Switch/Band Mounting **D-H7A1/D-H7A2/D-H7B**

#### Grommet



#### **Applicable Actuator Series**

| Series                                       | Bore size (mm)               |
|----------------------------------------------|------------------------------|
| CDJ2                                         | ø6, ø10, ø16                 |
| CDVJ3, CDVJ5                                 | ø10, ø16                     |
| CDLJ2                                        | ø16                          |
| CDM2, CDBM2, CDVM3, CDVM5, CDLM2, CDLG1, REC | ø20, ø25, ø32, ø40           |
| CDG1, MGG                                    | ø20, ø25, ø32, ø40, ø50, ø63 |
| RSDG                                         | ø40, ø50                     |
| MGC                                          | ø20, ø25, ø32, ø40, ø50      |
| RHC, MLGC                                    | ø20, ø25, ø32, ø40           |

#### Specifications


PLC: Programmable Logic Controller


| D-H7 (With indicator light)                                  |                                   |                                   |                       |  |  |  |  |  |  |
|--------------------------------------------------------------|-----------------------------------|-----------------------------------|-----------------------|--|--|--|--|--|--|
| Auto switch model number                                     | D-H7A1                            | D-H7A2                            | D-H7B                 |  |  |  |  |  |  |
| Wiring                                                       | 3 w                               | <i>v</i> ire                      | 2 wire                |  |  |  |  |  |  |
| Output                                                       | NPN                               | PNP                               | -                     |  |  |  |  |  |  |
| Application                                                  | IC circuit/F                      | IC circuit/Relay/PLC 24V DC Relay |                       |  |  |  |  |  |  |
| Power voltage                                                | 5/12/24V DC (4                    | -                                 |                       |  |  |  |  |  |  |
| Current consumption                                          | 10mA                              | -                                 |                       |  |  |  |  |  |  |
| Load voltage                                                 | 28V DC or less                    | —                                 | 24V DC (10 to 28V DC) |  |  |  |  |  |  |
| Load current                                                 | 40mA or less                      | 80mA or less                      | 5 to 40mA             |  |  |  |  |  |  |
| Internal voltage drop<br>(≤ 0.8V at 10mA)<br>of load current |                                   | 0.8V or less                      | 4V or less            |  |  |  |  |  |  |
| Current leakage                                              | ≤ 100 A a                         | ≤ 0.8mA at 24V DC                 |                       |  |  |  |  |  |  |
| Indicator light                                              | ON: When red light emitting diode |                                   |                       |  |  |  |  |  |  |

• Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm<sup>2</sup>, 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.6-18.


Internal Circuit

(): If not applicable for IEC Standard






Blue(Black)



Dimensions

Note 2) Refer to p.6-18 for lead wire length.



#### Operation Range ( *l* Dimension)

(mm)

| Actuator series          |   | Bore size |    |    |    |    |     |    |    |     |  |  |  |
|--------------------------|---|-----------|----|----|----|----|-----|----|----|-----|--|--|--|
| Actuator series          | 6 | 10        | 15 | 16 | 20 | 25 | 32  | 40 | 50 | 63  |  |  |  |
| CDJ2                     | 3 | 4         | —  | 4  | —  | -  | -   | —  | —  | -   |  |  |  |
| CDVJ3, CDVJ5             | — | 4         | _  | 4  | —  | -  | -   | —  | —  | —   |  |  |  |
| CDLJ2                    | - | -         | -  | 4  | —  | -  | -   | _  | —  | -   |  |  |  |
| CDM2, CDBM2, CDVM3,      |   |           |    |    | 4  | 4  | 4.5 | 5  |    |     |  |  |  |
| CDVM5, CDLM2, CDLG1, REC |   |           |    |    | 4  | 4  | 4.5 |    |    |     |  |  |  |
| CDG1, MGG                | - | _         | -  | -  | 4  | 4  | 4.5 | 5  | 6  | 6.5 |  |  |  |
| RSDG                     | - | —         | -  | -  | —  | -  | -   | 5  | 6  | -   |  |  |  |
| MGG, MGC                 | — | —         | —  | -  | 4  | 4  | 4.5 | 5  | 6  | -   |  |  |  |
| RHC, MLGC                | — | —         | —  | -  | 4  | 4  | 4.5 | 5  | —  | -   |  |  |  |

Note) Average value at normal temperature including hysteresis. (Tolerance  $\pm 30\%)$ 

## Solid State Switch/Band Mounting D-G59/D-G5P/D-K59

#### Grommet



#### **Applicable Actuator Series**

| Series                                   | Bore size (mm)                          |  |  |  |  |  |
|------------------------------------------|-----------------------------------------|--|--|--|--|--|
| CDG1, MGG                                | ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100 |  |  |  |  |  |
| CDA1, CDBA1, CDV3, CDVS, CDLA, CDL1, CNA | ø40, ø50, ø63, ø80, ø100                |  |  |  |  |  |
| MGC                                      | ø20, ø25, ø32, ø40, ø50                 |  |  |  |  |  |
| RHC, MLGC, REC                           | ø20, ø25, ø32, ø40                      |  |  |  |  |  |
| CE2                                      | ø40, ø50, ø63, ø80, ø100                |  |  |  |  |  |

#### Specifications


PLC: Programmable Logic Controller

| D-G5□/D-K59 (With indicator light) |                                                           |                   |                       |  |  |  |  |
|------------------------------------|-----------------------------------------------------------|-------------------|-----------------------|--|--|--|--|
| Auto switch model number           | D-G59                                                     | D-G5P             | D-K59                 |  |  |  |  |
| Wiring                             | 3 w                                                       | 2 wire            |                       |  |  |  |  |
| Output                             | NPN                                                       | NPN PNP           |                       |  |  |  |  |
| Application                        | IC circuit/F                                              | Relay/PLC         | 24V DC Relay/PLC      |  |  |  |  |
| Power voltage                      | 5/12/24V DC (4                                            | —                 |                       |  |  |  |  |
| Current consumption                | 10mA                                                      | —                 |                       |  |  |  |  |
| Load voltage                       | 28V DC or less                                            | —                 | 24V DC (10 to 28V DC) |  |  |  |  |
| Load current                       | 40mA or less                                              | 80mA or less      | 5 to 40mA             |  |  |  |  |
| Internal voltage drop              | 1.5V or less<br>(0.8V or less at 10mA)<br>of load current | 0.8V or less      | 4V or less            |  |  |  |  |
| Current leakage                    | ≤ 100 A a                                                 | ≤ 0.8mA at 24V DC |                       |  |  |  |  |
| Indicator light                    | ON: When red light emitting diode                         |                   |                       |  |  |  |  |


•Lead wire — Oilproof vinyl heavy insulation cable, ø4, 0.3mm<sup>2</sup>, 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.6-18. Note 2) Refer to p.6-18 for lead wire length.

#### **Internal Circuit**

(): If not applicable for IEC Standard



#### **Dimensions**



#### **Operation Range (** *l* **Dimension)**

| Actuator series                             |   | Bore size |     |    |    |     |     |     |  |
|---------------------------------------------|---|-----------|-----|----|----|-----|-----|-----|--|
|                                             |   | 25        | 32  | 40 | 50 | 63  | 80  | 100 |  |
| CDG1, MGG                                   | 4 | 4         | 4.5 | 5  | 6  | 6.5 | 6.5 | 7   |  |
| CDA1, CDBA1, CDV3, CDVS, CDLA,<br>CDL1, CNA | - | _         | -   | 5  | 6  | 6.5 | 6.5 | 7   |  |
| MGC                                         | 4 | 4         | 4.5 | 5  | 6  | -   | —   | -   |  |
| RHC, MLGC, REC                              | 4 | 4         | 4.5 | 5  | -  | -   | _   | -   |  |
| CE2                                         | - | -         | -   | 5  | 6  | 6.5 | 6.5 | 7   |  |

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)



(mm)

## Solid State Switch/Band Mounting D-H7C

#### Connector



#### **∧** Caution

#### **Precautions**

①Confirm that the connector is appropriately tightened. If tightened insufficiently, the water resistant performance will deteriorate. 2 Refer to p.6-88 for the details.

#### **Applicable Actuator Series**

| Series                                       | Bore size (mm)               |
|----------------------------------------------|------------------------------|
| CDJ2                                         | ø6, ø10, ø16                 |
| CDVJ3, CDVJ5                                 | ø10, ø16                     |
| CDLJ2                                        | ø16                          |
| CDM2, CDBM2, CDVM3, CDVM5, CDLM2, CDLG1, REC | ø20, ø25, ø32, ø40           |
| CDG1, MGG                                    | ø20, ø25, ø32, ø40, ø50, ø63 |
| RSDG                                         | ø40, ø50                     |
| MGC                                          | ø20, ø25, ø32, ø40, ø50      |
| RHC, MLGC                                    | ø20, ø25, ø32, ø40           |

#### **Specifications**


PLC: Programmable Logic Controller

(mm)

| D-H7C (With indicator    | 0-H7C (With indicator light)      |  |  |  |  |  |  |
|--------------------------|-----------------------------------|--|--|--|--|--|--|
| Auto switch model number | D-H7C                             |  |  |  |  |  |  |
| Wiring                   | 2 wire                            |  |  |  |  |  |  |
| Output                   | _                                 |  |  |  |  |  |  |
| Application              | 24V DC Relay/PLC                  |  |  |  |  |  |  |
| Power voltage            | _                                 |  |  |  |  |  |  |
| Current consumption      | _                                 |  |  |  |  |  |  |
| Load voltage             | 24V DC (10 to 28V DC)             |  |  |  |  |  |  |
| Load current             | 5 to 40mA                         |  |  |  |  |  |  |
| Internal voltage drop    | ≤ 4V                              |  |  |  |  |  |  |
| Current leakage          | ≤ 0.8mA at 24V DC                 |  |  |  |  |  |  |
| Indicator light          | ON: When red light emitting diode |  |  |  |  |  |  |


#### **Internal Circuit** (): If not applicable for IEC Standard

D-H7C



#### •Lead wire — Oilproof vinyl heavy insulation cab Note 1) Refer to common specifications on p.6-18. Note 2) Refer to p.6-18 for lead wire length. -Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm<sup>2</sup>, 2 cores (Brown, Blue), 0.5m

#### Dimensions



#### **Operation Range (***ℓ* **Dimension)**

| Actuator series         | Bore size |    |    |    |    |     |    |    |     |      |
|-------------------------|-----------|----|----|----|----|-----|----|----|-----|------|
| Actuator series         | 6         | 10 | 15 | 16 | 20 | 25  | 32 | 40 | 50  | 63   |
| CJ2                     | 5         | 8  | —  | 9  | _  | —   | —  | —  | —   | —    |
| CDVJ3, CDVJ5            | —         | 8  | —  | 9  | —  | —   | —  | —  | —   | —    |
| CDLJ2                   | _         | _  | —  | 9  | —  | —   | —  | —  | —   | -    |
| CDM2, CDBM2, CDVM3,     |           |    |    |    | 7  | 0.5 | 0  | 10 |     |      |
| CDVM5, CDM2, CDLG1, REC | _         | _  |    |    | 7  | 8.5 | 9  | 10 |     | _    |
| CDG1, MGG               | -         | _  | —  | —  | 7  | 8.5 | 9  | 10 | 9.5 | 10.5 |
| RSDQ                    | _         | _  | —  | —  | _  | —   | _  | 10 | 9.5 | -    |
| MGC                     | -         | _  | —  | —  | 7  | 8.5 | 9  | 10 | 9.5 | —    |
| RHC, MLGC               | -         | —  | —  | —  | 7  | 8.5 | 9  | 10 | —   | -    |

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)



## Solid State Switch/Band Mounting D-G39/D-K39

#### **Terminal conduit**



#### **Applicable Actuator Series**

| Series                              | Bore size (mm)                             |
|-------------------------------------|--------------------------------------------|
| CDA1, CDBA1, CDV3, CDVS1, CDLA, CNA | ø40, ø50, ø63, ø80, ø100                   |
| CDL1                                | ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160 |
| CDS1                                | ø125, ø140, ø160, ø180, ø200               |
| CE2                                 | ø40, ø50, ø63, ø80, ø100                   |
| RHC                                 | ø20, ø25, ø32, ø40                         |

#### **Specifications**

| Specifications           | PLC: Programmable Logic Controlle                    |                         |  |  |  |
|--------------------------|------------------------------------------------------|-------------------------|--|--|--|
| D-G39/D-K39 (Wit         | h indicator light)                                   |                         |  |  |  |
| Auto switch model number | D-G39                                                | D-K39                   |  |  |  |
| Wiring                   | 3 wire                                               | 2 wire                  |  |  |  |
| Output                   | NPN                                                  | —                       |  |  |  |
| Application              | IC circuit/Relay/PLC                                 | 24V DC Relay/PLC        |  |  |  |
| Power voltage            | 5/12/24V DC (4.5 to 28V DC)                          | —                       |  |  |  |
| Current consumption      | ≤ 10mA                                               | —                       |  |  |  |
| Load voltage             | ≤ 28V DC                                             | 24V DC (10 to 28V DC)   |  |  |  |
| Load current             | ≤ 40mA                                               | 5 to 40mA               |  |  |  |
| Internal voltage drop    | ≤ 1.5V<br>(0.8V or less at 10mA)<br>(of load current | ≤ 4V                    |  |  |  |
| Current leakage          | 100 A or less at 24V DC                              | 0.8mA or less at 24V DC |  |  |  |
| Indicator light          | ON: When red light emitting diode                    |                         |  |  |  |

#### **∧** Caution


#### **Precautions**

①Use cable whose O. D. is within the size in the figure to maintain water resistant performance.

②After wiring, confirm that tightening gland and all screws are tightened.

#### Note) Refer to common specifications on p.6-18

#### Dimensions




#### Operation Range ( *l* Dimension)

| Actuator series                        | Bore size |    |    |    |    |    |    |     |     |     |     |     |     |
|----------------------------------------|-----------|----|----|----|----|----|----|-----|-----|-----|-----|-----|-----|
| Actuator series                        | 20        | 25 | 32 | 40 | 50 | 63 | 80 | 100 | 125 | 140 | 160 | 180 | 200 |
| CDA1, CDBA1, CDV3,<br>CDVS1, CDLA, CNA | _         | _  |    | 9  | 9  | 10 | 10 | 11  | _   | _   | _   | _   | _   |
| CDL1                                   | -         | —  | —  | 9  | 9  | 10 | 10 | 11  | 11  | 11  | 10  | —   | _   |
| CDS1                                   | _         | _  | -  | _  | _  | _  | _  | -   | 11  | 11  | 10  | 10  | 10  |
| CE2                                    | —         | —  |    | 9  | 9  | 10 | 10 | 11  | —   | —   | —   | —   | —   |
| RHC                                    | 8         | 9  | 9  | 9  | _  | _  | -  | -   | _   | _   | -   | _   | _   |

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)

#### **Internal Circuit**



(mm)

## Solid State Switch/Band Mounting D-G39A/D-K39A

#### **Terminal conduit**




#### **∧** Caution

#### **Precautions**

1Use cable whose  $% \fbox{1}$  O. D. is within the size in the figure to maintain water resistant performance.

2 After wiring, confirm that tightening gland and all screws are tightened.

#### **Internal Circuit D-G39A** ĸ ODC(+) 1st terminal main OUT Switch 2nd terminal sircuit DC(-) 3rd terminal D-K39A



#### **Applicable Actuator Series**


| Series             | Bore size (mm)     |
|--------------------|--------------------|
| CDM2, CDBM2, CDLM2 | ø20, ø25, ø32, ø40 |

### Specifications

| Specifications           | <b>NS</b> PLC: Programmable Logic Controller              |                         |  |  |  |
|--------------------------|-----------------------------------------------------------|-------------------------|--|--|--|
| D-G39A/D-K39A            |                                                           |                         |  |  |  |
| Auto switch model number | D-G39A                                                    | D-K39A                  |  |  |  |
| Wiring                   | 3 wire                                                    | 2 wire                  |  |  |  |
| Output                   | NPN                                                       | —                       |  |  |  |
| Application              | IC circuit/Relay/PLC                                      | 24V DC Relay/PLC        |  |  |  |
| Power voltage            | 5/12/24V DC (4.5 to 28V DC)                               | —                       |  |  |  |
| Current consumption      | ≤ 10mA                                                    | —                       |  |  |  |
| Load voltage             | ≤ 28V DC                                                  | 24V DC (10 to 28V DC)   |  |  |  |
| Load current             | ≤ 40mA                                                    | 5 to 40mA               |  |  |  |
| Internal voltage drop    | 1.5V or less<br>(0.8V or less at 10mA)<br>of load current | 4V or less              |  |  |  |
| Current leakage          | 100 A or less at 24V DC                                   | 0.8mA or less at 24V DC |  |  |  |
| Indicator light          | ON: When red light emitting diode                         |                         |  |  |  |

Note) Refer to common specifications on p.6-18.

#### Dimensions



#### **Operation Range (***l* **Dimension)**

| Actuator series                                                          |   | Bore size |    |    |  |  |  |
|--------------------------------------------------------------------------|---|-----------|----|----|--|--|--|
|                                                                          |   | 25        | 32 | 40 |  |  |  |
| CDM2, CDBM2, CDLM2                                                       | 8 | 9         | 9  | 9  |  |  |  |
| late) A second second terms at the inclusion bustometic (Telescond 200%) |   |           |    |    |  |  |  |

(mm)

Note) Average value at normal temperature including hysteresis. (Tolerance  $\pm 30\%$ )

**SMC** 

## Solid State Switch/Rail Mounting D-F79/D-F7P/D-J79

#### Grommet



**Internal Circuit** 

nain

Switch 1

Switch main

circuit

circuit

**D-F79** 

D-F7P

(): If not applicable for IEC Standard

oDC(+) Brown(Red)

Black(White)

Blue(Black)

OUT

o DC(−)

DC(+) Brown(Red)

OUT

Black(White)

#### **Applicable Actuator Series**

| Series             | Bore size (mm)                                                                    |
|--------------------|-----------------------------------------------------------------------------------|
| CDJ2, CDVJ3, CDVJ5 | ø10, ø16                                                                          |
| CDQ2               | ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160               |
| CD□XW              | Plate mounted(P), ø10, ø16, ø20, ø25, ø32, Housing mounted(B), ø16, ø20, ø25, ø32 |
| CDY1S, CY1L        | ø6, ø10, ø15, ø20, ø25, ø32, ø40                                                  |
| RSDQ               | ø20, ø25, ø32, ø40, ø50                                                           |
| MDU                | ø25, ø32, ø40, ø50, ø63                                                           |
| CE1                | ø12, ø20, ø32, ø40, ø50, ø63                                                      |
| MK, MK2            | ø20, ø25, ø32, ø40, ø50, ø63                                                      |
| СХТ                | ø32, ø40                                                                          |

#### Specifications


PLC: Programmable Logic Controller


| D-F7□/D-J79 (With indicator light) |                                                           |                   |                       |  |  |  |  |  |  |  |  |
|------------------------------------|-----------------------------------------------------------|-------------------|-----------------------|--|--|--|--|--|--|--|--|
| Auto switch model number           | D-F79                                                     | D-F79 D-F7P       |                       |  |  |  |  |  |  |  |  |
| Wiring                             | 3 w                                                       | vire              | 2 wire                |  |  |  |  |  |  |  |  |
| Output                             | NPN                                                       | _                 |                       |  |  |  |  |  |  |  |  |
| Application                        | IC circuit/F                                              | 24V DC Relay/PLC  |                       |  |  |  |  |  |  |  |  |
| Power voltage                      | 5/12/24V DC (4                                            | —                 |                       |  |  |  |  |  |  |  |  |
| Current consumption                | ≤ 10                                                      |                   |                       |  |  |  |  |  |  |  |  |
| Load voltage                       | ≤ 28V DC                                                  |                   | 24V DC (10 to 28V DC) |  |  |  |  |  |  |  |  |
| Load current                       | ≤ 40mA                                                    | 80mA or less      | 5 to 40mA             |  |  |  |  |  |  |  |  |
| Internal voltage drop              | 1.5V or less<br>(0.8V or less at 10mA)<br>of load current | 0.8V or less      | 4V or less            |  |  |  |  |  |  |  |  |
| Current leakage                    | ≤ 100 A a                                                 | ≤ 0.8mA at 24V DC |                       |  |  |  |  |  |  |  |  |
| Indicator light                    | ON: When red light emitting diade                         |                   |                       |  |  |  |  |  |  |  |  |

Indicator light ON: When red light emitting diode


•Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm<sup>2</sup>, 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.6-18. Note 2) Refer to p.6-18 for lead wire length.

#### **Dimensions**





(mm)



Operation Range ( *ℓ* Dimension)

| Actuator series                                                                  |      |   |    |     |    |     |     |     | Bore | size |     |     |     |     |     |     |     |
|----------------------------------------------------------------------------------|------|---|----|-----|----|-----|-----|-----|------|------|-----|-----|-----|-----|-----|-----|-----|
| Actuator se                                                                      | lies | 6 | 10 | 12  | 15 | 16  | 20  | 25  | 32   | 40   | 50  | 63  | 80  | 100 | 125 | 140 | 160 |
| CDJ2, CDVJ3, C                                                                   | DVJ5 | — | 5  | —   | —  | 5   | —   | —   | —    | —    | —   | —   | —   | —   | —   | —   | —   |
| CDQ2                                                                             |      | _ | _  | 5.5 | —  | 6   | 5.5 | 5   | 6    | 6    | 6   | 6.5 | 6.5 | 7   | 9   | 9   | 8.5 |
| CDDXW B                                                                          | В    |   | -  | _   | _  | 4   |     | 3.5 | 4    |      |     |     |     |     |     |     |     |
|                                                                                  | Ρ    |   | 3  |     | _  | 2.5 | 3.5 | 3.5 | 2.5  |      | _   |     |     |     | _   |     |     |
| CDY1S, CY                                                                        | 1L   | 3 | 3  | —   | 4  | —   | 3   | 3   | 3    | 3.5  | —   | —   | _   | -   | —   | —   | —   |
| RSDQ                                                                             |      | _ | —  | —   | —  | —   | 5.5 | —   | 6    | 6    | 6   | —   |     | -   | —   | —   | —   |
| MDU                                                                              |      | — | -  | —   | _  | —   | -   | 6.5 | 7    | 6.5  | 6.5 | 6.5 | _   | -   | —   | —   | —   |
| CE1                                                                              |      | _ | -  | 5.5 | —  | —   | 5.5 | —   | 6    | 6    | 6   | 6.5 |     | -   | —   | —   | —   |
| MK, MK2                                                                          |      | _ | _  | _   | _  | _   | 5.5 | 5   | 6    | 6    | 6   | 6.5 | _   | -   | _   | —   | _   |
| СХТ                                                                              |      | — | —  | —   | —  | —   | _   | —   | 6    | 6    | —   | —   | —   | —   | —   | —   | -   |
| Note) Average value at normal temperature including hystoresis. (Telerance +20%) |      |   |    |     |    |     |     |     |      |      |     |     |     |     |     |     |     |

Note) Average value at normal temperature including hysteresis. (Tolerance  $\pm 30\%$ )



# Solid State Switch/Rail Mounting D-F7NV/D-F7PV/D-F7BV

#### Grommet Electrical entry: Perpendicular



#### **Applicable Actuator Series**

| Series             | Bore size (mm)                                                                    |
|--------------------|-----------------------------------------------------------------------------------|
| CDJ2, CDVJ3, CDVJ5 | ø10, ø16                                                                          |
| CDQ2               | ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160               |
| CD□XW              | Plate mounted(P), ø10, ø16, ø20, ø25, ø32, Housing mounted(B), ø16, ø20, ø25, ø32 |
| CDY1S, CY1L        | ø6, ø10, ø15, ø20, ø25, ø32, ø40                                                  |
| RSDQ               | ø20, ø32, ø40, ø50                                                                |
| MDU                | ø25, ø32, ø40, ø50, ø63                                                           |
| CE1                | ø12, ø20, ø32, ø40, ø50, ø63                                                      |
| MK, MK2            | ø20, ø25, ø32, ø40, ø50, ø63                                                      |
| СХТ                | ø32, ø40                                                                          |

#### Specifications


PLC: Programmable Logic Controller

| D-F7⊡V (With indicator light) |                                                           |                      |                       |  |  |  |  |  |  |  |  |  |
|-------------------------------|-----------------------------------------------------------|----------------------|-----------------------|--|--|--|--|--|--|--|--|--|
| Auto switch model number      | D-F7NV                                                    | D-F7BV               |                       |  |  |  |  |  |  |  |  |  |
| Wiring                        | 3 w                                                       | 2 wire               |                       |  |  |  |  |  |  |  |  |  |
| Output                        | NPN                                                       | _                    |                       |  |  |  |  |  |  |  |  |  |
| Application                   | IC circuit/F                                              | IC circuit/Relay/PLC |                       |  |  |  |  |  |  |  |  |  |
| Power voltage                 | 5/12/24V DC (4                                            |                      |                       |  |  |  |  |  |  |  |  |  |
| Current consumption           | ≤ 10                                                      | —                    |                       |  |  |  |  |  |  |  |  |  |
| Load voltage                  | ≤ 28V DC                                                  | —                    | 24V DC (10 to 28V DC) |  |  |  |  |  |  |  |  |  |
| Load current                  | ≤ 40mA                                                    | ≤ 80mA               | 5 to 40mA             |  |  |  |  |  |  |  |  |  |
| Internal voltage drop         | 1.5V or less<br>(0.8V or less at 10mA)<br>of load current | 0.8V or less         | 4V or less            |  |  |  |  |  |  |  |  |  |
| Current leakage               | ≤ 100 A a                                                 | ≤ 0.8mA at 24V DC    |                       |  |  |  |  |  |  |  |  |  |
| Indicator light               | ON: When red light emitting diode                         |                      |                       |  |  |  |  |  |  |  |  |  |

Indicator light ON: When red light emitting diod

•Lead wire —Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm<sup>2</sup>, 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.6-18. Note 2) Refer to p.6-18 for lead wire length.

#### Dimensions




| Actuator series                                                                  |   |    |     |    |     |     |     | Bore | size |     |     |     |     |     |     |     |
|----------------------------------------------------------------------------------|---|----|-----|----|-----|-----|-----|------|------|-----|-----|-----|-----|-----|-----|-----|
| Actuator series                                                                  | 6 | 10 | 12  | 15 | 16  | 20  | 25  | 32   | 40   | 50  | 63  | 80  | 100 | 125 | 140 | 160 |
| CDJ2, CDVJ3, CDVJ5                                                               | - | 5  | -   | —  | 5   | —   | —   | —    | -    | —   | -   | —   | —   | —   | —   | —   |
| CDQ2                                                                             | - | —  | 5.5 | —  | 6   | 5.5 | 5   | 6    | 6    | 6   | 6.5 | 6.5 | 7   | 9   | 9   | 8.5 |
| CDDXW B                                                                          |   | —  |     |    | 4   | 0.5 | 3.5 | 4    |      | -   | -   | -   | _   | _   | _   | _   |
|                                                                                  |   | 3  |     |    | 2.5 | 3.5 | 3.5 | 2.5  |      |     |     |     |     |     |     |     |
| CDY1S, CY1L                                                                      | 3 | 3  | -   | 4  | _   | 3   | 3   | 3    | 3.5  | _   | -   | _   | -   | _   | —   | —   |
| RSDQ                                                                             | - | —  | -   | —  | -   | 5.5 | —   | 6    | 6    | 6   | -   | —   | -   | -   | —   | —   |
| MDU                                                                              | - | _  | _   | _  | _   | —   | 6.5 | 7    | 6.5  | 6.5 | 6.5 | _   | _   | _   | _   | —   |
| CE1                                                                              | - | —  | 5.5 | —  | -   | 5.5 | —   | 6    | 6    | 6   | 6.5 | —   | —   | -   | —   | —   |
| MK, MK2                                                                          | - | —  | _   | —  | _   | 5.5 | 5   | 6    | 6    | 6   | 6.5 | _   | —   | _   | —   | —   |
| СХТ                                                                              | - | —  | —   | —  | —   | —   | —   | 6    | 6    | —   | —   | —   | —   | —   | —   | —   |
| Note) Average value at normal temperature including hystopolic (Talayana - 200/) |   |    |     |    |     |     |     |      |      |     |     |     |     |     |     |     |


Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)

#### Internal Circuit

#### (): If not applicable for IEC Standard


D-F7NV







# Solid State Switch/Rail Mounting **D-J79C**




# **∧** Caution

#### **Precautions**

①Confirm that the connector is appropriately tightened. If tightened insufficiently, the waterproof performance will deteriorate. 2 Refer to p.6-88 for the details.

# **Internal Circuit**

#### (): If not applicable for IEC Standard



#### **Applicable Actuator Series**

| Bore size (mm)                                                          |
|-------------------------------------------------------------------------|
| ø10, ø16                                                                |
| ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160     |
| Plate mounted ø10, ø16, ø20, ø25, ø32 Housing munted ø16, ø20, ø25, ø32 |
| ø6, ø10, ø15, ø20, ø25, ø32, ø40                                        |
| ø20, ø32, ø40, ø50                                                      |
| ø25, ø32, ø40, ø50, ø63                                                 |
| ø12, ø20, ø32, ø40, ø50, ø63                                            |
| ø20, ø25, ø32, ø40, ø50, ø63                                            |
| ø32, ø40                                                                |
|                                                                         |


# **Specifications**

| D-J79C                   |                                   |  |  |  |  |  |  |
|--------------------------|-----------------------------------|--|--|--|--|--|--|
| Auto switch model number | D-J79C                            |  |  |  |  |  |  |
| Wiring                   | 2 wire                            |  |  |  |  |  |  |
| Output                   | —                                 |  |  |  |  |  |  |
| Application              | 24V DC Relay/PLC                  |  |  |  |  |  |  |
| Power voltage            |                                   |  |  |  |  |  |  |
| Current consumption      | —                                 |  |  |  |  |  |  |
| Load voltage             | 24V DC (10 to 28V DC)             |  |  |  |  |  |  |
| Load current             | 5 to 40mA                         |  |  |  |  |  |  |
| Internal voltage drop    | ≤ 4V                              |  |  |  |  |  |  |
| Current leakage          | ≤ 0.8mA at 24V DC                 |  |  |  |  |  |  |
| Indicator light          | ON: When red light emitting diode |  |  |  |  |  |  |
|                          |                                   |  |  |  |  |  |  |

PLC: Programmable Logic Controller

Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm<sup>2</sup>, 2 cores (Brown, Blue), 0.5m
 Note 1) Refer to common specifications on p.6-18.
 Note 2) Refer to p.6-18 for lead wire length.

# Dimensions



#### Indicator light **Operation Range (** *t* **Dimension)**

| Actuator se    | rioc |   | Bore size |     |    |     |     |     |     |     |     |     |     |     |     |     |     |
|----------------|------|---|-----------|-----|----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| Actuator se    | lies | 6 | 10        | 12  | 15 | 16  | 20  | 25  | 32  | 40  | 50  | 63  | 80  | 100 | 125 | 140 | 160 |
| CDJ2, CDVJ3, C | DVJ5 | — | 5         | Ι   | -  | 5   |     | —   |     | —   | —   | —   |     | -   |     | —   | —   |
| CDQ2           |      | — | —         | 5.5 | —  | 6   | 5.5 | 5   | 6   | 6   | 6   | 6.5 | 6.5 | 7   | 9   | 9   | 8.5 |
| CD             | В    |   | —         |     |    | 4   | 0 F | 3.5 | 4   |     |     |     |     |     |     |     |     |
|                | Ρ    |   | 3         |     |    | 2.5 | 3.5 | 3.5 | 2.5 |     | _   |     |     |     |     |     |     |
| CDY1S, CY1     | L    | 3 | 3         | Ι   | 4  | —   | 3   | 3   | 3   | 3.5 | —   | —   |     | —   |     | —   | —   |
| RSDQ           |      | — | —         | —   | _  | —   | 5.5 | —   | 6   | 6   | 6   | —   | _   | —   | _   | —   | —   |
| MDU            |      | — | _         |     |    | —   |     | 6.5 | 7   | 6.5 | 6.5 | 6.5 |     | —   |     | —   | —   |
| CE1            |      | — | —         | 5.5 | _  | —   | 5.5 | —   | 6   | 6   | 6   | 6.5 | _   | —   | _   | —   | —   |
| MK, MK2        |      | — | -         | -   |    | —   | 5.5 | 5   | 6   | 6   | 6   | 6.5 |     | -   |     | —   | —   |
| СХТ            |      | _ | _         | _   | —  | -   | _   | —   | 6   | 6   | _   | -   | _   | -   | _   | —   | _   |

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)




(mm)

# Solid State Switch/Tie-rod Mounting **D-F5**□/**D**-J5□


# Grommet




# **Internal Circuit** (): If not applicable for IEC Standard



#### D-J59





#### **Applicable Actuator Series**

| Series                                 | Bore size (mm)                             |
|----------------------------------------|--------------------------------------------|
| CDA1, CDBA1, CDV3, CDVS1,<br>CDLA, CNA | ø40, ø50, ø63, ø80, ø100                   |
| CDL1                                   | ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160 |
| CDS1                                   | ø125, ø140, ø160, ø180, ø200               |
| CE2                                    | ø40, ø50, ø63, ø80, ø100                   |
| MDB                                    | ø32, ø40, ø63, ø80, ø100                   |

#### **Specifications**


PLC: Programmable Logic Controller


| D-F5□/D-J5□              |                                                           |                         |                       |                    |  |  |
|--------------------------|-----------------------------------------------------------|-------------------------|-----------------------|--------------------|--|--|
| Auto switch model number | D-F59                                                     | D-F5P                   | D-J59                 | D-J51              |  |  |
| Wiring                   | 3 w                                                       | vire                    | 2 w                   | /ire               |  |  |
| Output                   | NPN                                                       | PNP                     |                       |                    |  |  |
| Application              | IC circuit/F                                              | Relay/PLC               | 24V DC Relay/PLC      | AC Relay/PLC       |  |  |
| Power voltage            | 5/12/24V DC (4                                            | 4.5 to 28V DC)          |                       | _                  |  |  |
| Current consumption      | ≤ 1(                                                      | )mA                     |                       |                    |  |  |
| Load voltage             | ≤ 28V DC                                                  |                         | 24V DC (10 to 28V DC) | 80 to 260V AC      |  |  |
| Load current             | ≤ 40mA                                                    | ≤ 40mA ≤ 80mA 5 to 40mA |                       | 5 to 80mA          |  |  |
| Internal voltage drop    | 1.5V or less<br>(0.8V or less at 10mA)<br>of load current | 0.8V or less            | 4V or less            | 14V or less        |  |  |
| Current leakage          | ≤ 100 A a                                                 |                         | ≤ 0.8mA at 24V DC     | ≤ 1mA at 100 V DC  |  |  |
|                          | ≤ 100 A a                                                 | ai 24V DC               | ≤ 0.011A at 24V DC    | ≤ 1.5mA at 200V DC |  |  |
| Indicator light          | ON: When red light emitting diode                         |                         |                       |                    |  |  |

•Lead wire — Oilproof vinyl heavy insulation cable, ø4, 0.3mm<sup>2</sup>, 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on the p.6-18. Note 2) Refer to the p.6-18 for lead wire length.

#### Dimensions

\*D-J51 differs in the shape, most sensitive position and operation range from other switches. Contact SMC for the details.





# **Operation Range (** *t* **Dimension)**

| (m | m) |
|----|----|
| _  |    |

| Actuator series                        |     | Bore size |    |     |     |     |     |     |     |     |     |
|----------------------------------------|-----|-----------|----|-----|-----|-----|-----|-----|-----|-----|-----|
| Actuator series                        | 32  | 40        | 50 | 63  | 80  | 100 | 125 | 140 | 160 | 180 | 200 |
| CDA1, CDBA1, CDV3, CDVS1,<br>CDLA, CNA | -   | 4         | 4  | 4.5 | 4.5 | 4.5 | _   | _   | —   | —   | _   |
| CDL1                                   | -   | 4         | 4  | 4.5 | 4.5 | 4.5 | 5   | 5   | 5.5 | —   | —   |
| CDS1                                   | -   | —         | —  | —   | —   | —   | 5   | 5   | 5.5 | 6   | 6   |
| CE2                                    | -   | 4         | 4  | 4.5 | 4.5 | 4.5 | —   | —   | —   | —   | —   |
| MDB                                    | 3.5 | 4         | 4  | 4.5 | 4.5 | 4.5 | _   | _   | _   | _   |     |

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)



# Solid State Switch/Tie-rod Mounting **D-G39C/D-K39C**

# **Terminal conduit**



# **▲** Caution

#### **Precautions**

①Use cable whose O. D. is within the size in the figure to maintain water resistant performance.


②After wiring, confirm that tightening gland and all screws are tightened.

## **Applicable Actuator Series**

| Se                                       | Bore size (mm)                                  |                          |  |  |  |
|------------------------------------------|-------------------------------------------------|--------------------------|--|--|--|
| CDA1, CDBA1, CDV3, C                     | ø40, ø50, ø63, ø80, ø100                        |                          |  |  |  |
| C                                        | E2                                              | ø40, ø50, ø63, ø80, ø100 |  |  |  |
| Specifications PLC: Programmable Logic C |                                                 |                          |  |  |  |
| D-G39C/D-K39C                            |                                                 |                          |  |  |  |
| Auto switch model number                 | D-G39C                                          | D-K39C                   |  |  |  |
| Wiring                                   | 3 wire                                          | 2 wire                   |  |  |  |
| Output                                   | NPN                                             |                          |  |  |  |
| Application                              | IC circuit/Relay/PLC                            | 24V DC Relay/PLC         |  |  |  |
| Power voltage                            | 5/12/24V DC (4.5 to 28V DC)                     |                          |  |  |  |
| Current consumption                      | ≤ 10mA                                          |                          |  |  |  |
| Load voltage                             | ≤ 28V DC                                        | 24V DC (10 to 28V DC)    |  |  |  |
| Load current                             | ≤ 40mA                                          | 5 to 40mA                |  |  |  |
| Internal voltage drop                    | ≤ 1.5V (≤ 0.8V at 10mA of load current)         | ≤ 4V                     |  |  |  |
| Current leakage                          | 100 A or less at 24V DC                         | 0.8mA or less at 24V DC  |  |  |  |
| Indicator light                          | licator light ON: When red light emitting diode |                          |  |  |  |
| Note 1) Refer to common specifica        | ations on p.6-18.                               |                          |  |  |  |

Note 1) Refer to common specifications on p.6-18.

#### Dimensions



## **Operation Range (***t* **Dimension)**

| Actuator series                             | Bore size |    |    |    |     |  |  |  |
|---------------------------------------------|-----------|----|----|----|-----|--|--|--|
| Actuator series                             | 40        | 50 | 63 | 80 | 100 |  |  |  |
| CDA1, CDBA1, CDV3,<br>CDVS, CDLA, CDL1, CNA | 9         | 10 | 11 | 11 | 11  |  |  |  |
| CE2                                         | 9         | 10 | 11 | 11 | 11  |  |  |  |


Note) Average value at normal temperature including hysteresis. (Tolerance  $\pm 30\%$ )

#### **Dimensions**

| Auto switch part number | Bore size<br>(mm) | С  | нพ  | н    | H'   | Т    | T'  | z       |  |
|-------------------------|-------------------|----|-----|------|------|------|-----|---------|--|
| D-G39C-4, D-K39C-4      | 40                | 44 | 69  | 57   | 49.5 | 7.5  | 6.5 |         |  |
| D-G39C-5, D-K39C-5      | 50                | 52 | 77  | 58   | 50.5 | 8.5  | 6.5 | M5 X 16 |  |
| D-G39C-6, D-K39C-6      | 63                | 64 | 91  | 60.5 | 52   | 10.5 | 7.5 | M5 X 20 |  |
| D-G39C-8, D-K39C-8      | 80                | 78 | 107 | 64   | 53.5 | 12.5 | 9.5 |         |  |
| D-G39C-10, D-K39C-10    | 100               | 92 | 121 | 67   | 56.5 | 15.5 | 9.5 | M5 X 25 |  |

(mm)


# **Internal Circuit**



# Solid State Switches: Direct Mounting Type D-M9N(V), D-M9P(V), D-M9B(V)

# Grommet

- 2-wire load current is reduced (2.5 to 40 mA).
   Lead-free
- Use of lead wire compliant with UL standards (style 2844)
- 1.5 times the flexibility compared with conventional products (comparison with other SMC products)




# ▲Caution Operating Precautions

When the cable sheath is stripped, confirm the stripping direction.

The insulator may be split or damaged depending on the direction.



# Auto Switch Internal Circuit



# **Auto Switch Specifications**

Refer to www.smcworld.com for details of products compatible with overseas standards.

PLC: Programable Logia Controllor

Unit: g

|                                           |                        | PLC: Pro          | gramable Logic Controlle |  |  |  |  |  |  |
|-------------------------------------------|------------------------|-------------------|--------------------------|--|--|--|--|--|--|
| D-M9 <sup>[]</sup> (with indicator light) |                        |                   |                          |  |  |  |  |  |  |
| Switch model                              | D-M9N                  | D-M9P             | D-M9B                    |  |  |  |  |  |  |
| Wiring type                               | З-м                    | <i>v</i> ire      | 2-wire                   |  |  |  |  |  |  |
| Output type                               | NPN                    | PNP               | _                        |  |  |  |  |  |  |
| Applicable load                           | IC circuit, F          | 24 VDC relay, PLC |                          |  |  |  |  |  |  |
| Power supply voltage                      | 5, 12, 24 VDC          | _                 |                          |  |  |  |  |  |  |
| Current consumption                       | 10 mA                  | or less           | _                        |  |  |  |  |  |  |
| Load voltage                              | 28 VDC or less         | _                 | 24 VDC (10 to 28 VDC)    |  |  |  |  |  |  |
| Load current                              | 40 mA                  | or less           | 2.5 to 40 mA             |  |  |  |  |  |  |
| Internal voltage drop                     | 0.8 V (                | or less           | 4 V or less              |  |  |  |  |  |  |
| Leakage current                           | 100 A or les           | 0.8 mA or less    |                          |  |  |  |  |  |  |
| Indicator light                           | Red LED lights when ON |                   |                          |  |  |  |  |  |  |
|                                           |                        |                   |                          |  |  |  |  |  |  |

Lead wire ····· Oil proof heavy duty vinyl cord: 2.7 × 3.2 ellipse
 D-M9B 0.15 mm<sup>2</sup> × 2 cores

D-M9D, D-M9P 0.15 mm<sup>2</sup> × 3 cores


Note 1) Refer to page 6-18 for solid state auto switch common specifications and lead wire length.


# Weight

| Auto switch model  |     | D-M9N(V) | D-M9P(V) | D-M9B(V) |
|--------------------|-----|----------|----------|----------|
| Lood wire longth m | 0.5 | 8        | 8        | 7        |
| Lead wire length m | 3   | 41       | 41       | 38       |


# Dimensions

D-M9





# D-M9⊡V




# Solid State Switches: Direct Mounting Type D-F8N/D-F8P/D-F8B ( )




▲Caution Operating precautions

Fix the switch with appropriate screw installed on the switch body. If using other screws, switch may be damaged.

# Auto switch internal circuit





# **Auto Switch Specifications**

Refer to <u>www.smcworld.com</u> for details of products compatible with overseas standards.

|                            |                                                                         | PLC: Pro                 | gramable Logic Controlle |  |
|----------------------------|-------------------------------------------------------------------------|--------------------------|--------------------------|--|
| Auto switch part No.       | D-F8N                                                                   | D-F8P                    | D-F8B                    |  |
| Electrical entry direction | Perpendicular                                                           | Perpendicular            | Perpendicular            |  |
| Wiring type                | З-м                                                                     | vire                     | 2-wire                   |  |
| Output type                | NPN                                                                     | PNP                      | _                        |  |
| Applicable load            | IC circuit, 24 V                                                        | 24 VDC relay, PLC        |                          |  |
| Power supply voltage       | 5, 12, 24 VDC (                                                         | _                        |                          |  |
| Current consumption        | 10 mA                                                                   | or less                  | _                        |  |
| Load voltage               | 28 VDC or less                                                          | _                        | 24 VDC (10 to 28 VDC)    |  |
| Load current               | 40 mA or less                                                           | 80 mA or less            | 2.5 to 40 mA             |  |
| Internal voltage<br>drop   | 1.5 V or less<br>(0.8 V or less at 10 mA<br>load current) 0.8 V or less |                          | 4 V or less              |  |
| Leakage current            | 100 A or les                                                            | 0.8 mA or less at 24 VDC |                          |  |
| Indicator light            | Red LED lights when ON                                                  |                          |                          |  |

• Lead wires

Oilproof vinyl heavy insulation cable, ø2.7

D-F8N, D-F8P 0.15 mm<sup>2</sup> x 3-cores (Brown, Black, Blue [Red, White, Black]), 0.5 m D-F8B 0.18mm<sup>2</sup> x 2-cores (Brown, Blue [Red, Black]), 0.5 m

Note 1) Refer to page 6-18 for auto switch common specifications.

Note 2) Refer to page 6-18 for lead wire lengths.


# Weight

Unit: (g)

| Auto switch part No.    |     | D-F8N | D-F8P | D-F8B |
|-------------------------|-----|-------|-------|-------|
| Lead wire length<br>(m) | 0.5 | 7     | 7     | 7     |
|                         | 3   | 32    | 32    | 32    |
|                         | 5   | 52    | 52    | 52    |

## Dimensions

# D-F8N, D-F8P, D-F8B



# Solid State Switch/Direct Mounting D-Y59<sup>A</sup>/D-Y69<sup>A</sup>/D-Y7P(V)



### **Applicable Actuator Series**

| Series           | Bore size (mm)                                    |  |  |  |  |
|------------------|---------------------------------------------------|--|--|--|--|
| MGQ, MVGQ, MGP   | ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100 |  |  |  |  |
| CXS              | ø6, ø10, ø15, ø20, ø25, ø32                       |  |  |  |  |
| MY1B             | ø25, ø32, ø40, ø50, ø63, ø80, ø100                |  |  |  |  |
| MY1C, MY1M, CY1R | ø25, ø32, ø40, ø50, ø63                           |  |  |  |  |
| MY1H, ML2B       | ø25, ø32, ø40                                     |  |  |  |  |
| MGF              | ø40, ø63, ø100                                    |  |  |  |  |
| CY1H             | ø10, ø15, ø20, ø25, ø32                           |  |  |  |  |
| RSH              | ø20, ø32, ø50, ø63, ø80                           |  |  |  |  |

# Specifications

PLC: Programmable Logic Controller


(mm)

| D-Y5/D-Y6/D-Y7P/D-Y7PV (With indicator light) |                                                                        |                             |              |               |            |               |  |
|-----------------------------------------------|------------------------------------------------------------------------|-----------------------------|--------------|---------------|------------|---------------|--|
| Auto switch model number                      | D-Y59A                                                                 | D-Y69A                      | D-Y7P        | D-Y7PV        | D-Y59B     | D-Y69B        |  |
| Electrical entry                              | In-line                                                                | Perpendicular               | In-line      | Perpendicular | In-line    | Perpendicular |  |
| Wiring                                        |                                                                        | 3 w                         | vire         |               | 2 v        | vire          |  |
| Output                                        | N                                                                      | PΝ                          | PI           | NP            | -          | _             |  |
| Application                                   |                                                                        | IC circuit/F                | Relay/PLC    |               | 24V DC F   | Relay/PLC     |  |
| Power voltage                                 | 5/                                                                     | 5/12/24V DC (4.5 to 28V DC) |              |               |            |               |  |
| Current consumption                           |                                                                        | ≤ 10                        | )mA          |               | -          | -             |  |
| Load voltage                                  | ≤ 28                                                                   | V DC                        | -            | _             | 24V DC (10 | to 28V DC)    |  |
| Load current                                  | ≤ 40                                                                   | )mA                         | 80mA         | or less       | 5 to 4     | 40mA          |  |
| Internal voltage drop                         | 1.5V or less<br>(0.8V or less at 10mA)<br>of load current 0.8V or less |                             |              |               | 4V o       | r less        |  |
| Current leakage                               |                                                                        | 100 A or les                | 0.8mA or les | ss at 24V DC  |            |               |  |
| Indicator light                               | ON: When red light emitting diode                                      |                             |              |               |            |               |  |

 Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.15mm<sup>2</sup>, 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.6-18.

Note 1) Heter to common specifications on p.6-18. Note 2) Refer to p.6-18 for lead wire length.

# Dimensions




# Operation Range ( *t* Dimension)


**SMC** 

| Actuator series                                                                  |   |    |     |     |     | Bore | size |     |     |     |     |     |      |
|----------------------------------------------------------------------------------|---|----|-----|-----|-----|------|------|-----|-----|-----|-----|-----|------|
|                                                                                  | 6 | 10 | 12  | 15  | 16  | 20   | 25   | 32  | 40  | 50  | 63  | 80  | 100  |
| MGQ, MVGQ                                                                        | — | —  | 5   | —   | 6   | 6    | 6.5  | 8.5 | 8.5 | 9   | 10  | 10  | 11.5 |
| CXS                                                                              | 3 | 3  | —   | 3.5 | -   | 3.5  | 4    | 4.5 | —   | -   | -   | —   | -    |
| MGP                                                                              | - | —  | 5.5 | —   | 7.5 | 7.5  | 7    | 6.5 | 6   | 7   | 8   | 9.5 | 10   |
| MY1B                                                                             | - | —  | —   | —   | _   | -    | 6    | 9   | 10  | 3.5 | 3.5 | 3.5 | 3.5  |
| MY1C, MY1M                                                                       |   | —  | —   | —   |     | —    | 5    | 5   | 5   | 5.5 | 5.5 | _   | —    |
| MY1H                                                                             | - | _  | —   | —   | —   | -    | 6    | 9   | 10  | -   | -   | —   | -    |
| RSH                                                                              |   | —  | —   | —   |     | 7.5  | —    | 5   | —   | 6.5 | 7.5 | 10  | —    |
| CY1R                                                                             | — | _  | —   | —   | —   | -    | 7    | 6   | 6   | 7   | 6   | —   | -    |
| CY1H                                                                             |   | 6  | —   | 5   |     | 5    | 5    | 6   | —   | —   | —   | _   | —    |
| ML2B                                                                             | — | —  | —   | —   | —   | -    | 6    | 6   | 6   | -   | —   | —   | -    |
| MGF                                                                              |   | —  | —   | —   |     | -    | —    | —   | 9   | —   | 5   | —   | 7.5  |
| Note) Average value at normal temperature including hysteresis. (Tolerance ±30%) |   |    |     |     |     |      |      |     |     |     |     |     |      |

# (): If not applicable for IEC Standard D-Y59A, D-Y69A


**Internal Circuit** 






# Solid State Switch/Direct Mounting Switch


# D-S99(V)/D-S9P(V)/D-T99(V)



# Solid State Switch/Direct Mounting Type D-S79/D-S7P/D-T79(C)


# **Grommet, Connector Electrical Entry: In-line**






# Auto switch internal circuit

(): Before IEC standard



# D-S7P1/S7P2



OUT (-)

Blue (Black)

# Applicable rotary actuator series

| Series | Size                |
|--------|---------------------|
| CDRB1  | 20, 30, 50, 80, 100 |
| CDRBU  | 20, 30              |
| MDSUB  | 7, 20               |

# Auto switch specifications

PLC: Programmable Logic Controller


| D-S79/D-T79 (With     | indicator                              | light)                  |                               |  |  |
|-----------------------|----------------------------------------|-------------------------|-------------------------------|--|--|
| Auto switch model no. | D-S791/D-S792                          | D-S7P1/D-S7P2           | D-T791/D-T792/D-T791C/D-T792C |  |  |
| Wiring type           | 3 w                                    | /ire                    | 2 wire                        |  |  |
| Output                | NPN type                               | PNP type                | —                             |  |  |
| Applicable load       | IC circuit, Relay, PLC                 |                         | 24V DC Relay, PLC             |  |  |
| Power voltage         | 5, 12, 24V DC (4.5 to 28V DC)          |                         | _                             |  |  |
| Current consumption   | 10mA or less                           |                         | _                             |  |  |
| Load voltage          | 28V DC or less                         | —                       | 24V DC (10 to 28V DC)         |  |  |
| Load current          | 40mA ro less                           | 80mA or less            | 5 to 40mA                     |  |  |
| Internal voltage drop | 1.5V or less<br>(0.8V or less at 10mA) | 0.8V or less            | 4V or less                    |  |  |
| Leakage current       | 100 A or les                           | 0.8mA or less at 24V DC |                               |  |  |
| Indicator light       | ON: Red light emitting diode           |                         |                               |  |  |

2 wire (brown, blue) 0.5m H

Note 1) Refer to p.6-18 for common specifications of solid state switch. Note 2) Refer to p.6-18 for lead wire length.

# Dimensions

## D-S791: Right hand mounting **D-S7P1**




# D-T791: Right hand mounting

# Most sensitive position

D-S792: Left hand mounting

500 (3000) 

# D-T792: Left hand mounting




**D-S7P2** 

# D-T791C: Right hand mounting

# tive position 38

## D-T792C: Left hand mounting





# Solid State Switch/Direct Mounting D-M5N/D-M5P/D-M5B

# Grommet



## **Applicable Actuator Series**

| Series | Bore size (mm) |
|--------|----------------|
| MYC    | ø25, ø32, ø40  |
| МҮН    | ø25, ø32, ø40  |
| ML1    | ø25, ø32, ø40  |


## Specifications

PLC: Programmable Logic Controller

| D-M5□(With indicator light) |                                                           |                   |                       |  |  |  |
|-----------------------------|-----------------------------------------------------------|-------------------|-----------------------|--|--|--|
| Auto switch model number    | D-M5N                                                     | D-M5B             |                       |  |  |  |
| Wiring                      | 3 w                                                       | vire              | 2 wire                |  |  |  |
| Output                      | NPN                                                       | PNP               | —                     |  |  |  |
| Application                 | IC circuit/F                                              | 24V DC Relay/PLC  |                       |  |  |  |
| Power voltage               | 5/12/24V DC (4                                            | —                 |                       |  |  |  |
| Current consumption         | ≤ 10                                                      | ≤ 10mA            |                       |  |  |  |
| Load voltage                | ≤ 28V DC                                                  | _                 | 24V DC (10 to 28V DC) |  |  |  |
| Load current                | ≤ 40mA                                                    | ≤ 80mA            | 5 to 40mA             |  |  |  |
| Internal voltage drop       | 1.5V or less<br>(0.8V or less at 10mA)<br>of load current | 4V or less        |                       |  |  |  |
| Current leakage             | ≤ 100 A a                                                 | ≤ 0.8mA at 24V DC |                       |  |  |  |
| Indicator light             | ON: When red light emitting diode                         |                   |                       |  |  |  |

• Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm<sup>2</sup>, 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.6-18. Note 2) Refer to p.6-18 for lead wire length

#### Dimensions




# Operation Range ( *l* Dimension) (mm)

|                 | Bore size |    |    |  |
|-----------------|-----------|----|----|--|
| Actuator series | 25        | 32 | 40 |  |
| MYC             | 4         | 4  | 4  |  |
| MYH             | 4         | 4  | 4  |  |
| ML1             | 4         | 4  | 4  |  |
|                 |           |    |    |  |

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)

# **Internal Circuit** (): If not applicable for IEC Standard



.....

# 2 Colour Indication Style Solid State Switch/Band Mounting D-H7NW/D-H7PW/D-H7BW


# Grommet

The suitable operating point can be indicated with a green light. (Red Green Red)



# **Internal Circuit**

(): If not applicable for IEC Standard



# **Applicable Actuator Series**

| Series                                       | Bore size (mm)               |
|----------------------------------------------|------------------------------|
| CDJ2                                         | ø6, ø10, ø16                 |
| CDVJ3, CDVJ5                                 | ø10, ø16                     |
| CDLJ2                                        | ø16                          |
| CDM2, CDBM2, CDVM3, CDVM5, CDLM2, CDLG1, REC | ø20, ø25, ø32, ø40           |
| CDG1, MGG                                    | ø20, ø25, ø32, ø40, ø50, ø63 |
| RSDG                                         | ø40, ø50                     |
| MGC                                          | ø20, ø25, ø32, ø40, ø50      |
| RHC, MLGC                                    | ø20, ø25, ø32, ø40           |

## Specifications


PLC: Programmable Logic Controller

(mm)

| D-H7 W(With              | indicator light)                                                                                  |                         |            |  |
|--------------------------|---------------------------------------------------------------------------------------------------|-------------------------|------------|--|
| Auto switch model number | D-H7NW                                                                                            | D-H7PW                  | D-H7BW     |  |
| Wiring                   | 3 w                                                                                               | <i>v</i> ire            | 2 wire     |  |
| Output                   | NPN                                                                                               | PNP                     |            |  |
| Application              | IC circuit/F                                                                                      | 24V DC Relay/PLC        |            |  |
| Power voltage            | 5/12/24V DC (4                                                                                    |                         |            |  |
| Current consumption      | ≤ 10                                                                                              | )mA                     |            |  |
| Load voltage             | ≤ 28V DC                                                                                          | ≤ 28V DC —              |            |  |
| Load current             | ≤ 40mA                                                                                            | ≤ 80mA                  | 5 to 40mA  |  |
| Internal voltage drop    | 1.5V or less<br>(0.8V or less at 10mA)<br>of load current 0.8V or less                            |                         | 4V or less |  |
| Current leakage          | 100 A or les                                                                                      | 0.8mA or less at 24V DC |            |  |
| Indicator light          | Operating point: Red light emitting diode<br>Suitable operating point: Green light emitting diode |                         |            |  |

• Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm<sup>2</sup>, 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.6-18. Note 2) Refer to p.6-18 for lead wire length.

## Dimensions



# Operation Range ( *c* Dimension)

| Actuator series                                 |   |    | Bore size |    |    |    |     |    |    |     |  |  |  |
|-------------------------------------------------|---|----|-----------|----|----|----|-----|----|----|-----|--|--|--|
| Actuator series                                 | 6 | 10 | 15        | 16 | 20 | 25 | 32  | 40 | 50 | 63  |  |  |  |
| CDJ2                                            | 3 | 4  |           | 4  | —  | _  | —   | —  | -  | —   |  |  |  |
| CDVJ3, CDVJ5                                    | _ | 4  | _         | 4  | _  | _  | _   | _  | -  | _   |  |  |  |
| CDLJ2                                           | — | —  | -         | 4  | —  | _  | —   | —  | -  | —   |  |  |  |
| CDM2, CDBM2, CDVM3,<br>CDVM5, CDLM2, CDLG1, REC | _ | _  | _         | _  | 4  | 4  | 4.5 | 5  | _  | _   |  |  |  |
| CDG1, MGG                                       | _ | -  | —         | _  | 4  | 4  | 4.5 | 5  | 6  | 6.5 |  |  |  |
| RSDG                                            | — | —  | —         | —  | —  | —  | —   | 5  | 6  | —   |  |  |  |
| MGG, MGC                                        | _ | _  | -         | _  | 4  | 4  | 4.5 | 5  | 6  | _   |  |  |  |
| RHC, MLGC                                       | _ | _  | _         | _  | 4  | 4  | 4.5 | 5  | _  | _   |  |  |  |

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)


# 2 Colour Indication Style Solid State Switch/Band Mounting D-G59W/D-G5PW/D-K59W


# Grommet

The suitable operating point can be indicated with a green light. (Red Green Red)




# Internal Circuit (): If not applicable for IEC Standard






#### **D-K59W**



#### Indicator light/Operation



## **Applicable Actuator Series**

| ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100 |  |  |  |  |
|-----------------------------------------|--|--|--|--|
| 100                                     |  |  |  |  |
| <i>i</i> 50                             |  |  |  |  |
| )                                       |  |  |  |  |
| 100                                     |  |  |  |  |
| s!                                      |  |  |  |  |


#### Specifications

PLC: Programmable Logic Controller

| D-G5□/D-K59 (With indicator light) |                                                                                                   |                                 |                       |  |  |  |  |  |  |
|------------------------------------|---------------------------------------------------------------------------------------------------|---------------------------------|-----------------------|--|--|--|--|--|--|
| Auto switch model number           | D-G59W                                                                                            | D-K59W                          |                       |  |  |  |  |  |  |
| Wiring                             | 3 w                                                                                               | ire                             | 2 wire                |  |  |  |  |  |  |
| Output                             | NPN                                                                                               | PNP                             | —                     |  |  |  |  |  |  |
| Application                        | IC circuit/F                                                                                      | Relay/PLC                       | 24V DC Relay/PLC      |  |  |  |  |  |  |
| Power voltage                      | 5/12/24V DC (4                                                                                    | —                               |                       |  |  |  |  |  |  |
| Current consumption                | ≤ 10                                                                                              | —                               |                       |  |  |  |  |  |  |
| Load voltage                       | ≤ 28V DC                                                                                          | _                               | 24V DC (10 to 28V DC) |  |  |  |  |  |  |
| Load current                       | ≤ 40mA                                                                                            | 80mA or less                    | 5 to 40mA             |  |  |  |  |  |  |
| Internal voltage drop              |                                                                                                   | V or less at 10mA) 0.8V or less |                       |  |  |  |  |  |  |
| Current leakage                    | 100 A or less at 24V DC 0.8mA or less at 24V DC                                                   |                                 |                       |  |  |  |  |  |  |
| Indicator light                    | Operating point: Red light emitting diode<br>Suitable operating point: Green light emitting diode |                                 |                       |  |  |  |  |  |  |

•Lead wire—Oilproof vinyl heavy insulation cable, ø4, 0.3mm<sup>2</sup>, 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.6-18. Note 2) Refer to p.6-18 for lead wire length.

## Dimensions



# **Operation Range (** *l* **Dimension)**

| Actuator series                             | Bore size |    |     |    |    |     |     |     |  |  |
|---------------------------------------------|-----------|----|-----|----|----|-----|-----|-----|--|--|
| Actuator series                             | 20        | 25 | 32  | 40 | 50 | 63  | 80  | 100 |  |  |
| CDG1, MGG                                   | 4         | 4  | 4.5 | 5  | 6  | 6.5 | 6.5 | 7   |  |  |
| CDA1, CDBA1, CDV3, CDVS, CDLA,<br>CDL1, CNA | -         | _  | _   | 5  | 6  | 6.5 | 6.5 | 7   |  |  |
| MGC                                         | 4         | 4  | 4.5 | 5  | 6  | _   | _   | —   |  |  |
| RHC, MLGC, REC                              | 4         | 4  | 4.5 | 5  | _  | -   | —   | _   |  |  |
| CE2                                         | _         | _  | _   | 5  | 6  | 6.5 | 6.5 | 7   |  |  |

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)



(mm)

# 2 Colour Indication Style Solid State Switch/Rail Mounting D-F79W/D-F7PW/D-J79W

## Grommet

The suitable operating point can be indicated with a green light. (Red Green Red)



# **Applicable Actuator Series**

| Series         | Bore size (mm)                                                                    |
|----------------|-----------------------------------------------------------------------------------|
| CDJ2, CDVJ3, 5 | ø10, ø16                                                                          |
| CDQ2           | ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160               |
| CD□XW          | Plate mounted(P), ø10, ø16, ø20, ø25, ø32, Housing mounted(B), ø16, ø20, ø25, ø32 |
| CDY1S, CY1L    | ø6, ø10, ø15, ø20, ø25, ø32, ø40                                                  |
| RSDQ           | ø20, ø25, ø32, ø40, ø50                                                           |
| MDU            | ø25, ø32, ø40, ø50, ø63                                                           |
| CE1            | ø12, ø20, ø32, ø40, ø50, ø63                                                      |
| MK, MK2        | ø20, ø25, ø32, ø40, ø50, ø63                                                      |
| СХТ            | ø32, ø40                                                                          |

# Specifications

PLC: Programmable Logic Controller


(mm)

| D-F7□W/D-J79W                             |                                                      |           |                       |  |  |  |  |  |  |
|-------------------------------------------|------------------------------------------------------|-----------|-----------------------|--|--|--|--|--|--|
| Auto switch model number                  | D-F79W                                               | D-J79W    |                       |  |  |  |  |  |  |
| Wiring                                    | 3 wi                                                 | re        | 2 wire                |  |  |  |  |  |  |
| Output                                    | NPN                                                  | PNP       | —                     |  |  |  |  |  |  |
| Application                               | IC circuit/R                                         | lelay/PLC | 24V DC Relay/PLC      |  |  |  |  |  |  |
| Power voltage                             | 5/12/24V DC                                          | —         |                       |  |  |  |  |  |  |
| Current consumption                       | ≤ 10                                                 | —         |                       |  |  |  |  |  |  |
| Load voltage                              | ≤ 28V DC                                             |           | 24V DC (10 to 28V DC) |  |  |  |  |  |  |
| Load current                              | ≤ 40mA                                               | ≤ 80mA    | 5 to 40mA             |  |  |  |  |  |  |
| Internal voltage drop                     | ≤ 1.5V<br>(≤ 0.8V at 10mA load current)              | ≤ 0.8V    | ≤ 4V                  |  |  |  |  |  |  |
| Current leakage                           | ≤ 100µA at 24V DC ≤ 0.8mA at 24V DC                  |           |                       |  |  |  |  |  |  |
| Operating point: Red light emitting diode |                                                      |           |                       |  |  |  |  |  |  |
| Indicator light                           | Suitable operating point: Green light emitting diode |           |                       |  |  |  |  |  |  |

•Lead wire ——Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm<sup>2</sup>, 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.6-18.

Note 2) Refer to p.6-18 for lead wire length.

# Dimensions




# Operation Range ( *t* Dimension)

| Actuator series |          |   |    |     |    |     |     |     | Bore | size |     |     |     |     |     |     |     |
|-----------------|----------|---|----|-----|----|-----|-----|-----|------|------|-----|-----|-----|-----|-----|-----|-----|
| Actuator series | <b>`</b> | 6 | 10 | 12  | 15 | 16  | 20  | 25  | 32   | 40   | 50  | 63  | 80  | 100 | 125 | 140 | 160 |
| CDJ2, CDVJ3,    | 5        | - | 5  | —   | -  | 5   |     | —   |      | -    | -   | —   | —   | -   | _   | —   | —   |
| CDQ2            |          | - | —  | 5.5 | —  | 6   | 5.5 | 5   | 6    | 6    | 6   | 6.5 | 6.5 | 7   | 9   | 9   | 8.5 |
|                 | 3        |   | —  |     |    | 4   | 3.5 | 3.5 | 4    |      |     |     |     |     |     |     |     |
|                 |          | _ | 3  |     |    | 2.5 | 3.5 | 3.5 | 2.5  | _    | _   |     |     |     | _   |     | _   |
| CDY1S, CY1L     |          | 3 | 3  | -   | 4  | -   | 3   | 3   | 3    | 3.5  | _   | —   | —   | —   | -   | —   | _   |
| RSDQ            |          | - | —  | -   | —  | -   | 5.5 | —   | 6    | 6    | 6   | -   | —   | -   |     | —   | _   |
| MDU             |          | - | —  |     | —  | -   | -   | 6.5 | 7    | 6.5  | 6.5 | 6.5 | —   | -   | -   | —   | _   |
| CE1             |          | - | —  | 5.5 | -  | -   | 5.5 | -   | 6    | 6    | 6   | 6.5 | —   | -   |     | -   | _   |
| MK, MK2         |          | - | —  | Ι   | —  | _   | 5.5 | 5   | 6    | 6    | 6   | 6.5 | _   | -   | _   | _   | _   |
| CXT             |          | - | —  | —   | —  | -   | -   | —   | 6    | 6    | -   | —   | —   | -   | -   | —   | —   |

Note) Average value at normal temperature including hysteresis. (Tolerance  $\pm 30\%$ )

# Internal Circuit

( ): If not applicable for IEC



Suitable operating point

# 2 Colour Indication Style Solid State Switch/Rail Mounting D-F7NWV/D-F7BWV

# Grommet Electrical entry: Perpendicular

The suitable operating point can be indicated with a green light. (Red Green Red)



# **Applicable Actuator Series**


| Series                                           | Bore size (mm)                                                                   |  |  |  |  |  |  |
|--------------------------------------------------|----------------------------------------------------------------------------------|--|--|--|--|--|--|
| CDJ2, CDVJ3, 5                                   | ø10, ø16                                                                         |  |  |  |  |  |  |
| CDQ2                                             | ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160              |  |  |  |  |  |  |
| CD□XW                                            | late mounted(P), ø10, ø16, ø20, ø25, ø32, Housing mounted(B), ø16, ø20, ø25, ø32 |  |  |  |  |  |  |
| CDY1S, CY1L                                      | ø6, ø10, ø15, ø20, ø25, ø32, ø40                                                 |  |  |  |  |  |  |
| RSDQ                                             | ø20, ø25, ø32, ø40, ø50                                                          |  |  |  |  |  |  |
| MDU                                              | ø25, ø32, ø40, ø50, ø63                                                          |  |  |  |  |  |  |
| CE1                                              | ø12, ø20, ø32, ø40, ø50, ø63                                                     |  |  |  |  |  |  |
| MK, MK2                                          | ø20, ø25, ø32, ø40, ø50, ø63                                                     |  |  |  |  |  |  |
| СХТ                                              | ø32, ø40                                                                         |  |  |  |  |  |  |
| Specifications PLC: Programmable Logic Controlle |                                                                                  |  |  |  |  |  |  |
| D-F7 WV (With indicator light)                   |                                                                                  |  |  |  |  |  |  |
|                                                  |                                                                                  |  |  |  |  |  |  |

| <b>-</b> · · · <b>-</b> · · · · · · · · · · · · · · · · · · · | in indicator ingiti,                    |                         |  |  |
|---------------------------------------------------------------|-----------------------------------------|-------------------------|--|--|
| Auto switch model number                                      | D-F7NWV                                 | D-F7BWV                 |  |  |
| Wiring                                                        | 3 wire                                  | 2 wire                  |  |  |
| Output NPN                                                    |                                         |                         |  |  |
| Application IC circuit/Relay/PLC                              |                                         | 24V DC Relay/PLC        |  |  |
| Power voltage                                                 | 5/12/24V DC (4.5 to 28V DC)             |                         |  |  |
| Current consumption                                           | ≤ 10mA                                  |                         |  |  |
| Load voltage                                                  | ≤ 28V DC                                | 24V DC (10 to 28V DC)   |  |  |
| Load current                                                  | ≤ 40mA                                  | 5 to 40mA               |  |  |
| Internal voltage drop                                         | ≤ 1.5V<br>(≤ 0.8V at 10mA load current) | ≤ 4V                    |  |  |
| Current leakage                                               | 100μA or less at 24V DC                 | 0.8mA or less at 24V DC |  |  |
|                                                               | Operating point: Red light emit         | ting diode              |  |  |
| Indicator light                                               |                                         |                         |  |  |

Suitable operating point: Green light emitting diode

•Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm<sup>2</sup>, 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.6-18. Note 2) Refer to p.6-18 for lead wire length.

# Dimensions




# Operation Range ( *l* Dimension)

| Actuator se | rios  | Bore size |    |     |    |     |     |     |     |     | -   |     |     |     |     |     |     |
|-------------|-------|-----------|----|-----|----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| Actuator se | nes   | 6         | 10 | 12  | 15 | 16  | 20  | 25  | 32  | 40  | 50  | 63  | 80  | 100 | 125 | 140 | 160 |
| CDJ2, CDV   | J3, 5 | —         | 5  | -   | —  | 5   | -   | —   | _   | —   | —   | —   | _   | _   | —   | -   | -   |
| CDQ2        |       | —         | —  | 5.5 | —  | 6   | 5.5 | 5   | 6   | 6   | 6   | 6.5 | 6.5 | 7   | 9   | 9   | 8.5 |
| CD          | В     |           | —  |     |    | 4   | 0.5 | 3.5 | 4   |     |     |     |     |     |     |     |     |
|             | Ρ     | _         | 3  |     | _  | 2.5 | 3.5 | 3.5 | 2.5 |     |     | _   |     | _   | _   | _   | _   |
| CDY1S, CY   | '1L   | 3         | 3  | -   | 4  | -   | 3   | 3   | 3   | 3.5 | -   | —   | -   | —   | —   | _   | -   |
| RSDQ        |       | —         | —  | -   | —  | -   | 5.5 | —   | 6   | 6   | 6   | —   | —   | —   | —   | —   | -   |
| MDU         |       | _         | -  | -   | —  | -   | -   | 6.5 | 7   | 6.5 | 6.5 | 6.5 | -   | —   | —   | —   | -   |
| CE1         |       | —         | —  | 5.5 | _  | _   | 5.5 | —   | 6   | 6   | 6   | 6.5 | _   | _   | —   | _   | _   |
| MK, MK2     |       | —         | —  | —   | —  | _   | 5.5 | 5   | 6   | 6   | 6   | 6.5 | _   | _   | —   | _   | —   |
| СХТ         |       | —         | _  | _   | _  | _   | _   | _   | 6   | 6   | _   | _   | _   | _   | _   | _   | —   |
|             |       | _         | _  | _   | _  | _   | _   | _   | 6   | 6   | _   | _   | _   | _   | _   | _   | _   |


Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)




# (): If not applicable for IEC Standard



#### D-F7BWV



#### Indicator light/Operation



(mm)

# 2 Colour Indication Style Solid State Switch/Tie-rod Mounting D-F59W/D-F5PW/D-J59W

# Grommet


The suitable operating point can be indicated with a green light.


(Red Green Red)



# **Internal Circuit**


): If not applicable for IEC ( Starretand DC(+) Brown(Red) mair POUT Black(White) Switch DC(-) Blue(Black)





# **Indicator light/Operation**

6-64



## **Applicable Actuator Series**

| Series                                 | Bore size (mm)                             |
|----------------------------------------|--------------------------------------------|
| CDA1, CDBA1, CDV3, CDVS1,<br>CDLA, CNA | ø40, ø50, ø63, ø80, ø100                   |
| CDL1                                   | ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160 |
| CDS1                                   | ø125, ø140, ø160, ø180, ø200               |
| CE2                                    | ø40, ø50, ø63, ø80, ø100                   |
| MDB                                    | ø32, ø40, ø63, ø80, ø100                   |

# Specifications


| D-F5 W/D-J5              | D-F5 W/D-J59W (With indicator light)                 |                         |                       |  |  |  |  |  |  |  |
|--------------------------|------------------------------------------------------|-------------------------|-----------------------|--|--|--|--|--|--|--|
| Auto switch model number | D-F59W                                               | D-J59W                  |                       |  |  |  |  |  |  |  |
| Wiring                   | 3 wi                                                 | re                      | 2 wire                |  |  |  |  |  |  |  |
| Output                   | NPN                                                  | PNP                     | _                     |  |  |  |  |  |  |  |
| Application              | IC circuit/R                                         | lelay/PLC               | 24V DC Relay/PLC      |  |  |  |  |  |  |  |
| Power voltage            | 5/12/24V DC (                                        | —                       |                       |  |  |  |  |  |  |  |
| Current consumption      | 10                                                   | —                       |                       |  |  |  |  |  |  |  |
| Load voltage             | ≤ 28V DC                                             |                         | 24V DC (10 to 28V DC) |  |  |  |  |  |  |  |
| Load current             | ≤ 40mA                                               | ≤ 80mA                  | 5 to 40mA             |  |  |  |  |  |  |  |
| Internal voltage drop    | ≤ 1.5V<br>(≤ 0.8V at 10mA load current)              | ≤ 0.8V                  | ≤ 4V                  |  |  |  |  |  |  |  |
| Current leakage          | ≤ 100μA at 24V DC ≤ 0.8mA at 24V DC                  |                         |                       |  |  |  |  |  |  |  |
| Indicator light          | Operating point: Re                                  | ed light emitting diode |                       |  |  |  |  |  |  |  |
| indicator light          | Suitable operating point: Green light emitting diode |                         |                       |  |  |  |  |  |  |  |

PLC: Programmable Logic Controller

Lead wire - Oilproof vinyl heavy insulation cable, ø4, 0.3mm<sup>2</sup>, 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.6-18.

Note 2) Refer to p.6-18 for lead wire length

## Dimensions



# **Operation Range (***t* **Dimension)**

| Operation Range ( <i>l</i> Dimension) (mm) |     |           |    |     |     |     |     |     |     |     |     |
|--------------------------------------------|-----|-----------|----|-----|-----|-----|-----|-----|-----|-----|-----|
| Actuator series                            |     | Bore size |    |     |     |     |     |     |     |     |     |
| Actuator series                            | 32  | 40        | 50 | 63  | 80  | 100 | 125 | 140 | 160 | 180 | 200 |
| CDA1, CDBA1, CDV3, CDVS1,<br>CDLA, CNA     | -   | 4         | 4  | 4.5 | 4.5 | 4.5 | -   | -   | -   | -   | -   |
| CDL1                                       | -   | 4         | 4  | 4.5 | 4.5 | 4.5 | 5   | 5   | 5.5 | -   | -   |
| CDS1                                       | -   | -         | -  | -   | —   | —   | 5   | 5   | 5.5 | 6   | 6   |
| CE2                                        | -   | 4         | 4  | 4.5 | 4.5 | 4.5 | -   | -   | -   | -   | -   |
| MDB                                        | 3.5 | 4         | 4  | 4.5 | 4.5 | 4.5 | _   | -   | -   | —   | -   |
|                                            |     |           |    |     |     |     |     |     |     |     |     |

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)



# 2 Colour Indication Style Solid State Switch/Direct Mounting D-M5NW/D-M5PW/D-M5BW


# Grommet

The suitable operating point can be indicated with a green liaht.




# **Internal Circuit**


): If not applicable for IEC ( Standardv




## D-M5PW



#### D-M5BW



## **Indicator light/Operation**



# **Applicable Actuator Series**

| Series | Bore size (mm) |
|--------|----------------|
| MYC    | ø25, ø32, ø40  |
| МҮН    | ø25, ø32, ø40  |
| ML1    | ø25, ø32, ø40  |


# Specifications

| Specifications           | 3                                       | PLC: Programmable Logic Controller                                                                                                                         |                       |  |  |  |  |  |
|--------------------------|-----------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|--|--|--|--|--|
| D-M5 W (Wit              | h indicator light)                      |                                                                                                                                                            |                       |  |  |  |  |  |
| Auto switch model number | D-M5NW                                  | D-M5PW                                                                                                                                                     | D-M5BW                |  |  |  |  |  |
| Wiring                   | 3 w                                     | vire                                                                                                                                                       | 2 wire                |  |  |  |  |  |
| Output                   | NPN                                     | PNP                                                                                                                                                        |                       |  |  |  |  |  |
| Application              | IC circuit/R                            | 24V DC Relay/PLC                                                                                                                                           |                       |  |  |  |  |  |
| Power voltage            | 5/12/24V DC (*                          |                                                                                                                                                            |                       |  |  |  |  |  |
| Current consumption      | ≤ 10                                    |                                                                                                                                                            |                       |  |  |  |  |  |
| Load voltage             | ≤ 28V DC                                |                                                                                                                                                            | 24V DC (10 to 28V DC) |  |  |  |  |  |
| Load current             | ≤ 40mA                                  | ≤ 80mA                                                                                                                                                     | 5 to 40mA             |  |  |  |  |  |
| Internal voltage drop    | ≤ 1.5V<br>(≤ 0.8V at 10mA load current) | ≤ 0.8V                                                                                                                                                     | ≤ 4V                  |  |  |  |  |  |
| Current leakage          | ≤ 100μA a                               | ≤ 100μA at 24V DC                                                                                                                                          |                       |  |  |  |  |  |
| Indiantar light          | Operating point: Re                     | Operating point: Red light emitting diode                                                                                                                  |                       |  |  |  |  |  |
| Indicator light          | Suitable operating                      | D-M5PW       3 wire       PNP       cuit/Relay/PLC       DC (4.5 to 28V DC)       ≤ 10mA      2       ≤ 80mA       µrrent)     ≤ 0.8V       D0µA at 24V DC | l diode               |  |  |  |  |  |

Lead wire -- Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm<sup>2</sup>, 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.6-18.

Note 2) Refer to the p.6-18 for lead wire length.

# Dimensions



#### Operation Range ( *t* Dimension) (mm)

| <b>.</b>        | Bore size |    |    |  |  |  |  |  |
|-----------------|-----------|----|----|--|--|--|--|--|
| Actuator series | 25        | 32 | 40 |  |  |  |  |  |
| MYC             | 4         | 4  | 4  |  |  |  |  |  |
| MYH             | 4         | 4  | 4  |  |  |  |  |  |
| ML1             | 4         | 4  | 4  |  |  |  |  |  |

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)

# 2 Colour Indication Style Solid State Switch/Direct Mounting D-Y7NW(V)/D-Y7PW(V)/D-Y7BW(V)


# Grommet

The suitable operating point can be indicated with a green light.




# Internal Circuit


(): If not applicable for IEC




# D-Y7PW(V)



# D-Y7BW(V)



## Indicator light/Operation



# **Applicable Actuator Series**

| Series    | Bore size (mm)                                    |
|-----------|---------------------------------------------------|
| CXS       | ø6, ø10, ø15, ø20, ø25, ø32                       |
| MGQ, MVGQ | ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100 |
| MGP       | ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100 |
| MY1B      | ø25, ø32, ø40, ø50, ø63, ø80, ø100                |
| MY1C      | ø25, ø32, ø40, ø50, ø63                           |
| MY1H      | ø25, ø32, ø40                                     |
| MY1M      | ø25, ø32, ø40, ø50, ø63                           |
| RSH       | ø20, ø32, ø50, ø63, ø80                           |


## Specifications

PLC: Programmable Logic Controller

| D-Y7 W/D-Y7 WV (With indicator light) |                             |                                        |                                             |               |                       |               |  |  |  |
|---------------------------------------|-----------------------------|----------------------------------------|---------------------------------------------|---------------|-----------------------|---------------|--|--|--|
| Auto switch model number              | D-Y7NW                      | D-Y7NWV                                | D-Y7PW                                      | D-Y7PWV       | D-Y7BW                | D-Y7BWV       |  |  |  |
| Electrical entry                      | In-line                     | Perpendicular                          | In-line                                     | Perpendicular | In-line               | Perpendicular |  |  |  |
| Wiring                                |                             | 3 wi                                   | re                                          |               | 2 wire                |               |  |  |  |
| Output                                | N                           | PN                                     | PN                                          | IP            | _                     |               |  |  |  |
| Application                           |                             | IC circuit/Relay/PLC 24V DC Relay/PLC  |                                             |               |                       |               |  |  |  |
| Power voltage                         | 5/12/24V DC (4.5 to 28V DC) |                                        |                                             |               |                       |               |  |  |  |
| Current consumption                   |                             | 10mA o                                 |                                             | —             |                       |               |  |  |  |
| Load voltage                          | 28V DC                      | or less                                |                                             | -             | 24V DC (10 to 28V DC) |               |  |  |  |
| Load current                          | 40mA c                      | or less                                | 80mA o                                      | r less        | 5 to 40mA             |               |  |  |  |
| Internal voltage drop                 |                             | ≤1.5V<br>(≤ 0.8V at 10mA load current) |                                             | 3V            | ≤ 4                   | ŧV            |  |  |  |
| Current leakage                       |                             | 100µA or les                           | μA or less at 24V DC 0.8mA or less at 24V D |               |                       |               |  |  |  |
| Indicator light                       |                             | erating point:<br>itable operati       | 0                                           | 0             | ing diode             |               |  |  |  |

●Lead wire —— Oilproof vinyl heavy insulation cable, ø3.4, 0.15mm<sup>2</sup>, 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.6-18. Note 2) Refer to p.6-18 for lead wire length.

Note 2) Refer to p.6-18 for lead wire



\_

5

- 5 5 5 5.5 5.5

7.5

5 5 6

6 9 10

7 6 6 7 6 -

6 6 6

5

6.5 7.5

5

9

10

7.5

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)

6

MY1C, MY1M

MY1H

RSH

CY1R

CY1H

**MI 2B** 

MGF

# 2 Colour Indication Style with Diagnostic Output Solid State Switch/Band Mounting **D-H7LF** (Latching Style)


### Grommet

The output signal can be detected in an unsteady detecting area.



#### **Internal Circuit**

#### ( ): If not applicable for IEC



#### **Applicable Actuator Series**

| Series                                   | Bore size (mm)               |  |  |  |  |
|------------------------------------------|------------------------------|--|--|--|--|
| CDJ2                                     | ø6, ø10, ø16                 |  |  |  |  |
| CDVJ3, 5                                 | ø10, ø16                     |  |  |  |  |
| CDLJ2                                    | ø16                          |  |  |  |  |
| CDM2, CDBM2, CDVM3, 5, CDLM2, CDLG1, REC | ø20, ø25, ø32, ø40           |  |  |  |  |
| CDG1, MGG                                | ø20, ø25, ø32, ø40, ø50, ø63 |  |  |  |  |
| RSDG                                     | ø40, ø50                     |  |  |  |  |
| MGC                                      | ø20, ø25, ø32, ø40, ø50      |  |  |  |  |
| RHC, MLGC                                | ø20, ø25, ø32, ø40           |  |  |  |  |

#### Specifications

PLC: Programmable Logic Controller


| D-H7LF (With indicator light) |                                                                                                                                                                      |  |  |  |  |  |  |  |
|-------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|--|--|--|
| Auto switch model number      | D-H7LF                                                                                                                                                               |  |  |  |  |  |  |  |
| Wiring                        | 4 wire                                                                                                                                                               |  |  |  |  |  |  |  |
| Output                        | NPN                                                                                                                                                                  |  |  |  |  |  |  |  |
| Diagnostic output             | Latching operation                                                                                                                                                   |  |  |  |  |  |  |  |
| Application                   | 24V DC Relay/PLC                                                                                                                                                     |  |  |  |  |  |  |  |
| Power voltage                 | 24V DC (20 to 26V DC)                                                                                                                                                |  |  |  |  |  |  |  |
| Current consumption           | ≤ 20mA                                                                                                                                                               |  |  |  |  |  |  |  |
| Load voltage                  | ≤ 26V DC                                                                                                                                                             |  |  |  |  |  |  |  |
| Load current                  | ≤ 40mA                                                                                                                                                               |  |  |  |  |  |  |  |
| Internal voltage drop         | ≤ 0.8V                                                                                                                                                               |  |  |  |  |  |  |  |
| Current leakage               | ≤ 100 A at 24V DC                                                                                                                                                    |  |  |  |  |  |  |  |
| Indicator light               | Operating point: Red light emitting diode<br>Suitable operating point: Green light emitting diode<br>Orange colour indicator lights on when diagnostic output is ON. |  |  |  |  |  |  |  |

•Lead wire —— Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm<sup>2</sup>, 4 cores (Brown, Black, Orange, Blue), 0.5m Note 1) Refer to common specifications on p.6-18.


Note 2) Refer to p.6-18 for lead wire length.

#### **Diagnostic Output Operation**

The diagnostic signal is output when detecting position remains within unsteady area (where indicator light is Red.) for more than 0.5 sec. This signal keeps outputing even after normal output goes to OFF. The diagnostic output becomes OFF when detecting position remains within the most suitable operating range (where indicator light is Green.) for more than 0.5 sec.



#### Dimensions



#### **Operation Range (** *l* **Dimension)**

|                                                 |   |           |    |    |    |    |     |    |    | ((((((((((((((((((((((((((((((((((((((( |
|-------------------------------------------------|---|-----------|----|----|----|----|-----|----|----|-----------------------------------------|
| A studen series                                 |   | Bore size |    |    |    |    |     |    |    |                                         |
| Actuator series                                 | 6 | 10        | 15 | 16 | 20 | 25 | 32  | 40 | 50 | 63                                      |
| CDJ2                                            | 4 | 5         | —  | 5  | —  | -  | —   | -  | —  | —                                       |
| CDVJ3, 5                                        | - | 5         | -  | 5  | -  | -  | -   | -  | -  | -                                       |
| CDLJ2                                           | - | -         | -  | 5  | -  | -  | -   | -  | -  | -                                       |
| CDM2, CDBM2, CDVM3,<br>CDVM5, CDLM2, CDLG1, REC | _ | _         | _  | _  | 5  | 5  | 5.5 | 6  | _  | _                                       |
| CDG1, MGG                                       | - | -         | -  | -  | 5  | 5  | 5.5 | 6  | 7  | 7.5                                     |
| RSDG                                            | - | -         | —  | -  | -  | -  | -   | 6  | 7  | -                                       |
| MGC                                             | _ | -         | _  | _  | 5  | 5  | 5.5 | 6  | 7  | _                                       |
| RHC, MLGC                                       | - | -         | -  | -  | 4  | 4  | 4.5 | 5  | —  | _                                       |

Note) Average value at normal temperature including hysteresis. (Tolerance  $\pm 30\%$ )



m)

# 2 Colour Indication Style with Diagnostic Output Solid State Switch/Band Mounting D-H7NF

# Grommet

The output signal can be detected in an unsteady detecting area.



# **Internal Circuit**

**Dimensions** 

#### 

# **Applicable Actuator Series**

| Series                                  | Bore size (mm)               |
|-----------------------------------------|------------------------------|
| CDJ2                                    | ø6, ø10, ø16                 |
| CDVJ3, 5                                | ø10, ø16                     |
| CDLJ2                                   | ø16                          |
| CDM2, CDBM, CDVM3, 5, CDLM2, CDLG1, REC | ø20, ø25, ø32, ø40           |
| CDG1, MGG                               | ø20, ø25, ø32, ø40, ø50, ø63 |
| RSDG                                    | ø40, ø50                     |
| MGC                                     | ø20, ø25, ø32, ø40, ø50      |
| RHC, MLGC                               | ø20, ø25, ø32, ø40           |

# Specifications


PLC: Programmable Logic Controller


| D-H7NF (With indicator light) |                                                                                                   |  |  |  |  |  |  |  |
|-------------------------------|---------------------------------------------------------------------------------------------------|--|--|--|--|--|--|--|
| Auto switch model number      | D-H7NF                                                                                            |  |  |  |  |  |  |  |
| Wiring                        | 4 wire                                                                                            |  |  |  |  |  |  |  |
| Output                        | NPN                                                                                               |  |  |  |  |  |  |  |
| Diagnostic output             | Normal operation                                                                                  |  |  |  |  |  |  |  |
| Application                   | IC circuit/Relay/PLC                                                                              |  |  |  |  |  |  |  |
| Power voltage                 | 5/12/24V DC (4.5 to 28V DC)                                                                       |  |  |  |  |  |  |  |
| Current consumption           | ≤ 10mA                                                                                            |  |  |  |  |  |  |  |
| Load voltage                  | ≤ 28V DC                                                                                          |  |  |  |  |  |  |  |
| Load current                  | ≤ 40mA                                                                                            |  |  |  |  |  |  |  |
| Internal voltage drop         | ≤ 1.5V (≤ 0.8V at 10mA)                                                                           |  |  |  |  |  |  |  |
| Current leakage               | ≤ 100 A at 24V DC                                                                                 |  |  |  |  |  |  |  |
| Indicator light               | Operating point: Red light emitting diode<br>Suitable operating point: Green light emitting diode |  |  |  |  |  |  |  |


•Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm<sup>2</sup>, 4 cores (Brown, Black, Orange, Blue), 0.5m Note 1) Refer to common specifications on p.6-18. Note 2) Refer to p.6-18 for lead wire length.

# **Diagnostic Output Operation**

The diagnostic output is detected when detecting position remains at unsteady area only, not available at the most suitable operating area, thus diagnostic signal can be output only when the detecting position is far from the suitable position for normal operation.







#### **Operation Range (***t* **Dimension)**

|                                                 |   |           |    |    |    | -  |     |    |    | (   |
|-------------------------------------------------|---|-----------|----|----|----|----|-----|----|----|-----|
| A                                               |   | Bore size |    |    |    |    |     |    |    |     |
| Actuator series                                 | 6 | 10        | 15 | 16 | 20 | 25 | 32  | 40 | 50 | 63  |
| CDJ2                                            | 4 | 5         | -  | 5  | -  | -  | -   | -  | -  | -   |
| CDVJ3, 5                                        | - | 5         | -  | 5  | -  | -  | -   | -  | -  | -   |
| CDLJ2                                           | - | -         |    | 5  | -  | -  | -   | -  | —  | -   |
| CDM2, CDBM2, CDVM3,<br>CDVM5, CDLM2, CDLG1, REC | _ | _         | _  | _  | 5  | 5  | 5.5 | 6  | _  | _   |
| CDG1, MGG                                       | - | _         | _  | _  | 5  | 5  | 5.5 | 6  | 7  | 7.5 |
| RSDG                                            | - | -         | -  | —  | —  | -  | -   | 6  | 7  | —   |
| MGC                                             | - | _         | _  | _  | 5  | 5  | 5.5 | 6  | 7  | _   |
| RHC, MLGC                                       | - | -         | -  | -  | 4  | 4  | 4.5 | 5  | -  |     |

(mm)

Note) Average value at normal temperature including hysteresis. (Tolerance  $\pm 30\%)$ 



# 2 Colour Indication Style with Diagnostic Output Solid State Switch/Band Mounting **D-G59F**

# Grommet

The output signal can be detected in an unsteady detecting area.



#### **Internal Circuit**

): If not applicable for IEC ( Standard DC(+) Brown(Red) OUT(Normal output) Black(White) OUT (Diagnostic output) Switch

Orange(Yellow)

oDC(–) Blue(Black)

# **Applicable Actuator Series**

| Series                                    | Bore size (mm)                                       |
|-------------------------------------------|------------------------------------------------------|
| CDG1, MGG                                 | ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100              |
| CDA1, CDBA1, CDV3, CDVS1, CDLA, CDL1, CNA | ø40 <sup>*</sup> , ø50 <sup>*</sup> , ø63, ø80, ø100 |
| MGC                                       | ø20, ø25, ø32, ø40, ø50                              |
| RHC, MLGC                                 | ø20, ø25, ø32, ø40                                   |
| CE2                                       | ø40, ø50, ø63, ø80, ø100                             |

\* Can not be used for lube type.

#### Specifications


PLC: Programmable Logic Controller

| D-G59F (With indicator light) |                                                      |  |  |  |  |  |  |  |  |
|-------------------------------|------------------------------------------------------|--|--|--|--|--|--|--|--|
| Auto switch model number      | D-G59F                                               |  |  |  |  |  |  |  |  |
| Wiring                        | 4 wire                                               |  |  |  |  |  |  |  |  |
| Output                        | NPN                                                  |  |  |  |  |  |  |  |  |
| Application                   | IC circuit/Relay/PLC                                 |  |  |  |  |  |  |  |  |
| Diagnostic output             | Normal operation                                     |  |  |  |  |  |  |  |  |
| Current consumption           | ≤ 10mA                                               |  |  |  |  |  |  |  |  |
| Load voltage                  | ≤ 28V DC                                             |  |  |  |  |  |  |  |  |
| Load current                  | ≤ 40mA                                               |  |  |  |  |  |  |  |  |
| Internal voltage drop         | ≤ 1.5V (≤ 0.8V at 10mA)                              |  |  |  |  |  |  |  |  |
| Current leakage               | ≤ 100 A at 24V DC                                    |  |  |  |  |  |  |  |  |
| Indicator light               | Operating point: Red light emitting diode            |  |  |  |  |  |  |  |  |
| Indicator light               | Suitable operating point: Green light emitting diode |  |  |  |  |  |  |  |  |


Lead wire Oilproof vinyl heavy insulation cable, ø4, 0.2mm<sup>2</sup>, 4 cores (Brown, Black, Orange, Blue), 0.5m Note 1) Refer to common specifications on the p.6-18. Note 2) Refer to the p.6-18 for lead wire length.


## **Diagnostic Output Operation**

#### The diagnostic output is detected when detecting position remains at unsteady area only, not available at the most suitable operating area, that is to say, diagnostic signal can be output only when the detecting position is far from the suitable position for normal operation.



#### Dimensions





#### Operation Range ( *l* Dimension)

| Speration Range ( <sup>2</sup> Dimension)    |           |    |     |    |    |     |     |     |  |  |  |  |
|----------------------------------------------|-----------|----|-----|----|----|-----|-----|-----|--|--|--|--|
| A                                            | Bore size |    |     |    |    |     |     |     |  |  |  |  |
| Actuator series                              | 20        | 25 | 32  | 40 | 50 | 63  | 80  | 100 |  |  |  |  |
| CDG1, MGG                                    | 5         | 5  | 5.5 | 6  | 7  | 7.5 | 7.5 | 8   |  |  |  |  |
| CDA1, CDBA1, CDV3,<br>CDVS1, CDLA, CDL1, CNA | -         | _  | -   | 6  | 7  | 7.5 | 7.5 | 8   |  |  |  |  |
| MGC                                          | 5         | 5  | 5.5 | 6  | 7  | -   | -   | -   |  |  |  |  |
| RHC, MLGC                                    | 5         | 5  | 5.5 | 6  | -  | -   | -   | -   |  |  |  |  |
| CE2                                          | —         | —  | —   | 6  | 7  | 7.5 | 7.5 | 8   |  |  |  |  |

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)

# 2 Colour Indication Style with Diagnostic Output Solid State Switch/Rail Mounting **D-F7LF** (Latching Style)

# Grommet

The output signal can be detected in an unsteady detecting area.



# **Applicable Actuator Series**

| Series         | Bore size (mm)                                                      |
|----------------|---------------------------------------------------------------------|
| CDJ2, CDVJ3, 5 | ø10, ø16                                                            |
| CDQ2           | ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160 |
| CD             | Housing mounted(B), ø16, ø20, ø25, ø32                              |
| CDY1S, CY1L    | ø6, ø10, ø15, ø20, ø25, ø32, ø40                                    |
| RSDQ           | ø20, ø25, ø32, ø40, ø50                                             |
| MDU            | ø25, ø32, ø40, ø50, ø63                                             |
| CE1            | ø12, ø20, ø32, ø40, ø50, ø63                                        |
| MK, MK2        | ø20, ø25, ø32, ø40, ø50, ø63                                        |
| СХТ            | ø32, ø40                                                            |


# Specifications

PLC: Programmable Logic Controller

| D-F7LF (With indicator light) |                                                                                                   |  |  |  |  |  |  |  |  |
|-------------------------------|---------------------------------------------------------------------------------------------------|--|--|--|--|--|--|--|--|
| Auto switch model number      | D-F7LF                                                                                            |  |  |  |  |  |  |  |  |
| Wiring                        | 4 wire                                                                                            |  |  |  |  |  |  |  |  |
| Output                        | NPN                                                                                               |  |  |  |  |  |  |  |  |
| Diagnostic output             | Latching operation                                                                                |  |  |  |  |  |  |  |  |
| Application                   | 24V DC Relay/PLC                                                                                  |  |  |  |  |  |  |  |  |
| Power voltage                 | 24V DC (20 to 26V DC)                                                                             |  |  |  |  |  |  |  |  |
| Current consumption           | ≤ 20mA                                                                                            |  |  |  |  |  |  |  |  |
| Load voltage                  | ≤ 26V DC                                                                                          |  |  |  |  |  |  |  |  |
| Load current                  | ≤ 40mA                                                                                            |  |  |  |  |  |  |  |  |
| Internal voltage drop         | ≤ 0.8V                                                                                            |  |  |  |  |  |  |  |  |
| Current leakage               | ≤ 100 A at 24V DC                                                                                 |  |  |  |  |  |  |  |  |
| Indicator light               | Operating point: Red light emitting diode<br>Suitable operating point: Green light emitting diode |  |  |  |  |  |  |  |  |

## **Internal Circuit**


# ( ): If not applicable for IEC



•Lead wire — Oilproof vinyl heavy insulation cable, Ø3.4, 0.2mm<sup>2</sup>, 4 cores (Brown,Black, Orange, Blue), 0.5m Note 1) Refer to common specifications on p.6-18. Note 2) Refer to p.6-18 for lead wire length.

# **Diagnostic Output Operation**


The diagnostic signal is output when detecting position remains within unsteady area (where indicator light is Red.) for more than 0.5 sec. This signal keeps outputting even after normal output goes to OFF. The diagnostic output becomes OFF when detecting position remains within the most suitable operating range (where indicator light is Green.) for more than 0.5 sec.



(mm)

Orange colour indicator lights on when diagnostic output is ON.

## Dimensions



## **Operation Range (** *t* **Dimension)**

| Actuator           |     | Bore size |    |     |     |     |     |     |     |    |     |    |     |      |     |      |
|--------------------|-----|-----------|----|-----|-----|-----|-----|-----|-----|----|-----|----|-----|------|-----|------|
| series             | 6   | 10        | 12 | 15  | 16  | 20  | 25  | 32  | 40  | 50 | 63  | 80 | 100 | 125  | 140 | 160  |
| CDJ2, CDVJ3, CDVJ5 | -   | 6.5       | -  | -   | 5.5 | -   | -   | -   | -   | -  | -   | -  | -   | -    | -   | -    |
| CDQ2               | —   | -         | 6  | _   | 7   | 7   | 7   | 8   | 7   | 8  | 8.5 | 8  | 9   | 10.5 | 11  | 10.5 |
| CD XW B            | _   | -         | _  | -   | 4.5 | 4.5 | 5   | 4.5 | -   | _  | -   | -  | -   | -    | -   | -    |
| CDY1S, CY1L        | 4.5 | 4.5       | -  | 4.5 | _   | 4.5 | 4.5 | 4.5 | 4.5 | —  | -   | _  | -   | -    | -   | _    |
| RSDQ               | -   | -         | -  | -   | -   | 7   | _   | 8   | 7   | 7  | -   | -  | -   | -    | -   | -    |
| MDU                | _   | -         | _  | _   | _   | -   | 7   | 7.5 | 7   | 7  | 7   | _  | -   | -    | -   | _    |
| СХТ                | -   | -         | -  | —   | _   | —   | _   | 6   | 6   | -  | —   | _  | -   | -    | -   | -    |
| CE1                | -   | -         | 6  | -   | _   | 7   | 7   | 8   | 7   | 8  | 8.5 | _  | -   | -    | -   | -    |
| MK, MK2            | -   | -         | -  | —   | _   | 7   | 7   | 8   | 7   | 8  | 8.5 | _  | -   | -    | -   | -    |
|                    |     |           |    |     |     |     |     |     |     |    |     |    |     |      |     |      |

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)

# 2 Colour Indication Style with Diagnostic Output Solid State Switch/Rail Mounting **D-F79F**


# Grommet

The output signal can be detected in an unsteady detecting area.




# **Internal Circuit**

( ): If not applicable for IEC Standard



# Dimensions



## **Applicable Actuator Series**

| Series         | Bore size (mm)                                                                |
|----------------|-------------------------------------------------------------------------------|
|                |                                                                               |
| CDJ2, CDVJ3, 5 | ø10, ø16                                                                      |
| CDQ2           | ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160           |
| CD             | Plate mounted(P), ø10, ø16, ø20, ø25, ø32 Housing mounted, ø16, ø20, ø25, ø32 |
| CDY1S, CY1L    | ø6, ø10, ø15, ø20, ø25, ø32, ø40                                              |
| RSDQ           | ø20, ø32, ø40, ø50                                                            |
| MDU            | ø25, ø32, ø40, ø50, ø63                                                       |
| СХТ            | ø32, ø40                                                                      |
| CE1            | ø12, ø20, ø32, ø40, ø50, ø63                                                  |
| MK, MK2        | ø20, ø25, ø32, ø40, ø50, ø63                                                  |

# Specifications


PLC: Programmable Logic Controller

| D-F79F (With indicator light) |                                                                                                   |  |  |  |  |  |  |  |  |  |
|-------------------------------|---------------------------------------------------------------------------------------------------|--|--|--|--|--|--|--|--|--|
| Auto switch model number      | D-F79F                                                                                            |  |  |  |  |  |  |  |  |  |
| Wiring                        | 4 wire                                                                                            |  |  |  |  |  |  |  |  |  |
| Output                        | NPN                                                                                               |  |  |  |  |  |  |  |  |  |
| Diagnostic output             | Normal operation                                                                                  |  |  |  |  |  |  |  |  |  |
| Application                   | IC circuit/Relay/PLC                                                                              |  |  |  |  |  |  |  |  |  |
| Power voltage                 | 5/12/24V DC (4.5 to 28V DC)                                                                       |  |  |  |  |  |  |  |  |  |
| Current consumption           | ≤ 10mA                                                                                            |  |  |  |  |  |  |  |  |  |
| Load voltage                  | ≤ 28V DC                                                                                          |  |  |  |  |  |  |  |  |  |
| Load current                  | ≤ 40mA                                                                                            |  |  |  |  |  |  |  |  |  |
| Internal voltage drop         | ≤ 1.5V (0.8V at 10mA)                                                                             |  |  |  |  |  |  |  |  |  |
| Current leakage               | ≤ 100 A at 24V DC                                                                                 |  |  |  |  |  |  |  |  |  |
| Indicator light               | Operating point: Red light emitting diode<br>Suitable operating point: Green light emitting diode |  |  |  |  |  |  |  |  |  |

●Lead wire —— Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm<sup>2</sup>, 4 cores (Brown, Black, Orange, Blue), 0.5m Note 1) Refer to common specifications on p.6-18. Note 2) Refer to p.6-18 for lead wire length.

# **Diagnostic Output Operation**

The diagnostic output is detected when detecting position remains at unsteady area only, not available at the most suitable operating area, that is to say, diagnostic signal can be output only when the detecting position is far from the suitable position for normal operation.



# Operation Range ( *l* Dimension)

| Actuator         |    |       | Bore size |      |        |       |        |        |      |        |       |       |       |     |          |     |      |
|------------------|----|-------|-----------|------|--------|-------|--------|--------|------|--------|-------|-------|-------|-----|----------|-----|------|
| series           |    | 6     | 10        | 12   | 15     | 16    | 20     | 25     | 32   | 40     | 50    | 63    | 80    | 100 | 125      | 140 | 160  |
| CDJ2, CDVJ3, CDV | J5 | -     | 6.5       | —    | -      | 5.5   | -      | -      | -    | -      | -     | -     | -     | -   | -        | -   | -    |
| CDQ2             |    | -     | —         | 6    | -      | 7     | 7      | 7      | 8    | 7      | 8     | 8.5   | 8     | 9   | 10.5     | 11  | 10.5 |
| <b>CD</b> DXW    | В  |       | —         |      |        | 4.5   | 4.5    | 5      | 4.5  |        |       |       |       |     |          |     |      |
|                  | Ρ  | _     | 4.5       |      | -      | 3.5   | 4.5    | 5      | 3.5  | _      | _     |       | _     | _   | _        | _   | _    |
| CDY1S, CY1       | L  | 4.5   | 4.5       | -    | 4.5    | -     | 4.5    | 4.5    | 4.5  | 4.5    | -     | -     | -     | -   | -        | -   | -    |
| RSDQ             |    | -     | -         | -    | -      | -     | 7      | -      | 8    | 7      | 7     | -     | -     | -   | -        | -   | -    |
| MDU              |    | -     | -         | -    | -      | -     | -      | 7      | 7.5  | 7      | 7     | 7     | _     | -   | -        | -   | _    |
| СХТ              |    | -     | —         | —    | -      | -     | -      | -      | 6    | 6      | -     | -     | _     | -   | -        | -   | -    |
| CE1              |    | -     | —         | 6    | -      | -     | 7      | -      | 8    | 7      | 8     | 8.5   | -     | -   | —        | -   | -    |
| MK, MK2          | 2  | -     | —         | -    | -      | -     | 7      | 7      | 8    | 7      | 8     | 8.5   | _     | _   | _        | -   | -    |
| Note) Avera      | an | value | atn       | orma | l tomr | orati | iro in | aludir | a hu | storoc | ic (T | olora | nco 4 | 30% | <b>`</b> |     |      |

Note) Average value at normal temperature including hysteresis. (Tolerance  $\pm 30\%$ )



(mm)


# 2 Colour Indication Style with Diagnostic Output Solid State Switch/Tie-rod Mounting **D-F59F**

## Grommet

The output signal can be detected in an unsteady detecting area.



## **Internal Circuit**



### **Applicable Actuator Series**

| Series                              | Bore size (mm)                             |
|-------------------------------------|--------------------------------------------|
| CDA1, CDBA1, CDV3, CDVS1, CDLA, CNA | ø40, ø50, ø63, ø80, ø100                   |
| CDL1                                | ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160 |
| CDS1                                | ø125, ø140, ø160, ø180, ø200               |
| CE2                                 | ø40, ø50, ø63, ø80, ø100                   |
| MDB                                 | ø32, ø40, ø50, ø63, ø80, ø100              |

## Specifications

PLC: Programmable Logic Controller


| D-F59F                   |                                                                                                   |
|--------------------------|---------------------------------------------------------------------------------------------------|
| Auto switch model number | D-F59F                                                                                            |
| Wiring                   | 4 wire                                                                                            |
| Output                   | NPN                                                                                               |
| Diagnostic output        | Normal operation                                                                                  |
| Application              | IC circuit/Relay/PLC                                                                              |
| Power voltage            | 5/12/24V DC (4.5 to 28V DC)                                                                       |
| Current consumption      | ≤ 10mA                                                                                            |
| Load voltage             | ≤ 28V DC                                                                                          |
| Load current             | ≤ 40mA                                                                                            |
| Internal voltage drop    | ≤ 1.5V (≤ 0.8V at 10mA)                                                                           |
| Current leakage          | ≤ 100 A at 24V DC                                                                                 |
| Indicator light          | Operating point: Red light emitting diode<br>Suitable operating point: Green light emitting diode |

Lead wire -— Oilproof vinyl heavy insulation cable, ø4, 0.2mm<sup>2</sup>, 4 cores (Brown, Black, Orange, Blue), 0.5m Note 1) Refer to common specifications on p.6-18.


#### Note 2) Refer to p.6-18 for lead wire length.


#### **Diagnostic Output Operation**

The diagnostic output is detected when detecting position remains at unsteady area only, not available at the most suitable operating area, that is to say, diagnostic signal can be output only when the detecting position is far from the suitable position for normal operation.



#### Dimensions





## **Operation Range (***t* **Dimension)**

| Operation Range ( <i>l</i> Dimension) (mm) |           |         |         |        |          |         |         |      |     |     |     |  |  |
|--------------------------------------------|-----------|---------|---------|--------|----------|---------|---------|------|-----|-----|-----|--|--|
| A shushan sanisa                           | Bore size |         |         |        |          |         |         |      |     |     |     |  |  |
| Actuator series                            | 32        | 40      | 50      | 63     | 80       | 100     | 125     | 140  | 160 | 180 | 200 |  |  |
| CDA1, CDBA1, CDV3,<br>CDVS1, CDLA, CNA     | _         | 5.5     | 5       | 5.5    | 5.5      | 5.5     | -       | _    | _   | _   | _   |  |  |
| CDL1                                       | -         | 5.5     | 5       | 5.5    | 5.5      | 5.5     | 5.5     | 6    | 6.5 | -   | —   |  |  |
| CDS1                                       | -         | -       | -       | -      | -        | -       | 5.5     | 6    | 6.5 | 7   | 7   |  |  |
| CE2                                        | -         | 5.5     | 5       | 5.5    | 5.5      | 5.5     | -       | -    | —   | -   | —   |  |  |
| MDB                                        | 5         | 5.5     | 5.5     | 6      | 6        | 6       | _       | -    | _   | _   | _   |  |  |
| Note) Average value at norma               | l temp    | erature | includi | na hvs | teresis. | (Tolera | ance ±3 | 30%) |     |     |     |  |  |

Note ng nys

# SMC 🌀

# Water Resistant 2 Colour Inudication Style Solid State Switch/Band Mounting **D-H7BAL**

## Grommet

# Water (coolant) resistant performance



# **▲** Caution

#### **Precautions**

Consult SMC if using coolant liquid other than water based solution.

## **Applicable Actuator Series**

| Series                                   | Bore size (mm)               |  |  |  |  |  |  |
|------------------------------------------|------------------------------|--|--|--|--|--|--|
| CDJ2                                     | ø6, ø10, ø16                 |  |  |  |  |  |  |
| CDVJ3, 5                                 | ø10, ø16                     |  |  |  |  |  |  |
| CDLJ2                                    | ø16                          |  |  |  |  |  |  |
| CDM2, CDBM2, CDVM3, 5, CDLM2, CDLG1, REC | ø20, ø25, ø32, ø40           |  |  |  |  |  |  |
| CDG1, MGG                                | ø20, ø25, ø32, ø40, ø50, ø63 |  |  |  |  |  |  |
| RSDG                                     | ø40, ø50                     |  |  |  |  |  |  |
| MGC                                      | ø20, ø25, ø32, ø40, ø50      |  |  |  |  |  |  |
| MLGC                                     | ø20, ø25, ø32, ø40           |  |  |  |  |  |  |

#### Specifications


PLC: Programmable Logic Controller

# D-H7BAL (With indicator light)

| Auto switch model number | D-H7BAL                                                                                           |
|--------------------------|---------------------------------------------------------------------------------------------------|
| Wiring                   | 2 wire                                                                                            |
| Output                   | _                                                                                                 |
| Application              | 24V DC Relay/PLC                                                                                  |
| Power voltage            | -                                                                                                 |
| Current consumption      | _                                                                                                 |
| Load voltage             | 24V DC (10 to 28V DC)                                                                             |
| Load current             | ≤ 5 to 40mA                                                                                       |
| Internal voltage drop    | ≤ 4V                                                                                              |
| Current leakage          | ≤ 0.8mA at 24V DC                                                                                 |
| Indicator light          | Operating point: Red light emitting diode<br>Suitable operating point: Green light emitting diode |


# Internal Circuit

## ( ): If not applicable for IEC Standard



•Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm<sup>2</sup>, 2 cores (Brown, Blue), 3m (Standard) Note 1) Refer to common specifications on p.6-18. Note 2) Refer to p.6-18 for lead wire length.

#### **Dimensions**



# **Operation Range (***t* **Dimension)**

|                                            |   | Bore size |    |    |    |    |     |    |    |     |  |
|--------------------------------------------|---|-----------|----|----|----|----|-----|----|----|-----|--|
| Actuator series                            | 6 | 10        | 15 | 16 | 20 | 25 | 32  | 40 | 50 | 63  |  |
| CDJ2                                       | 4 | 5         | -  | 5  | -  | -  | -   | -  | -  | -   |  |
| CDVJ3, 5                                   | - | 5         | -  | 5  | -  | -  | -   | -  | -  | -   |  |
| CDLJ2                                      | - | -         | -  | 5  | _  | -  | -   | —  | —  | -   |  |
| CDM2, CDBM2, CDVM3, 5<br>CDLM2, CDLG1, REC | - | -         | _  | _  | 5  | 5  | 5.5 | 6  | -  | _   |  |
| CDG1, MGG                                  | _ | _         | _  | _  | 5  | 5  | 5.5 | 6  | 7  | 7.5 |  |
| RSDG                                       | - | —         | —  | _  | —  | -  | -   | 6  | 7  | -   |  |
| MGC                                        | - | _         | _  | _  | 5  | 5  | 5.5 | 6  | 7  | -   |  |
| RHC, MLGC                                  | - | -         | -  | -  | 5  | 5  | 5.5 | 6  | -  | -   |  |

Note) Average value at normal temperature including hysteresis. (Tolerance  $\pm 30\%$ )



(mm)

# Water Resistant 2 Colour Indication Style Solid State Switch/Band Mounting **D-G5BAL**

#### Grommet

# Water (coolant) resistant performance



# **▲** Caution

#### Precautions

Consult SMC if using coolant liquid other than water based solution.

#### **Applicable Actuator Series**

| Series                                    | Bore size (mm)                                       |
|-------------------------------------------|------------------------------------------------------|
| CDG1, MGG                                 | ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100              |
| CDA1, CDBA1, CDV3, CDVS1, CDLA, CDL1, CNA | ø40 <sup>*</sup> , ø50 <sup>*</sup> , ø63, ø80, ø100 |
| MGC                                       | ø20, ø25, ø32, ø40, ø50                              |
| RHC, MLGC, REC                            | ø20, ø25, ø32, ø40                                   |
| CE2                                       | ø40, ø50, ø63, ø80, ø100                             |

\* Can not be used for lube type.


# Specifications

PLC: Programmable Logic Controller

(mm)

| D-G5BAL (With indicator light) |                                                                                                   |  |  |  |  |  |  |  |
|--------------------------------|---------------------------------------------------------------------------------------------------|--|--|--|--|--|--|--|
| Auto switch model number       | D-G5BAL                                                                                           |  |  |  |  |  |  |  |
| Wiring                         | 2 wire                                                                                            |  |  |  |  |  |  |  |
| Output                         | -                                                                                                 |  |  |  |  |  |  |  |
| Application                    | 24V DC Relay/PLC                                                                                  |  |  |  |  |  |  |  |
| Power voltage                  | -                                                                                                 |  |  |  |  |  |  |  |
| Current consumption            | -                                                                                                 |  |  |  |  |  |  |  |
| Load voltage                   | 24V DC (10 to 28V DC)                                                                             |  |  |  |  |  |  |  |
| Load current                   | ≤ 5 to 40mA                                                                                       |  |  |  |  |  |  |  |
| Internal voltage drop          | ≤ 4V                                                                                              |  |  |  |  |  |  |  |
| Current leakage                | ≤ 0.8mA at 24V DC                                                                                 |  |  |  |  |  |  |  |
| Indicator light                | Operating point: Red light emitting diode<br>Suitable operating point: Green light emitting diode |  |  |  |  |  |  |  |


**Internal Circuit** 



•Lead wire — Oilproof vinyl heavy insulation cable, ø4, 0.3mm<sup>2</sup>, 2 cores (Brown, Blue), 3m (Standard) Note 1) Refer to common specifications on p.6-18.

Note 2) Refer to p.6-18 for lead wire length.

## Dimensions



## **Operation Range (***t* **Dimension)**

| Actuator series                           |   | Bore size |     |    |    |     |     |     |  |  |  |
|-------------------------------------------|---|-----------|-----|----|----|-----|-----|-----|--|--|--|
|                                           |   | 25        | 32  | 40 | 50 | 63  | 80  | 100 |  |  |  |
| CDG1, MGG                                 | 5 | 5         | 5.5 | 6  | 7  | 7.5 | 7.5 | 8   |  |  |  |
| CDA1, CDBA1, CDV3, CDVS1, CDLA, CDL1, CNA | — | -         | -   | 6  | 7  | 7.5 | 7.5 | 8   |  |  |  |
| MGC                                       | 5 | 5         | 5.5 | 6  | 7  | -   | -   | —   |  |  |  |
| RHC, MLGC, REC                            | 5 | 5         | 5.5 | 6  | _  | -   | -   | _   |  |  |  |
| CE2                                       | - | -         | -   | 6  | 7  | 7.5 | 7.5 | 8   |  |  |  |

Note) Average value at normal temperature including hysteresis.(Tolerance ±30%)



# Water Resistant 2 Colour Indication Style Solid State Switch/Rail Mounting **D-F7BAL**

### Grommet

# Water (coolant) resistant performance



# **▲** Caution

#### Precautions

Consult SMC if using coolant liquid other than water based solution.


# **Applicable Actuator Series**

| Series         | Bore size (mm)                                                                    |
|----------------|-----------------------------------------------------------------------------------|
| CDJ2, CDVJ3, 5 | ø10, ø16                                                                          |
| CDQ2           | ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160               |
| CD□XW          | Plate mounted(P), ø10, ø16, ø20, ø25, ø32, Husuing mounted(B), ø16, ø20, ø25, ø32 |
| CDY1S, CY1L    | ø6, ø10, ø15, ø20, ø25, ø32, ø40                                                  |
| RSDQ           | ø20, ø25, ø32, ø40, ø50                                                           |
| MDU            | ø25, ø32, ø40, ø50, ø63                                                           |
| CE1            | ø12, ø20, ø32, ø40, ø50, ø63                                                      |
| МК, МК2        | ø20, ø25, ø32, ø40, ø50, ø63                                                      |
| СХТ            | ø32, ø40                                                                          |
|                |                                                                                   |


| Specifications           | PLC: Programmable Logic Controller                                                                |
|--------------------------|---------------------------------------------------------------------------------------------------|
| D-F7BAL (With indica     | tor light)                                                                                        |
| Auto switch model number | D-F7BAL                                                                                           |
| Wiring                   | 2 wire                                                                                            |
| Output                   | _                                                                                                 |
| Application              | 24V DC Relay/PLC                                                                                  |
| Power voltage            | _                                                                                                 |
| Current consumption      | -                                                                                                 |
| Load voltage             | 24V DC (10 to 28V DC)                                                                             |
| Load current             | ≤ 5 to 40mA                                                                                       |
| Internal voltage drop    | ≤ 4V                                                                                              |
| Current leakage          | ≤ 0.8mA at 24V DC                                                                                 |
| Indicator light          | Operating point: Red light emitting diode<br>Suitable operating point: Green light emitting diode |

●Lead wire —— Oilproof vinyl heavy insulation cable, ø4, 0.3mm<sup>2</sup>, 2 cores (Brown, Blue), 3m (Standard) Note 1) Refer to common specifications on p.6-18. Note 2) Refer to p.6-18 for lead wire length.

# **Internal Circuit**



## Dimensions



| СХТ     | — | - | -   | _ | - | -   | -   | 6 | 6   | —   | -   | — | - | - |
|---------|---|---|-----|---|---|-----|-----|---|-----|-----|-----|---|---|---|
| MK, MK2 | - | - | -   | — | - | 5.5 | 5   | 6 | 6   | 6   | 6.5 | — | - | - |
| CE1     | _ | - | 5.5 | _ | - | 5.5 | -   | 6 | 6   | 6   | 6.5 | — | - | - |
| MDU     | - | - | -   | - | - | -   | 6.5 | 7 | 6.5 | 6.5 | 6.5 | — | - | - |

5.5

6

6 6

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)



RSDQ

# Water Resistant 2 Colour Indication Style Solid State Switch/Tie-rod Mounting **D-F5BAL**

#### Grommet

Water (coolant) resistant performance



# **Caution**

**Internal Circuit** 

(

Standard

#### Precautions

): If not applicable for IEC

Consult SMC if using coolant liquid other than water based solution.

# **Applicable Actuator Series**

| Series                                 | Bore size (mm)                             |
|----------------------------------------|--------------------------------------------|
| CDA1, CDBA1, CDV3, CDVS1,<br>CDLA, CNA | ø40, ø50, ø63, ø80, ø100                   |
| CDL1                                   | ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160 |
| CDS1                                   | ø125, ø140, ø160, ø180, ø200               |
| CE2                                    | ø40, ø50, ø63, ø80, ø100                   |
| MDB                                    | ø32, ø40, ø63, ø80, ø100                   |

PLC: Programmable Logic Controller


# Specifications


| D-F5BAL (With indicator light) |                                                                                                   |  |  |  |  |  |  |  |  |
|--------------------------------|---------------------------------------------------------------------------------------------------|--|--|--|--|--|--|--|--|
| Auto switch model number       | D-F5BAL                                                                                           |  |  |  |  |  |  |  |  |
| Wiring                         | 2 wire                                                                                            |  |  |  |  |  |  |  |  |
| Output                         | _                                                                                                 |  |  |  |  |  |  |  |  |
| Application                    | 24V DC Relay/PLC                                                                                  |  |  |  |  |  |  |  |  |
| Power voltage                  | _                                                                                                 |  |  |  |  |  |  |  |  |
| Current consumption            | _                                                                                                 |  |  |  |  |  |  |  |  |
| Load voltage                   | 24V DC (10 to 28V DC)                                                                             |  |  |  |  |  |  |  |  |
| Load current                   | ≤ 5 to 40mA                                                                                       |  |  |  |  |  |  |  |  |
| Internal voltage drop          | ≤ 4V                                                                                              |  |  |  |  |  |  |  |  |
| Current leakage                | ≤ 0.8mA at 24V DC                                                                                 |  |  |  |  |  |  |  |  |
| Indicator light                | Operating point: Red light emitting diode<br>Suitable operating point: Green light emitting diode |  |  |  |  |  |  |  |  |

•Lead wire — Oilproof vinyl heavy insulation cable, ø4, 0.3mm<sup>2</sup>, 2 cores (Brown, Blue), 3m (Standard) Note 1) Refer to common specifications on p.6-18.

Note 2) Refer to p.6-18 for lead wire length.

# Dimensions






# **Operation Range (***t* **Dimension)**

| Actuator series                        |     | Bore size |    |     |     |     |     |     |     |     |     |  |  |
|----------------------------------------|-----|-----------|----|-----|-----|-----|-----|-----|-----|-----|-----|--|--|
|                                        |     | 40        | 50 | 63  | 80  | 100 | 125 | 140 | 160 | 180 | 200 |  |  |
| CDA1, CDBA1, CDV3, CDVS1,<br>CDLA, CNA | -   | 4         | 4  | 4.5 | 4.5 | 4.5 | I   | _   | _   | _   | _   |  |  |
| CDL1                                   | -   | 4         | 4  | 4.5 | 4.5 | 4.5 | 5   | 5   | 5.5 | —   | -   |  |  |
| CDS1                                   | —   | -         | -  | -   | -   | —   | 5   | 5   | 5.5 | 6   | 6   |  |  |
| CE2                                    | -   | 4         | 4  | 4.5 | 4.5 | 4.5 | _   | _   | -   | _   | -   |  |  |
| MDB                                    | 3.5 | 4         | 4  | 4.5 | 4.5 | 4.5 | -   | —   | —   | —   | -   |  |  |

Note) Average value at normal temperature including hysteresis. (Tolerance  $\pm 30\%$ )

# OUT(+) Brown(Red) Undicator light/Operation



(mm)

# Solid State Switch with Timer/Band Mounting **D-G5NTL**


#### Grommet

With built-in OFF-delay timer (200ms)



# Internal Circuit

( ): If not applicable for IEC Standard



# **Applicable Actuator Series**

| Series                         |                       | Bore size (mm)                          |  |  |  |  |
|--------------------------------|-----------------------|-----------------------------------------|--|--|--|--|
| CDM2, CDBM2, CDVM3, 5, CDL     | M2, CDLG1             | ø20, ø25, ø32, ø40                      |  |  |  |  |
| CDG1, MGG                      |                       | ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100 |  |  |  |  |
| CDA1, CDBA1, CDV3, CDVS1, CDLA | , CDL1, CNA           | ø40, ø50, ø63, ø80, ø100                |  |  |  |  |
| MGC                            |                       | ø20, ø25, ø32, ø40, ø50                 |  |  |  |  |
| RHC, MLGC, REC                 |                       | ø20, ø25, ø32, ø40                      |  |  |  |  |
| CE2                            |                       | ø40, ø50, ø63, ø80, ø100                |  |  |  |  |
| Specifications                 |                       | PLC: Programmable Logic Controller      |  |  |  |  |
| D-G5NTL (With indicator        | light)                |                                         |  |  |  |  |
| Auto switch model number       | D-G5NTL               |                                         |  |  |  |  |
| Wiring                         | 3 wire                |                                         |  |  |  |  |
| Output                         | NPN                   |                                         |  |  |  |  |
| Output operation               | Off-delay             |                                         |  |  |  |  |
| Operation time                 |                       | ≤ 1ms                                   |  |  |  |  |
| Off-delay time                 |                       | 200±50ms                                |  |  |  |  |
| Application                    |                       | IC circuit/Relay/PLC                    |  |  |  |  |
| Power voltage                  |                       | 5/12/24V DC (4.5 to 28V DC)             |  |  |  |  |
| Current consumption            | ≤ 10mA                |                                         |  |  |  |  |
| Load voltage                   | ≤ 28V DC              |                                         |  |  |  |  |
| Load current                   | ≤ 80mA                |                                         |  |  |  |  |
| Internal voltage drop          | ≤ 2V (≤ 0.8V at 10mA) |                                         |  |  |  |  |
| Current leakage                | ≤ 100 A at 24V DC     |                                         |  |  |  |  |
| Indicator light                |                       | ON: When red light emitting diode       |  |  |  |  |
|                                |                       |                                         |  |  |  |  |

 OLead wire —— Ollproof vinyl heavy insulation cable, ø4, 0.3mm<sup>2</sup>, 3 cores (Brown, Black, Blue), 3m (Standard) Note 1) Refer to common specifications on p.6-18.

Note 2) Refer to p.6-18 for lead wire length.

# **Timer Operation**

#### Detection of immediate positioning for high-speed cylinder Switch operating range(mm) ON OFF -/Cylinder speed(mm/s) Switch detecting Detecting point dispersion occurs due to response time of PLC (sequencer); e. g. scanning. time Ex.)Cylinder speed - 1000 mm/sec. ON(200ms) Sequencer response time - 0.1 sec. OFF Switch output ON Detecting point despersion - Within time 100mm ( = 1000mm/sec. X 0.1 sec.) Take PLC response time into consideration when using. PLC response time Dimensions ø4.5 mounting hole 6.5 14.3 Operation range (Refer to the table below.) Most sensitive position 14 11.2 3000 33 94 4 Indicator light **Operation Range (** *l* **Dimension)** (mm) Bore size Actuator series 20 25 32 40 50 63 80 100 CDM2, CDBM2, CDVM3, 5, CDLM2, CDLG1 4 4 4.5 5 CDG1, MGG 7 4 4 4.5 5 6 6.5 6.5 CDA1, CDBA1, CDV3, CDVS1, CDLA, CDL1, CNA 5 6 6.5 6.5 7 MGC 4 4 4.5 5 6 RHC, MLGC, REC 4 4 4.5 5 CE2 7 5 6 6.5 6.5

Note) Average value at normal temperature including hysteresis. (Tolerance  $\pm 30\%$ )



# Solid State Switch with Timer/Rail Mounting **D-F7NTL**


# Grommet

With built-in OFF-delay timer (200ms)



## **Internal Circuit**

( ): If not applicable for IEC



# **Applicable Actuator Series**

| Series         | Bore size (mm)                                                                    |
|----------------|-----------------------------------------------------------------------------------|
| CDJ2, CDVJ3, 5 | ø10, ø16                                                                          |
| CDQ2           | ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160               |
| CD□XW          | Plate mounted(P), ø10, ø16, ø20, ø25, ø32, Housing mounted(B), ø16, ø20, ø25, ø32 |
| CDY1S, CY1L    | ø6, ø10, ø15, ø20, ø25, ø32, ø40                                                  |
| RSDQ           | ø20, ø25, ø32, ø40, ø50                                                           |
| MDU            | ø25, ø32, ø40, ø50, ø63                                                           |
| CE1            | ø12, ø20, ø32, ø40, ø50, ø63                                                      |
| МК, МК2        | ø20, ø25, ø32, ø40, ø50, ø63                                                      |
| СХТ            | ø32, ø40                                                                          |

## Specifications

PLC: Programmable Logic Controller

(mm)

| D-F7NTL (With indicator light) |                                   |  |  |  |  |
|--------------------------------|-----------------------------------|--|--|--|--|
| Auto switch model number       | D-F7NTL                           |  |  |  |  |
| Wiring                         | 3 wire                            |  |  |  |  |
| Output                         | NPN                               |  |  |  |  |
| Output operation               | Off-delay                         |  |  |  |  |
| Operation time                 | ≤ 1ms                             |  |  |  |  |
| Off-delay time                 | 200±50ms                          |  |  |  |  |
| Application                    | IC circuit/Relay/PLC              |  |  |  |  |
| Power voltage                  | 5/12/24V DC (4.5 to 28V DC)       |  |  |  |  |
| Current consumption            | ≤ 10mA                            |  |  |  |  |
| Load voltage                   | ≤ 28V DC                          |  |  |  |  |
| Load current                   | ≤ 80mA                            |  |  |  |  |
| Internal voltage drop          | ≤ 1.5V (≤0.8V at 10mA)            |  |  |  |  |
| Current leakage                | ≤ 100μ A at 24V DC                |  |  |  |  |
| Indicator light                | ON: When red light emitting diode |  |  |  |  |


•Lead wire —— Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm<sup>2</sup>, 3 cores (Brown, Black, Blue), 3m (Standard) Note 1) Refer to common specifications on p.6-18.


Note 2) Refer to p.6-18 for lead wire length.

# **Timer Operation**

Detection of immediate positioning for high-speed cylinder ON Switch operating range(mm) Detecting point dispersion occurs due to response time of PLC (sequencer); Switch detecting OFF /Cylinder speed(mm/s) e.g. scanning. time Ex.) Cylinder speed-1000 mm/sec. ON(200ms) Switch output ON Sequencer response time-0.1 sec. OFF time Detecting point despersion-Within 100mm (=1000mm/sec. X 0.1sec.) PLC response time Take PLC response time into consideration when using.

# Dimensions





# Operation Range ( *l* Dimension)

| Actuator series       |       |                  | Bore size        |     |    |     |                      |             |                  |                    |                    |     |     |     |     |     |     |
|-----------------------|-------|------------------|------------------|-----|----|-----|----------------------|-------------|------------------|--------------------|--------------------|-----|-----|-----|-----|-----|-----|
| Actuator se           | nes   | 6                | 10               | 12  | 15 | 16  | 20                   | 25          | 32               | 40                 | 50                 | 63  | 80  | 100 | 125 | 140 | 160 |
| CDJ2, CDV             | J3, 5 | -                | 5                | -   | —  | 5   | -                    | -           | —                | -                  | -                  | -   | —   | -   | —   | —   | -   |
| CDQ2                  |       | _                | —                | 5.5 | -  | 6   | 5.5                  | 5           | 6                | 6                  | 6                  | 6.5 | 6.5 | 7   | 9   | 9   | 8.5 |
| CD                    | В     |                  | -                |     |    | 4   | 0.5                  | 3.5         | 4                |                    |                    |     |     |     |     |     |     |
|                       | Ρ     |                  | 3                |     |    | 2.5 | 3.5                  | 3.5         | 2.5              |                    | _                  |     |     |     |     | _   |     |
| CDY1S, CY             | /1L   | 3                | 3                | -   | 4  | -   | 3                    | 3           | 3                | 3.5                | —                  | -   | —   | -   | -   | —   | -   |
| RSDQ                  |       | -                | -                | -   | _  | -   | 5.5                  | -           | 6                | 6                  | 6                  | -   | _   | -   | Ι   | -   | -   |
| MDU                   |       | —                | —                | -   | —  | -   | —                    | 6.5         | 7                | 6.5                | 6.5                | 6.5 | —   | -   | —   | —   | -   |
| CE1                   |       | -                | -                | 5.5 | _  | -   | 5.5                  | -           | 6                | 6                  | 6                  | 6.5 | _   | -   | Ι   | -   | -   |
| MK, MK2               |       | _                | _                | -   | _  | -   | 5.5                  | 5           | 6                | 6                  | 6                  | 6.5 | _   | _   | _   | _   | _   |
| СХТ                   |       | _                | -                | -   | -  | -   | —                    | _           | 6                | 6                  | —                  | -   | _   | _   | —   | —   | _   |
| MDU<br>CE1<br>MK, MK2 |       | -<br>-<br>-<br>- | -<br>-<br>-<br>- | -   | -  |     | _<br>5.5<br>5.5<br>_ | _<br>5<br>_ | 7<br>6<br>6<br>6 | 6.5<br>6<br>6<br>6 | 6.5<br>6<br>6<br>– | 6.5 |     |     |     |     |     |

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)

# **SMC**


# Solid State Switch with Timer/Tie-rod Mounting **D-F5NTL**

# Grommet

With built-in OFF-delay timer (200ms)



**Internal Circuit** ): If not applicable for IEC Standard



# Applicable Actuator Series

| Series                                    | Bore size (mm)                                                           |  |  |
|-------------------------------------------|--------------------------------------------------------------------------|--|--|
|                                           |                                                                          |  |  |
| CDA1, CDBA1, CDV3, CDVS1,                 | ø40, ø50, ø63, ø80, ø100                                                 |  |  |
| CDLA, CNA                                 |                                                                          |  |  |
| CDL1                                      | ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160                               |  |  |
| CDS1                                      | ø125, ø140, ø160, ø180, ø200                                             |  |  |
| CE2                                       | ø40, ø50, ø63, ø80, ø100                                                 |  |  |
| MDB                                       | ø32, ø40, ø63, ø80, ø100                                                 |  |  |
| Specifications                            | PLC: Programmable Logic Controller                                       |  |  |
| D-F5NTL (With indicator lig               | ght)                                                                     |  |  |
| Auto switch model number                  | D-F5NTL                                                                  |  |  |
| Wiring                                    | 3 wire                                                                   |  |  |
| Output                                    | NPN                                                                      |  |  |
| Output operation                          | Off-delay                                                                |  |  |
| Operation time                            | ≤ 1ms                                                                    |  |  |
| Off-delay time                            | 200±50ms                                                                 |  |  |
| Application                               | IC circuit/Relay/PLC                                                     |  |  |
| Power voltage                             | 5/12/24V DC (4.5 to 28V DC)                                              |  |  |
| Current consumption                       | ≤ 10mA                                                                   |  |  |
| Load voltage                              | ≤ 28V DC                                                                 |  |  |
| Load current                              | ≤ 80mA                                                                   |  |  |
| Internal voltage drop                     | ≤ 1.5V (≤ 0.8V at 10mA)                                                  |  |  |
| Current leakage                           | ≤ 100 A at 24V DC                                                        |  |  |
| Indicator light                           | ON: When red light emitting diode                                        |  |  |
| l oad wire Oilproof vipyl boavy insulatio | in cable @4_0.3mm <sup>2</sup> _3.cores (Brown Black Blue)_3m (Standard) |  |  |

I ead wire Oilproof vinyl heavy insulation cable, ø4, 0.3mm<sup>2</sup>, 3 cores (Brown, Black, Blue), 3m (Standard) Note 1) Refer to common specifications on p.6-18.


Note 2) Refer to p.6-18 for lead wire length.

# **Timer Operation**


Detection of immediate positioning for high-speed cylinder

Detecting point dispersion occurs due to response time of PLC (sequencer); e.g. scanning.

- Ex.) Cylinder speed-1000 mm/sec. Sequencer response time-0.1 sec. Detecting point despersion-Within
- 100mm (=1000mm/sec. X 0.1sec.) Take PLC response time into consideration when using.



Dimensions



| (mr                                    |           |    |    |     |     | (mm) |     |     |     |     |     |
|----------------------------------------|-----------|----|----|-----|-----|------|-----|-----|-----|-----|-----|
| Actuator series                        | Bore size |    |    |     |     |      |     |     |     |     |     |
| Actuator series                        | 32        | 40 | 50 | 63  | 80  | 100  | 125 | 140 | 160 | 180 | 200 |
| CDA1, CDBA1, CDV3, CDVS1,<br>CDLA, CNA | -         | 4  | 4  | 4.5 | 4.5 | 4.5  | _   | _   | _   | _   | _   |
| CDL1                                   | -         | 4  | 4  | 4.5 | 4.5 | 4.5  | 5   | 5   | 5.5 | -   | -   |
| CDS1                                   | —         | —  | —  | -   | -   | —    | 5   | 5   | 5.5 | 6   | 6   |
| CE2                                    | -         | 4  | 4  | 4.5 | 4.5 | 4.5  | _   | _   | -   | -   | -   |
| MDB                                    | 3.5       | 4  | 4  | 4.5 | 4.5 | 4.5  | -   | -   | -   | -   | -   |

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)

**SMC** 

# Solid State Switch with Timer/Direct Mounting D-M5NTL/D-M5PTL

## Grommet

With built-in OFF-delay timer (200ms)



# **Applicable Actuator Series**

| Series | Bore size (mm) |
|--------|----------------|
| MYC    | ø25, ø32, ø40  |
| МҮН    | ø25, ø32, ø40  |
| ML1    | ø25, ø32, ø40  |

### Specifications


PLC: Programmable Logic Controller

| D-M5⊡TL (With indicator light)                                                                                         |                                   |         |  |  |  |  |
|------------------------------------------------------------------------------------------------------------------------|-----------------------------------|---------|--|--|--|--|
| Auto switch model number                                                                                               | D-M5NTL                           | D-M5PTL |  |  |  |  |
| Wiring                                                                                                                 | 3 \                               | vire    |  |  |  |  |
| Output                                                                                                                 | NPN                               | PNP     |  |  |  |  |
| Output operation                                                                                                       | Off-                              | delay   |  |  |  |  |
| Operation time                                                                                                         | s                                 | lms     |  |  |  |  |
| Off-delay time                                                                                                         | 200±50ms                          |         |  |  |  |  |
| Application                                                                                                            | IC circuit/Relay/PLC              |         |  |  |  |  |
| Power voltage                                                                                                          | 5/12/24V DC (4.5 to 28V DC)       |         |  |  |  |  |
| Current consumption                                                                                                    | ≤ 10mA                            | ≤ 12mA  |  |  |  |  |
| Load voltage                                                                                                           | ≤ 28V DC                          | -       |  |  |  |  |
| Load current                                                                                                           | ≤ 80mA                            |         |  |  |  |  |
| later a la colta da aluara                                                                                             | ≤ 2V                              | 0.01/   |  |  |  |  |
| Internal voltage drop                                                                                                  | (≤ 0.8V at 10mA load current)     | ≤ 0.8V  |  |  |  |  |
| Current leakage                                                                                                        | 100 A or less at 24V DC           |         |  |  |  |  |
| Indicator light                                                                                                        | ON: When red light emitting diode |         |  |  |  |  |
| el and wire Oilevent visual house inculation apple, 50.4,00mm <sup>2</sup> ,0 anno (Drawn, Plank, Plue), 2m (Standard) |                                   |         |  |  |  |  |


Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm<sup>2</sup>, 3 cores (Brown, Black, Blue), 3m (Standard) Lead wire


Note 1) Refer to common specifications on the p.6-18. Note 2) Refer to the p.6-18 for lead wire length


# **Timer Operation**



## (): If not applicable for IEC Standard







# **Operation Range (** *l* **Dimension)**

| Operation Range ( <i>l</i> Dimension) (m |    |           |  |  |  |  |
|------------------------------------------|----|-----------|--|--|--|--|
| Bore size                                |    |           |  |  |  |  |
| 25                                       | 32 | 40        |  |  |  |  |
| 4                                        | 4  | 4         |  |  |  |  |
| 4                                        | 4  | 4         |  |  |  |  |
| 4                                        | 4  | 4         |  |  |  |  |
|                                          |    | Bore size |  |  |  |  |

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)



# Water Resistant 2 Colour Indication Style Solid State Switch/Direct Mounting

### Grommet

# Improved coolant-resistant performance




# **▲** Caution

## Precautions

Consult SMC if using coolant liquid other than water based solution.

# **Internal Circuit**



# **Applicable Actuator Series**


| Series    | Bore size (mm)                                    |  |  |  |  |
|-----------|---------------------------------------------------|--|--|--|--|
| CXS       | ø6, ø10, ø15, ø20, ø25, ø32                       |  |  |  |  |
| MGQ, MVGQ | ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100 |  |  |  |  |
| MGP       | ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100 |  |  |  |  |
| RSH       | ø20, ø32, ø50, ø63, ø80                           |  |  |  |  |
|           |                                                   |  |  |  |  |

#### Specifications PLC: Programmable Logic Controller D-Y7BAL (With indicator light) Auto switch model number D-Y7BAL Wiring 2 wire Application 24V DC Relay/PLC 24V DC (10 to 28V DC) Load voltage Load current ≤ 5 to 40mA Internal voltage drop ≤ 4V Current leakage ≤ 0.8mA at 24V DC Operating point: Red light emitting diode Indicator light Suitable operating point: Green light emitting diode

•Lead wire —— Oilproof vinyl heavy insulation cable, ø3.4, 0.15mm<sup>2</sup>, 2 cores (Brown, Blue), 3m (Standard) Note 1) Refer to common specifications on p.6-18. Note 2) Refer to p.6-18 for lead wire length.

Note 2) Refer to p.6-18 for lead wire length

# Dimensions



7.5

5.5 - 7.5 7.5 9 -

9

5

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)



\_

RSH

MGF

7.5

# Strong Magnetic Field Resistant 2 Colours Indication Style Solid State Switch/Rail Mounting D-P5DWL

# Grommet

Possible to use in an environment where disturbance magnetic field is generated.



# ∧ Caution

#### Precautions

Monophase current welding. Not applicable for DC inverter welding, arc welding nor capacitor welding.

# **Applicable Actuator Series**

| Series       | Bore size(mm)            |  |  |  |
|--------------|--------------------------|--|--|--|
| CDQ2         | ø40, ø50, ø63, ø80, ø100 |  |  |  |
| CDA1         | ø40, ø50, ø63, ø80, ø100 |  |  |  |
| MK, MK2, MDU | ø40, ø50, ø63            |  |  |  |

# **Specifications**


| Specifications                | PLC: Programmable Logic Controller                                                                |  |  |  |  |  |
|-------------------------------|---------------------------------------------------------------------------------------------------|--|--|--|--|--|
| D-P5DW (With indicator light) |                                                                                                   |  |  |  |  |  |
| Auto switch model number      | D-P5DWL                                                                                           |  |  |  |  |  |
| Wiring                        | 2 wire (Non-polar)                                                                                |  |  |  |  |  |
| Application                   | 24V DC Relay/PLC                                                                                  |  |  |  |  |  |
| Load voltage                  | 24V DC (20 to 28V DC)                                                                             |  |  |  |  |  |
| Load current                  | 6 to 40mA                                                                                         |  |  |  |  |  |
| Internal voltage drop         | ≤ 5V                                                                                              |  |  |  |  |  |
| Current leakage               | ≤ 1mA at 24V DC                                                                                   |  |  |  |  |  |
| Operation time                | ≤ 40ms                                                                                            |  |  |  |  |  |
| Indicator light               | Operating point: Red light emitting diode<br>Suitable operating point: Green light emitting diode |  |  |  |  |  |

Lead wire Oilproof vinyl heavy insulation cable, ø6, 0.5mm<sup>2</sup>, 2 cores (Brown, Blue), 3m Note 1) Refer to common specifications on p.6-18. Note 2) Refer to p.6-18 for lead wire length.


# **Strong Magnetic Field Resistance**

It is possible to use switches next to welding conductor (gun cable) in case that A. C. welding current is ≤ 16,000A. Consult SMC if exceeding 16,000A.

# **Internal Circuit**



## Dimensions



Ø6

(mm)

4

# **Operation Range(** *t* **Dimension)**

| • • • •         |    |    | Bore size |    |     |
|-----------------|----|----|-----------|----|-----|
| Actuator series | 40 | 50 | 63        | 80 | 100 |
| CDQ2            | 5  | 5  | 5         | 5  | 5.5 |
| CDA1            | 4  | 4  | 4.5       | 4  | 4.5 |
| MDL             | 5  | 5  | 5         | —  | _   |
| MK, MK2         | 5  | 5  | 5         | —  | _   |

32





# 2 Colour Indication Style with Diagnostic Output Solid State Switch/Tie-rod Mounting **D-F5LF (Latching Style)**

### Grommet

The output signal can be detected in an unsteady detecting area.




### **Applicable Actuator Series**

| Series                                          | Bore size(mm)                                                                                                                                                       |
|-------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| CDA1, CDBA1, CDV3, CDVS1,<br>CDLA, CNA          | ø40, ø50, ø63, ø80, ø100                                                                                                                                            |
| CDL1                                            | ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160                                                                                                                          |
| CDS1                                            | ø125, ø140, ø160, ø180, ø200                                                                                                                                        |
| CE2                                             | ø40, ø50, ø63, ø80, ø100                                                                                                                                            |
| MDB                                             | ø32, ø40, ø63, ø80, ø100                                                                                                                                            |
| Specifications<br>D-F5LF (With indicator light) | PLC: Programmable Logic Controller                                                                                                                                  |
| Auto switch model number                        | D-F5LF                                                                                                                                                              |
| Wiring                                          | 4 wire                                                                                                                                                              |
| Output                                          | NPN                                                                                                                                                                 |
| Diagnostic output                               | Latching operation                                                                                                                                                  |
| Application                                     | 24V DC Relay/PLC                                                                                                                                                    |
| Power voltage                                   | 24V DC (10 to 26V DC)                                                                                                                                               |
| Current consumption                             | 20mA                                                                                                                                                                |
| Load voltage                                    | ≤ 26V DC                                                                                                                                                            |
| Load current                                    | ≤ 40mA                                                                                                                                                              |
| Internal voltage drop                           | ≤ 0.8V                                                                                                                                                              |
| Current leakage                                 | ≤ 100 A at 24V DC                                                                                                                                                   |
| Indicator light                                 | Operating point: Red light emitting diode<br>Suitable operating point: Green light emitting diode<br>Orange colour indicator lights on when diagnostic output is ON |


•Lead wire —— Oilproof vinyl heavy insulation cable, ø4, 0.2mm<sup>2</sup>, 4 cores (Brown, Black, Orange, Blue), 0.5m Note 1) Refer to common specifications on p.6-18. Note 2) Refer to p.6-18 for lead wire length.

# **Diagnostic Output Operation (Latching Style)**


The diagnostic signal is output when detecting position remains within unsteady area (where indicator light is Red.) for more than 0.5 sec. This signal keeps outputting even after normal output goes to OFF. The diagnostic output becomes OFF when detecting position remains within the most suitable operating range (where indicator light is Green.) for more than 0.5 sec.



#### **Internal Circuit**



#### **Dimensions**



# Operation Range ( *l* Dimension)

| Actuator series                        |    |     |     |     |     | Bore | size |     |     |     |     |
|----------------------------------------|----|-----|-----|-----|-----|------|------|-----|-----|-----|-----|
| Actuator series                        | 32 | 40  | 50  | 63  | 80  | 100  | 125  | 140 | 160 | 180 | 200 |
| CDA1, CDBA1, CDV3,<br>CDVS1, CDLA, CNA | -  | 5.5 | 5   | 5.5 | 5.5 | 5.5  | _    | _   | _   | _   | _   |
| CDL1                                   | -  | 5.5 | 5   | 5.5 | 5.5 | 5.5  | 5.5  | 6   | 6.5 | —   | -   |
| CDS1                                   | —  | —   | —   | —   | —   | -    | 5.5  | 6   | 6.5 | 7   | 7   |
| CE2                                    | -  | 5.5 | 5   | 5.5 | 5.5 | 5.5  | -    | -   | -   | -   | -   |
| MDB                                    | 5  | 5.5 | 5.5 | 6   | 6   | 6    | -    | -   | -   | _   | -   |

Note) Average value at normal temperature including hysteresis. (Tolerance  $\pm 30\%$ )



(mm)



# Water Resistant 2 Colour Indication Style Solid State Switch/Direct Mounting **D-M9BAL**

# Grommet

# Water (coolant) resistant performance




# ▲ Caution

#### Precautions

Consult SMC if using coolant liquid other than water based solution.

## **Internal Circuit**

( ): If not applicable for IEC Standard



#### **Applicable Actuator Series**

| Series | Bore size (mm)                |
|--------|-------------------------------|
| CDU    | ø6, ø10, ø16, ø20, ø25, ø32   |
| CDQ2*  | ø32, ø40, ø50, ø63, ø80, ø100 |
| CDQS   | ø12, ø16, ø20, ø25            |
| МК     | ø12, ø16                      |
| MK2    | ø32, ø40, ø50, ø63            |


\*Not available for series CDQP2

#### Specifications PLC: Programmable Logic Controller D-M9BAL (With indicator light) Auto switch model number D-M9BAL Wiring 2 wire Output Application 24V DC Relay/PLC Power voltage \_ Current consumption Load voltage 24V DC (20 to 28V DC) Load current 5 to 30mA Internal voltage drop ≤ 5V Current leakage ≤ 1mA at 24V DC Operating point: Red light emitting diode Indicator light Suitable operating point: Green light emitting diode

•Lead wire —— Oilproof vinyl heavy insulation cable, ø2.7, 2 cores (Brown, Blue), 0.18mm<sup>2</sup>, 0.5m Note 1) Refer to common specifications on p.6-18.

Note 2) Refer to p.6-18 for lead wire length.

#### Dimensions



# **Operation Range (** *l* **Dimension)**

| (mi | m |
|-----|---|
|     |   |

| Actuator series           |   |   |     |    |    | B   | ore si | ze  |     |     |     |     |     |     |
|---------------------------|---|---|-----|----|----|-----|--------|-----|-----|-----|-----|-----|-----|-----|
| Actuator series           | 6 | 8 | 10  | 12 | 15 | 16  | 20     | 25  | 32  | 40  | 50  | 63  | 80  | 100 |
| CDU(Without shield plate) | 3 | - | 3.5 | _  | -  | 5.5 | 6.5    | 7   | 7   | -   | -   | —   | -   | _   |
| CDQ2                      | _ | - | —   | _  | -  | —   | -      | _   | 5.5 | 5.5 | 5.5 | 6.5 | 5.5 | 6.5 |
| CDQS                      | - | - | -   | 3  | -  | 4   | 5      | 5.5 | -   | -   | _   | _   | -   | _   |
| МК                        | _ | _ | —   | 3  | _  | 4   | _      | _   | _   | _   | —   | _   | -   | —   |
| MK2                       | - | — | —   | I  | —  | —   | —      | _   | 5.5 | 5.5 | 5.5 | 6.5 | -   | —   |

Note) Average value at normal temperature including hysteresis. (Tolerance  $\pm 30\%$ )



# **Solid State Switch with Prewired Connector**


• Eliminates harnessing work by using a cable with a pre-wired connector specification.

- Adopts global standardised connector (IEC947-5-2).
- IP67 construction



# How to Order

**Connector Specifications** 



L 3.0 m Note) L is available for the D-P4DW, D-M9N, D-M9P and D-M9B types

# Connector type

the D-P4DW type. Note 2) D-M9NL, D-M9PL and D-M9BL types are only available with M8-3 pin connector

| Connector type        | M8-3 pins                                                              | M8-4 pins              | M12-4 pins   |  |  |  |
|-----------------------|------------------------------------------------------------------------|------------------------|--------------|--|--|--|
| Pin arrangement       | 1<br>4<br>3                                                            | 1 2 3 4                |              |  |  |  |
| Conformed standard    | JIS C 4524, J                                                          | IS C 4525, IEC 947-5-2 | 2, NECA 0402 |  |  |  |
| Impact resistance     |                                                                        | 300 m/s <sup>2</sup>   |              |  |  |  |
| Enclosure             | IP67 (IEC60529 standard)                                               |                        |              |  |  |  |
| Insulation resistance | 100 $M\Omega$ or more (at 500 VDC measured via Megohmmeter)            |                        |              |  |  |  |
| Withstand voltage     | 1500 VAC for 1 minute (between contacts), Leakage current 1 mA or less |                        |              |  |  |  |

# **Applicable Auto Switches**

| Manualian        | Eurotian                 | Electrical                 | A such a state such as a state | Lead v | vire len | gth (m) |
|------------------|--------------------------|----------------------------|--------------------------------|--------|----------|---------|
| Mounting         | Function                 | entry                      | Applicable model               | 0.5    | 1.0      | 3.0     |
|                  |                          | Grommet (In-line)          | F79, F7P, J79                  | •      | •        | —       |
|                  | _                        | Grommet<br>(Perpendicular) | F7NV, F7PV, F7BV               | ٠      | ٠        | —       |
|                  | 2-colour                 | Grommet (In-line)          | F79W, F7PW, J79W               |        |          | —       |
| Rail             | indication               | Grommet<br>(Perpendicular) | F7NWV, F7BWV                   | ٠      | ٠        | —       |
| mounting         | With diagnostic output   | Grommet (In-line)          | F79F                           | ٠      | ٠        | —       |
| style            | Water resistant          |                            | F7BA                           | •      |          | —       |
|                  | water resistant          | Grommet<br>(Perpendicular) | F7BAV                          | ٠      | ٠        | —       |
|                  | With timer               |                            | F7NT                           | ٠      | •        | —       |
|                  | Magnetic field resistant |                            | P4DW                           | ٠      | ٠        | ٠       |
|                  |                          |                            | H7A1, H7A2, H7B                | ٠      | ٠        | —       |
|                  |                          |                            | G59, G5P, K59                  | ٠      | ٠        | —       |
|                  | 2-colour                 |                            | H7NW, H7PW, H7BW               | •      |          | —       |
| Band<br>mounting | indication               |                            | G59W, G5PW, K59W               | ٠      | ٠        | —       |
| style            | Diagnostic output        | Grommet (In-line)          | H7NF, G59F                     | •      | •        | —       |
|                  | Water resistant          |                            | H7BA, G5BA                     | ٠      | ٠        | —       |
|                  | With timer               |                            | G5NT                           | ٠      |          | —       |
|                  | Wide detection           |                            | G5NB                           | •      | •        | —       |
|                  | _                        |                            | F59, F5P, J59                  | ٠      | •        | -       |
| Tie-rod          | 2-colour indication      |                            | F59W, F5PW, J59W               | ٠      | ٠        | _       |
| mounting         | Diagnostic output        |                            | F59F                           |        | ٠        | _       |
| style            | Water resistant          |                            | F5BA                           | ٠      | •        | _       |
|                  | With timer               |                            | F5NT                           | ٠      | ٠        | _       |

| Mounting        | Function        | Electrical                 | Applicable model       | Lead v | vire lenç | gth (m) |
|-----------------|-----------------|----------------------------|------------------------|--------|-----------|---------|
| Mounting        | Function        | entry                      | Applicable model       | 0.5    | 1.0       | 3.0     |
|                 |                 | Grommet (In-line)          | Y59A, Y7P, Y59B        | •      | •         | —       |
|                 |                 | Grommet<br>(Perpendicular) | Y69A, Y7PV, Y69B       | ٠      |           | —       |
|                 |                 | Grommet (In-line)          | M9N, M9P, M9B          | ٠      | •         | ٠       |
|                 |                 | Grommet                    | M9NV, M9PV, M9BV       | ٠      | •         | —       |
|                 |                 | (Perpendicular)            | F8N, F8P, F8B          | ٠      | •         | —       |
|                 |                 | Grommet (In-line)          | F6N, F6P, F6B          | ٠      | ٠         | —       |
| Direct          | Normally        | Grommet (In-line) Y7G, Y7H |                        | ٠      |           | —       |
| mounting        | closed          |                            | F9G, F9H               | ٠      |           | —       |
| style           |                 | Grommet (In-line)          | Y7NW, Y7PW, Y7BW       | ٠      | •         | —       |
|                 | 2-colour        | Grommet<br>(Perpendicular) | Y7NWV, Y7PWV, Y7BWV    | ٠      | •         | —       |
|                 | indication      | Grommet (In-line)          | M9NW, M9PW, M9BW       |        | •         | —       |
|                 |                 | Grommet<br>(Perpendicular) | M9NWV, M9PWV, M9BWV    | ٠      |           | —       |
|                 |                 | Grommet (In-line)          | Y7BA                   | ٠      |           | —       |
|                 | Water resistant | . ,                        | M9NA, M9PA, M9BA       | ٠      | •         | —       |
|                 |                 | Grommet<br>(Perpendicular) | M9NAV, M9PAV, M9BAV    | ٠      | ٠         | _       |
| Deterry         |                 | Grommet (In-line)          | S791/2, S7P1/2, T791/2 | ٠      | ٠         | _       |
| Rotary actuator | —               | . ,                        | S991/2, S9P1/2, T991/2 |        |           | _       |
|                 |                 | Grommet<br>(Perpendicular) | S99V1/2, T99V1/2       |        |           | _       |

# Series **D**-



M8-3 pinos



M8-4 pin



M12–4 pin


# **Connector Pin Layout**

| 0                    |       | Lead wi | re colors |       | Connector number designations |                      |        |         |  |
|----------------------|-------|---------|-----------|-------|-------------------------------|----------------------|--------|---------|--|
| Sensor configuration | 1 pin | 2 pin   | 3 pin     | 4 pin | 1 pin                         | 2 pin                | 3 pin  | 4 pin   |  |
| DC 2 wire            | Brown | -       | -         | Blue  | OUT (+)                       | -                    | -      | OUT (–) |  |
| DC 2 wire non-polar  | -     | -       | Brown     | Blue  | -                             | -                    | OUT () | OUT()   |  |
| DC 3 wire            | Brown | -       | Blue      | Black | DC (+)                        | -                    | DC (–) | OUT     |  |
| DC 4 wire            | Brown | Orange  | Blue      | Black | DC (+)                        | Diagnostic<br>output | DC (-) | OUT     |  |

#### **Connector specifications**

| Connector type          | M8–3 pin                                                                | M8–4 pin             | M12–4 pin    |  |  |
|-------------------------|-------------------------------------------------------------------------|----------------------|--------------|--|--|
| Pin<br>arrangement      |                                                                         |                      |              |  |  |
| Applicable<br>standards | JIS C 4524, JI                                                          | S C 4525, IEC 947-5- | 2, NECA 0402 |  |  |
| Impact<br>resistance    |                                                                         | 300m/s² {30, 6G}     |              |  |  |
| Enclosure               | IF                                                                      | P67 (standard IEC52  | 9)           |  |  |
| Insulation resistance   | 100 $M\Omega$ or more (at 500 VDC measured via Megohmmeter)             |                      |              |  |  |
| Withstand voltage       | 1500VAC for 1 min. (between connectors),<br>leakage current 1mA or less |                      |              |  |  |

# Dimensions



# Matching (Female) Connector Cables

Since these are not supplied by SMC, refer to the table below for applicable examples. (Contact the respective manufacturers for catalogs or other details.)

| Connector size | Number of pins | Manufacturer              | Applicable series example |
|----------------|----------------|---------------------------|---------------------------|
|                | 0              | Phoenix Contact           | SAC-3P                    |
| M8             | 3              | Corrence Corporation      | M8-3D                     |
| INIO           |                | Conferce Corporation      | M8-4D                     |
|                |                | OMROM Corporation         | XS3                       |
|                |                | Phoenix Contact           | SAC-4P                    |
|                | 4              | Corrence Corporation      | VA-4D                     |
| M12            | 4              | OMROM Corporation         | XS2                       |
| 10112          |                | Azbil Corp.               | PA5-4I                    |
|                |                | Hirose Electric Co., Ltd. | HR24                      |
|                |                | DDK Ltd.                  | CM01-8DP4S                |

# Weight for Connector Type


| Part no.                               | Connector<br>type | Weight     |
|----------------------------------------|-------------------|------------|
| D-DDDAPC                               | M8-3 pins         | 4 g        |
| D-DDBPC                                | M8-4 pins         | 4 g        |
| D-DDDDDDDDDDDDDDDDDDDDDDDDDDDDDDDDDDDD | M12-4 pins        | About 11 g |



# Information ① Plug-in Connector Assembly/How to Use DIN Terminal

# Plug-in Connector Assembly

### D-A73C, D-A80C, D-J79C D-C73C, D-C80C, D-H7C



With the convex port of the connector, insert the connector into the auto switch into the sleeve. Screw the locking ring onto the switch. (Do not tighten with pliers.)

# How to Use DIN Terminal/D-A44/A44A/

#### A44C Connection

①Loosen the set screw and pull out the connector from the pin plug. ②Be sure to remove the set screw first and then insert a screw driver into a recessed groove under the terminal block to separate the terminal cover from the terminal block.

 $\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ensuremath{(3)}\xspace{\ens$ 


④In standard cases, crimp-style terminals are used to connect wires. Please select proper crimp-style terminals so that the wire can be properly connected to terminal fittings.

#### Method of connection



AC: Connect to terminal No.1 and No.2

DC: Connect (+) to No.1 terminal and (-) to No.2 terminal.



#### How to change position of electrical entry

After separating the terminal block from the terminal cover, change the position of the terminal cover to any desired direction (4 directions at every 90°) to change the position of electrical entry.

Caution

When taking in or out the connector pin to or from the pin plug, hold the connector as perpendicular as possible.

Applicable cable (heavy insulation cable) Applicable to cable O. D. of ø6.8 to ø11.5. Applicable crimp-style terminal


1.25Y-3L, 1.25-3.5S, 1.25-4M


# Information **2** How to Mount and Move the Auto Switch

# Mounting Bracket Band mounting

# ▲ <u>∧</u> Caution


①Tighten the screw under the specified torque when mounting auto switch.





## How to mount and move the auto switch

D-G5NTL



①Put a mounting band on the cylinder tube and set it at the auto switch mounting position.

②Put the mounting section of the auto switch between the band mounting holes, then adjust the position of mounting holes of switch to those of mounting band.
③Lightly thread the auto switch mounting screw through the mounting hole into the thread part of band fitting.

④After setting the whole body to the detecting position by sliding, tighten the mounting screw to secure the auto switch. (The tightening torque of M4 screw should be about 1 to 1.2Nm.)


⑤Modification of the detection position should be made in the condition of ③. Part No. of auto switch mounting bracket (including band and screw)

| Cylinder series        |            | Bore size (mm) |            |      |     |       |       |       |  |  |
|------------------------|------------|----------------|------------|------|-----|-------|-------|-------|--|--|
| Cylinder series        | 20         | 25             | 32         | 40   | 50  | 63    | 80    | 100   |  |  |
| CDM2, CDBM2            | BA2        | BA2            | BA2        | BA2  |     |       |       |       |  |  |
| CDVM3, 5, CDLM2        | -020       | -025           | -032       | -040 |     | _     |       | _     |  |  |
| CDG1, MGG              | <b>D</b> A | •              | <b>D</b> A |      | BA  | BA-06 | BA-08 | BA-10 |  |  |
| MGC                    | BA         | BA             | BA         |      | -05 | _     | _     | _     |  |  |
| CDLG1                  | -01        | -02            | -32        | BA   | _   | -     | _     | _     |  |  |
| CDA1, CDBA1, CDV3, CNA |            |                |            | -04  | BA  | BA    | BA    | BA    |  |  |
| CDVŚ, CDLA, CDL1, CE2  |            | _              |            |      | -05 | -06   | -08   | -10   |  |  |
| RHC, MLGC, REC         | BA-<br>01  | BA-<br>02      | BA-<br>32  |      | -   | -     | -     | _     |  |  |

#### Mounting screw set (Stainless steel specification)

Use the following mounting screw set (Set screw included.) according to the required operating conditions. (Mounting band is not included.)

BBA3: For D-B5/B6/G5/K5 D-G5BAL is mounted on the cylinder with the above stainless steel screw BBA3 before shipment or BBA3 is enclosed with D-G5BAL when shipped without cylinder.



①For series CDJ2/Put a mounting bracket on the cylinder tube. For series CDM2/Put a mounting band on the cylinder tube and set it at the auto switch mounting position.

②Put the mounting part of auto switch in the interval of stationary fitting to fit the mounting hole to the hole of stationary fitting.

③Screw lightly the auto switch mounting screw through the mounting hole into the thread part of band fitting.

(4)After setting the whole body to the detecting position by sliding, tighten the mounting screw to secure the auto switch. (The tightening torque of M3 screw should be about 0.8 to 1Nm.)

 $\textcircled{5}\ensuremath{\mathsf{Modification}}$  of the detection position should be made in the condition of

| Part No. of auto switch mounting  | n bracket (includin | a band and screw) |
|-----------------------------------|---------------------|-------------------|
| I all No. Of auto Switch mounting | j bracket (includin | y band and Sciew) |

|                                |         |      | -  |             | •           |             | -           |              |              |              |
|--------------------------------|---------|------|----|-------------|-------------|-------------|-------------|--------------|--------------|--------------|
| Cylinder                       |         |      |    | В           | ore si      | ze (mr      | n)          |              |              |              |
| series                         | 6       | 10   | 15 | 16          | 20          | 25          | 32          | 40           | 50           | 63           |
| CDJ2                           | BJ2-006 | BJ2  | -  |             | -           | —           | -           | -            | -            | -            |
| CDVJ3, 5                       | -       | -010 | -  | BJ2<br>-016 | -           | -           | -           | -            | -            | -            |
| CDLJ2                          | -       | —    | —  | -010        | -           | —           | -           | -            | -            | -            |
| CDM2, CDBM2<br>CDVM3, 5, CDLM2 | -       | -    | -  | -           | BM2<br>-020 | BM2<br>-025 | BM2<br>-032 | BM2<br>-040  | -            | -            |
| CDG1, MGG                      | -       | -    | -  | -           |             |             |             |              | BMA2<br>-050 | BMA2<br>-063 |
| CDLG1                          | -       | -    | -  | -           | BMA2        | BMA2        | BMA2        |              | -            | -            |
| MGC                            | -       | _    | _  | _           | -020        | -025        | -032        | BMA2<br>-040 | BMA2<br>-050 | _            |
| RHC, MLGC, REC                 | -       | -    | -  | -           |             |             |             |              | -            | -            |
| RSDG                           | -       | -    | -  | -           | -           | —           | -           |              | BMA2<br>-050 | -            |

Mounting screw set (Stainless steel specification)

Use the following mounting screw set according to the required operating conditions. (Mounting band is not included.)

BBA4: For D-C7/C8/H7

D-H7BAL is mounted on the cylinder with the above stainless steel screw BBA4 before shipment or BBA4 is enclosed with D-H7BAL when shipped without cylinder.




# Information **2**

# How to Mount and Move the Auto Switch

#### Mounting Bracket Band mounting

<Applicable auto switch> Reed switch ...... D-A33, D-A34, D-A44 Solid state switch ..... D-G39, D-K39



 $\ensuremath{\mathbbm D}\xspace{-1.5}$  Loosen the auto switch mounting screws at both sides to pull down the hook.

②Put a mounting band on the cylinder tube and set it at the auto switch mounting position, and then hook the band.

③Screw lightly the auto switch mounting screw.


④Set the whole body to the detecting position by sliding, tighten the mounting screw to secure the auto switch. (The tightening torque should be about 2 to 3Nm.)

(5)Modification of the detecting position should be made in the condition of (3).

| Part No.   | of auto | switch  | mounting | ı band  |
|------------|---------|---------|----------|---------|
| 1 uit 110. | or uuto | 0000000 | mounting | , Nulla |

| i aitiit                                  | • • •       |    |    |             |       |       |             |      |     |      |     |             |             |  |  |
|-------------------------------------------|-------------|----|----|-------------|-------|-------|-------------|------|-----|------|-----|-------------|-------------|--|--|
| Cylinder                                  |             |    |    |             | l     | Bore  | size (      | (mm) |     |      |     |             |             |  |  |
| series                                    | 20          | 25 | 32 | 40          | 50    | 63    | 80          | 100  | 125 | 140  | 160 | 180         | 200         |  |  |
| CDA1, CDBA1, CDV3<br>CDVS, CDLA, CE2, CNA | _           | _  | _  | BD1<br>-04M |       |       | BD1<br>-08M |      | _   | _    | _   |             | _           |  |  |
| CDL1                                      |             |    |    | 0 1101      | 00111 | 00111 | 00111       |      | BS1 | BS1  | BQ1 | -           | _           |  |  |
| CDS1                                      | -           | _  | _  | -           | _     | _     | _           | _    |     | -140 |     | BS1<br>-180 | BS1<br>-200 |  |  |
| RHC                                       | BD1<br>-01M |    |    | BD1<br>-04M | _     | _     | _           | _    | _   | _    | _   |             | _           |  |  |

<Applicable auto switch> Reed switch ...... D-A33A, D-A34A, D-A44A Solid state switch ..... D-G39A, D-K39A



①Tighten completely the switch mounting screw on the switch body side. ②Put a mounting band on the cylinder tube and set it at the auto switch mounting position. Put the mounting section of auto switch between the interval of mounting band, then adjust the position of mounting holes of switch to those of mounting band.

 $\textcircled{3}\mbox{Lightly thread the auto switch mounting screw through the mounting hole into the thread part of band fitting.$ 

④After reconfirming the detecting position, tighten the mounting screw to secure the auto switch. (The tightening torque of M5 screw should be about 2 to 3Nm.)
⑤Modification of the detecting position should be made in the condition of ③.


#### Part No. of auto switch mounting bracket (including band and screw)

|                      | 0              | ,       | •       | ,       |  |  |  |  |
|----------------------|----------------|---------|---------|---------|--|--|--|--|
| Ordinadau aaniaa     | Bore size (mm) |         |         |         |  |  |  |  |
| Cylinder series      | 20             | 32      | 40      |         |  |  |  |  |
| CDM2, CDBM2<br>CDLM2 | BM3-020        | BM3-025 | BM3-032 | BM3-040 |  |  |  |  |

# Information **2**

How to Mount and Move the Auto Switch

Mounting Bracket Rail mounting



1 Slide the auto switch mounting nut inserted into the mounting rail and set it at the auto switch mounting position.

<sup>(2)</sup>Fit the convex part of auto switch mounting arm into the concave part of auto switch mounting rail. Then slide the switch over the nut.

(CDQ2 series: Fit the convex part of auto switch mounting arm through the auto switch spacer into the concave part of auto switch mounting rail.)

3 Push the auto switch mounting screw lightly into the mounting nut through the hole of auto switch mounting arm.

(4)After reconfirming detection position, tighten the mounting screw to secure the auto switch. (Tightening torque of M3 screw should be 0.5 to 0.7Nm.)

(5) Modification of the detecting position should be made in the condition of (3).

# Part No. of auto switch mounting bracket (including nut, screw and spacer)

| Culinder ceries | Bore size (mm) |      |      |          |             |             |          |          |      |      |      |      |      |
|-----------------|----------------|------|------|----------|-------------|-------------|----------|----------|------|------|------|------|------|
| Cylinder series | 12             | 16   | 20   | 25       | 25 32 40    | 40          | 50       | 63       | 80   | 100  | 125  | 140  | 160  |
| CDQ2            | BQ-1           | BQ-1 | BQ-1 | BQ-1     | BQ-2        | BQ-2        | BQ-2     | BQ-2     | BQ-2 | BQ-2 | BQ-2 | BQ-2 | BQ-2 |
| MDU             | -              | -    | -    | BMU1-025 | BMU1-025    | BMU1-025    | BMU1-025 | BMU1-025 | -    | -    | -    | -    | -    |
| RSDQ            | -              | -    |      | BQ-1     |             |             |          | -        | -    | -    | -    | -    | -    |
| MK, MK2         | -              | -    | BQ-1 | DQ-1     | <b>DO 0</b> | <b>DO 0</b> | BQ-2     |          | -    | —    | -    | -    | -    |
| CE1             | BQ-1           | -    |      | _        | BQ-2        | BQ-2        |          | BQ-2     | -    | -    | -    | _    | -    |
| СХТ             | -              | -    | -    | _        | ]           |             | -        | -        | _    | -    | -    | -    | -    |

Mounting screw set (Stainless steel specification)

Use the following mounting screw set (Nut included.) according to the required oper-

ating conditions. (Auto switch spacer is not included.)

BBA2: For D-A7/A8/F7/J7

D-F7BAL is mounted on the cylinder with the above stainless steel screw BBA2 before shipment of BBA2 is enclosed with D-F7BAL when shipped without cylinder.




# Information **2**

# How to Mount and Move the Auto Switch

# Mounting Bracket Tie-rod mounting

<Applicable auto switch> Reed switch ...... D-A53, D-A54, D-A56, D-A64, D-A67 D-A59W Solid state switch ..... D-F59, D-F5P D-J59, D-J51, D-F5BAL D-F59W, D-F5PW, D-J59W D-F59F, D-F5LF D-F5NTL

## How to mount and move the auto switch



TFix the auto switch on the auto switch mounting bracket with the mounting screw (M4) and install the set screw.

②Fit the mounting bracket into the cylinder tie-rod and then fix the auto switch at the detecting position with the hexagonal wrench. (Be sure to put the auto switch on the surface of cylinder tube.)

③When changing the detecting position, loosen the set screw to move the auto switch and then re-fix the auto switch on the cylinder tube. (Tightening torque of M4 screw should be 1 to 1.2 Nm.)

# Part No. of auto switch mounting bracket (including bracket, mounting screw and set screw)

| Cylinder                                  |       | Bore size (mm) |       |       |       |       |     |     |     |            |           |
|-------------------------------------------|-------|----------------|-------|-------|-------|-------|-----|-----|-----|------------|-----------|
| series                                    | 32    | 40             | 50    | 63    | 80    | 100   | 125 | 140 | 160 | 180        | 200       |
| CDA1, CDBA1, CDV3<br>CDVS, CDLA, CE2, CNA | -     | BT             | BT    | BT    | BT    | BT    | -   | -   | -   | -          | -         |
| CDL1                                      | -     | -04            | -04   | -06   | -08   | -08   | вт  | вт  | вт  | -          | -         |
| CDS1                                      | _     | _              | _     | _     | _     | _     | -12 | -12 | -16 | BT<br>-18A | BT<br>-20 |
| MDB/MDBB                                  | BT-03 | BT-03          | BT-05 | BT-05 | BT-06 | BT-06 | -   | -   | —   | —          | —         |

#### Mounting screw set (Stainless steel specification)


Use the following mounting screw set (Set screw included.) according to the required operating conditions. (Mounting bracket is not included.) BBA1: For D-A5/A6/F5/J5

BBA1: For D-A5/A6/F5/J5

D-F5BAL is mounted on the cylinder with the above stainless steel screw BBA1 before shipment or BBA1 is enclosed with D-F5BAL when shipped without cylinder.

#### <Applicable auto switch> Reed switch ...... D-A33C, D-A34C, D-A44C Solid state switch ..... D-G39C, D-K39C

#### How to mount and move the auto switch



①Fix the mounting bracket A on the auto switch with the set screw.
 ②Fit the convex part of mounting bracket into tie-rod and set the auto switch

at the mounting position.

③Insert the mounting bracket B from the underneath and put lightly in the tie-rod with the mounting screw.

ASet the whole body to the detecting position by sliding, tighten the mounting screw to secure the auto switch. (Tightening torque of M5 screw should be 2 to 3Nm.)

<sup>©</sup>Modification of the detecting position should be made in the condition of Part No. of auto switch mounting bracket (including bracket and screw)

| Culinder series            | Bore size (mm) |      |      |      |      |  |  |  |
|----------------------------|----------------|------|------|------|------|--|--|--|
| Cylinder series            | 40             | 50   | 63   | 80   | 100  |  |  |  |
| CDA1, CDBA1                | BA3            | BA3  | BA3  | BA3  | BA3  |  |  |  |
| CDV3, CDVS, CDL1, CE2, CNA | -040           | -050 | -063 | -080 | -100 |  |  |  |




# Information **2** How to Mount and Move the Auto Switch

# Mounting Bracket Direct mounting

#### <Applicable auto switch> Reed switch ..... D-90/97, D-90A/93A

# How to mount and move the auto switch




#### Part No. of auto switch mounting bracket (including bracket and screw)

| Cylinder |      | Bore size (mm) |      |      |      |      |      |  |  |
|----------|------|----------------|------|------|------|------|------|--|--|
| series   | 6    | 10             | 15   | 16   | 20   | 25   | 32   |  |  |
| CDJP-□D  | BP-1 | BP-1           | BP-1 | —    | —    | —    | —    |  |  |
| CDU      | BU-1 | BU-1           | —    | BU-1 | BU-1 | BU-1 | BU-1 |  |  |

# <Applicable auto switch>


# Reed switch D-A90(V)/A93(V)/A96(V) Solid state switch D-M9N(V)/M9P(V)/M9B(V)/M9NW(V)/ M9PW(V)/M9BW(V)/M9BAL

## How to mount and move the auto



<Applicable auto switch> Reed switch ...... D-E73A/E76A/E80A Solid state switch ..... D-M5N/M5P/M5B D-M5NW/M5PW/M5BW D-M5NTL/M5PTL

#### How to mount and move the auto switch



①Insert the auto switch mounting nut into the auto switch mounting groove and then set the switch at the mounting position by sliding. ②Put the convex part of auto switch into the mounting groove and slide it over the nut.

③Push the auto switch mounting screw lightly into the mounting nut through the mounting hole.

(4)After reconfirming detecting position, tighten the mounting screw to secure the auto switch. (Tightening torque of M2.5 screw should be 0.1 to 0.2Nm.)


#### Part No. of auto switch mounting bracket (including nut and screw)

|                 | 3              | · 5      | /        |  |  |  |  |
|-----------------|----------------|----------|----------|--|--|--|--|
| Cylinder        | Bore size (mm) |          |          |  |  |  |  |
| series          | 25             | 32       | 40       |  |  |  |  |
| ML1 M2.5 X 12 ℓ | BMY2-025       | BMY2-025 | BMY2-025 |  |  |  |  |
|                 |                |          |          |  |  |  |  |

#### <Applicable auto switch>

Reed switch ...... D-Z73/Z76/Z80 Solid state switch ..... D-Y59<sup>A</sup>/Y69<sup>A</sup>/D-Y7P(V) D-Y7NW(V)/Y7PW(V)/Y7BW(V) D-Y7BAL

#### How to mount and move the auto switch



]Insert the auto switch into the mounting groove and set it at the auto switch mounting position.

②After confirming the detecting position, tighten the mounting screw to secure the auto switch.

 $\textcircled{3}\label{eq:model}$  Modification of the detecting position should be made in step 1.


€SMC

# Information **2** How to Mount and Move the Auto Switch

Mounting Bracket Direct mounting

<Applicable auto switch> Solid state switch ..... D-P5DWL

# How to mount and move the auto switch



Mount the mounting bracket onto the mounting nut by tightening bracket fixing screw lightly through the mounting hole on the top of bracket.

(2) Insert the mounting bracket assembly (bracket+nut) into the mounting groove and set it at the auto switch mounting position.

③Push the auto switch mounting screw lightly into the auto switch through the mounting hole to secure.

(4)After reconfirming detection position, tighten the mounting screw to secure the auto switch. (Tightening torque should be 0.5 to 0.7Nm.)

#### Part No. of auto switch mounting bracket (including bracket and screw)

| Culinder corico | Bore size (mm) |          |          |  |  |
|-----------------|----------------|----------|----------|--|--|
| Cylinder series | 40             | 50       | 63       |  |  |
| MK, MK2         | BQP1-050       | BQP1-050 | BQP1-050 |  |  |

# Auto Switch Weight (Single Unit)

(g)

# **Band mounting**

| Applicable            |                  |        |                  | (y) |      |  |
|-----------------------|------------------|--------|------------------|-----|------|--|
| auto                  | Model            |        | Lead wire length |     |      |  |
| switch                |                  |        | 0.5m             | 3m  | None |  |
| -<br>Reed switch      | D-C7<br>D-C8     | 2 wire | 9                | 46  | _    |  |
|                       |                  | 3 wire | 10               | 50  |      |  |
|                       | D-C73C<br>D-C80C |        | 14               | 53  | _    |  |
|                       | D-B5<br>D-B6     |        | 22               | 78  | _    |  |
|                       | D-B59W           |        | 20               | 76  | —    |  |
|                       | D-A3             |        | _                |     | 116  |  |
|                       | D-A4             |        | _                |     | 114  |  |
|                       | D-A3⊡A<br>D-A44A |        | _                | _   | 110  |  |
| Solid state<br>switch |                  | 2 wire | 11               | 50  | —    |  |
|                       | D-H7             | 3 wire | 13               | 57  | _    |  |
|                       |                  | 4 wire | 13               | 56  | _    |  |
|                       | D-K5             | 2 wire | 18               | 68  | _    |  |
|                       | D-G5             | 3 wire | 20               | 78  | _    |  |
|                       |                  | 4 wire | 20               | 74  | _    |  |
|                       | D-□39            |        | -                | _   | 116  |  |
|                       | D-□39A           |        | _                | _   | 110  |  |
|                       | D-H7C            |        | 15               | 54  |      |  |

# **Tie-rod mounting**

| Tie-rod               | mounting     |        |                  |    | (g)  |
|-----------------------|--------------|--------|------------------|----|------|
| Applicable<br>auto    | Model        |        | Lead wire length |    |      |
| switch                |              |        | 0.5m             | 3m | None |
|                       | D-A5<br>D-A6 | 2 wire | 24               | 80 |      |
|                       |              | 3 wire | 24               | 80 |      |
|                       | D-A59W       |        | 25               | 80 | _    |
|                       | D-A3⊟C       | ø40    | —                |    | 162  |
|                       |              | ø50    | —                | -  | 166  |
|                       |              | ø63    | —                | -  | 184  |
| Reed switch           |              | ø80    | —                | _  | 210  |
|                       |              | ø100   | —                | -  | 232  |
|                       | D-A44C       | ø40    | _                | -  | 160  |
|                       |              | ø50    | _                | -  | 164  |
|                       |              | ø63    | —                | -  | 182  |
|                       |              | ø80    | —                |    | 208  |
|                       |              | ø100   | —                | _  | 230  |
| Solid state<br>switch | D-J5         | 2 wire | 21               | 71 | _    |
|                       | D-F5         | 3 wire | 23               | 81 | —    |
|                       |              | 4 wire | 22               | 77 | —    |

# **Rail mounting**

| Rail mounting (g)     |                  |        |                  |    |
|-----------------------|------------------|--------|------------------|----|
| Applicable<br>auto    | Model            |        | Lead wire length |    |
| switch                | Woder            | Model  |                  | 3m |
| Reed switch           |                  | 2 wire | 10               | 47 |
|                       |                  | 3 wire | 11               | 52 |
|                       | D-A73C<br>D-A80C |        | 12               | 54 |
|                       | D-A79W           |        | 11               | 53 |
| Solid state<br>switch | D-J7             | 2 wire | 11               | 50 |
|                       | D 57             | 3 wire | 13               | 57 |
|                       | D-F7             | 4 wire | 13               | 56 |
|                       | D-J79C           |        | 13               | 52 |

| Direct mounting (g) |                            |        |                  |    |    |
|---------------------|----------------------------|--------|------------------|----|----|
| Applicable<br>auto  | Model                      |        | Lead wire length |    |    |
| switch              |                            |        | 0.5m             | 3m |    |
|                     | D-A9/A9⊡V 2 wire<br>3 wire |        | 2 wire           | 7  | 35 |
|                     |                            |        | 8                | 41 |    |
|                     | D-9                        |        |                  | 5  | 23 |
| Reed switch         | D-9□A                      |        |                  | 9  | 47 |
| neeu switch         | D-E7⊡A<br>D-E8⊡A           |        | 2 wire           | 10 | 47 |
|                     |                            |        | 3 wire           | 11 | 55 |
|                     | D-Z7<br>D-Z8               |        | 2 wire           | 9  | 49 |
|                     |                            |        | 3 wire           | 10 | 55 |
|                     | D-Y□                       | 1      | 2 wire           | 9  | 50 |
|                     |                            | colour | 3 wire           | 10 | 53 |
|                     |                            | 2      | 2 wire           | 11 | 54 |
|                     |                            | colour | 3 wire           | 11 | 54 |
|                     | D-M5                       |        | 2 wire           | 14 | 53 |
| Solid state switch  |                            |        | 3 wire           | 16 | 60 |
| ownon               | D-Y7BA                     |        |                  | -  | 54 |
|                     | D-M9□                      | 1      | 2 wire           | 6  | 31 |
|                     |                            | colour | 3 wire           | 7  | 37 |
|                     |                            | 2      | 2 wire           | 7  | 32 |
|                     |                            | colour | 3 wire           | 7  | 34 |
|                     | D-M9BA                     |        |                  | -  | 37 |