



### **ABM13W SERIES**



1.20 x 1.00 x 0.33mm RoHS/RoHS II Complaint

MSL = N/A: Not Applicable

### **FEATURES**

- World's smallest At-Cut MHz Crystal (1.20 x 1.00 x 0.33 mm package)
- Ideally suited for space constraint IoT, Wearables & Wireless applications
- Simultaneously optimized for low plating load & ESR over extended temperature range
- Enhanced performance for start-up time and power savings with Low Energy SoC's
- Low profile ideal for height constraint designs
- Available with  $\pm 10$  ppm set-tolerance

### **APPLICATIONS**

- Wearables
- Wireless Modules
- Internet of Things (IoT)
- Bluetooth / Bluetooth Low Energy (BLE)
- Machine-to-Machine (M2M) Connectivity
- Ultra-Low Power MCU's, SoC's, Transceivers
- Near Field Communication
- ISM Band Applications

### **Electrical Specifications**

Parameters	Min.	Тур.	Max.	Units	Note	
Frequency Range	32.0000		80.0000	MHz		
Standard Available Frequencies	32.0000, 37.4000, 38.4000, 40.0000, 45.0000, 48.0000, 52.0000, 60.0000, 76.8000, 80.0000			MHz	Contact Abracon for Nonstandard Frequencies	
Operation Mode	Fundamental					
Operating Temperature Range	-40		+85	°C	See Options	
Storage Temperature	-40		+125	°C		
Frequency Tolerance @ +25°C	-10		+10	ppm	See options	
Frequency Stability over the Operating Temperature ( ref. to +25°C)	-15		+15	ppm	See options	
		< 45	100		32.0000-32.9999MHz	
Equivalent series resistance (R1) (over -40°C to +125°C)		< 35	80	Ω	33.0000-36.9999MHz	
		< 25	50		37.0000-80.0000MHz	
Shunt capacitance (C0)			1.0	pF		
Load capacitance (CL)		5.0		pF	See options	
Drive Level		10	100	μW		
Aging (1 year)	-2		+2	ppm	@25°C± 3°C	
Insulation Resistance	500			ΜΩ	@100 Vdc ± 15V	



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit:

www.abracon.com

ABRACON IS

ABRACON IS ISO9001-2015 CERTIFIED

**REVISED: 08.15.2018** 





### **ABM13W SERIES**




1.20 x 1.00 x 0.33mm

**RoHS/RoHS II Complaint** 

MSL = N/A: Not Applicable

**Options and Part Identification** [Note 1]



(\*) Only offered @ Operating Temp. Range options: B & N

 $Z: \pm 50 \text{ ppm}$ 

- (\*\*) Only offered @ Operating Temp. Range options: B, N, & D
- (\*\*\*) Only offered @ Operating Temp. Range options: B, N, D, & J
- Contact ABRACON for tighter Frequency Stability options.

### Note 1:

Contact Abracon for part number requests with carrier frequency callouts up to 5 & 6 digit accuracy after the decimal.



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISED: 08.15.2018** 






### **ABM13W SERIES**

Pb


1.20 x 1.00 x 0.33mm RoHS/RoHS II Complaint

MSL = N/A: Not Applicable

Typical Frequency vs. Temperature Characteristics (ref. to +25°C):



### Typical ESR (Equivalent Series Resistance) vs. Temperature Characteristics:





8069 58 Svicit: ABRACON IS ISO9001-2015 CERTIFIED

**REVISED: 08.15.2018** 






### **ABM13W SERIES**



1.20 x 1.00 x 0.33mm


RoHS/RoHS II Complaint
MSL = N/A: Not Applicable

### SPICE Models (based on typical values at $25^{\circ}C \pm 3^{\circ}C$ ):



Frequency: 32.0000MHz			Frequency: 38.4000MHz					
Plating Load: 8pF			Plating Load: 6pF					
C0	=	0.46	pF	C0	=	0.48	pF	
R1	=	41.19	Ω	R1	=	22.48	Ω	
L1	=	16.91	mH	L1	=	10.99	mH	
C1	=	1.46	fF	C1	=	1.57	fF	
	Frequency: 48.0000MHz				Frequency: 76.8000MHz			
Plating Load: 6pF			Plating Load: 6pF					
C0	=	0.86	pF	C0	=	0.77	pF	
R1	=	19.50	Ω	R1	=	16.97	Ω	
L1	=	5.73	mH	L1	=	1.58	mH	
C1	=	1.92	fF	C1	=	2.74	fF	

### Typical Frequency Tolerance Distribution (at $25^{\circ}C \pm 3^{\circ}C$ ):





5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com **REVISED: 08.15.2018** 






### **ABM13W SERIES**





1.20 x 1.00 x 0.33mm RoHS/RoHS II Complaint

MSL = N/A: Not Applicable

Typical ESR Distribution (at  $25^{\circ}C \pm 3^{\circ}C$ ):









5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com **REVISED: 08.15.2018** 





### **ABM13W SERIES**





1.20 x 1.00 x 0.33mm


**RoHS/RoHS II Complaint** 

MSL = N/A: Not Applicable

### **Mechanical Dimensions**







# Internal connection #4 #3 #4 #3 #4 #2

Pin #2: GND Pin #4: NC

### **Dimensions: mm**



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com **REVISED: 08.15.2018** 





## ABM13W SERIES




1.20 x 1.00 x 0.33mm

MSL = N/A: Not Applicable

**RoHS/RoHS II Complaint** 

### **Reflow Profile**



Zone	Description	Temperature	Time
1	Preheat / Soak	$\begin{array}{c} T_{_{SMIN}} \sim T_{_{SMAX}} \\ 160 \pm 10 ^{\circ}C \end{array}$	80 ~ 100 sec.
2	Reflow	${ m T_L}  m 220^{\circ}C$	50 ~ 70 sec.
3	Peak heat	${ m T_{_{ m P}}}$ $260{\pm}5^{\circ}{ m C}$	5 sec. MAX.



**REVISED: 08.15.2018** 





### **ABM13W SERIES**

Pb


1.20 x 1.00 x 0.33mm


MSL = N/A: Not Applicable


**RoHS/RoHS II Complaint** 

Packaging:

T5: Tape and reel (5,000pcs/reel)







**Dimensions: mm** 

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com **REVISED: 08.15.2018**