

# ES-FT-BPC-B/S 35-70 OG - Connector



1228829

<https://www.phoenixcontact.com/gb/products/1228829>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, Range of articles: BPC, color: orange, number of positions: 1, min. conductor cross section: 35 mm<sup>2</sup>, max. conductor cross section: 70 mm<sup>2</sup>, rated voltage: 1500, rated current: 250 A, Connection method: Screw/Solder connection, Contact connection type: Pin

## Your advantages

- Patented design, with 3 proofs and one rotation
- Safety lock
- 360° free rotation and flexible wiring
- Foolproof mechanism installed
- Touch-proof
- Mismatching and short circuit proof

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1228829       |
| Packing unit                         | 15 pc         |
| Minimum order quantity               | 15 pc         |
| Sales key                            | ABLDBA        |
| Product key                          | ABLDBA        |
| GTIN                                 | 4063151324667 |
| Weight per piece (including packing) | 65.9 g        |
| Weight per piece (excluding packing) | 55.65 g       |
| Country of origin                    | CN            |

## Technical data

### Notes

#### Safety note

##### Safety note

- **WARNING:** Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.
- **WARNING:** Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.
- WARNING:** The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.
- The products are suitable for applications in plant, controller, and electrical device engineering.
- Assembled products may not be manipulated or improperly opened.
- Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at [phoenixcontact.com/products](https://www.phoenixcontact.com/products)).
- When using the product in direct connection with third-party manufacturers, the user is responsible.
- For operating voltages > 50 V AC, conductive connector housings must be grounded
- Ensure that the protective or functional ground has been properly connected.
- Observe the corresponding technical data. You will find information:
  - o On the product
  - o On the packing label
  - o In the supplied documentation
  - o Online at [phoenixcontact.com/products](https://www.phoenixcontact.com/products) under the product
- The installation notes/Design In documents online on the download page at [phoenixcontact.com/products](https://www.phoenixcontact.com/products) must be observed for this product.
- Use a protective cap to protect connectors that are not in use. The suitable accessories are available online in the accessory section of the product at [phoenixcontact.com/products](https://www.phoenixcontact.com/products)
- The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).
- Operate the connector only when it is fully plugged in and interlocked.
- Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.

# ES-FT-BPC-B/S 35-70 OG - Connector



1228829

<https://www.phoenixcontact.com/gb/products/1228829>

- Observe the minimum bending radius of the cable. Lay the cable without twisting it.

## Product properties

|                     |                               |
|---------------------|-------------------------------|
| Product type        | Connectors for energy storage |
| Product family      | BPC                           |
| Number of positions | 1                             |

## Insulation characteristics

|                     |   |
|---------------------|---|
| Degree of pollution | 2 |
|---------------------|---|

## Electrical properties

|                                |                                                                                       |
|--------------------------------|---------------------------------------------------------------------------------------|
| Rated voltage (III/2)          | 1500 V DC                                                                             |
| Nominal voltage ATD            | 1500 (III/2.00)                                                                       |
|                                | 1000 (III/2.00) AC                                                                    |
| Rated surge voltage            | 12 kV                                                                                 |
| Rated current                  | 250 A (with 70 mm <sup>2</sup> conductor cross-section, in accordance with IEC 61984) |
|                                | 200 A (with 50 mm <sup>2</sup> conductor cross-section, in accordance with IEC 61984) |
|                                | 250 A (with AWG 2/0, in accordance with UL 4128)                                      |
| Contact resistance             | ≤ 0.5 mΩ                                                                              |
| Insulation resistance          | 1000 MΩ                                                                               |
| Nominal voltage U <sub>N</sub> | 1500 V                                                                                |

## Connection data

|                   |                         |
|-------------------|-------------------------|
| Connection method | Screw/Solder connection |
| Tightening torque | 0.6 ... 0.6 Nm          |

## Material specifications

|                                        |           |
|----------------------------------------|-----------|
| Color                                  | orange    |
| Material Housing                       | Polyamide |
| Material Contact                       | Copper    |
| Material Seal                          | Silicon   |
| Flammability rating according to UL 94 | V0        |
| Insulating material                    | PA        |
| Contact surface material               | Ni/Ag     |

## Cable/line

|                            |                                       |
|----------------------------|---------------------------------------|
| Single wire, cross section | 35 mm <sup>2</sup> 70 mm <sup>2</sup> |
|----------------------------|---------------------------------------|

## Mechanical properties

### Mechanical data

|                             |        |
|-----------------------------|--------|
| Insertion/withdrawal cycles | 100    |
| Insertion force             | ≤ 75 N |
| Withdrawal force            | ≥ 10 N |

# ES-FT-BPC-B/S 35-70 OG - Connector



1228829

<https://www.phoenixcontact.com/gb/products/1228829>

## Environmental and real-life conditions

### Ambient conditions

|                                         |                            |
|-----------------------------------------|----------------------------|
| Degree of protection (when plugged in)  | IP65 (With clearance hole) |
|                                         | IP65 (With clearance hole) |
| Degree of protection (not plugged in)   | IP20                       |
| Degree of protection                    | IP65/IP67                  |
| Ambient temperature (operation)         | -40 °C ... 80 °C           |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C           |
| Altitude                                | 4000 m                     |

## Standards and regulations

|                          |                |
|--------------------------|----------------|
| Standards/specifications | IEC 61984:2008 |
|                          | EN 61984:2008  |
|                          | UL 4128        |
|                          | PPP 51090A     |

# ES-FT-BPC-B/S 35-70 OG - Connector



1228829

<https://www.phoenixcontact.com/gb/products/1228829>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1228829>



### TÜV SÜD Type tested

Approval ID: 704071905102-03

|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | 1500 V                | 250 A                 | -                 | 50 - 70                     |



### UL Recognized

Approval ID: E511681-20200609

|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | 1500 V                | 250 A                 | 1/0 - 2/0         | -                           |

# ES-FT-BPC-B/S 35-70 OG - Connector



1228829

<https://www.phoenixcontact.com/gb/products/1228829>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27440390 |
| ECLASS-12.0 | 27440390 |
| ECLASS-13.0 | 27440312 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002641 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# ES-FT-BPC-B/S 35-70 OG - Connector



1228829

<https://www.phoenixcontact.com/gb/products/1228829>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)