



DYNATECH® torque wrenches for rectangular bits + clip

DYTC-350-0-FME

DYTC-...-0-FME

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 08:53:50





DESCRIPTION

DYNATECH® torque wrenches for rectangular bits + clip

Safety: To ensure your interventions are safe, to avoid dropping tools and wasting time, to prevent industrial accidents and improve productivity = Opt for the SAM anti-dropping solution. All the products in the FME range are equipped with a clip preventing you from dropping your tools.

Versatile, precise wrench for performing multiple interventions without having to change tool. Repeatability guaranteed to ensure the safety of your tightening operations. Ergonomic Handle that withstands hydrocarbons, solvents, brake fluid and paraffin. Efficient, comfortable grip for the operator, reducing risks of musculoskeletal disorders. Comfortable Scale in Nm with utilisation range going from 1 to 350 Nm, allowing you to have the right tool whatever the situation. Wrench supplied with a 3-point calibration certificate in a plastic case or in a box depending on the number of accessories. Precision Precision guaranteed to within +/- 3% for up to 5,000 cycles, i.e. 25% better than the requirements of standard ISO 6789 (except models with capacities of 1-5 Nm: +/- 6%). New spring withstanding 1,000,000-cycle fatigue tests at each wrench's max. torque value. Mark on the handle for perfect positioning of the contact point ensuring precise tightening. Each wrench is numbered and supplied with a verification report in compliance with standard NF EN ISO 6789-1. Mechanical click-type torque wrench. Type II - Class A.

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>



STANDARDS / DIRECTIVES

NF ISO 3315, NF ISO 6789-1

SPECIFIC DATA

Designation	DYNATECH WRENCH 350 RECTANGULAR BITS WITH FME CLIP
Sales reference	DYTC-350-0-FME
Weight (kg)	1.760
Container	Tube
Capacity (Nm)	70-350
Ratchet	-
double square	-
Graduation (Nm)	1
Ends	14x18
only wrench length	543
Length with ratchet (mm)	-
Ratchet reference	-
Dimensions containing (mm)	565 x 45 x 45
Guarantee	M

Guarantee applied

M1 | SAM Equipment and Machine Guarantee:

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

SAM Outillage

10 rue Camille de RochetaillÃ©e
 42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>



[>> Find out more](#)

Toolset

	x 1	DYNATECH® torque wrenches with removable ends DYTC-...-0
	x 1	Set of 5 locking-clips for FME tool holder CLIP-25-FME

FME (FOREIGN MATERIAL EXCLUSION)

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 08:53:50

