




SINGLE ROW



DOUBLE ROW



ORDERING INFORMATION



TECHNICAL SPECIFICATION

INSULATOR MATERIAL : SELF EXTINGUISHING THERMOPLASTIC (UL94 VO)

CONTACT MATERIAL : COPPER ALLOY

MAXIMUM VOLTAGE : 500 V rms.

NOMINAL CURRENT : 3A AT 20°C

INSULATION RESISTANCE : ≥ 1000 MΩ

CONTACT RESISTANCE : ≤ 20 mΩ

CLIMATIC CATAGORY : -40°C TO +100°C / 21 DAYS EXPOSURE TO- INDUSTRIAL ENVIRONMENT HUMIDITY TEST AS HE-14.

| INDEX | DATE | REVISION DESCRIPTION |
|-------|------------|--|
| A | 2006-08-31 | Dim 'T' for Spl Code 320 modified from 11.5 to 4.2 mm |
| 0 | 2003-05-02 | REDRAWING AND UPDATED DRAWING NO: C3-1563 d AND PLATING CODE-15 ADDED. |

| 13 | 8614-00-XX-X-YO-X-313 | 890-XX-XXX-10-808 | 892-XX-XXX-10-808 | 4.5 | 21.0 | 5.7 | 12.76 |
|--------|-----------------------|-------------------|-------------------|------------|-------|-------|-------|
| 12 | 8614-00-XX-X-YO-X-314 | 890-XX-XXX-10-801 | 892-XX-XXX-10-801 | 5.8 | 19.6 | 7.0 | 10.06 |
| 11 | 8614-00-XX-X-YO-X-315 | 890-XX-XXX-10-807 | 892-XX-XXX-10-807 | 4.5 | 18.3 | 5.7 | 10.06 |
| 10 | 8614-00-XX-X-YO-X-316 | 890-XX-XXX-10-806 | 892-XX-XXX-10-806 | 4.5 | 15.8 | 5.7 | 7.56 |
| 09 | 8614-00-XX-X-YO-X-317 | 890-XX-XXX-10-805 | 892-XX-XXX-10-805 | 4.8 | 13.5 | 6.0 | 4.96 |
| 08 | 8614-00-XX-X-YO-X-318 | 890-XX-XXX-10-811 | 892-XX-XXX-10-811 | 14.2 | 21.0 | 15.4 | 3.06 |
| 07 | 8614-00-XX-X-YO-X-319 | 890-XX-XXX-10-804 | 892-XX-XXX-10-804 | 4.6 | 11.8 | 5.8 | 3.46 |
| 06 | 8614-00-XX-X-YO-X-320 | 890-XX-XXX-10-810 | 892-XX-XXX-10-810 | 4.2 | 18.3 | 12.7 | 3.06 |
| 05 | 8614-00-XX-X-YO-X-321 | 890-XX-XXX-10-800 | 892-XX-XXX-10-800 | 5.5 | 12.5 | 6.7 | 3.26 |
| 04 | 8614-00-XX-X-YO-X-322 | 890-XX-XXX-10-000 | 892-XX-XXX-10-000 | 5.8 | 12.5 | 7.0 | 2.96 |
| 03 | 8614-00-XX-X-YO-X-323 | 890-XX-XXX-10-803 | 892-XX-XXX-10-803 | 4.6 | 11.3 | 5.8 | 2.96 |
| 02 | 8614-00-XX-X-YO-X-324 | 890-XX-XXX-10-809 | 892-XX-XXX-10-809 | 7.3 | 13.5 | 8.5 | 2.46 |
| 01 | 8614-00-XX-X-YO-X-325 | 890-XX-XXX-10-802 | 892-XX-XXX-10-802 | 4.5 | 10.8 | 5.7 | 2.56 |
| SL No. | OEN PART NO: | SINGLE ROW | DOUBLE ROW | T | L±0.1 | Y±0.2 | Z±0.2 |
| | | PRECIDIP PART NOS | | DIMENSIONS | | | |

NOTES:

- 1, THE REMAINING AREA ON THE CONTACT SIDE FOLLOWING THE DIMENSION 'T' SHOULD BE PLATED WITH GOLD FLASH
- 2, THE PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008

| | | | | | | | | |
|-------------|----------------|---|-----------------|---------------------------------------|--------|-----------------------------------|--------------------------|------|
| mat'l. code | | surface ISO 1302 <input checked="" type="checkbox"/> tolerance ISO 406 ISO 1101 | | projection | | product family 8614 | | |
| ltr | ecn no | dr | date | tolerances unless otherwise specified | | title | | |
| A | 106-0179 | AB | 2006-08-29 | angles | linear | 8614 OPEN HEADER (STRAIGHT SPILL) | | |
| | | | | ±1° | | MM | scale - | |
| | | dr | MINI K V | 2003-05-02 | | | | |
| | | enr | GEORGE.V.JOSEPH | 2003-05-02 | | | | |
| | | chr | Alex Babu | 2006-08-29 | | | | |
| | | appd | Biju K Paul | 2006-08-29 | | | | |
| sheet index | revision sheet | A | 1 | | | dwg no | sheet 1 of 1 | size |
| | | | | | | C-8614-0127 | A3 | |
| | | | | | | type | Product Customer Drawing | |