

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

KIMBERLY-CLARK PROFESSIONAL* Fresh Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 10.12.2018
1.6	10.12.2018	100000003457	Date of first issue: 16.11.2015

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name : KIMBERLY-CLARK PROFESSIONAL* Fresh Fragrance Refill
Product code : 6184

1.2 Relevant identified uses of the substance or mixture and uses advised against

Use of the Sub-
stance/Mixture : Aircare

1.3 Details of the supplier of the safety data sheet

Company : Kimberly-Clark Europe Limited
40 London Road
Reigate
Surrey RH2 9QP
United Kingdom
Telephone : +44 1737 736000
Telefax : +44 1737 736670
E-mail address Respon-
sible/issuing person : sdscontact@kcc.com

1.4 Emergency telephone number

: +44 1865 407333
This telephone number is available 24 hours per day, 7 days
per week.

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification (REGULATION (EC) No 1272/2008)

Flammable liquids, Category 3 H226: Flammable liquid and vapour.

Eye irritation, Category 2 H319: Causes serious eye irritation.

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)

KIMBERLY-CLARK PROFESSIONAL* Fresh Fragrance Refill

Version 1.6 Revision Date: 10.12.2018 SDS Number: 100000003457 Date of last issue: 10.12.2018
Date of first issue: 16.11.2015

Hazard pictograms :



Signal word : Warning

Hazard statements : H226 Flammable liquid and vapour.
H319 Causes serious eye irritation.

Precautionary statements :

Prevention:
P210 Keep away from heat/sparks/open flames/hot surfaces. No smoking.

Response:
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P337 + P313 If eye irritation persists: Get medical advice/attention.
P370 + P378 In case of fire: Use dry sand, dry chemical or alcohol-resistant foam for extinction.

Storage:
P403 + P235 Store in a well-ventilated place. Keep cool.

Disposal:
P501 Dispose of contents/ container to an approved waste disposal plant.

2.3 Other hazards

This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

This product is a mixture. Health hazard information is based on its components.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Hazardous components

Chemical name	CAS-No. EC-No. Registration number	Classification	Concentration (% w/w)
propan-2-ol	67-63-0 200-661-7	Flam. Liq. 2; H225 Eye Irrit. 2; H319 STOT SE 3; H336	>= 10 - < 20

KIMBERLY-CLARK PROFESSIONAL* Fresh Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 10.12.2018
1.6	10.12.2018	100000003457	Date of first issue: 16.11.2015

For explanation of abbreviations see section 16.

SECTION 4: First aid measures

4.1 Description of first aid measures

General advice : No hazards which require special first aid measures.

If inhaled : Not required under normal use.

In case of skin contact : Wash off with soap and plenty of water.
If skin irritation persists, call a physician.

In case of eye contact : Immediately flush eye(s) with plenty of water.

If swallowed : Do NOT induce vomiting.

4.2 Most important symptoms and effects, both acute and delayed

Symptoms : No information available.

4.3 Indication of any immediate medical attention and special treatment needed

Treatment : No information available.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media : Alcohol-resistant foam
Carbon dioxide (CO₂)
Dry chemical

Unsuitable extinguishing media : Do NOT use water jet.

5.2 Special hazards arising from the substance or mixture

Specific hazards during fire-fighting : Highly flammable liquid and vapour.

Hazardous combustion products : Carbon monoxide, carbon dioxide and unburned hydrocarbons (smoke).

5.3 Advice for firefighters

Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus.

Further information : Use water spray to cool unopened containers.
Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.

KIMBERLY-CLARK PROFESSIONAL* Fresh Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 10.12.2018
1.6	10.12.2018	100000003457	Date of first issue: 16.11.2015

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : Ensure adequate ventilation.
Remove all sources of ignition.

6.2 Environmental precautions

Environmental precautions : Prevent product from entering drains.

6.3 Methods and material for containment and cleaning up

Methods for cleaning up : Wipe up with absorbent material (e.g. cloth, fleece).

6.4 Reference to other sections

For personal protection see section 8.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Advice on safe handling : No special handling advice required.

Advice on protection against fire and explosion : Keep product and empty container away from heat and sources of ignition.

Hygiene measures : Handle in accordance with good industrial hygiene and safety practice.

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers : Keep container tightly closed in a dry and well-ventilated place.

Advice on common storage : No special restrictions on storage with other products.

Other data : No decomposition if stored and applied as directed.

7.3 Specific end use(s)

Specific use(s) : Aircare

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Occupational Exposure Limits

Components	CAS-No.	Value type (Form of exposure)	Control parameters	Basis
------------	---------	-------------------------------	--------------------	-------

SAFETY DATA SHEET
according to Regulation (EC) No. 1907/2006

**KIMBERLY-CLARK PROFESSIONAL* Fresh
Fragrance Refill**

Version 1.6 Revision Date: 10.12.2018 SDS Number: 100000003457 Date of last issue: 10.12.2018
Date of first issue: 16.11.2015

propan-2-ol	67-63-0	TWA	400 ppm 999 mg/m ³	GB EH40
		STEL	500 ppm 1,250 mg/m ³	GB EH40

8.2 Exposure controls

Personal protective equipment

Eye protection : Not required under normal use.

Hand protection
Remarks : For prolonged or repeated contact use protective gloves.

Skin and body protection : not required under normal use

Respiratory protection : Not required under normal use.

Protective measures : No special protective equipment required.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance : liquid

Colour : clear

Odour : pleasant

pH : 6.15

Boiling point/boiling range : 100 °C

Flash point : 32 °C

Upper explosion limit : 12 %(V)

Lower explosion limit : 2 %(V)

Relative density : 0.980

Solubility(ies)
Water solubility : soluble

9.2 Other information

No data available

SECTION 10: Stability and reactivity

10.1 Reactivity

Stable under recommended storage conditions.

KIMBERLY-CLARK PROFESSIONAL* Fresh Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 10.12.2018
1.6	10.12.2018	100000003457	Date of first issue: 16.11.2015

10.2 Chemical stability

No decomposition if stored and applied as directed.

10.3 Possibility of hazardous reactions

Hazardous reactions : Stable under recommended storage conditions.
No decomposition if used as directed.

Vapours may form explosive mixture with air.

10.4 Conditions to avoid

Conditions to avoid : Heat, flames and sparks.

10.5 Incompatible materials

Materials to avoid : Strong acids and oxidizing agents

10.6 Hazardous decomposition products

Stable under recommended storage conditions.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity

Components:

propan-2-ol:

Acute oral toxicity : LD50 Oral (Rat): 5,840 mg/kg
Method: OECD Test Guideline 401
GLP: no

Acute inhalation toxicity : LC50 (Rat, male and female): > 10000 ppm
Exposure time: 6 h
Method: OECD Test Guideline 403
GLP: yes

Acute dermal toxicity : LD50 Dermal (Rabbit): 12,800 mg/kg
Method: OECD Test Guideline 402
GLP: no

Skin corrosion/irritation

Product:

Remarks: According to the classification criteria of the European Union, the product is not considered as being a skin irritant.

Components:

propan-2-ol:

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

KIMBERLY-CLARK PROFESSIONAL* Fresh Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 10.12.2018
1.6	10.12.2018	100000003457	Date of first issue: 16.11.2015

Species: Rabbit
Method: No information available.
Result: No skin irritation
GLP: no

Serious eye damage/eye irritation

Product:

Assessment: Irritating to eyes.
Remarks: Contact with eyes may cause irritation.

Components:

propan-2-ol:

Species: Rabbit
Method: OECD Test Guideline 405
Result: Irritating to eyes.
GLP: no

Respiratory or skin sensitisation

Product:

Remarks: No data available

Components:

propan-2-ol:

Test Type: Buehler Test
Species: Guinea pig
Method: OECD Test Guideline 406
Result: Did not cause sensitisation on laboratory animals.
GLP: yes

Germ cell mutagenicity

Product:

Germ cell mutagenicity- Assessment : Contains no ingredient listed as a mutagen

Carcinogenicity

Product:

Carcinogenicity - Assessment : Contains no ingredient listed as a carcinogen

Reproductive toxicity

Product:

Reproductive toxicity - Assessment : Contains no ingredient listed as toxic to reproduction

KIMBERLY-CLARK PROFESSIONAL* Fresh Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 10.12.2018
1.6	10.12.2018	100000003457	Date of first issue: 16.11.2015

essment

STOT - single exposure

Product:

Remarks: No data available

STOT - repeated exposure

Product:

Remarks: No data available

Further information

Product:

Remarks: Health injuries are not known or expected under normal use.
Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting.

SECTION 12: Ecological information

12.1 Toxicity

Product:

Toxicity to fish : Remarks: No information available.

Toxicity to daphnia and other aquatic invertebrates : Remarks: No information available.

Toxicity to algae : Remarks: No information available.

Components:

propan-2-ol:

Toxicity to fish : LC50 (Pimephales promelas (fathead minnow)): 9,640 mg/l
Exposure time: 96 h
Test Type: flow-through test
Method: OECD Test Guideline 203
GLP: no

LC50 (Pimephales promelas (fathead minnow)): 10,000 mg/l
Exposure time: 96 h
Test Type: flow-through test
Method: OECD Test Guideline 203
GLP: no

Toxicity to daphnia and other aquatic invertebrates : EC50 (Daphnia magna (Water flea)): 9,714 mg/l
Exposure time: 24 h
Test Type: static test
Method: OECD Test Guideline 202

KIMBERLY-CLARK PROFESSIONAL* Fresh Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 10.12.2018
1.6	10.12.2018	100000003457	Date of first issue: 16.11.2015

GLP: no

12.2 Persistence and degradability

Product:

Biodegradability : Remarks: No information available.

12.3 Bioaccumulative potential

Product:

Bioaccumulation : Remarks: Does not bioaccumulate.

12.4 Mobility in soil

Product:

Mobility : Remarks: No information available.

12.5 Results of PBT and vPvB assessment

Product:

Assessment : This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher..

: This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher..

12.6 Other adverse effects

Product:

Additional ecological information : There is no data available for this product.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Product : Dispose of in accordance with local regulations.

Contaminated packaging : Dispose of as unused product.
Do not re-use empty containers.

SECTION 14: Transport information

14.1 UN number

KIMBERLY-CLARK PROFESSIONAL* Fresh Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 10.12.2018
1.6	10.12.2018	100000003457	Date of first issue: 16.11.2015

ADR : UN 1993
IMDG : UN 1993
IATA : UN 1993

14.2 UN proper shipping name

ADR : FLAMMABLE LIQUID, N.O.S.
(Isopropanol)
IMDG : FLAMMABLE LIQUID, N.O.S.
(Isopropanol)
IATA : Flammable liquid, n.o.s.
(Isopropanol)

14.3 Transport hazard class(es)

ADR : 3
IMDG : 3
IATA : 3

14.4 Packing group

ADR
Packing group : III
Classification Code : F1
Hazard Identification Number : 33
Labels : 3
Tunnel restriction code : (D/E)
IMDG
Packing group : III
Labels : 3
EmS Code : F-E, S-E
IATA
Packing instruction (cargo aircraft) : 366
Packing instruction (LQ) : Y344
Packing group : III
Labels : Flammable Liquids

14.5 Environmental hazards

ADR
Environmentally hazardous : no
IMDG
Marine pollutant : no

14.6 Special precautions for user

Not applicable

14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Remarks : No information available.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

KIMBERLY-CLARK PROFESSIONAL* Fresh Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 10.12.2018
1.6	10.12.2018	100000003457	Date of first issue: 16.11.2015

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Seveso III: Directive 2012/18/EU of the European Parliament and of the Council on the control of major-accident hazards involving dangerous substances.

P5c	FLAMMABLE LIQUIDS	Quantity 1 5,000 t	Quantity 2 50,000 t
-----	-------------------	-----------------------	------------------------

The components of this product are reported in the following inventories:

REACH : This mixture contains only ingredients which have been subject to a pre-registration according to Regulation (EC) No. 1907/2006 (REACH).

15.2 Chemical safety assessment

No information available.

SECTION 16: Other information

Full text of H-Statements

H225 : Highly flammable liquid and vapour.
H319 : Causes serious eye irritation.
H336 : May cause drowsiness or dizziness.

Full text of other abbreviations

Eye Irrit. : Eye irritation
Flam. Liq. : Flammable liquids
STOT SE : Specific target organ toxicity - single exposure

ADN - European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways; ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road; AICS - Australian Inventory of Chemical Substances; ASTM - American Society for the Testing of Materials; bw - Body weight; CLP - Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECHA - European Chemicals Agency; EC-Number - European Community number; ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

KIMBERLY-CLARK PROFESSIONAL* Fresh Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 10.12.2018
1.6	10.12.2018	100000003457	Date of first issue: 16.11.2015

Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RID - Regulations concerning the International Carriage of Dangerous Goods by Rail; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; SVHC - Substance of Very High Concern; TCSI - Taiwan Chemical Substance Inventory; TRGS - Technical Rule for Hazardous Substances; TSCA - Toxic Substances Control Act (United States); UN - United Nations; vPvB - Very Persistent and Very Bioaccumulative

Further information

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

GB / EN