

1705996

https://www.phoenixcontact.com/gb/products/1705996

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, Range of articles: SUNCLIX, color: black, number of positions: 1, min. conductor cross section: 2.5 mm², rated voltage: 1000 V DC, rated current: 27 A, Connection method: Crimp, Contact connection type: Pin, cable length: 300

Commercial data

Item number	1705996
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	ABLBAA
Product key	ABLBAA
GTIN	4046356828314
Weight per piece (including packing)	17.96 g
Weight per piece (excluding packing)	17.706 g
Customs tariff number	85366990
Country of origin	DE



1705996

https://www.phoenixcontact.com/gb/products/1705996

Technical data

Notes

Safety note

Safety note

- WARNING: Commission properly functioning products only.
 The products must be regularly inspected for damage.
 Decommission defective products immediately. Replace damaged products. Repairs are not possible.
- WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.

WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.

- The products are suitable for applications in plant, controller, and electrical device engineering.
- Assembled products may not be manipulated or improperly opened.
- Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products).
- When using the product in direct connection with third-party manufacturers, the user is responsible.
- For operating voltages > 50 V AC, conductive connector housings must be grounded
- Ensure that the protective or functional ground has been properly connected.
- Observe the corresponding technical data. You will find information:
- o On the product
- o On the packing label
- o In the supplied documentation
- o Online at phoenixcontact.com/products under the product
- The installation notes/Design In documents online on the download page at phoenixcontact.com/products must be observed for this product.
- Use a protective cap to protect connectors that are not in use.
 The suitable accessories are available online in the accessory section of the product at phoenixcontact.com/products
- The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).
- Operate the connector only when it is fully plugged in and interlocked.
- Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.



1705996

https://www.phoenixcontact.com/gb/products/1705996

Material Housing

	 Observe the minimum bending radius of the cable. Lay the cable without twisting it.
Product properties	
Product type	Panel feed-through
Product family	SUNCLIX
Number of positions	1
Insulation characteristics	
Protection class	II
Degree of pollution	2
Connection data	
Conductor connection	
Tightening torque	1.8 Nm ±0.1 Nm
Dimensions	
Dimensional drawing	
	18.6 41.6 41.6 41.6 41.6 41.6 41.6 41.6 41
Width	26.3 mm
Height	26.3 mm
Length	41.5 mm
Electrical properties	
Rated voltage (III/2)	1000 V
Nominal voltage ATD	1000 V DC in accordance with IEC 62852:2014/AMD1:2020
Rated surge voltage (III/2)	12 kV
Rated current (2.5 mm²)	27 A (in accordance with IEC 62852:2014/AMD1:2020)
Contact resistance	0.45 mΩ
Contact resistance	≤ 0.45 mΩ (when plugged in (without cable))
Mechanical properties	
Mechanical data	
Insertion/withdrawal cycles	100
Insertion force	45 N ±10 N
Withdrawal force	250 N ±50 N (when locked)
Material specifications	
Color	black
Color of the housing part	black
Solor of the flouding part	DIGUIX

PPE



1705996

https://www.phoenixcontact.com/gb/products/1705996

Material Contact carrier	PPE
Material Contact	Cu alloy (silver-plated)
Material Seal	EPDM
Material Contact surface	Ag
Flammability rating according to UL 94	V0
Insulating material group	III
Insulating material	mPPE
Contact surface	Silver Ag
Cable seal material	Elastosil LR 3065/50
Outer sheath, material	PE-X

Cable/line

Cable length	300 mm
Cable type	S01
Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	50x0.25
Cable type	Hose line
Cable structure	50 x 0.25 mm Ø litz wires, tin-plated, 1x bunched
External cable diameter	4.25 mm ±0.15 mm
Outer sheath, material	PE-X
External sheath, color	red, similar to RAL 3000
Single wire, material	Cu
Single wire, cross section	2.5 mm²
Cable cross section	2.5 mm²
Nominal voltage, cable	1.8 kV DC (max U (conductor / conductor, ungrounded system))
Test voltage, cable	≥ 8 kV AC (Spark test online (standard designation))
Smallest bending radius, fixed installation	21.25 mm (5x Ø)
Smallest bending radius, movable installation	40.25 mm (10x Ø)
Cable pull-out force	> 80 N
Halogen-free	yes
Resistance to oil	no
Flame resistance	no

Environmental and real-life conditions

Ambient conditions

Degree of protection (when plugged in)	IP66/IP68 (2 m / 24 h)
Degree of protection (not plugged in)	IP20
Ambient temperature (operation)	-40 °C 85 °C
Ambient temperature (assembly)	-25 °C 50 °C
Resistance to oil	no

Standards and regulations

Flame resistance	no
Resistance to oil	no



1705996

https://www.phoenixcontact.com/gb/products/1705996

Standards/specifications

IEC 62852:2014/AMD1:2020



1705996

https://www.phoenixcontact.com/gb/products/1705996

Drawings

18,6

Dimension x = cable length c: panel thickness - plastic: 2 - 6 mm; metal: 2 - 5 mm


41,6 STOP! DO NOT DISCONNECT UNDER LOAD



1705996

https://www.phoenixcontact.com/gb/products/1705996

Dimensional drawing





1705996

https://www.phoenixcontact.com/gb/products/1705996

Approvals

🌣 To download certificates, visit the product detail page: https://www.phoenixcontact.com/gb/products/1705996



TÜV Rheinland

Approval ID: R 60165003-0001



1705996

https://www.phoenixcontact.com/gb/products/1705996

Classifications

ECLASS		
	ECLASS-13.0	27440107
ETIM		
	ETIM 9.0	EC002635
UNSPSC		
	UNSPSC 21.0	39121400



1705996

https://www.phoenixcontact.com/gb/products/1705996

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions	
China RoHS		
Environment friendly use period (EFUP)	EFUP-E	
	No hazardous substances above the limits	
EU REACH SVHC		
REACH candidate substance (CAS No.)	Triphenyl phosphate(CAS: 115-86-6)	
SCIP	31945240-458d-4c77-96d3-93b76b73e3f0	

Phoenix Contact 2025 @ - all rights reserved https://www.phoenixcontact.com

PHOENIX CONTACT Ltd Halesfield 13, Telford Shropshire, TF7 4PG 01952 681700 info@phoenixcontact.co.uk