

FEATURES

- **High chemical resistance:** Suitable for use with a wide range of chemicals, ensuring versatility in various applications
- **Temperature tolerance up to 280 °C:** Capable of withstanding high temperatures, providing durability in extreme conditions
- **Maximum operating pressure of 3000 kPa:** Ensures reliable sealing under high-pressure conditions
- **Rotary speed of 18 m/s:** Suitable for high-speed applications, enhancing operational efficiency
- **Section size of 6.5 mm:** Offers a compact and effective sealing solution

RS PRO 8m Gland Packing, Polytetrafluoroethylene

RS Stock No: 606-552



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO gland packing is designed for sealing applications in industrial environments. Made from high-quality polytetrafluoroethylene, it provides excellent resistance to chemicals and high temperatures, making it ideal for use in demanding conditions. With a maximum operating pressure of 3000 kPa and a temperature tolerance up to 280 °C, this gland packing ensures reliable performance and longevity.

General Specifications

Maximum Operating Pressure	3000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	18 m/s
Section	6.5 mm
Sub Type	Gland Packing

Mechanical Specifications

Length	8 m
Material	Polytetrafluoroethylene

Operation Environment Specifications

Maximum Operating Temperature	280 °C
-------------------------------	--------

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, BAM, FDA, RoHS
---------------------	--------------------------------------