

QUINT-BAT/24DC/ 7.2AH

Order No.: 2866352




<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=2866352>

Rechargeable battery module, lead AGM, VRLA technology, 24 V DC, 7.2 Ah. Connection via male cable lug, 14 mm.



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

Commercial data

EAN	 4 017918 959753
Pack	1
Customs tariff	85072098
Product key	CMUP43
Country of Origin	CN
Catalog page information	Page 591 (IF-2009)

Technical data

Input data

Nominal input voltage	24 V DC
-----------------------	---------

Output data

Nominal output voltage	24 V DC
Output current	max. 50 A
Connection in parallel	Yes, for increasing the buffer period
Connection in series	No
Output fuse	2x 25 A

General data

IQ technology	No
Width	164 mm
Height	156 mm
Depth	110 mm
Net weight	6 kg
Memory medium	battery 7.2 Ah
Degree of protection	IP20
Protection class	III
Ambient temperature (operation)	0 °C ... 40 °C
Ambient temperature (storage/transport)	0 °C ... 40 °C
Shipbuilding approval	Germanischer Lloyd (EMC 2), ABS

Certificates




Certification GL

Accessories

Item	Designation	Description
Fuse		
0913757	SI FORM C 25 A DIN 72581	Flat-type plug-in fuse, type C, color code: white, nominal current: 25 A
General		
2866857	QUINT-ADAPTER/4	Assembly adapter for QUINT-BAT/24DC... on 35mm rail

Drawings

Block diagram



Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford / Shropshire / TF7 4PG,England
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.
Technical modifications reserved;