



## Safety Data Sheet

Copyright, 2019, 3M Company All rights reserved. Copying and/or downloading of this information for the purpose of properly utilising 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

<b>Document group:</b>	18-6946-0	<b>Version number:</b>	10.05
<b>Revision date:</b>	25/10/2019	<b>Supersedes date:</b>	27/09/2018
<b>Transportation version number:</b>	2.00 (09/08/2015)		

This Safety Data Sheet has been prepared in accordance with the REACH Regulation (EC) 1907/2006 and its modifications.

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

3M VHB Cleaning Sachet

#### Product Identification Numbers

DT-2729-9061-5

7000071715

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

##### Identified uses

Industrial use.

#### 1.3. Details of the supplier of the safety data sheet

**Address:** 3M United Kingdom PLC, 3M Centre, Cain Road, Bracknell, Berkshire, RG12 8HT.  
**Telephone:** +44 (0)1344 858 000  
**E Mail:** tox.uk@mmm.com  
**Website:** www.3M.com/uk

#### 1.4. Emergency telephone number

+44 (0)1344 858 000

### SECTION 2: Hazard identification

#### 2.1. Classification of the substance or mixture

CLP REGULATION (EC) No 1272/2008

##### CLASSIFICATION:

Flammable Liquid, Category 2 - Flam. Liq. 2; H225

Serious Eye Damage/Eye Irritation, Category 2 - Eye Irrit. 2; H319

Specific Target Organ Toxicity-Single Exposure, Category 3 - STOT SE 3; H336

For full text of H phrases, see Section 16.

#### 2.2. Label elements

**CLP REGULATION (EC) No 1272/2008**

**SIGNAL WORD**

DANGER.

**Symbols:**

GHS02 (Flame) |GHS07 (Exclamation mark) |

**Pictograms**



**Ingredients:**

Ingredient	CAS Nbr	EC No.	% by Wt
Propan-2-ol	67-63-0	200-661-7	60 - 90

**HAZARD STATEMENTS:**

H225	Highly flammable liquid and vapour.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.

**PRECAUTIONARY STATEMENTS**

**Prevention:**

P210A	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P261A	Avoid breathing vapours.

**Response:**

P305 + P351 + P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P370 + P378G	In case of fire: Use a fire fighting agent suitable for flammable liquids such as dry chemical or carbon dioxide to extinguish.

**For containers not exceeding 125 ml the following Hazard and Precautionary statements may be used:**

No hazard statements are required for containers <=125 mL.

**Notes on labelling**

Updated per Regulation (EC) No. 648/2004 on detergents.

Per Article 29 of Regulation (EC) No 1272/2008, where the packaging is so small that it is impossible to include the complete label information, the label on the inner packaging must contain the hazard pictograms (GHS02, GHS07), product identifier, and name and telephone number of the supplier.

**2.3. Other hazards**

None known.

**SECTION 3: Composition/information on ingredients**

Ingredient	CAS Nbr	EC No.	REACH Registration	% by Wt	Classification
------------	---------	--------	--------------------	---------	----------------

## 3M VHB Cleaning Sachet

			No.		
Propan-2-ol	67-63-0	200-661-7		60 - 90	Flam. Liq. 2, H225; Eye Irrit. 2, H319; STOT SE 3, H336
Non hazardous ingredient	Mixture			15 - 40	Substance not classified as hazardous

Please see section 16 for the full text of any H statements referred to in this section

For information on ingredient occupational exposure limits or PBT or vPvB status, see sections 8 and 12 of this SDS

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

#### Inhalation

Remove person to fresh air. If you feel unwell, get medical attention.

#### Skin contact

Immediately wash with soap and water. Remove contaminated clothing and wash before reuse. If signs/symptoms develop, get medical attention.

#### Eye contact

Immediately flush with large amounts of water. Remove contact lenses if easy to do. Continue rinsing. Get medical attention.

#### If swallowed

Rinse mouth. If you feel unwell, get medical attention.

### 4.2. Most important symptoms and effects, both acute and delayed

See Section 11.1 Information on toxicological effects

### 4.3. Indication of any immediate medical attention and special treatment required

Not applicable

## SECTION 5: Fire-fighting measures

### 5.1. Extinguishing media

In case of fire: Use a fire fighting agent suitable for flammable liquids such as dry chemical or carbon dioxide to extinguish.

### 5.2. Special hazards arising from the substance or mixture

Closed containers exposed to heat from fire may build pressure and explode.

### Hazardous Decomposition or By-Products

#### Substance

Carbon monoxide.  
Carbon dioxide.  
Irritant vapours or gases.

#### Condition

During combustion.  
During combustion.  
During combustion.

### 5.3. Advice for fire-fighters

Water may not effectively extinguish fire; however, it should be used to keep fire-exposed containers and surfaces cool and prevent explosive rupture. Wear full protective clothing, including helmet, self-contained, positive pressure or pressure demand breathing apparatus, bunker coat and pants, bands around arms, waist and legs, face mask, and protective covering for exposed areas of the head.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Evacuate area. Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Use only non-sparking tools. Ventilate the area with fresh air. For large spill, or spills in confined spaces, provide mechanical ventilation to disperse or exhaust vapours, in accordance with good industrial hygiene practice. Warning! A motor could be an ignition source and could cause flammable gases or vapours in the spill area to burn or explode. Refer to other sections of this SDS for information regarding physical and health hazards, respiratory protection, ventilation, and personal protective equipment.

### 6.2. Environmental precautions

Avoid release to the environment. For larger spills, cover drains and build dykes to prevent entry into sewer systems or bodies of water.

### 6.3. Methods and material for containment and cleaning up

Contain spill. Cover spill area with a fire-extinguishing foam designed for use on solvents, such as alcohols and acetone, that can dissolve in water. An AR-AFFF type foam is recommended. Working from around the edges of the spill inward, cover with bentonite, vermiculite, or commercially available inorganic absorbent material. Mix in sufficient absorbent until it appears dry. Remember, adding an absorbent material does not remove a physical, health, or environmental hazard. Collect as much of the spilled material as possible using non-sparking tools. Place in a metal container approved for transportation by appropriate authorities. Clean up residue with water. Seal the container. Dispose of collected material as soon as possible.

### 6.4. Reference to other sections

Refer to Section 8 and Section 13 for more information

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Vapours may travel long distances along the ground or floor to an ignition source and flash back. For industrial/occupational use only. Not for consumer sale or use. Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Take precautionary measures against static discharge. Avoid breathing dust/fume/gas/mist/vapours/spray. Do not get in eyes, on skin, or on clothing. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Avoid release to the environment. Avoid contact with oxidising agents (eg. chlorine, chromic acid etc.) Wear low static or properly grounded shoes.

### 7.2. Conditions for safe storage including any incompatibilities

Store in a well-ventilated place. Keep cool. Keep container tightly closed. Protect from sunlight. Store away from heat. Store away from acids. Store away from oxidising agents. Store away from amines.

### 7.3. Specific end use(s)

See information in Section 7.1 and 7.2 for handling and storage recommendations. See Section 8 for exposure controls and personal protection recommendations.

## SECTION 8: Exposure controls/personal protection

### 8.1 Control parameters

#### Occupational exposure limits

If a component is disclosed in section 3 but does not appear in the table below, an occupational exposure limit is not available for the component.

Ingredient	CAS Nbr	Agency	Limit type	Additional comments
Propan-2-ol	67-63-0	UK HSC	TWA:999 mg/m <sup>3</sup> (400 ppm);STEL:1250 mg/m <sup>3</sup> (500 ppm)	

UK HSC : UK Health and Safety Commission

TWA: Time-Weighted-Average  
STEL: Short Term Exposure Limit  
CEIL: Ceiling

### Biological limit values

No biological limit values exist for any of the components listed in Section 3 of this safety data sheet.

**Recommended monitoring procedures:** Information on recommended monitoring procedures can be obtained from UK HSC

## 8.2. Exposure controls

### 8.2.1. Engineering controls

Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below relevant Exposure Limits and/or control dust/fume/gas/mist/vapours/spray. If ventilation is not adequate, use respiratory protection equipment.

### 8.2.2. Personal protective equipment (PPE)

#### Eye/face protection

Select and use eye/face protection to prevent contact based on the results of an exposure assessment. The following eye/face protection(s) are recommended:

Indirect vented goggles.

#### *Applicable Norms/Standards*

Use eye protection conforming to EN 166

#### Skin/hand protection

Select and use gloves and/or protective clothing approved to relevant local standards to prevent skin contact based on the results of an exposure assessment. Selection should be based on use factors such as exposure levels, concentration of the substance or mixture, frequency and duration, physical challenges such as temperature extremes, and other use conditions. Consult with your glove and/or protective clothing manufacturer for selection of appropriate compatible gloves/protective clothing.

Gloves made from the following material(s) are recommended:

Material	Thickness (mm)	Breakthrough Time
Butyl rubber.	0.5	> 8 hours
Nitrile rubber.	0.35	> 8 hours

The glove data presented are based on the substance driving dermal toxicity and the conditions present at the time of testing. Breakthrough time may be altered when the glove is subjected to use conditions that place additional stress on the glove.

#### *Applicable Norms/Standards*

Use gloves tested to EN 374

#### Respiratory protection

Under normal use conditions, airborne exposures are not expected to be significant enough to require respiratory protection. An exposure assessment may be needed to decide if a respirator is required. If a respirator is needed, use respirators as part of a full respiratory protection program. Based on the results of the exposure assessment, select from the following respirator type(s) to reduce inhalation exposure:

Half facepiece or full facepiece air-purifying respirator suitable for organic vapours

For questions about suitability for a specific application, consult with your respirator manufacturer.

#### *Applicable Norms/Standards*

Use a respirator conforming to EN 140 or EN 136: filter type A

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

#### Appearance

Physical state  
Colour

Liquid.  
Colourless

#### Specific Physical Form:

Sachet with alcohol filled towel.

#### Odor

Alcohol

#### Odour threshold

*No data available.*

#### pH

*Not applicable.*

#### Boiling point/boiling range

82.4 °C

#### Melting point

*Not applicable.*

#### Flammability (solid, gas)

Not applicable.

#### Explosive properties

Not classified

#### Oxidising properties

Not classified

#### Flash point

12 °C

#### Autoignition temperature

425 °C

#### Flammable Limits(LEL)

2 % volume

#### Flammable Limits(UEL)

12.7 % volume

#### Vapour pressure

*No data available.*

#### Relative density

0.786 [Ref Std: WATER=1]

#### Water solubility

Complete

#### Solubility- non-water

*No data available.*

#### Partition coefficient: n-octanol/water

*No data available.*

#### Evaporation rate

*No data available.*

#### Vapour density

2.07 [Ref Std: AIR=1]

#### Decomposition temperature

*No data available.*

#### Viscosity

*No data available.*

### 9.2. Other information

EU Volatile Organic Compounds

*No data available.*

Molecular weight

*No data available.*

Percent volatile

100 % weight

## SECTION 10: Stability and reactivity

### 10.1 Reactivity

This material may be reactive with certain agents under certain conditions - see the remaining headings in this section

### 10.2 Chemical stability

Stable.

### 10.3 Possibility of hazardous reactions

Hazardous polymerisation will not occur.

### 10.4 Conditions to avoid

Sparks and/or flames.

Heat.

### 10.5 Incompatible materials

Alkali and alkaline earth metals.

## 3M VHB Cleaning Sachet

Aluminium  
Amines.  
Strong oxidising agents.

### 10.6 Hazardous decomposition products

<u>Substance</u>	<u>Condition</u>
None known.	

Refer to section 5.2 for hazardous decomposition products during combustion.

## SECTION 11: Toxicological information

The information below may not agree with the EU material classification in Section 2 and/or the ingredient classifications in Section 3 if specific ingredient classifications are mandated by a competent authority. In addition, statements and data presented in Section 11 are based on UN GHS calculation rules and classifications derived from 3M assessments.

### 11.1 Information on Toxicological effects

#### Signs and Symptoms of Exposure

Based on test data and/or information on the components, this material may produce the following health effects:

#### Inhalation

Respiratory tract irritation: Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain. May cause additional health effects (see below).

#### Skin contact

Dermal Defatting: Signs/symptoms may include localised redness, itching, drying and cracking of skin.

#### Eye contact

Severe eye irritation: Signs/symptoms may include significant redness, swelling, pain, tearing, cloudy appearance of the cornea, and impaired vision.

#### Ingestion

Physical Blockage: Signs/symptoms may include cramping, abdominal pain, and constipation. Gastrointestinal irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhoea. May cause additional health effects (see below).

#### Additional Health Effects:

#### Single exposure may cause target organ effects:

Central nervous system (CNS) depression: Signs/symptoms may include headache, dizziness, drowsiness, incoordination, nausea, slowed reaction time, slurred speech, giddiness, and unconsciousness.

#### Toxicological Data

If a component is disclosed in section 3 but does not appear in a table below, either no data are available for that endpoint or the data are not sufficient for classification.

#### Acute Toxicity

Name	Route	Species	Value
Overall product	Ingestion		No data available; calculated ATE >5,000 mg/kg
Propan-2-ol	Dermal	Rabbit	LD50 12,870 mg/kg
Propan-2-ol	Inhalation-Vapour (4 hours)	Rat	LC50 72.6 mg/l

**3M VHB Cleaning Sachet**

Propan-2-ol	Ingestion	Rat	LD50 4,710 mg/kg
-------------	-----------	-----	------------------

ATE = acute toxicity estimate

**Skin Corrosion/Irritation**

Name	Species	Value
Propan-2-ol	Multiple animal species	No significant irritation

**Serious Eye Damage/Irritation**

Name	Species	Value
Propan-2-ol	Rabbit	Severe irritant

**Skin Sensitisation**

Name	Species	Value
Propan-2-ol	Guinea pig	Not classified

**Respiratory Sensitisation**

For the component/components, either no data is currently available or the data is not sufficient for classification.

**Germ Cell Mutagenicity**

Name	Route	Value
Propan-2-ol	In Vitro	Not mutagenic
Propan-2-ol	In vivo	Not mutagenic

**Carcinogenicity**

Name	Route	Species	Value
Propan-2-ol	Inhalation	Rat	Some positive data exist, but the data are not sufficient for classification

**Reproductive Toxicity****Reproductive and/or Developmental Effects**

Name	Route	Value	Species	Test result	Exposure Duration
Propan-2-ol	Ingestion	Not classified for development	Rat	NOAEL 400 mg/kg/day	during organogenesis
Propan-2-ol	Inhalation	Not classified for development	Rat	LOAEL 9 mg/l	during gestation

**Target Organ(s)****Specific Target Organ Toxicity - single exposure**

Name	Route	Target Organ(s)	Value	Species	Test result	Exposure Duration
Propan-2-ol	Inhalation	central nervous system depression	May cause drowsiness or dizziness	Human	NOAEL Not available	
Propan-2-ol	Inhalation	respiratory irritation	Some positive data exist, but the data are not sufficient for classification	Human	NOAEL Not available	
Propan-2-ol	Inhalation	auditory system	Not classified	Guinea pig	NOAEL 13.4 mg/l	24 hours
Propan-2-ol	Ingestion	central nervous system depression	May cause drowsiness or dizziness	Human	NOAEL Not available	poisoning and/or abuse

**Specific Target Organ Toxicity - repeated exposure**



**3M VHB Cleaning Sachet**

Name	Route	Target Organ(s)	Value	Species	Test result	Exposure Duration
Propan-2-ol	Inhalation	kidney and/or bladder	Not classified	Rat	NOAEL 12.3 mg/l	24 months
Propan-2-ol	Inhalation	nervous system	Not classified	Rat	NOAEL 12 mg/l	13 weeks
Propan-2-ol	Ingestion	kidney and/or bladder	Not classified	Rat	NOAEL 400 mg/kg/day	12 weeks

**Aspiration Hazard**

For the component/components, either no data is currently available or the data is not sufficient for classification.

Please contact the address or phone number listed on the first page of the SDS for additional toxicological information on this material and/or its components.

**SECTION 12: Ecological information**

The information below may not agree with the EU material classification in Section 2 and/or the ingredient classifications in Section 3 if specific ingredient classifications are mandated by a competent authority. In addition, statements and data presented in Section 12 are based on UN GHS calculation rules and classifications derived from 3M assessments.

**12.1. Toxicity**

No product test data available.

Material	CAS #	Organism	Type	Exposure	Test endpoint	Test result
Propan-2-ol	67-63-0	Crustacea	Experimental	24 hours	LC50	>10,000 mg/l
Propan-2-ol	67-63-0	Green Algae	Experimental	72 hours	EC50	>1,000 mg/l
Propan-2-ol	67-63-0	Ricefish	Experimental	96 hours	LC50	>100 mg/l
Propan-2-ol	67-63-0	Water flea	Experimental	48 hours	EC50	>1,000 mg/l
Propan-2-ol	67-63-0	Green algae	Experimental	72 hours	NOEC	1,000 mg/l
Propan-2-ol	67-63-0	Water flea	Experimental	21 days	NOEC	100 mg/l

**12.2. Persistence and degradability**

Material	CAS Nbr	Test type	Duration	Study Type	Test result	Protocol
Propan-2-ol	67-63-0	Experimental Biodegradation	14 days	BOD	86 % BOD/ThBOD	OECD 301C - MITI test (I)

**12.3 : Bioaccumulative potential**

Material	Cas No.	Test type	Duration	Study Type	Test result	Protocol
Propan-2-ol	67-63-0	Experimental Bioconcentration		Log Kow	0.05	Other methods

**12.4. Mobility in soil**

Please contact manufacturer for more details

**12.5. Results of the PBT and vPvB assessment**

This material does not contain any substances that are assessed to be a PBT or vPvB

#### 12.6. Other adverse effects

No information available.

### SECTION 13: Disposal considerations

#### 13.1 Waste treatment methods

Dispose of contents/ container in accordance with the local/regional/national/international regulations.

Incinerate in a permitted waste incineration facility. As a disposal alternative, utilize an acceptable permitted waste disposal facility. Empty drums/barrels/containers used for transporting and handling hazardous chemicals (chemical substances/mixtures/preparations classified as Hazardous as per applicable regulations) shall be considered, stored, treated & disposed of as hazardous wastes unless otherwise defined by applicable waste regulations. Consult with the respective regulating authorities to determine the available treatment and disposal facilities.

The coding of a waste stream is based on the application of the product by the consumer. Since this is out of the control of 3M, no waste code(s) for products after use will be provided. Please refer to the European Waste Code (EWC - 2000/532/EC and amendments) to assign the correct waste code to your waste stream. Ensure national and/or regional regulations are complied with and always use a licensed waste contractor.

#### EU waste code (product as sold)

15 02 02*	Absorbents, filter materials (including oil filters not otherwise specified), wiping cloths, protective clothing contaminated by dangerous substances
20 01 13*	Solvents

### SECTION 14: Transportation information

DT-2729-9061-5

**ADR/RID:** UN3175, NOT RESTRICTED - SPECIAL PROVISION 216 FULFILLED, II , (--).

**IMDG-CODE:** UN3175, NOT RESTRICTED - SPECIAL PROVISION 216 FULFILLED, II , IMDG-Code segregation code: NONE, EMS: --.

**ICAO/IATA:** NOT RESTRICTED, AS PER SPECIAL PROVISION A46, II , information required for air way bill.

### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### 15.2. Chemical Safety Assessment

A chemical safety assessment has not been carried out for this substance/mixture in accordance with Regulation (EC) No 1907/2006, as amended.

### SECTION 16: Other information

#### List of relevant H statements

H225	Highly flammable liquid and vapour.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.

#### Revision information:

Section 7: Precautions safe handling information information was modified.

Section 8: Personal Protection - Eye information information was modified.  
Section 8: Personal Protection - Skin/hand information information was modified.  
Section 09: Color information was added.  
Section 09: Odor information was added.  
Sections 3 and 9: Odour, colour, grade information information was deleted.  
Section 11: Reproductive and/or Developmental Effects text information was deleted.  
Section 15: Regulations - Inventories information was deleted.  
Section 16: UK disclaimer information was modified.

**DISCLAIMER:** The information on this Safety Data Sheet is based on our experience and is correct to the best of our knowledge at the date of publication, but we do not accept any liability for any loss, damage or injury resulting from its use (except as required by law). The information may not be valid for any use not referred to in this Data Sheet or use of the product in combination with other materials. For these reasons, it is important that customers carry out their own test to satisfy themselves as to the suitability of the product for their own intended applications. In addition, this SDS is being provided to convey health and safety information. If you are the importer of record of this product into the European Union, you are responsible for all regulatory requirements, including, but not limited to, product registrations/notifications, substance volume tracking, and potential substance registration.

**3M United Kingdom MSDSs are available at [www.3M.com/uk](http://www.3M.com/uk)**