



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Receptacle**

PCB Mount Orientation: **Right Angle**

Connector System: **Board-to-Board**

Number of Positions: **60**

Number of Rows: **2**

Features

Product Type Features

Applied Pressure	High, Standard
PCB Connector Type	PCB Mount Receptacle
Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Stackable	Yes
PCB Mount Orientation	Right Angle
Number of Positions	60
Number of Rows	2

Electrical Characteristics

Operating Voltage	333 VAC
Insulation Resistance	5000 MΩ
Dielectric Withstanding Voltage (Max)	750 VAC

Body Features

Connector Profile	Standard
Primary Product Color	Black



Contact Features

Contact Mating Area Plating Material Thickness	.762 μm[30 μin]
Mating Square Post Dimension	.64 mm[.025 in]
	10 μin
Contact Shape & Form	Short Point
Contact Protection Type	Closed Entry Housing
Contact Mating Area Length	3 mm[.1 in]
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Tin-Lead
Contact Mating Area Plating Material	Gold (Au)
Contact Type	Socket
Contact Current Rating (Max)	2 A

Termination Features

Rectangular Termination Post & Tail Width	.69 mm[.027 in]
Rectangular Termination Post & Tail Thickness	.2 mm[.008 in]
Termination Post & Tail Length	2.92 mm[.115 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	Without

Housing Features

Mating Entry Location	Side
Housing Material	Polyester - GF
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Row-to-Row Spacing	2.54 mm, 7.87 mm[.31 in]
Stack Height	8.13 mm[.32 in]
PCB Thickness (Recommended)	1.4 – 2.4 mm[.055 – .094 in]
Connector Height	6.05 mm[.238 in]

Usage Conditions

--	--



Housing Temperature Rating	High
Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]

Operation/Application

Solder Process Feature	Board Standoff
Circuit Application	Signal

Industry Standards

Compatible With Approved Standards Products	CSA LR7189, UL E28476
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	7
Packaging Method	Box, Tube

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer





This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>











Compatible Parts

 <p>TE Part # 86479-7 24 MODII HDR DRRA UNSHRD .100</p>	 <p>TE Part # 3-86479-4 60 MODII HDR DRRA UNSHRD .100</p>	 <p>TE Part # 4-86479-4 80 MODII HDR DRRA UNSHRD .100</p>	 <p>TE Part # 3-87215-0 60 MODII HDR DRST UNSHRD .100</p>
--	---	--	--

Also in the Series | Modu Connector System

 <p>Board-to-Board Headers & Receptacles(814)</p>	 <p>Board-to-Board Jumpers & Shunts(5)</p>	 <p>Connector Hardware(4)</p>	 <p>PCB Headers & Receptacles(814)</p>
---	---	---	--

Customers Also Bought

 <p>TE Part #1SNA115185R0500 M4/6.DE</p>	 <p>TE Part #66025-2 TAB,PIDG TERMI-BK 12-10</p>	 <p>TE Part #M15570-12 TOOL INSERTS</p>	 <p>TE Part #1-535512-8 16 MODII HORZ DR CE EESS .100</p>
 <p>TE Part #5-104477-4 40 SYSTEM 50 HDR DRRA SHRD SN</p>	 <p>TE Part #66024-4 TAB,PIDG TERMI-BK 16-14</p>	 <p>TE Part #1SNK505214R0000 ZS4-D-CH-UD</p>	 <p>TE Part #3-1617033-1 HFW1230K06P = M39016/6-105P</p>



Documents

Product Drawings

60 MODII HORZ DR CE EESS .100

English

CAD Files

Customer View Model

ENG_CVM_3-535512-0_Y1.3d_igs.zip

English

Customer View Model

ENG_CVM_3-535512-0_Y1.3d_stp.zip

English

Customer View Model

ENG_CVM_3-535512-0_Y1.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English