



Semiconductor relay, 1-phase 3RF2 Overall width 45 mm, 90 A 48-460 V / 24 V DC screw terminal

product brand name	SIRIUS
product designation	solid-state relay
design of the product	single-phase
product type designation	3RF20
General technical data	
product function	zero-point switching
power loss [W] for rated value of the current at AC in hot operating state	118 W
• per pole	118 W
power loss [W] for rated value of the current without load current share typical	0.4 W
insulation voltage rated value	600 V
type of voltage of the control supply voltage	DC
shock resistance acc. to IEC 60068-2-27	15g / 11 ms
vibration resistance acc. to IEC 60068-2-6	2g
reference code acc. to IEC 81346-2	Q
Substance Prohibance (Date)	28.05.2009
Main circuit	
number of poles for main current circuit	1
number of NO contacts for main contacts	1
number of NC contacts for main contacts	0
operating voltage at AC	
• at 50 Hz rated value	48 ... 460 V
• at 60 Hz rated value	48 ... 460 V
operating frequency rated value	50 ... 60 Hz
relative symmetrical tolerance of the operating frequency	10 %
operating range relative to the operating voltage at AC	
• at 50 Hz	40 ... 506 V
• at 60 Hz	40 ... 506 V
operational current	
• at AC-51 rated value	50 A
• acc. to UL 508 rated value	50 A
ampacity maximum	90 A
operational current minimum	500 mA
rate of voltage rise at the thyristor for main contacts maximum permissible	1 000 V/μs
blocking voltage at the thyristor for main contacts maximum permissible	1 200 V
reverse current of the thyristor	10 mA

derating temperature	40 °C
surge current resistance rated value	1 150 A
I ² t value maximum	6 600 A ² ·s
Control circuit/ Control	
type of voltage of the control supply voltage	DC
control supply voltage 1	
• at DC rated value	30 V
• at DC	15 ... 24 V
control supply voltage	
• at DC initial value for signal <1> detection	15 V
• at DC full-scale value for signal<0> recognition	5 V
control current at minimum control supply voltage	
• at DC	13 mA
control current at DC rated value	15 mA
ON-delay time	1 ms; additionally max. one half-wave
OFF-delay time	1 ms; additionally max. one half-wave
Auxiliary circuit	
number of NC contacts for auxiliary contacts	0
number of NO contacts for auxiliary contacts	0
number of CO contacts for auxiliary contacts	0
Installation/ mounting/ dimensions	
fastening method	screw fixing
• side-by-side mounting	Yes
tightening torque of fixing screw maximum	1.5 N·m
tightening torque [lbf·in] of fixing screw maximum	13 lbf·in
height	58 mm
width	45 mm
depth	48 mm
Connections/ Terminals	
type of electrical connection	
• for main current circuit	screw-type terminals
• for auxiliary and control circuit	screw-type terminals
type of connectable conductor cross-sections	
• for main contacts	
— solid	2x (1.5 ... 2.5 mm ²), 2x (2.5 ... 6 mm ²)
— finely stranded with core end processing	2x (1 ... 2.5 mm ²), 2x (2.5 ... 6 mm ²), 1x 10 mm ²
• at AWG cables for main contacts	2x (14 ... 10)
connectable conductor cross-section for main contacts	
• solid or stranded	1.5 ... 6 mm ²
• finely stranded with core end processing	1 ... 10 mm ²
type of connectable conductor cross-sections	
• for auxiliary and control contacts	
— solid	1x (0.5 ... 2.5 mm ²), 2x (0.5 ... 1.0 mm ²)
— finely stranded with core end processing	1x (0.5 ... 2.5 mm ²), 2x (0.5 ... 1.0 mm ²)
— finely stranded without core end processing	1x (0.5 ... 2.5 mm ²), 2x (0.5 ... 1.0 mm ²)
• at AWG cables for auxiliary and control contacts	1x (AWG 20 ... 12)
AWG number as coded connectable conductor cross section for main contacts	14 ... 10
tightening torque	
• for main contacts with screw-type terminals	2 ... 2.5 N·m
• for auxiliary and control contacts with screw-type terminals	0.5 ... 0.6 N·m
tightening torque [lbf·in]	
• for main contacts with screw-type terminals	7 ... 10.3 lbf·in
• for auxiliary and control contacts with screw-type terminals	4.5 ... 5.3 lbf·in
design of the thread of the connection screw	
• for main contacts	M4
• of the auxiliary and control contacts	M3

stripped length of the cable <ul style="list-style-type: none">• for main contacts• for auxiliary and control contacts		10 mm	
		7 mm	
Safety related data			
protection class IP on the front acc. to IEC 60529		IP20	
touch protection on the front acc. to IEC 60529		finger-safe, for vertical contact from the front	
Ambient conditions			
installation altitude at height above sea level maximum		1 000 m	
ambient temperature <ul style="list-style-type: none">• during operation• during storage		-25 ... +60 °C	
		-55 ... +80 °C	
Electromagnetic compatibility			
conducted interference <ul style="list-style-type: none">• due to burst acc. to IEC 61000-4-4• due to conductor-earth surge acc. to IEC 61000-4-5• due to conductor-conductor surge acc. to IEC 61000-4-5• due to high-frequency radiation acc. to IEC 61000-4-6		2 kV / 5 kHz behavior criterion 2	
		2 kV behavior criterion 2	
		1 kV behavior criterion 2	
		140 dBuV in the frequency range 0.15 ... 80 MHz, behavior criterion 1	
field-based interference acc. to IEC 61000-4-3		80 MHz ... 1 GHz 10 V/m, behavior criterion 1	
electrostatic discharge acc. to IEC 61000-4-2		4 kV contact discharging / 8 kV air discharging, behavior criterion 2	
conducted HF interference emissions acc. to CISPR11		Class A for industrial environment	
field-bound HF interference emission acc. to CISPR11		Class B for the domestic, business and commercial environments	
Short-circuit protection, design of the fuse link			
manufacturer's article number <ul style="list-style-type: none">• of full range R fuse link for semiconductor protection at NH design usable• of back-up R fuse link for semiconductor protection at NH design usable• of back-up R fuse link for semiconductor protection at cylindrical design 22 x 58 mm usable		3NE1021-2	
		3NE8021-1	
		3NC2280	
manufacturer's article number of the gG fuse <ul style="list-style-type: none">• at NH design usable• at cylindrical design 22 x 58 mm usable		3NA6812: These fuses have a smaller rated current than the semiconductor relays	
		3NW6212-1: These fuses have a smaller rated current than the semiconductor relays	
manufacturer's article number <ul style="list-style-type: none">• of DIAZED fuse usable• of NEOZED fuse usable		5SB4111: These fuses have a smaller rated current than the semiconductor relays	
		5SE2335: These fuses have a smaller rated current than the semiconductor relays	
Certificates/ approvals			
General Product Approval	EMC	Declaration of Conformity	Test Certificates




[Type Test Certificates/Test Report](#)



other

[Confirmation](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)
<https://www.siemens.com/ic10>





last modified:

12/15/2020