




Switches > DIP & SIP Switches



DIP & SIP Switch Type: **DIP**  
Switch Contact Plating Material: **Gold**  
Case Color: **Blue**  
Case Material: **Polyester GF**  
Sealed Device: **Yes**

Features

Product Type Features

|                       |                       |
|-----------------------|-----------------------|
| DIP & SIP Switch Type | DIP                   |
| Sealed Device         | Yes                   |
| Actuator Style        | Rocker (Top Actuated) |

Configuration Features

|                            |                            |
|----------------------------|----------------------------|
| Number of Positions        | 5                          |
| Number of Switches         | 5                          |
| Configuration (Pole-Throw) | Single Pole - Single Throw |

Electrical Characteristics

|                        |        |
|------------------------|--------|
| Contact Current Rating | 1 A    |
| Operating Voltage      | 40 VDC |

Body Features

|                     |                                        |
|---------------------|----------------------------------------|
| Sealing Method      | Strippable Transparent Protective Seal |
| Product Orientation | Vertical                               |
| Case Color          | Blue                                   |
| Case Material       | Polyester GF                           |



Contact Features

|                                               |              |
|-----------------------------------------------|--------------|
|                                               | 30 µin       |
| PCB Contact Termination Area Plating Material | Tin          |
| Switch Contact Plating Material               | Gold         |
| Contact Base Material                         | Copper Alloy |

Termination Features

|                                |                       |
|--------------------------------|-----------------------|
| Termination Post & Tail Length | 3.56 mm[.14 in]       |
| Termination Method to PCB      | Through Hole - Solder |

Housing Features

|                    |                |
|--------------------|----------------|
| Centerline (Pitch) | 2.54 mm[.1 in] |
|--------------------|----------------|

Dimensions

|                |                  |
|----------------|------------------|
| Product Length | 14.73 mm[.58 in] |
| Product Height | 8.64 mm[.34 in]  |

Industry Standards

|                        |          |
|------------------------|----------|
| UL Flammability Rating | UL 94V-0 |
|------------------------|----------|

Packaging Features

|                    |      |
|--------------------|------|
| Packaging Method   | Tube |
| Packaging Quantity | 21   |

Product Compliance

For compliance documentation, visit the product page on TE.com>


|                                               |                                                                                                                                |
|-----------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                      |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                      |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                        |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JUNE 2023 (235)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.                                                                                 |
| Solder Process Capability                     | Wave solder capable to 265°C                                                                                                   |

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 3-5435668-4  
DIP SW 4 POSN W/TAPE AU



TE Part # 2-5435668-8  
DIP SW 8 POSN W/TAPE AU



TE Part # 2-5435668-5  
DIP SW 6 POSN W/TAPE AU



TE Part # 435668-7  
LO PROFILE DIP SW 8P AU

Customers Also Bought



TE Part #203540-E  
MJ HS VG \* 8 8 4 \* \* \* \* 30 3/4 J 3 2035



TE Part #1-1971817-3  
3P,RAST 2.5 Tab Header,Ex- Locking, THV




TE Part #EM7084-000  
THA-PDKG-15



TE Part #709822-2  
XCT 185-12



TE Part #254117-E  
STVC 96 F ABC VVV 7-00 EE 2,9 \* 247 E007



TE Part #87215-7  
20 MODII HDR DRST UNSHRD .100



TE Part #8-1879225-4  
CPF 0603 332K 0.1% 25PPM 1K RL



TE Part #5-641125-4  
24P MTA100 ASSY P/RA SQ LF





TE Part #2-6609951-2  
[PS0SSDS6A=C4436](#)



TE Part #7-1393779-2  
[T81N5D312-24](#)

Documents

Product Drawings

[DIP SW 5 POSN SEALED](#)

English

CAD Files

[3D PDF](#)

English

Customer View Model

[ENG\\_CVM\\_3-5435640-6\\_A1.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_3-5435640-6\\_A1.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_3-5435640-6\\_A1.2d\\_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_3-5435640-6\\_C.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_3-5435640-6\\_C.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_3-5435640-6\\_C.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

