



Image may differ from product. See technical specification for details.

32205 BJ2/Q

Single row tapered roller bearing

Single row tapered roller bearings are designed to accommodate combined radial and axial loads and provide low friction during operation. The inner ring, with rollers and cage, can be mounted separately from the outer ring. These separable and interchangeable components facilitate mounting, dismounting and maintenance. By mounting one single row tapered roller bearing against another and applying a preload, a rigid bearing application can be achieved.

- High radial and axial load carrying capacity
- Accommodate axial loads in one direction
- Low friction and long service life
- Separable and interchangeable components

Overview

Dimensions

Bore diameter	25 mm
Outside diameter	52 mm
Width, total	19.25 mm
Width, inner ring	18 mm
Width, outer ring	15 mm
Contact angle	21.3 °

Performance

Basic dynamic load rating	35.8 kN
Basic static load rating	44 kN
Reference speed	9 500 r/min
Limiting speed	13 000 r/min

Properties

Bearing part	Complete bearing
Number of rows	1
Locating feature, bearing outer ring	Without
Bore type	Cylindrical
Cage	Sheet metal
Arrangement of contact angle (double-row bearing)	Not applicable
Matched arrangement	No
Coating	Without
Sealing	Without
Lubricant	None
Relubrication feature	Without
Unit system	Metric
Indicative carbon footprint for new product	0.69 kg CO ₂ e

Logistics

Product net weight	0.191 kg
eClass code	23-05-09-10

UNSPSC code

31171516



Terms of use