

CA-19P1N128007 - Cable connector



1619660
<https://www.phoenixcontact.com/gb/products/1619660>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: CA, straight, shielded: yes, Screw locking mechanism, No. of pos. : 16+3, Direction of rotation: Standard, contact connection type: Pin, Solder connection, cable diameter range: 6 mm ... 10 mm, coding: N, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1243749

Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Solder connection: proven connection technology for various litz wires

Commercial data

Item number	1619660
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ABRAEA
Product key	ABRAEA
Catalog page	Page 87 (C-2-2019)
GTIN	4046356822183
Weight per piece (including packing)	97.6 g
Weight per piece (excluding packing)	94.4 g
Customs tariff number	85366990
Country of origin	DE

CA-19P1N128007 - Cable connector



1619660

<https://www.phoenixcontact.com/gb/products/1619660>

Technical data

Product properties

Product type	Circular connector (cable-side)
Data management status	
Article revision	06

Connector

Insulating body	
Coding	N
Insulation body material	PA 6.6
Contact material	CuZn
Contact surface material	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder connection
Contact switching type	Pin
Application	Signal
Number of positions	19
Direction of rotation	Standard
Connection profile	16+3
Contact diameter	1.5 mm
Power contacts	
Litz wire cross-section	1 mm²
Rated current	10 A
Rated voltage	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Contact diameter	1 mm
Signal contacts	
Litz wire cross-section	1 mm²
Nominal current per signal contact	8 A
Installation height	2000 m

Housing

Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Type of locking	Screw locking mechanism
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23

Seal

CA-19P1N128007 - Cable connector



1619660

<https://www.phoenixcontact.com/gb/products/1619660>

External cable diameter	6 mm ... 10 mm
Seal material	NBR

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

CA-19P1N128007 - Cable connector


1619660

<https://www.phoenixcontact.com/gb/products/1619660>



Drawings

Schematic diagram



Connector pin assignment

CA-19P1N128007 - Cable connector





1619660

<https://www.phoenixcontact.com/gb/products/1619660>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1619660>

<div> cUL Recognized Approval ID: E335019-20141210</div>				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Power	48 V	6 A	18 - 18	-
Signal	48 V	5 A	18 - 18	-

<div> UL Recognized Approval ID: E335019-20141210</div>				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Power	48 V	10 A	18 - 18	-
Signal	48 V	8 A	18 - 18	-

cULus Recognized				
-------------------------	--	--	--	--

CA-19P1N128007 - Cable connector



1619660

<https://www.phoenixcontact.com/gb/products/1619660>

Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CA-19P1N128007 - Cable connector



1619660
<https://www.phoenixcontact.com/gb/products/1619660>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	79ba5dd1-d849-4702-99ad-9d6f9dcb4682

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk