


K-12 - OE/2,0-E00/M23 F8-N2 - Cable plug in molded plastic



1619247

<https://www.phoenixcontact.com/gb/products/1619247>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable plug in molded plastic, Straight, plastic molded, number of positions: 12, type of locking: Screw locking mechanism, cable length: 2 m, shielded: yes, color of outer sheath: orange RAL 2003

Your advantages

- Our standard: robust halogen-free PUR cable
- Simple and safe: 100% electrically tested and assembled ready for use
- Designs with preassembled cables on one or both sides
- High flexibility: customer-specific assemblies and cable lengths can be supplied

Commercial data

Item number	1619247
Packing unit	1 pc
Minimum order quantity	2 pc
Sales key	ABRDFA
Product key	ABRDFA
Catalog page	Page 216 (C-2-2019)
GTIN	4046356833417
Weight per piece (including packing)	318.7 g
Weight per piece (excluding packing)	282.567 g
Customs tariff number	85444290
Country of origin	DE

K-12 - OE/2,0-E00/M23 F8-N2 - Cable plug in molded plastic



1619247

<https://www.phoenixcontact.com/gb/products/1619247>

Technical data

Product properties

Product type	Signal and power cable
--------------	------------------------

Connector

Connector specifications

Type	Straight, plastic molded
Housing material	Die-cast zinc
Type of locking	Screw locking mechanism
Degree of protection	IP67, when in locked state
No. of pos.	12
Direction of rotation	Standard
Contact switching type	Socket
Insertion/withdrawal cycles	50
Contact resistance	< 0.3 mΩ
Max. current	8 A
Voltage	48 V AC 74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV
Ambient temperature (operation)	-40 °C ... 105 °C

Cable specifications

Cable type	RSL9YSLC11Y
Shielded	yes
Cable structure	4 x 2 x 0.25 mm ² + 2 x 0.5 mm ²
Cable structure (AWG)	24 AWG/4pr + 20 AWG/2c
External cable diameter	8.00 mm
Outer sheath, material	TPU
Material wire insulation	PP
External sheath, color	orange RAL 2003
Test voltage	1 kV
Rated current	9 A
Smallest bending radius, fixed installation	40 mm
Smallest bending radius, movable installation	60 mm
Ambient temperature (operation) for fixed installation	-40 °C ... 80 °C
Ambient temperature (operation) for flexible installation	-20 °C ... 60 °C

Electrical properties

Nominal current I _N	9 A
--------------------------------	-----

K-12 - OE/2,0-E00/M23 F8-N2 - Cable plug in molded plastic



1619247
<https://www.phoenixcontact.com/gb/products/1619247>

Cable/line

Cable length	2 m
--------------	-----

K-12 - OE/2,0-E00/M23 F8-N2 - Cable plug in molded plastic




1619247

<https://www.phoenixcontact.com/gb/products/1619247>

Drawings

Dimensional drawing




Dimensional drawing

K-12 - OE/2,0-E00/M23 F8-N2 - Cable plug in molded plastic

1619247

<https://www.phoenixcontact.com/gb/products/1619247>

Schematic diagram




Connector pin assignment

K-12 - OE/2,0-E00/M23 F8-N2 - Cable plug in molded plastic

1619247

<https://www.phoenixcontact.com/gb/products/1619247>

Circuit diagram



Contact assignment of M23 plugs/sockets

K-12 - OE/2,0-E00/M23 F8-N2 - Cable plug in molded plastic



1619247

<https://www.phoenixcontact.com/gb/products/1619247>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1619247>



EAC

Approval ID: 19060508



UL Listed

Approval ID: E335019-20140707

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Power	48 V	5 A	-	-
Signal	48 V	2 A	-	-



cUL Listed

Approval ID: E335019-20140707

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Power	48 V	5 A	-	-
Signal	48 V	2 A	-	-

K-12 - OE/2,0-E00/M23 F8-N2 - Cable plug in molded plastic



1619247
<https://www.phoenixcontact.com/gb/products/1619247>

Classifications

ECLASS

ECLASS-13.0	27060106
-------------	----------

ETIM

ETIM 9.0	EC003250
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

K-12 - OE/2,0-E00/M23 F8-N2 - Cable plug in molded plastic



1619247

<https://www.phoenixcontact.com/gb/products/1619247>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(b), 6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	d786a6f9-f2b9-45d1-999f-90f723bf150

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk