





THIS PRINT IS A COPY. UNCONTROLLED DOCUMENT BY THE REVISION SERVICE! THIS DRAWING IS A COPY AND IS NOT SUBJECT TO CHANGE SERVICE!				
PARTS LIST / BILL OF ITEMS 110-03700 / EVO7p				
POS US		TITLE / NAME	Material	PC. / STK.
1		ISO14583-A2-M2_5x6	1_4303	1
2	110-037	Label serial number	1_0038	1
3	110-03720	Housing right complete.		1
4	110-03721	Left housing complete.		1
5	110-03722	Label left Evo7p Label right EVO7p	PVC_FOIL_LABEL_0_3	1
6	110-03723	110-03730 Cylinder complete	PVC_FOIL_LABEL_0_3	1
7				1
8	110-03750	Ventil Evo7p kpl.		1
9	110-03760	Air connection bottom complete.		1
10	110-03770	Tension adjustment EVO7p cam cutting EVO7p 110-03782		1
11	110-03781	Blade lever EVO7p	1_4548	1
12			1_3505	1
13	110-03784	PUN-H 3x0,5 150mm	EVEN THOUGH	1
14	110-03785	Zugsperre A EVO7p	1_2842	2
15	110-03786	Air connection at top	1_4548	1
16	110-03787	M5 socket trailer	1_4548	1
17	110-03788	Trigger	PA6_30GF	1
18	110-03789	Intermediate lever	PA6_30GF	1
19	110-03790	Cover for drive pin EVO7p	AKROTEK_PK-VM_4774	1
20	110-03791	Drawbar socket	1_4305	1
21	110-70011	EVO7i forehead cap		1
22	110-70021	Messer		1
23	110-70022	Blade Lever Spring	DIN_EN_10270-1	1
24	110-70048	Cap Adjustment Knob Ball 2.5mm Diameter	PA66	1
25	110-70051		1_3505	1
26	110-70072	Spring Detent Adjustment Knob	DIN_EN_10270-1	1
27	110-78010	Adjustment knob	PA6_30GF	1
28	110-78011	ratchet adjustment knob	PA6_30GF	1
29	123-10149	EJOT Delta PT WN 5421 25x12	1_0601	5
30	123-10228	ISO14580-A2-M3x10	1_4303	1
31	123-13014	DIN 6325 - ISO 8734 - 2x14	1_2067	3
32	123-13021	DIN 6325 - ISO 8734 - 3x12	1_2067	1
33	123-13026	DIN 6325 - ISO 8734 - 3x24	1_2067	1
34	123-13047	DIN 6325 - ISO 8734 - 3x20	1_2067	2
35	123-13060	DIN 6325 - ISO 8734 - 2,5x16	1_2067	1
36	123-16752	D-104	1_0038	1
37	123-16753	VD-026R-22	DIN_EN_10270-2_VDC_VD	1

				0,5 to 3	>3 to 6 >6 to 30	>30 to 120 DRAWN / GEZEICHNET		DATE 03.12.25	DIMS / UNIT MM	MATERIAL	WEIGHT [kg] / GEWICHT [g] 620.76	D. SIZE / FORMAT A3
				± 0,1	± 0,1	± 0,2	± 0,3	APPO / TESTED	DATE	SCALE / STANDARD 1:2	TITLE EVO7p	
				TOLERANCES/TOLERANCES ISO 2768-m				HellermannTyton HellermannTyton GmbH & Co. KG Großer Moorweg 45, 25436 Tornesch Tel.: +49 4122 701 - 0 DESIGNATION EVO7p				
				THE COPYRIGHT OF THIS DRAWING IS RESERVED BY HELLERMANNTYTON GMBH. IT IS ISSUED ON CONDITION THAT IT IS NOT REPRODUCED, COPIED, OR DISCLOSED TO A THIRD PARTY, EITHER WHOLLY OR IN PART, WITHOUT THE CONSENT OF HELLERMANNTYTON GMBH.		COPYRIGHT OF THIS DRAWING LOCATED AT HELLERMANNTYTON GMBH THE DRAWING MAY NOT BE USED WITHOUT PERMISSION VON HELLERMANNTYTON GMBH DO NOT COPY, REPRESENT OR MADE AVAILABLE TO THIRD PARTIES.						
NO. / NO.	DESCRIPTION	DATE / DATUM	NAME					US 110-03700				
								INDEX 1	PAGE 1/2 DRAWING NO. 23-0759-300-ASM_STD		PAGE 1/2	



				0,5 to 3	>3 to 6 >6 to 30	>30 to 120 DRAWN / GEZEICHNET		DATE 02.12.25	DIMS / UNIT MM	MATERIAL	WEIGHT [kg] / GEWICHT [kg] 620.76	D. SIZE / FORMAT A3
				± 0,1	± 0,1	± 0,2	± 0,3	APPD / TESTED	DATE	SCALE / STANDARD 1:1	TITLE EVO7p	
				TOLERANCES/TOLERANCES ISO 2768-m				HellermannTyton HellermannTyton GmbH & Co. KG Großer Moorweg 45, 25436 Tornesch Tel.: +49 4122 701 - 0				
				THE COPYRIGHT OF THIS DRAWING IS RESERVED BY HELLERMANN TYTON GMBH. IT IS ISSUED ON CONDITION THAT IT IS NOT REPRODUCED, COPIED, OR DISCLOSED TO A THIRD PARTY, EITHER WHOLLY OR IN PART, WITHOUT THE CONSENT OF HELLERMANN TYTON GMBH.		COPYRIGHT OF THIS DRAWING LOCATED AT HELLERMANN TYTON GMBH. THE DRAWING MAY NOT BE USED WITHOUT PERMISSION VON HELLERMANN TYTON GMBH. DO NOT COPY, REPRESENT OR MAKE AVAILABLE TO THIRD PARTIES.						
NO. / NO.	DESCRIPTION	DATE / DATUM	NAME					US 110-03700				
								INDEX 1	PAGE 2 / 2 DRAWING NO. 23-0759-300-ASM_STD		PAGE 2/2	