

STANLEY



STANLEY® FATMAX® XTREME™ 60CM MAGNETIC LEVEL FMHT43673-1

The STANLEY® FATMAX® XTREME™ 60cm Magnetic Level delivers long-term accuracy, durability and ergonomic design for professionals in roofing, framing, carpentry and more. Backed by a 10-year accuracy warranty, key features include secured vial technology designed to protect the vials against drop damage, fine milled edges to provide a 0.5mm/m primary accuracy and 90% larger plumb vials, to provide better bubble visibility. This level also incorporates strong magnets for a positive lock to metal surfaces, ideal for specialised applications like drywall construction.

- 60CM LENGTH
- SECURED VIAL TECHNOLOGY: Full frame vial carrier design to protect the vials against drop damage
- FINE MILLED LEVELLING EDGES: Provides 0.5mm/m primary edge vial accuracy
- CONTINUOUS EDGE: Easy to draw and scribe along the full length of the level due to the uninterrupted continuous edge
- 90% LARGER PLUMB VIALS: provide better bubble visibility
- GRIP ACCESS AND ONE-HANDED USE: Ergonomically designed grip rails and handles for easy one-handed use
- REMOVABLE END CAPS: Allows end user accuracy and precision due to easier 90° angle/corner access
- ANTI-SLIP SURFACE PROTECTORS AND STRONG MAGNETS: Raised rubber profiles on the end caps helps protect against slipping and surface marking, while strong rare-earth magnets ensure a positive lock on metal surfaces
- AVAILABLE IN A RANGE OF LENGTHS: 40cm to 200cm versions available, as well as combination packs and magnetic models for professionals such as drywall specialists



THE MEASURE OF A PRO™
STANLEYTOOLS.COM