



Connectors > Rectangular Connectors > Rectangular Contact Inserts



Rectangular Connector Insert Type: **Insert for Contacts**

Contact Type: **Pin**

Pole Configuration: **14**

Number of Positions: **14**

Wire Size: **14 AWG, 15 AWG**

Features

Product Type Features

Rectangular Connector Insert Type	Insert for Contacts
-----------------------------------	---------------------

Configuration Features

Number of Positions	14
---------------------	----

Body Features

Primary Product Material	Thermoplastic, Thermoset
--------------------------	--------------------------

Contact Features

Contact Type	Pin
Pole Configuration	14

Mechanical Attachment

Polarization Code	B
-------------------	---

Dimensions

Wire Size	14 AWG, 15 AWG
-----------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JAN 2025
(247)
Candidate List Declared Against: OCT
2008 (15)
SVHC > Threshold:
Not Yet Reviewed

Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Hand solderable with lead free solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Customers Also Bought

TE Part #2221860-6
AMPLIMITE IP67,SZ6, 90, 104 POS,IFS, PLUG

TE Part #172167-1
4 CIR UNIV M-N-L PLUG

TE Part #6162-229-1677
COAX PIN ASSY

TE Part #1445022-2
MICRO MNL RECEPT HSG SINGLE R

TE Part #5-794630-0
20P MICRO MNL ASSY,VRT,HDR,LF

TE Part #2-520184-2
ULTRAFAST 250 ASSY REC 22-18 TPBR LP

TE Part #YDIV46E17-35PNC009
PLUG ASSY

TE Part #2-102618-3
50 MODII HDR DRST SHRD .100CL



Documents

Datasheets & Catalog Pages
ARINC 600 Next Generation Receptacle Connector
English