

M12 D-coded Cable Assembly 5m



Image is for illustration purposes only. Please refer to product description.

Part number	21 33 232 3401 050
Specification	M12 D-coded Cable Assembly 5m
HARTING eCatalogue	https://harting.com/21332323401050

Identification

Category	System cabling
Series	Circular connectors M12
Identification	PushPull
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 D-coding
	Male Straight
	PushPull
	Press&Go
Connector 2	M12 D-coding
	Male Straight
	PushPull
	Press&Go
Type of cable	Copper cable (round)
Description of the cable	for railway applications

Version

Cable length	5 m
Number of cores	4
Core structure	4x AWG 22/7
Shielding	Shielded
Coding	D-coding

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
------------------------------	------------------------------



Pushing Performance
Since 1945

Technical characteristics

Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-40 ... +85 °C unmoved
Cable diameter	6.6 mm ± 0.2 mm
Minimum bending radius	6x Cable diameter (repeated bending) 5x Cable diameter (singular bending)
Impedance	100 Ω ±5 %

Material properties

Material (cable)	Elastomer
Colour (cable)	Black

Specifications and approvals

Specifications	EN 45545-1 EN 45545-2 EN 45545-5
----------------	--

Commercial data

Packaging size	1
Net weight	1 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140248014
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600