

Rotary Hammer LXT®

DHR183

18V, SDS-PLUS, 18 mm, 1.7 J

Model DHR183 is a cordless 18mm SDS-PLUS rotary hammer powered by 18V LXT® Li-Ion battery.

Feature and Benefits: 2 operation modes Rotation only, Rotation and Hammering, Variable speed control, Constant speed control, Electric brake, Anti-Vibration technology (AVT).



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
Impact Energy	1,7 J
Optimum Drilling Diameter Range in Concrete	3,2 - 10 mm
Max. Drilling Diameter in Concrete	18 mm
Max. Drilling Diameter in Wood	24 mm
Max. Drilling Diameter in Steel	13 mm
Impacts per Minute (IPM)	0 - 5000 min ⁻¹
No load speed	0 - 1100 min ⁻¹
Adapted for SDS-PLUS bits	✓
Tool weight with battery	2,1 - 2,9 kg
Electronic brake	✓
Vibration Level, Hammer Drilling Into	7,5 m/s ²

User benefits

- Brushless maintenance-free and long-life motor
- 2-mode operation for "Rotation Only" or "Hammering with Rotation"
- Three position vibration absorbing side handle for increased comfort
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.com



Related products

Other

User manual

Parts drawing