

11 Relays; 7 Analog outputs; cable gland

ZARBB7A11W

EAN Code: 3606489485481

Main

Range of product	Harmony eXLhoist	
Product or component type	Base station	
Device short name	ZARB	
Product specific application	Material handling Hoisting applications	

Complementary

cable entry	Cable gland	
Material	ABS + PC	
[Us] rated supply voltage	12230 V AC 1224 V DC	
Provided equipment	External antenna	
Nominal output current	0.5 A at 48 V AC conforming to IEC 60947-5-1	
Number of relays	11	
Relay type	Motion relay outputs Auxiliary relay outputs with 11 NO contact	
Safety outputs	2 NC relay outputs	
Maximum switching current	90 mA AC	
Maximum switching voltage	240 V AC (+/- 20 %)	
Communication network type	Wireless	
Transmission frequency	433 MHz	
Maximum sensing distance	100 m in free field	
Fixing mode	4 holes	
Electrical durability	100000 cycles	
Mechanical durability	10000000 cycles	
Service life	10 year(s)	
Width	176 mm	
Height	126 mm	
Depth	75 mm	
Net weight	0.95 kg	

Environment

IP degree of protection IP66

Relative humidity	097 %
Ambient air temperature for operation	-2055 °C
Ambient air temperature for storage	-4070 °C
Product certifications	CE

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	21.0 cm
Package 1 Width	24.0 cm
Package 1 Length	13.0 cm
Package 1 Weight	956.0 g

Logistical informations

Country of origin CN

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Under investigation

Use Again

○ Repack and remanufacture		
Take-back	No	

ZARBB7A11W

Dimensions Drawings

Dimensions

