
mini slide DGST-16-20-PA Part number: 8085131



Data sheet

Feature	Value
Stroke	20 mm
Adjustable endposition range/front length	21.7 mm
Adjustable endposition range/rear length	22 mm
Piston diameter	16 mm
Operating mode of drive unit	Yoke
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Guide	Recirculating ball bearing guide
Design structure	twin piston
	Yoke
	Piston rod
	Slide
Position detection	For proximity sensor
Operating pressure	1 8 bar
Max. speed	0.8 m/s
Repetition accuracy	<= 0,3 mm
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
Ambient temperature	-10 60 °C
Impact energy in end positions	0.25 Nm
Cushioning length	1 mm
Max. force Fy	840 N
Max. force Fz	840 N
Max. torque Mx	11.3 Nm
Max. torque My	7 Nm
Max. torgue Mz	7 Nm
Theoretical force at 6 bar, return stroke	207 N
Theoretical force at 6 bar, advance stroke	241 N
Moving mass	319 g
Product weight	608 g
Mounting type	with through hole
Pneumatic connection	M5
Materials note	Free of copper and PTFE
	Conforms to RoHS
Material cover	Wrought Aluminium alloy
Material seals	HNBR
Material of guide	РОМ
	TPE-E
	High alloy steel
Material housing	Wrought Aluminium alloy
Material piston rod	High alloy steel, non-corrosive



FESTO