



Powercenter 1100 up to 24 SENTRON COM devices, 24 V DC please consider wireless approval! list of countries: see certificates

Model	
product brand name	SETRON
product designation	Data transceiver
design of the product	data transceiver for SETRON COM circuit protection devices via radio protocol
product type designation	Powercenter 1100
design of the housing	DIN rail device
General technical data	
degree of pollution according to EN 60664-1	2
number of interfaces according to wireless	wireless, Bluetooth
guideline via radio-controlled system	2014/53/EU
frequency with radio transmission minimum	2 402 MHz
frequency with radio transmission maximum	2 480 MHz
vibration resistance under ambient conditions according to IEC 60068-2-6	1-6 Hz, 15 mm, 6-500 Hz, 20 m/s <sup>2</sup>
consumed current maximum	100 mA
Supply voltage	
supply voltage at DC rated value	
• minimum	19.2 V
• maximum	28.8 V
type of voltage of the supply voltage	24 V DC SELV
Protection class	
protection class IP	IP20
protection class IP on the front	IP20
Suitability	
suitability for use	SETRON COM circuit protection devices (radio)
suitability for use safety-related function	Yes
Communication	
number of interfaces according to wireless	2
standard for wireless communication bluetooth note	V5.1,
number of interfaces according to Industrial Ethernet	2
protocol is supported	
• MODBUS protocol	Yes
• other protocols	Yes
Number	
number of supported devices	24
type of terminals screwless	yes
connectable conductor cross-section	
• minimum	0.2 mm <sup>2</sup>
• maximum	1.5 mm <sup>2</sup>

Mechanical Design	
height	90 mm
width	18 mm
depth	70 mm
fastening method rail mounting	Yes
<b>Net Weight</b>	70 g
Environmental conditions	
relative humidity with condensation according to IEC 60068-2-38 maximum	95 %
relative humidity with condensation according to IEC 60068-2-38	RH incl. condensation/frost (no commissioning with condensation)
shock acceleration during operation according to EN 60068-2-27	150 m/s <sup>2</sup> , 11 ms
ambient temperature during operation	
• minimum	-25 °C
• maximum	60 °C
ambient temperature during storage and transport	
• minimum	-40 °C
• maximum	80 °C

#### Approvals Certificates

General Product Approval	Radio Equipment Type Approval Certificate	other
	 EG-Konf.	<a href="#">Miscellaneous</a> <a href="#">Miscellaneous</a> <a href="#">Confirmation</a>
		



#### Environment



[Environmental Confirmations](#)

#### Further information

- Information on the packaging  
<https://support.industry.siemens.com/cs/ww/en/view/109813875>
- Information for data generation and storage  
<https://support.industry.siemens.com/cs/ww/en/view/109995012>
- Information- and Downloadcenter (Catalogs, Brochures,...)  
<http://www.siemens.com/lowvoltage/catalogs>
- Industry Mall (Online ordering system)  
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=7KN1111-0MC00>
- Service&Support (Manuals, Certificates, Characteristics, FAQs,...)  
<https://support.industry.siemens.com/cs/ww/en/ps/7KN1111-0MC00>
- Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)  
[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=7KN1111-0MC00](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=7KN1111-0MC00)
- CAx-Online-Generator  
<http://www.siemens.com/cax>
- Tender specifications  
<http://www.siemens.com/specifications>



---

last modified:

8/6/2025 

