Product data sheet Characteristics

XACB12

empty pendant control station XAC-B - 12 openings in 2 columns



Main

Range of product	Harmony XAC
Product or component type	Pendant control station
Device short name	XACB

Complementary

Control station type	Double insulated
Enclosure material	Glass reinforced polyester
Electrical circuit type	Power circuit Control circuit
Enclosure type	Empty enclosure
Number of cut-out	12 cut-outs in 2 rows
Control station colour	Yellow
Cable entry	Rubber sleeve with stepped entry 1022 mm
Guard rail	Without
Vertical operator cut-out centre	40 Mm
Standards	CSA C22.2 No 14 EN/IEC 60947-5-1
Product certifications	CSA type 4
Protective treatment	TH
Ambient air temperature for operation	-2570 °C
Ambient air temperature for storage	-4070 °C
Vibration resistance	15 gn (f= 10500 Hz) conforming to IEC 60068-2-6
Shock resistance	100 gn conforming to IEC 60068-2-27
Overvoltage category	Class II conforming to IEC 61140
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 50102
Mechanical durability	1000000 Cycles
Net weight	1.46 Kg

Packing Units

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Weight	1.532 Kg	
Package 1 Height	10.8 Cm	
Package 1 width	16.2 Cm	
Package 1 Length	66 Cm	

Package 2 Weight	1.685 Kg	
Package 3 Weight	36.85 Kg	
Offer Sustainability		
REACh Regulation	☑ REACh Declaration	
REACh free of SVHC	Yes	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
Toxic heavy metal free	Yes	
Mercury free	Yes	
RoHS exemption information	₫Yes	
China RoHS Regulation	China RoHS Declaration	
WEEE	The product must be disposed on European Union markets following speci- fic waste collection and never end up in rubbish bins	

Contractual warranty

Warranty 18 months

Product Life Status : Commercialised

