



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Tab**

Connector & Housing Type: **Tab Housing**

Number of Positions: **2**

Terminal Orientation: **Straight**

Primary Product Color: **Blue**

Features

Product Type Features

Sealable	No
Connector & Housing Type	Tab Housing

Configuration Features

Number of Positions	2
---------------------	---

Body Features

Primary Product Color	Blue
-----------------------	------

Contact Features

Terminal Type	Tab
Terminal Orientation	Straight
Contact Mating Retention	With

Mechanical Attachment

Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

--	--



Housing Material	Polyamide
Centerline (Pitch)	7.4 mm[.291 in]

Dimensions

Product Length	31.5 mm[1.24 in]
----------------	------------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Quantity	3000
Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts







TE Part # 1-180908-0
FF 250 TAB HSG 2P NYLON NAT




TE Part # 180908-5
FF 250 TAB HSG 2P NYLON BLACK




TE Part # 180907-3
FF 250 REC HSG 2P NYLON BLUE




TE Part # 180908-4
FF 250 TAB HSG 2P NYLON YELLOW




TE Part # 180901
FF 250 TAB HSG 4P NYLON NAT



TE Part # 180908
FF 250 TAB HSG 2P NYLON NAT



TE Part # 180908-1
FF 250 TAB HSG 2P NYLON RED



TE Part # 1-880298-0
FASTON .250 SERIES (6.3 MM)
HOUSING




TE Part # 1-480282-0
FF 250 TAB HSG 6P NYLON BLACK



TE Part # 880310-1
2 WAY FF 250 HOUSING TAB NYLON
6.6 NAT

Also in the Series | FASTIN-FASTON 250



Crimp Terminal Housings(195)



Insertion & Extraction Tools(2)




Quick Disconnects(216)

Customers Also Bought



TE Part #CAT-H3399-CH8172
Heavy Duty Sealed Connector Series
Housings



TE Part #1217124-1
187 FASTON,PCB TAB,TNBR



Documents

Product Drawings
FF 250 TAB HSG 2P NYLON BLUE
English

CAD Files
Customer View Model
ENG_CVM_CVM_180908-3_AB.2d_dxf.zip
English

3D PDF
3D
Customer View Model
ENG_CVM_CVM_180908-3_AB.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_180908-3_AB.3d_stp.zip
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
White Paper: Nylon Discoloration
English

Product Specifications
Application Specification
English

Agency Approvals
UL Report
English