

Description

With the increasing speed and complexity of applications a simple magnetic switch may be insufficient to meet the increased risks, therefore Sipha's design incorporates several magnetically sensitive elements which must be triggered in a particular sequence to operate correctly. The Sipha sensor, designed to operate with its own actuator, helps prevent defeatability by a simple magnet.

The Sipha with its molded-in brackets and diminutive size, is extremely versatile and simple to install. The Sipha sensor must be connected to the Sipha control unit giving a monitored circuit. For high-risk applications the control unit is used with a single sensor to give a high-integrity system. For other applications, multiple sensors (including mechanical switches) can be connected to one Sipha control unit. Sipha has facilities for connecting a manual reset button and for monitoring external devices such as contactors.

Four types of sensors and actuators are available incorporating different operating distances and physical sizes.

Features

- Non-contact actuation
- · Magnetic coded sensing
- Four housing styles
- Must be operated with its own safety control unit

Specifications

Opcomoditorio			
Safety Ratings			
Standards	EN954-1, ISO13849-1, IEC/EN60204-1, NFPA79, EN1088, ISO14119, IEC60947-5- 1, IEC/EN60947-5-3, ANSI B11.19, AS4024.1		
Safety Classification	Rating dependent on control unit and application.		
Functional Safety Data Note: For up-to-date information, visit http://www.ab.com/Safety/	B10d: > 2 x 10 ⁶ operations at min. PFH _D : > 3 x 10 ⁻⁷ MTTFd: > 385 years Dual channel interlock may be suitable for performance levels PLe or PLd (according to ISO 13849-1:2006) and for use in SIL2 or SIL3 systems (according to IEC 62061) depending on application characteristics		
Certifications	CE Marked for all applicable directives, cULus, and TÜV		
Outputs (Guard Door Closed, A	Actuator in Place)		
Auxiliary Output Switching	300V DC, 250V AC, 0.5 A including inrush. 15V A/10 W suitable for AC/DC circuits		
Operating Characteristics			
Sensing Distance, Make [mm (in.)]	Style S1: 5 (0.20) Style S2: 9 (0.35) Style S3: 5 (0.20) Style S4: 10 (0.39)		
Sensing Distance, Break [mm (in.)]	Style S1: 11 (0.43) Style S2: 12 (0.47) Style S3: 12 (0.47) Style S4: 13 (0.51)		
Environmental			
Enclosure Type Rating	IP67 (NEMA 6P)		
Operating Temperature [C (F)]	S1, S2, S3: -10+55° (+14+131°) S4 (GD2): -25+125° (-13+257°)		
Vibration	1 mm, 1055 Hz		
Shock	30 g, 11 ms half-sine		
Physical Characteristics			
Cable Size	0.54 mm ² (20 AWG) 4-wire PVC Jacket OD—4 mm (0.16 in.)		
Material	S1, S2: Molded ABS S30 (Actuator): Polyester S31 (Sensor): Nylon (Trogamid) S4 (GD2): Stainless Steel		
Mounting	Any position		
Weight [g (lbs)]	S1: Sensor: 18 (0.04); Actuator: 15 (0.03) S2: Sensor: 20 (0.04); Actuator: 30 (0.07) S3: Sensor: 18 (0.04) Actuator: 6 (0.01) S4: Sensor: 150 (0.33); Actuator: 170 (0.37)		



Product Selection

Housing Style	Housing Material	Safety Contacts	Auxiliary Contacts	Туре	Connection	Cat. No.
		Nana	011	3 m Cable	440N-S32014	
			None	S11	10 m Cable	440N-S32016
			1 N.C.	S12	3 m Cable	440N-S32022
					10 m Cable	440N-S32032
			1 N.O.	S13	3 m Cable	440N-S32037
S1	ABS plastic		I N.O.	313	10 m Cable	440N-S32036
M A	ADS plastic		None	S21	3 m Cable	440N-S32015
00			None	521	10 m Cable	440N-S32017
B B			1 N.C.	S22	3 m Cable	440N-S32023
		1 N.C. & 1 N.O.	I N.C.	522	10 m Cable	440N-S32033
			1 N.O.	S23	3 m Cable	440N-S32038
S2					10 m Cable	440N-S32039
000	Actuator: Polyester Sensor: Nylon [Trogamid]		None	S31	3 m Cable	440N-S32101
S3					4-Pin Micro (M12)	440N-S32024
Stainless Steel		1 N.C.	S42	8-Pin Micro (M12)	440N-S32047	
				3 m Cable	440N-S32055	
				10 m Cable	440N-S32056	
				8-Pin Micro (M12)	440N-S32046	
	1		1 N.O.	S43	3 m Cable	440N-S32053
S4					10 m Cable	440N-S32054

Recommended Logic Interfaces

Housing	Supply Voltage	Safety Contacts	Auxiliary Contacts	Housing Width	Туре	Cat. Page No.	Cat. No.
	24V AC/DC	1 N.O.	1 N.C. Solid State	22.5 mm	Control Unit 1		440N-S32013
	24V AC/DC; 115/230V AC	2 N.O.	1 N.C.	45 mm	Control Unit 2	5-74	440N-S32021
	24V AC/DC; 115/230V AC	2 N.O. + 1 N.O. delayed	1 N.C.	90 mm	Sipha 6		440N-S32052

Connection Systems

Description	4-Pin Micro (M12)	8-Pin Micro (M12)	
Cordset	889D-F4ECA-*	889D-F8AB-∗	
Patchcord	889D-F4ECRM-*	889D-F8ABDM-*	

* Replace symbol with 2 (2 m), 5 (5 m), or 10 (10 m) for standard cable lengths. * Replace symbol with 1 (1 m), 2 (2 m), 3 (3 m), 5 (5 m), or 10 (10 m) for standard cable lengths.


* Note: For additional information, see page 7-1.




Approximate Dimensions

Dimensions are shown in mm (in.). Dimensions are not intended to be used for installation purposes.


Sipha S1




Sipha S2



Sipha S3



Sipha S4



Accessories

Description	Cat. No.
Actuator S10	440N-A32019
Actuator S20	440N-A32020
Actuator S30	440N-A32025
Actuator S40 (GD2)	440N-A32041
Bag of 40 washers for S2 models	440N-A17127

Typical Wiring Diagrams

		S11, S21	S42, S12, S22	S43, S13, S23	
Description		1 N.O. + 1 N.C.	2 N.C. + 1 N.O.	1 N.C. + 2 N.O.	
	Red	Safety A_N.C.	Safety A_N.C.	Safety A_N.C.	
	Blue	Salety A_N.O.	Salety A_N.O.		
	Yellow	Safety B_N.O.	Safety B_N.O.	Safety B_N.O.	
Cable Versions	Green	Outety B_IV.O.		Culcty B_IV.C.	
	Black	_	Aux A_N.C.	Aux A_N.O.	
	White		_		
	Green/Yellow	_	External Ground	External Ground	
Desc	ription	S31	S42	S43	
4-Pin Micro (M12)		1-Safety A NC Safety B NO	_	_	
8-Pin Micro (M12)		_	3-Ground 2-Safety A N.C. 8-Safety B N.O. 1-Safety A N.C. 4-Safety B N.O. 7-NA 5-Aux A N.C. 6-Aux A N.C.	2-Safety A N.C. 8-Safety B N.O. 1-Safety A N.C. 4-Safety B N.O. 5-Aux A N.O.	
Brown		Safety A_N.C.		_	
4-Pin Cordset	Blue	Salety A_IV.O.			
889D-F4AC-*	White	Safety B_N.O.	_	_	
	Black	Outety B_IV.O.			
8-Pin Cordset 889D-F8AB-*	White Brown	Safety A	Safety A_N.C.	Safety A_N.C.	
	Red Yellow	Safety B	Safety B_N.O.	Safety B_N.O.	
	Grey Pink	Aux A	Aux A_N.C.	Aux A_N.O.	
	Green Blue	NA	Gnd	Gnd	

 $[\]boldsymbol{*}$ Replace symbol with 2 (2 m), 5 (5 m) or 10 (10 m) for standard cable lengths.

