

TXR32AB00-2816AIJ

✓ ACTIVE

RAYCHEM | RAYCHEM TXR

TE Internal #: 343767-000

Ruggedized, Backshell, .2 – 25.4 mm [.01 – 1 in] Cable Entry,
Aluminum, Straight, 28 Shell Size, 16 Entry Size, RAYCHEM TXR

[View on TE.com >](#)



Connectors > Connector Accessories > Connector Backshells



Connector Backshell Product Style: **Ruggedized**

Connector Backshell Product Type: **Backshell**

Cable Entry Diameter: **.2 – 25.4 mm [.01 – 1 in]**

Primary Product Material: **Aluminum**

Body Orientation: **Straight**

Features

Product Type Features

Termination Device Included	TR16AI
Connector Backshell Product Style	Ruggedized
Connector Backshell Product Type	Backshell
Termination Device Type	Side-Entry Tinel-Lock Ring, Tinel-Lock Adapter, Tinel-Lock Ring

Body Features

Primary Product Color	Olive Drab
Primary Product Material	Aluminum
Primary Product Plating Material	Cadmium (AMS-QQ-P-416, Type II, Class 3)

Housing Features

Body Orientation	Straight
Compatible With Connector Shape	Circular

Dimensions

Product Length	34.5 mm[1.35 in]
Compatible Cable Diameter Range	12.7 – 20.3 mm[.5 – .8 in]
Cable Entry Diameter	.2 – 25.4 mm[.01 – 1 in]

Usage Conditions

Salt Spray Resistance	500 Hr
-----------------------	--------



Operating Temperature Range-65 – 175 °C[-85 – 347 °F]

Operation/Application

Compatible With Connector Shell Size	28
--------------------------------------	----

Industry Standards

Connector Detail Specification Number	MS17343, MS17344, MS17345, MS17346, MS17347, MS17348
---------------------------------------	--

Other

Connector Interface Specification	MIL-DTL-22992 Class C,J,R, MIL-DTL-22992 Class C,R
TE Connector Interface Code	32
Entry Size Code	16

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Cd (.28% in Component Part) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 173643-000
RH-3960-1-TINEL-KIT-120V

Also in the Series | RAYCHEM TXR

Circular Connector Backshells & Clamps(2043)

Connector Backshells(2043)

Ruggedized Backshells & Adapters (2043)

Customers Also Bought

TE Part #CF7713-000
TXR40AB00-1612AIJ

TE Part #CF7703-000
TXR40AB00-1208AIJ

TE Part #EM8986-000
RBK-105-KIT-0107-A0



TE Part #CF8121-000
TXR40AB00-1814AIJ

TE Part #CM7396-000
TXR32AB00-2210AIJ

TE Part #F57065-000
TXR54AB00-1610AIJ

TE Part #741895-000
TXR32AB00-3220AIJ

TE Part #CB5434-000
XFFR-07X25



Documents

Product Drawings

TXR32AB00-2816AIJ

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_343767-000_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_343767-000_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_343767-000_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

5-1654025-5_sec6_Adapters

English

Circular Backshells

English

Product Specifications

General Information Package for Tinel-Lock Adapters

English

Braid termination using a Tinel Lock Ring installed using a resistance heater.

French

Braid termination using a Tinel Lock Ring installed using a resistance heater.

English

PERFORMANCE SPECIFICATION Tinel-Lock Rings, Heat Recoverable for Braid Termination

English

General Harness Repair Manual

English



Product Specification

English