



#### Main

Range	EasyPact
Product name	EasyPact TVR
Product or component type	Contacteur
Device short name	LC1R
Contactor application	Resistive load Motor control Reversing
Utilisation category	AC-3 AC-1
Poles description	3P
Power pole contact composition	3 NO
[Ie] rated operational current	25 A (at <40 °C) at <= 400 V AC AC-3 for power circuit 32 A (at <40 °C) at <= 400 V AC AC-1 for power circuit
[Uc] control circuit voltage	220 V AC 50 Hz
Auxiliary contact composition	1 NO
[Ue] rated operational voltage	Power circuit: 690 V AC 50 Hz Signalling circuit: 690 V AC 50 Hz

#### Complementary

Motor power kW	5.5 kW at 220/230 V AC 50 Hz 11 kW at 380/400 V AC 50 Hz 15 kW at 660/690 V AC 50 Hz
Electrical durability	1 Mcycles 25 A AC-3 at Ue <= 440 V
Mechanical durability	10 Mcycles
Maximum operating rate	1200 cyc/h 40 °C
Operating time	12...22 ms closing 4...19 ms opening
Control circuit voltage limits	Operational: 0.85...1.1 Uc Drop-out: 0.2...0.75 Uc
Hold-in power consumption in VA	8.3 VA cos phi 0.3
[Ith] conventional free air thermal current	32 A (at 40 °C) for power circuit 10 A (at 40 °C) for signalling circuit
Average impedance	2.5 mOhm - Ith 32 A 50 Hz for power circuit
Power dissipation per pole	AC-3: 1.25 W AC-1: 3.2 W
Heat dissipation	2...3 W at 50 Hz
Irms rated making capacity	250 A 380 V AC power circuit AC-3 IEC 60947 250 A 380 V AC power circuit AC-3 GB 14048
Rated breaking capacity	200 A at 380 V for power circuit AC-3 conforming to IEC 60947 200 A at 380 V for power circuit AC-3 conforming to GB 14048
[Icw] rated short-time withstand current	100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit 145 A 40 °C - 10 s for power circuit 84 A 40 °C - 1 min for power circuit 40 A 40 °C - 10 min for power circuit

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the Schneider Electric group. It is not intended to be used as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Associated fuse rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 32 A gG at ≤ 690 V coordination type 1 for power circuit
Overvoltage category	III
[Ui] rated insulation voltage	Power circuit: 690 V conforming to IEC 60947-4-1 Signalling circuit: 690 V conforming to IEC 60947-1 Power circuit: 690 V conforming to GB 14048.4
Coil technology	Without built-in suppressor module
Auxiliary contacts type	Type mechanically linked 1 NO conforming to IEC 60947-5-1
Signalling circuit frequency	50 Hz
Minimum switching current	5 mA for signalling circuit
Switching voltage	17 V for signalling circuit
Non-overlap time	1.5 Ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact
Insulation resistance	> 10 MOhm for signalling circuit
Mounting support	Rail Plate
Connections - terminals	Control circuit: screw clamp terminals 2 1...2.5 mm <sup>2</sup> - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 1 1.5...6 mm <sup>2</sup> - external diameter: 10 mm - cable stiffness: flexible without cable end Power circuit: screw clamp terminals 2 1.5...6 mm <sup>2</sup> - external diameter: 10 mm - cable stiffness: flexible without cable end Power circuit: screw clamp terminals 1 1...6 mm <sup>2</sup> - external diameter: 10 mm - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 2 1...4 mm <sup>2</sup> - external diameter: 10 mm - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 1 1.5...6 mm <sup>2</sup> - external diameter: 10 mm - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 1.5...6 mm <sup>2</sup> - external diameter: 10 mm - cable stiffness: solid without cable end Control circuit: screw clamp terminals 1 1...2.5 mm <sup>2</sup> - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 1...2.5 mm <sup>2</sup> - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 1...2.5 mm <sup>2</sup> - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 1...2.5 mm <sup>2</sup> - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 1...2.5 mm <sup>2</sup> - cable stiffness: solid without cable end
Tightening torque	Control circuit: 1.2 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.2 N.m - on screw clamp terminals - with screwdriver Philips No 2 Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm M4 Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 M4
Height	74 mm
Width	45 mm
Depth	85 mm
Standards	IEC 60947-1 IEC 60947-4-1 GB 14048.4 GB 14048.1
Product certifications	CCC

## Environment

Pollution degree	3
Protective treatment	TH conforming to IEC 60068-2-30
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-40...60 °C
Permissible ambient air temperature around the device	-20...55 °C at U <sub>c</sub>
Operating altitude	2000 m without derating
Fire resistance	850 °C conforming to IEC 60695-2-11
Mechanical robustness	Vibrations contactor open (1.2 gn, 5...300 Hz) conforming to IEC 60068-2-6 Vibrations contactor closed (2.5 Gn, 5...300 Hz) conforming to IEC 60068-2-6 Shocks 11 ms contactor closed (8 gn) conforming to IEC 60068-2-27 Shocks 11 ms contactor open (4 gn) conforming to IEC 60068-2-27

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	8.5 cm
Package 1 Length	7.4 cm
Package 1 Weight	345 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins