


ALS60, Aluminum Electrolytic, 2,700 uF, 20%, 550 VDC, -40/+85°C

**General Information**

Supplier:	KEMET
Series:	ALS60
Dielectric:	Aluminum Electrolytic
Description:	High Voltage, Screw Terminal, Aluminum Electrolytic
Features:	High Voltage
RoHS:	Yes
AEC-Q200:	No
Notes:	Dimensions D And L Include Slewing. MS (MxH) = M12x16

Dimensions

D	77mm +/-1mm
L	131mm +/-2mm
T	5.5mm +/-0.5mm
S	31.8mm +/-0.5mm
DT	13mm +/-0.5mm
LT	135mm +/-1mm
TD	10mm MIN
V	19mm NOM
Z	10mm NOM

Specifications

Capacitance:	2,700 uF
Capacitance Tolerance:	20%
Voltage DC:	550 VDC, 605 VDC (Surge)
Temperature Range:	-40/+85°C
Rated Temperature:	85°C
Life:	20000 Hrs
Resistance:	113.4 mOhms (100Hz 20C), 100.35 mOhms (10kHz 20C)
Ripple Current:	13.17 Amps (100Hz 85C), 19.11 Amps (10kHz 85C)
Leakage Current:	6000 uA (5min 20°C)

Packaging Specifications

Weight:	860 g
Slewing:	Yes
Packaging:	Bulk, Box