

Blacklight BL368 Linear & Circline

F40W/T12/2FT/BL368

0001638



Kenmerken productreeks

- BL368 tubes emit an upgraded highly concentrated radiation with peak around 368 nm. Flying insects eye sensitivity is generally at or near this frequency
- 100% improvement in effectiveness (at 368nm)
- Depreciation of UV-A output over time is significantly reduced (80% at 5000hrs of original 100 hour output)
- Performs longer and better throughout the insect season
- Same shape, structural and electrical characteristics and control circuits as standard T12, T8 or T5 tubes
- Applications
 - Insect traps, insect attraction is strongly increased
 - Restaurants, kitchens, food shops, supermarkets
 - Diazo printing machines
 - Photo Polymerisation
 - Chemical processing
 - Mineral detection
 - Various technical applications
- Directions for use
- Maximum exposure limits are set by EN60335-2-59:1997 at an effective 1.0 milliWatt per metre squared (1.0 mW/m²) measured at a distance of 1 metre originally based on the recommendations of the National Radiological Protection Board in the UK. The irradiance value for a single BL368-lamp measured without reflector and/or fixture, in free air at 25 celsius, is varying between 0.2 and 0.4 mW/m² depending on the wattage



PRODUCT OVERZICHT

Bestelnummer	0001638
Afwerking lamp	Coated
Dimbaar	Yes
Top	T12-Special
EAN-code	5410288016382
Watt (nominaal) (W)	40

Blacklight BL368 Linear & Circline

F40W/T12/2FT/BL368

0001638

GEGEVENSTABEL

Algemene informatie

Bestelnummer	0001638
Afwerking lamp	Coated
Dimbaar	Yes
Top	T12-Special
EAN-code	5410288016382
E-nummer FI	4940437
Lange beschrijving	BL368 tubes emit an upgraded highly concentrated radiation with peak around 368 nm. Flying insects eye sensitivity is generally at or near this frequency. 100% improvement in effectiveness (at 368nm). Depreciation of UV-A output over time is significantly reduced (80% at 5000hrs of original 100 hour output). Performs longer and better throughout the insect season. Same shape, structural and electrical characteristics and control circuits as standard T12,T8 or T5 tubes. Applications. Insect traps, insect attraction is strongly increased. Restaurants, kitchens, food shops, supermarkets. Diazo printing machines. Photo Polymerisation. Chemical processing. Mineral detection. Various technical applications. Directions for use. Maximum exposure limits are set by EN60335-2-59:1997 at an effective 1.0 milliWatt per metre squared (1.0 mW/m ²) measured at a distance of 1 metre originally based on the recommendations of the National Radiological Protection Board in the UK. The irradiance value for a single BL368-lamp measured without reflector and/or fixture, in free air at 25 celsius, is varying between 0.2 and 0.4 mW/m ² depending on the wattage
Productnaam	F40W/T12/2FT/BL368
Ballast vereist	Yes
Hoeveelheid verpakking verkoop	25

Elektrotechnische gegevens

Watt (nominaal) (W)	40
-----------------------------	----

Fysieke gegevens

Gewicht (kg)	0.14
Lengte voet tot voet (mm) - A	589.8
Lengte voet tot pen Min-Max - B	594.5-596.9
Lamplengte (mm) - C/L	604
Lampdiameter (mm) - D	38
Beschrijving verpakking	Box/Sleeve
Single package dimensions (L x W x H) (cm)	60.30 x 4.30 x 4.10
Outer package dimensions (L x W x H) (cm)	63.00 x 22.00 x 21.00

Blacklight BL368 Linear & Circline

F40W/T12/2FT/BL368

0001638

TECHNISCHE TEKENINGEN

