

Main

Range of product	EcoStruxure Machine Expert
Product or component type	License
Format	Digital
Software type	Professional
Type of license	Floating license
Software version	V2.2
Operating system requirement	Windows 10 64 bit Windows 11 64 bit
User language	English Spanish Chinese French German Italian Portuguese (Brazilian) Turkish Japanese

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Complementary

License category	Permanent
Software function	Engineering Programming PLC
Range compatibility	Modicon M241 Modicon M251 Modicon M262 Modicon TM3 Modicon TM5 Modicon TM7 PacDrive LMC Eco PacDrive LMC Pro PacDrive LMC Pro2 Preventa XPSMC Preventa XPSMCM Lexium 32 Lexium 32i Lexium 32M Lexium 52 Lexium 62 Lexium ILA Lexium ILE Lexium ILS Lexium SD3 Altivar 320 Altivar 340 Altivar&Nbsp;Process ATV600 Altivar Easy 610 Altivar 660 Drive System Altivar&Nbsp;Process ATV900 Altivar Process 980 Regenerative Drive System Harmony XB5R Harmony XB4R OsiSense XG OsiSense XUW TeSys U TeSys T TeSys island Magelis XBT GH Magelis GTO Magelis GTU Magelis GTUX Magelis iPC Magelis STO & STU Magelis GK Magelis SCU EcoStruxure Machine Expert Twin
Communication port protocol	Modbus SL Modbus TCP EtherNet/IP CANopen Sercos III CANmotion
Hosting option	On-premise
License size	Entity (100 users)
System requirements	8 GB RAM 15 GB hard disk space
Processor requirement	Intel Core 2 Duo
Display resolution	1280 x 1024 pixels