



## Power MOSFET

| PRODUCT SUMMARY           |                 |       |
|---------------------------|-----------------|-------|
| $V_{DS}$ (V)              | 500             |       |
| $R_{DS(on)}$ ( $\Omega$ ) | $V_{GS} = 10$ V | 0.087 |
| $Q_g$ (Max.) (nC)         | 380             |       |
| $Q_{gs}$ (nC)             | 80              |       |
| $Q_{gd}$ (nC)             | 190             |       |
| Configuration             | Single          |       |



### FEATURES

- Superfast Body Diode Eliminates the Need for External Diodes in ZVS Applications
- Lower Gate Charge Results in Simpler Drive Requirements
- Enhanced  $dV/dt$  Capabilities Offer Improved Ruggedness
- Higher Gate Voltage Threshold Offers Improved Noise Immunity
- Compliant to RoHS Directive 2002/95/EC



**RoHS\***  
COMPLIANT

### APPLICATIONS

- Zero Voltage Switching SMPS
- Telecom and Server Power Supplies
- Uninterruptible Power Supplies
- Motor Control Applications

| ORDERING INFORMATION |                 |
|----------------------|-----------------|
| Package              | Super-247       |
| Lead (Pb)-free       | IRFPS40N50LPbF  |
|                      | SiHFPS40N50L-E3 |
| SnPb                 | IRFPS40N50L     |
|                      | SiHFPS40N50L    |

| ABSOLUTE MAXIMUM RATINGS ( $T_C = 25^\circ\text{C}$ , unless otherwise noted) |                          |                           |                     |      |
|---|--------------------------|---------------------------|---------------------|------|
| PARAMETER   | SYMBOL                   | LIMIT                     | UNIT                |      |
| Drain-Source Voltage  | $V_{DS}$                 | 500                       | V                   |      |
| Gate-Source Voltage   | $V_{GS}$                 | $\pm 30$                  |                     |      |
| Continuous Drain Current  | $V_{GS}$ at 10 V         | $T_C = 25^\circ\text{C}$  | 46                  |      |
|   |                          | $T_C = 100^\circ\text{C}$ |                     | 29   |
| Pulsed Drain Current <sup>a</sup>   | $I_{DM}$                 | 180                       | A                   |      |
| Linear Derating Factor  |                          | 4.3                       | W/ $^\circ\text{C}$ |      |
| Single Pulse Avalanche Energy <sup>b</sup>                                    | $E_{AS}$                 | 920                       | mJ                  |      |
| Repetitive Avalanche Current <sup>a</sup>                                     | $I_{AR}$                 | 46                        | A                   |      |
| Repetitive Avalanche Energy <sup>a</sup>                                      | $E_{AR}$                 | 54                        | mJ                  |      |
| Maximum Power Dissipation   | $T_C = 25^\circ\text{C}$ | $P_D$                     | 540                 | W    |
| Peak Diode Recovery $dV/dt^c$   |                          | $dV/dt$                   | 34                  | V/ns |
| Operating Junction and Storage Temperature Range                              | $T_J, T_{stg}$           | - 55 to + 150             | $^\circ\text{C}$    |      |
| Soldering Recommendations (Peak Temperature)                                  | for 10 s                 | 300 <sup>d</sup>          |                     |      |

#### Notes


- Repetitive rating; pulse width limited by maximum junction temperature (see fig. 11).
- Starting  $T_J = 25^\circ\text{C}$ ,  $L = 0.86$  mH,  $R_g = 25 \Omega$ ,  $I_{AS} = 46$  A (see fig. 12).
- $I_{SD} \leq 46$  A,  $di/dt \leq 550$  A/ $\mu\text{s}$ ,  $V_{DD} \leq V_{DS}$ ,  $T_J \leq 150^\circ\text{C}$ .
- 1.6 mm from case.

\* Pb containing terminations are not RoHS compliant, exemptions may apply

| THERMAL RESISTANCE RATINGS                    |            |      |      |      |
|---|------------|------|------|------|
| PARAMETER                                     | SYMBOL     | TYP. | MAX. | UNIT |
| Maximum Junction-to-Ambient <sup>a</sup>      | $R_{thJA}$ | -    | 40   | °C/W |
| Case-to-Sink, Flat, Greased Surface           | $R_{thCS}$ | 0.24 | -    |      |
| Maximum Junction-to-Case (Drain) <sup>a</sup> | $R_{thJC}$ | -    | 0.23 |      |

**Note**

a.  $R_{th}$  is measured at  $T_J$  approximately 90 °C.

| SPECIFICATIONS ( $T_J = 25\text{ °C}$ , unless otherwise noted) |                            |  |   |       |           |               |
|---|----------------------------|--|---|-------|-----------|---------------|
| PARAMETER   | SYMBOL                     | TEST CONDITIONS  | MIN.  | TYP.  | MAX.      | UNIT          |
| <b>Static</b>   |                            |  |   |       |           |               |
| Drain-Source Breakdown Voltage                                  | $V_{DS}$                   | $V_{GS} = 0\text{ V}, I_D = 250\text{ }\mu\text{A}$  | 500   | -     | -         | V             |
| $V_{DS}$ Temperature Coefficient                                | $\Delta V_{DS}/T_J$        | Reference to 25 °C, $I_D = 1\text{ mA}$  | -   | 0.60  | -         | V/°C          |
| Gate-Source Threshold Voltage                                   | $V_{GS(th)}$               | $V_{DS} = V_{GS}, I_D = 250\text{ }\mu\text{A}$  | 3.0   | -     | 5.0       | V             |
| Gate-Source Leakage   | $I_{GSS}$                  | $V_{GS} = \pm 30\text{ V}$   | -   | -     | $\pm 100$ | nA            |
| Zero Gate Voltage Drain Current                                 | $I_{DSS}$                  | $V_{DS} = 500\text{ V}, V_{GS} = 0\text{ V}$   | -   | -     | 50        | $\mu\text{A}$ |
|   |                            | $V_{DS} = 400\text{ V}, V_{GS} = 0\text{ V}, T_J = 125\text{ °C}$  | -   | -     | 2.0       | mA            |
| Drain-Source On-State Resistance                                | $R_{DS(on)}$               | $V_{GS} = 10\text{ V}, I_D = 28\text{ A}^b$  | -   | 0.087 | 0.100     | $\Omega$      |
| Forward Transconductance  | $g_{fs}$                   | $V_{DS} = 50\text{ V}, I_D = 46\text{ A}$  | 21  | -     | -         | S             |
| <b>Dynamic</b>  |                            |  |   |       |           |               |
| Input Capacitance   | $C_{iss}$                  | $V_{GS} = 0\text{ V}, V_{DS} = 25\text{ V}, f = 1.0\text{ MHz}, \text{ see fig. 5}$  | -   | 8110  | -         | pF            |
| Output Capacitance  | $C_{oss}$                  |  | -   | 960   | -         |               |
| Reverse Transfer Capacitance                                    | $C_{rss}$                  |  | -   | 130   | -         |               |
| Output Capacitance  | $C_{oss}$                  | $V_{GS} = 0\text{ V}$  | $V_{DS} = 1.0\text{ V}, f = 1.0\text{ MHz}$ | -     | 11200     | -             |
| Effective Output Capacitance                                    | $C_{oss\text{ eff.}}$      |  | $V_{DS} = 400\text{ V}, f = 1.0\text{ MHz}$ | -     | 240       | -             |
| Effective Output Capacitance (Energy Related)                   | $C_{oss\text{ eff. (ER)}}$ | $V_{DS} = 0\text{ V to } 400\text{ V}^c$   | -   | 310   | -         |               |
| Total Gate Charge   | $Q_g$                      | $V_{GS} = 10\text{ V}, I_D = 46\text{ A}, V_{DS} = 400\text{ V}, \text{ see fig. 7 and 15}^b$  | -   | -     | 380       | nC            |
| Gate-Source Charge  | $Q_{gs}$                   |  | -   | -     | 80        |               |
| Gate-Drain Charge   | $Q_{gd}$                   |  | -   | -     | 190       |               |
| Internal Gate Resistance  | $R_G$                      | $f = 1\text{ MHz}, \text{ open drain}$   | -   | 0.90  | -         | $\Omega$      |
| Turn-On Delay Time  | $t_{d(on)}$                | $V_{DD} = 250\text{ V}, I_D = 46\text{ A}, R_G = 0.85\text{ }\Omega, V_{GS} = 10\text{ V}, \text{ see fig. 14a and 14b}^b$                           | -   | 27    | -         | ns            |
| Rise Time   | $t_r$                      |  | -   | 170   | -         |               |
| Turn-Off Delay Time   | $t_{d(off)}$               |  | -   | 50    | -         |               |
| Fall Time   | $t_f$                      |  | -   | 69    | -         |               |
| <b>Drain-Source Body Diode Characteristics</b>                  |                            |  |   |       |           |               |
| Continuous Source-Drain Diode Current                           | $I_S$                      | MOSFET symbol showing the integral reverse p - n junction diode  | -   | -     | 46        | A             |
| Pulsed Diode Forward Current <sup>a</sup>                       | $I_{SM}$                   |  | -   | -     | 180       |               |
| Body Diode Voltage  | $V_{SD}$                   | $T_J = 25\text{ °C}, I_S = 46\text{ A}, V_{GS} = 0\text{ V}^b$   | -   | -     | 1.5       | V             |
| Body Diode Reverse Recovery Time                                | $t_{rr}$                   | $T_J = 25\text{ °C}, I_F = 46\text{ A}$  | -   | 170   | 250       | ns            |
|   |                            | $T_J = 125\text{ °C}, di/dt = 100\text{ A}/\mu\text{s}^b$  | -   | 220   | 330       |               |
| Body Diode Reverse Recovery Charge                              | $Q_{rr}$                   | $T_J = 25\text{ °C}, I_S = 46\text{ A}, V_{GS} = 0\text{ V}^b$   | -   | 705   | 1060      | nC            |
|   |                            | $T_J = 125\text{ °C}, di/dt = 100\text{ A}/\mu\text{s}^b$  | -   | 1.3   | 2.0       |               |
| Reverse Recovery Current  | $I_{RRM}$                  | $T_J = 25\text{ °C}$   | -   | 9.0   | -         | A             |
| Forward Turn-On Time  | $t_{on}$                   | Intrinsic turn-on time is negligible (turn-on is dominated by $L_S$ and $L_D$ )  |   |       |           |               |

**Notes**

- a. Repetitive rating; pulse width limited by maximum junction temperature (see fig. 11).
- b. Pulse width  $\leq 400\text{ }\mu\text{s}$ ; duty cycle  $\leq 2\%$ .
- c.  $C_{oss\text{ eff.}}$  is a fixed capacitance that gives the same charging time as  $C_{oss}$  while  $V_{DS}$  is rising from 0 % to 80 %  $V_{DS}$ .  $C_{oss\text{ eff. (ER)}}$  is a fixed capacitance that stores the same energy as  $C_{oss}$  while  $V_{DS}$  is rising from 0 % to 80 %  $V_{DS}$ .

## TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Fig. 1 - Typical Output Characteristics




Fig. 3 - Typical Transfer Characteristics




Fig. 2 - Typical Output Characteristics




Fig. 4 - Normalized On-Resistance vs. Temperature




Fig. 5 - Typical Capacitance vs. Drain-to-Source Voltage




Fig. 7 - Typical Gate Charge vs. Gate-to-Source Voltage




Fig. 6 - Typical Output Capacitance Stored Energy vs.  $V_{DS}$




Fig. 8 - Typical Source Drain Diode Forward Voltage




Fig. 9 - Maximum Drain Current vs. Case Temperature




Fig. 10a - Switching Time Test Circuit



Fig. 10b - Switching Time Waveforms




Fig. 11 - Maximum Effective Transient Thermal Impedance, Junction-to-Case




Fig. 12a - Unclamped Inductive Test Circuit




Fig. 12b - Unclamped Inductive Waveforms




Fig. 12c - Maximum Avalanche Energy vs. Drain Current




Fig. 12d - Maximum Safe Operating Area




Fig. 13a - Gate Charge Test Circuit






Fig. 13b - Basic Gate Charge Waveform






**Note**  
 a.  $V_{GS} = 5 V$  for logic level devices



**Fig. 14 - For N-Channel**

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see [www.vishay.com/ppg?91260](http://www.vishay.com/ppg?91260).

### TO-274AA (HIGH VOLTAGE)



⊕ 0.10 (0.25) ⊕ B A ⊕



Detail "A"  
Scale: 2:1

| DIM. | MILLIMETERS |       | INCHES |       |
|------|-------------|-------|--------|-------|
|      | MIN.        | MAX.  | MIN.   | MAX.  |
| A    | 4.70        | 5.30  | 0.185  | 0.209 |
| A1   | 1.50        | 2.50  | 0.059  | 0.098 |
| A2   | 2.25        | 2.65  | 0.089  | 0.104 |
| b    | 1.30        | 1.60  | 0.051  | 0.063 |
| b2   | 1.80        | 2.20  | 0.071  | 0.087 |
| b4   | 3.00        | 3.25  | 0.118  | 0.128 |
| c    | 0.80        | 1.20  | 0.031  | 0.047 |
| D    | 19.80       | 20.80 | 0.780  | 0.819 |

| DIM. | MILLIMETERS |       | INCHES    |       |
|------|-------------|-------|-----------|-------|
|      | MIN.        | MAX.  | MIN.      | MAX.  |
| D1   | 15.50       | 16.10 | 0.610     | 0.634 |
| D2   | 0.70        | 1.30  | 0.028     | 0.051 |
| E    | 15.10       | 16.10 | 0.594     | 0.634 |
| E1   | 13.30       | 13.90 | 0.524     | 0.547 |
| e    | 5.45 BSC    |       | 0.215 BSC |       |
| L    | 13.70       | 14.70 | 0.539     | 0.579 |
| L1   | 1.00        | 1.60  | 0.039     | 0.063 |
| R    | 2.00        | 3.00  | 0.079     | 0.118 |

ECN: S-82247-Rev. A, 06-Oct-08  
DWG: 5975

#### Notes

1. Dimensioning and tolerancing per ASME Y14.5M-1994.
2. Dimension D and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outer extremes of the plastic body.
3. Outline conforms to JEDEC outline to TO-274AA.





## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## Material Category Policy

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.**

**Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.**

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.**