



Main


Range	ClimaSys
Product name	ClimaSys CV
Product or component type	Fanbox without grille and filter
Product specific application	Outdoor heavy duty
Range compatibility	Spacial SFHD Spacial S3HD Thalassa PHD
Air flow	550 m3/h at 60 Hz Free flow rate: 550 m3/h at 50 Hz
[Us] rated supply voltage	230 V AC +/- 10 %
Input voltage	230 V AC 50/60 Hz
Product certifications	Ecodesign directive 2009/125/EC UL conforming to UL 508 A CSA conforming to CSA C22.2 CE

Complementary

Power range	72...88 W
[In] rated current	0.3...0.4 A 50 Hz
Noise level	60 dB
Bearing type	Ball
Height	External: 223 mm
Width	External: 223 mm
Depth	External: 90 mm
Product weight	1.7 kg
Colour	Dark grey RAL 7016
Ambient air temperature for operation	-40...65 °C
Ambient air temperature for storage	-40...80 °C
Maximum pressure	350 Pa flow rate 0 m³/h
Connections - terminals	Spring clamp terminal
IP degree of protection	IP55 with grid (NSYCAG223LFHD) IP44
Device composition	1 fanbox 4 screw

Condition of use	<p>Outside temperature must be 5 °C lower than inside temperature</p> <p>Filter must be cleaned and replaced regularly</p> <p>Surrounding environment must be relatively clean</p> <p>Overfrequent filter replacement should be avoided</p> <p>Flow rates depends on the work point, see ProClima software</p>
------------------	--

Offer Sustainability

RoHS (date code: YYWW)	<p>Compliant - since 0940 - Schneider Electric declaration of conformity</p> <p> Schneider Electric declaration of conformity</p>
REACH	<p>Reference not containing SVHC above the threshold</p> <p>Reference not containing SVHC above the threshold</p>