

## Features

- Designed to prevent molded electrical plugs from being inserted into outlets during maintenance or servicing work, ensuring worker safety.
- Capable of locking out almost all standard plugs and connectors, making it suitable for a wide range of industrial applications.
- Made from yellow polypropylene for high visibility and durability, ensuring long-lasting use in industrial environments.
- Features a sliding lock mechanism that provides a two-step locking process for additional security.
- Suitable for plugs upto 115mm dia. X 257mm length (Cable dia. up to 35mm)

## RS PRO Molded Plug Lockout Device - Large - Yellow

RS Stock No.: 0276132



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

- *The Molded Plug Lockout Devices are crucial safety tools designed to prevent molded electrical plugs from being inserted into outlets, protecting workers from accidental start-ups during maintenance or servicing work. They're particularly crucial when the plug isn't under the exclusive control of the technician or the maintenance personnel.*
- *They can lockout almost all standard plugs and connectors, ensuring a broad range of industrial applications.*
- *Made of yellow polypropylene for visibility and durability.*
- *Suitable for plugs up to 115mm dia. x 257mm length (Cable dia. up to 35mm).*
- *It is designed to house up to 4 padlocks (not included), and can accept padlocks with shackles up to 9mm in diameter, ensuring multiple personnel can collaborate in the safety procedure.*
- *The sliding lock feature offers a two-step locking process for enhanced safety.*

## General Specifications

Type	Plug Lockout
Material	Polypropylene
Colour	Yellow
Number of Locks	4

## Mechanical Specifications

Dimensions (L x W x H)	317mm x 160mm x 127mm
Length	317mm
Width	160mm
Height	127mm
Lock Shackle Maximum Diameter	9mm
Weight	456 Grams

## Operation Environment Specifications

Withstand temperature	-19°C to 60°C
-----------------------	---------------