



TECH RUNNER - FLEX S3

Réf. : 70805



Suitable for :	Inside/Outside
Type :	Ankle shoe
Activity :	Construction / Storage, Logistic, Transport / Electronic Industry, ESD
Upper :	Water resistant full supple leather and CORDURA® material
Lining :	ARTICO® black color, up to the toes, slipper feeling
Tongue :	Bellows tongue in ON STEAM® microfibre, lining ARTICO® and padded with 10mm thick foam
Ankle protection :	CORDURA® material, ARTICO® lining and padded with 10mm thick foam
Fastening :	Round polyester black laces with "Quick lock" system
Toe cap :	Ultralight and extra wide 200 joules, Composite LIGHT SYSTEM®
Midsole :	Composite FLEX SYSTEM®, anti-magnetic and thermal insulated
Insole :	Thermoformed in active carbon dual density foam, antistatic, ESD and antibacterial FRESH TECH®
Sole :	PU 2D, TECH SOLE® ankle anti-twist system, oil resistant FO, antistatic, HI-CI
Sole pattern :	Multi-purpose cleated indoor/outdoor outsole, well-defined heel, cleated arch, SRC standard
Weight (Kg/pair) :	1.200
Colors :	Black upper and dark grey/light grey outsole
Sizes :	35-48 (2-13)
Standard :	EN ISO 20345:2011 SRC / EN 61340-4-3 / DGUV 112-191
CE certificate of conformity N° :	0075/020/161/04/18/0585 EXT 08/04/18
Special features :	Quick fastening system "Quick lock"
Special features 2 :	Reflective piping on the heel part
Special features 3 :	

SPECIAL FEATURES

-  Integral 100% composite (Air System + Light System + Flex System)
-  Metal free, non magnetic
-  Water absorption and penetration resistance of upper (WRU)
-  Electro Static Discharge Standard EN 61340-5-1

CORDURA



ARTICO

GENERAL FEATURES

	Antistatic properties (A)	200 J	200 J
	Heel energy absorption (E)	200 J	200 J
	Abrasion resistance	200 J	200 J
	Crampon sole	200 J	200 J
	Heat-insulated sole (HI)	200 J	200 J
	Cold-insulated sole (CI)	200 J	200 J
	200 joule extra-wide toecap	200 J	200 J
	Hyper-ventilated lining	200 J	200 J
	Perforation-resistance 1100 N (P)	200 J	200 J