

PSR-ME20-3NO-1NC-24DC-SC-SET35 - Safety relays



1301404

<https://www.phoenixcontact.com/in/products/1301404>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Set comprised of 35 safety relays for emergency stops, safety doors, and light grids up to SIL 2, Cat. 3, PL d, 1- or 2-channel operation, automatic or manual, monitored start, 3 enabling current paths, 1 signaling current path, $U_S = 24\text{ V DC}$, plug-in screw terminal block

Your advantages

- Up to Cat. 3/PL d in acc. with EN ISO 13849-1, SIL 2 in acc. with EN IEC 62061, SIL 2 in acc. with IEC 61508
- 3 enabling current paths, 1 signaling current path
- 1- and 2-channel control
- Manually monitored and automatic activation

Commercial data

Item number	1301404
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DNA
Product key	DNA121
GTIN	4063151547127
Weight per piece (including packing)	5,866 g
Weight per piece (excluding packing)	5,467.7 g
Customs tariff number	85371098
Country of origin	DE

PSR-ME20-3NO-1NC-24DC-SC-SET35 - Safety relays



1301404

<https://www.phoenixcontact.com/in/products/1301404>

Set consists of

PSR-ME20-3NO-1NC-24DC-SC - Safety relays

1301402

<https://www.phoenixcontact.com/in/products/1301402>



Safety relay for emergency stops, safety doors, and light grids up to SIL 2, Cat. 3, PL d, 1- or 2-channel operation, automatic or manual, monitored start, 3 enabling current paths, 1 signaling current path, $U_S = 24 \text{ V DC}$, plug-in screw terminal block

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Safety relays
Product family	PSRclassic
Application	Emergency stop
	Safety door
	Light grid
Control	1 and 2 channel
Mechanical service life	approx. 10^7 cycles
Relay type	Electromechanical relay with force-guided contacts in accordance with IEC/EN 61810-3

Times

Typical response time	200 ms (automatic start)
	200 ms (manual, monitored start)
Typ. starting time with U_s	200 ms (when controlled via A1)
Typical release time	25 ms (on demand via the sensor circuit)
	60 ms (on demand via A1)
Restart time	< 1 s (Boot time)
Recovery time	< 500 ms (following demand of the safety function)

Electrical properties

Maximum power dissipation for nominal condition	16.6 W ($U_S = 26.4$ V, $I_L^2 = 72$ A ² , $P_{Total\ max} = 2.2$ W + 14.4 W)
Nominal operating mode	100% operating factor

Air clearances and creepage distances between the power circuits

Rated insulation voltage	250 V
Rated surge voltage/insulation	Basic insulation 4 kV between all output current paths
	Basic insulation 4 kV between all output current paths/logic paths and housing
	Safe isolation, reinforced insulation 6 kV between 250 V load current paths and 24 V logic paths

Supply

Designation	A1/A2
Rated control circuit supply voltage U_S	24 V DC -15 % / +10 %
Rated control supply current I_S	typ. 70 mA (at U_S)
Power consumption at U_S	typ. 1.68 W
Inrush current	< 5.2 A (typ. with U_S , $\Delta t = 2$ ms)
Filter time	5 ms (in the event of voltage dips at U_S)

Protective circuit	Serial protection against polarity reversal; Suppressor diode
--------------------	---

Input data

General

Rated control supply current I_S	typ. 70 mA (at U_S)
------------------------------------	------------------------

Digital: Sensor circuit (S10, S12, S22)

Description of the input	safety-related sensor inputs
Number of inputs	3
Input voltage range "0" signal	0 V DC ... 5 V DC (S10, S12)
Input voltage range "1" signal	20.4 V ... 26.4 V
Input current range "0" signal	0 mA ... 2 mA
Inrush current	< 100 mA (typ. with U_S at S10/S12) > -100 mA (typ. with U_S at S22)
Filter time	1 ms (Test pulse width of low test pulses) 1 s (Test pulse rate for low test pulse) No brightness test pulses / high test pulses permitted.
Concurrence	∞
Max. permissible overall conductor resistance	50 Ω
Protective circuit	Suppressor diode
Current consumption	38 mA (typ. with U_S at S10/S12) -38 mA (typ. with U_S at S22)

Digital: Start circuit (S34, S35)

Description of the input	non-safety-related
Number of inputs	2
Input voltage range "1" signal	20.4 V ... 26.4 V
Inrush current	< 7 mA (typ. with U_S at S34) < 8 mA (typ. with U_S at S35)
Filter time	No test pulses permitted
Max. permissible overall conductor resistance	50 Ω
Protective circuit	Suppressor diode
Current consumption	2 mA (typ. with U_S at S34) 3 mA (typ. with U_S at S35)

Output data

Relay: Enabling current paths (13/14, 23/24, 33/34)

Output description	2 N/O contacts each in series, safety-related, floating
Number of outputs	3
Contact switching type	3 enabling current paths
Contact material	AgSnO ₂
Switching voltage	min. 10 V AC/DC max. 250 V AC/DC
Switching capacity	min. 100 mW

1301404

<https://www.phoenixcontact.com/in/products/1301404>

Inrush current	min. 10 mA
	max. 6 A
Switching capacity in accordance with IEC 60947-5-1	5 A (AC15)
	6 A (DC13)
Limiting continuous current	6 A (Observe derating and load limit curve)
Sq. Total current	72 A ² (observe derating)
Switching frequency	max. 0.5 Hz
Mechanical service life	10x 10 ⁶ cycles
Output fuse	10 A gL/gG
	4 A gL/gG (for low-demand applications)

Relay: Signaling current path (41/42)

Output description	2 N/C contacts parallel, non-safety-related, floating
Number of outputs	1
Contact switching type	2 NC parallel
Contact material	AgSnO ₂
Switching voltage	min. 10 V AC/DC
	max. 250 V AC/DC
Switching capacity	min. 100 mW
Inrush current	min. 10 mA
	max. 6 A
Switching capacity in accordance with IEC 60947-5-1	3 A (AC15)
	2 A (DC13)
Limiting continuous current	6 A
Sq. Total current	36 A ²
Switching frequency	max. 0.5 Hz
Mechanical service life	10x 10 ⁶ cycles
Output fuse	6 A gL/gG

Connection data

Connection technology

pluggable	yes
-----------	-----

Conductor connection

Connection method	Screw connection
Conductor cross section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12
Stripping length	7 mm
Screw thread	M3
Tightening torque	0.5 Nm ... 0.6 Nm

Signaling

Status display	2 x LED (green)
Operating voltage display	1 x LED (green)

Dimensions

Width	22.5 mm
Height	112.2 mm
Depth	114.5 mm

Material specifications

Color (Housing)	traffic grey B (RAL 7043)
Housing material	PBT

Characteristics

Safety data

Stop category	0
---------------	---

Safety data: EN ISO 13849

Category	3
Performance level (PL)	d

Safety data: IEC 61508 - High demand

Safety Integrity Level (SIL)	2
------------------------------	---

Safety data: IEC 61508 - Low demand

Safety Integrity Level (SIL)	2
------------------------------	---

Safety data: EN IEC 62061

Safety Integrity Level (SIL)	2
------------------------------	---

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Min. degree of protection of inst. location	IP54
Ambient temperature (operation)	-20 °C ... 55 °C (observe derating)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Maximum altitude	≤ 2000 m (Above sea level)
Max. permissible humidity (storage/transport)	75 % (on average, 85% infrequently, non-condensing)
Max. permissible relative humidity (operation)	75 % (on average, 85% infrequently, non-condensing)
Shock	15g
Vibration (operation)	10 Hz ... 150 Hz, 2g

Approvals

CE

Identification	CE-compliant
----------------	--------------

Standards and regulations

Air clearances and creepage distances between the power circuits

PSR-ME20-3NO-1NC-24DC-SC-SET35 - Safety relays



1301404

<https://www.phoenixcontact.com/in/products/1301404>


Standards/regulations	DIN EN 60947-1
-----------------------	----------------

Mounting


Mounting type	DIN rail mounting
Assembly note	See derating curve
Mounting position	vertical or horizontal

Drawings

Circuit diagram




Block diagram



1301404

<https://www.phoenixcontact.com/in/products/1301404>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1301404>



Functional Safety

Approval ID: 44-780-15124324



Functional Safety

Approval ID: 44-205-15124324



cULus Listed

Approval ID: E140324

1301404

<https://www.phoenixcontact.com/in/products/1301404>

Classifications

ECLASS

ECLASS-11.0	27371819
ECLASS-13.0	27371819
ECLASS-12.0	27371819

ETIM

ETIM 9.0	EC001449
----------	----------

UNSPSC

UNSPSC 21.0	39122200
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	66adeb0f-24ea-46e2-9921-0a65bb3c3c18

PSR-ME20-3NO-1NC-24DC-SC-SET35 - Safety relays



1301404

<https://www.phoenixcontact.com/in/products/1301404>

Accessories

PSR-ME20-3NO-1NC-24DC-SC - Safety relays

1301402

<https://www.phoenixcontact.com/in/products/1301402>



Safety relay for emergency stops, safety doors, and light grids up to SIL 2, Cat. 3, PL d, 1- or 2-channel operation, automatic or manual, monitored start, 3 enabling current paths, 1 signaling current path, $U_S = 24 \text{ V DC}$, plug-in screw terminal block

CP-MSTB - Coding profile

1734634

<https://www.phoenixcontact.com/in/products/1734634>



Coding profile, is inserted into the slot on the plug or inverted header, red insulating material

PSR-ME20-3NO-1NC-24DC-SC-SET35 - Safety relays



1301404

<https://www.phoenixcontact.com/in/products/1301404>

CR-MSTB - Coding section

1734401

<https://www.phoenixcontact.com/in/products/1734401>

Coding section, inserted into the recess in the header or the inverted plug, red insulating material



CRIMPFOX 6 - Crimping pliers

1212034

<https://www.phoenixcontact.com/in/products/1212034>



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.25 mm² ... 6.0 mm², lateral entry, trapezoidal crimp

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in