

CABLE-OPER. SWITCH METAL HOUSING, 2X M20X1.5 1NO+1NC, LATCHES, ISO 13850 BUTTON RESET FOR CABLES UP TO TO 25M









Figure similar

<b>Product designation</b>	cable-operated switch
<b>General technical data:</b>	
<b>Product function</b>	
• EMERGENCY STOP function	Yes
<b>Protection class IP</b>	IP65
<b>Equipment marking</b>	
• acc. to DIN EN 61346-2	S
• acc. to DIN EN 81346-2	S
<b>Enclosure:</b>	
<b>Material of the enclosure</b>	metal
<b>Product component</b>	
• EMERGENCY STOP device	No
<b>Color</b>	
• of top part of the enclosure	grey
<b>Ambient conditions:</b>	
<b>Ambient temperature</b>	
• during operation	-25 ... +70 °C

## Installation/ mounting/ dimensions:

Mounting type	screw fixing
Height	164.5 mm
Width	52 mm
Depth	57.5 mm

## Certificates/approvals

General Product Approval	Declaration of Conformity	Shipping Approval
 CCC	 EG-Konf.	 ABS
 CSA		 LRS

## Shipping Approval



## Further information

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE71501BD00>

### Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE71501BD00>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SE71501BD00>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SE71501BD00&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE71501BD00&lang=en)

last modified:

07.12.2015