

Cable marking flags - MM-WML-FLAGV 6 (20X10)R C1 WH/ BK - 1116190

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable marking flags, Roll, white/black, unlabeled, can be labeled with: THERMOMARK GO, mounting type: adhesive, lettering field size: 20 x 10 mm, Number of individual labels: 145

Product Description

MM-WML-Flag polyolefin self-adhesive labels are available as prepunched material for wire marking. There are both horizontal and vertical versions.

Your advantages

- ✓ High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing
- ✓ The pre-punched geometry enables easy and convenient use
- ✓ Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- ✓ No visible difference between retrospective marking and existing markings created with a desktop roll printer
- ✓ The self-adhesive cable marking flag can be printed on both sides
- ✓ The material is cUL certified
- ✓ Thanks to the innovative material composition, each label can be printed which results in zero wastage



Key Commercial Data

Packing unit	1 pc
GTIN	 4 063151 042202
GTIN	4063151042202
Weight per Piece (excluding packing)	55.000 g
Country of origin	China
Sales Key	BG221E

Technical data

Dimensions

Length (b)	50 mm
Width (a)	20 mm

Cable marking flags - MM-WML-FLAGV 6 (20X10)R C1 WH/ BK - 1116190

Technical data

Dimensions

Cable diameter	≤ 6 mm
----------------	--------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
---------------------------------	------------------

General

Color	white/black
Type	Label
Components	free from silicone, halogen, and cadmium
Material	Polyolefine
Number of individual labels	145
Marking mounting type	adhesive
Testing substances harmful to the wetting properties of lacquers (LABS conformity)	VW PV 3.10.7:2005-02
Result	Test passed
UV resistance	Following ISO 4892-2:2013-03
Result	Test passed
Test duration	96 h
Testing in a condensation changing climate in the presence of sulfur dioxide	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1,0 S
Cycles	2
Salt spray test	DIN EN 60068-2-11:2000-02
Result	Test passed

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27400401
eCl@ss 11.0	27281102
eCl@ss 9.0	27400401

ETIM

ETIM 7.0	EC001530
----------	----------

Approvals

Approvals

Cable marking flags - MM-WML-FLAGV 6 (20X10)R C1 WH/ BK - 1116190

Approvals

Approvals

cULus Recognized

Ex Approvals

Approval details

cULus Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

MH48542