




Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Pb (13% in Component Plating) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Also in the Series | **NECTOR M Series**



[Connector Hardware\(3\)](#)



[Standard Circular Connectors\(45\)](#)

Customers Also Bought




TE Part #5-1622820-2
[3520 4R7 5%](#)



TE Part #7-1393243-8
[RT424615](#)



TE Part #1-6600333-2
[MBXL VERT HDR 2P+24S+2P](#)



TE Part #1326030-8
[2.8MM RECP,UNSEAL,10-12AWG,REV](#)



TE Part #205690-2
[SOC. BLOCK 28 POS. SPL.](#)




TE Part #6-1393224-1
[RY213012](#)



TE Part #9-1879377-0
[CRGH0805 5% 4K7 0.33W](#)



TE Part #T4140012051-000
[M12,REAR MOUNTING,MALE,A CODE,5P](#)



TE Part #963292-1
[WIRE SEALING 2,2](#)



TE Part #5-1814400-2
[SMA R/A PCB Skt GZD](#)

Documents

Product Drawings

[V.35,PIN ASY,RA,34P,W/BRKT](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_213289-1_R.3d_stp.zip](#)



English

Customer View Model

[ENG_CVM_CVM_213289-1_R.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_213289-1_R.3d_igs.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

[Datasheets & Catalog Pages](#)

[M_SERIES_PIN_AND_SOCKET_CONNECTORS](#)

English

[Product Specifications](#)

[Connector, Series "M"](#)

English

[Product Specification](#)

English